



Anixter Return Policy

Returns will not be accepted without a predetermined Return Authorization number, provided by Anixter.

In order to receive a return authorization, a return request must be made within 30 days of material receipt.

Credit will be issued for goods returned with prior Anixter approval and with a current return authorization (RA) number.

Return Authorizations must be coordinated through your Inside Sales Representative.

Anixter will only accept the return of materials that were purchased from Anixter.

Goods approved for return should be sent back to the authorized Anixter warehouse within 30 days of return approval.

Approved return material must be new, unopened and in the original package in order to receive credit.

Material returned within 30 days of material receipt may not be subject to a re-stocking charge.

Anixter reserves the right to apply re-stock charges to any return.

Anixter reserves the right to deny return authorization for product customized in any way (dyed, twisted, etc).

Any non-stock product that cannot be returned to Anixter's material vendor will not receive return authorization and will not be credited.

Material deemed not creditable will either be scrapped or returned to the customer at the customer's expense.