

RVUTT01 Connectivity Accessories - REVConnect Termination Tool



For more Information
please call

1-800-Belden1

General Description:

REVConnect Universal Termination Tool

Usage (Overall)

Suitable Applications: To terminate REVConnect Jacks and Plugs

Physical Characteristics (Connectivity)

Dimensions

Dimensions:

| Height (in.) | Width (in.) | Length (in.) |
|--------------|-------------|--------------|
| 5.910 | 4.620 | 1.350 |

Materials

Materials:

| Description | Material | Color |
|-----------------|----------------------------------|-------|
| Frame | Aluminum | |
| Handle grip | Plastic | Black |
| Blade Block | Steel | |
| Blades & Knives | Steel | |
| Press Head | Nickel plated zinc alloy diecast | |

Color

Color: Blue

Weight

Weight: 0.650 lbs.

Packaging

Packaging: Individually packaged in a plastic clamshell, shipped in cardboard box (40/Box)

Mechanical Characteristics (Connectivity)

Termination Interface:

| Connection | Durabilities |
|------------|--------------|
| Blades | 20000 |
| Handle | 40000 |

Storage Temperature Range: -40°C To +60°C

Installation Temperature Range: -10°C To +50°C

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU Directive 2011/65/EU (ROHS II): Yes

Suitability

Suitability - Indoor: Yes - Indoor

Notes (Overall)

Product Family

Part Number List:

| Accessory | Part Number |
|------------------------|-------------|
| Termination Tool | RVUTT01 |
| Cable Preparation Tool | RVUCT01 |
| Belt Clip | RVUTC01 |
| Spare Blades | RVUTB01 |

RVUTT01 Connectivity Accessories - REVConnect Termination Tool

Physical Properties (Overall)

Put Ups and Colors:

| Item # | Putup | Ship Weight | Color | Notes | Item Desc |
|--------|-------|-------------|-------|-------|-----------|
|--------|-------|-------------|-------|-------|-----------|

Revision Number: 0 Revision Date: 09-12-2016

© 2016 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale.