

## LEVITON OPT-X<sup>®</sup> SDX PLATFORM | FIBER OPTIC ENCLOSURES, ADAPTER PLATES, AND ACCESSORIES

| LEVITON                                |   | ANIXTER  |
|--|---|----------|
| <b>2000i SDX RACK-MOUNT ENCLOSURES</b> |   |          |
| PART NO.                               | DESCRIPTION   | PART NO. |
| 5R1UH-S03                              | 1RU, empty, sliding tray, accepts 3 adapter plates  | 377050   |
| 5R2UH-S06                              | 2RU, empty, sliding tray, accepts 6 adapter plates  | 377051   |
| 5R4UH-S12                              | 4RU, empty, sliding tray, accepts 12 adapter plates | 391059   |

| <b>500i SDX RACK-MOUNT ENCLOSURES</b> |                                      |          |
|---------------------------------------|--------------------------------------|----------|
| PART NO.                              | DESCRIPTION                          | PART NO. |
| 5R1UL-F03                             | 1RU, empty, accepts 3 adapter plates | 447475   |
| 5R2UL-F06                             | 2RU, empty, accepts 6 adapter plates | 447476   |

| <b>SDX MOLDED ADAPTER PLATES WITH ZIRCONIA CERAMIC SLEEVE</b> |   |          |
|---|---|----------|
| PART NO.  | DESCRIPTION   | PART NO. |
| 5F100-2QL   | Plate (aqua), 50 µm LOMM (OM3 and OM4) Duplex LC, 12-fiber  | 489670   |
| 5F100-2LL   | Plate (blue), SM (OS2), Duplex LC, 12-fiber                 | 489679   |
| 5F100-4QL   | Plate (aqua), 50 µm LOMM (OM3 and OM4) Quad LC, 24-fiber    | 507956   |
| 5F100-4LL   | Plate (blue), SM (OS2), Quad LC, 24-fiber                   | 507955   |
| 5F100-6QC   | Plate (aqua), 50 µm LOMM (OM3 and OM4), Duplex SC, 6-fiber  | 507039   |
| 5F100-6LC   | Plate (blue), SM (OS2), Duplex SC, 6-fiber                  | 506932   |
| 5F100-2QC   | Plate (aqua), 50 µm LOMM (OM3 and OM4), Duplex SC, 12-fiber | 495909   |
| 5F100-2LC   | Plate (blue), SM (OS2), Duplex SC, 12-fiber                 | 489543   |
| 5F100-PLT   | Plate (black), Blank  | 488844   |

| <b>LEVITON FIBER OPTIC FAN KITS AND SPLICE TRAYS</b> |  |          |
|--|--|----------|
| PART NO.   | DESCRIPTION  | PART NO. |
| 49887-12S  | Fan-Out Kit 24" Length, 12-Fiber   | 380707   |
| 49887-12L  | Fan-Out Kit 36" Length, 12-Fiber   | 559543   |
| T5PLS-12F  | 12-Fiber Mini, 3.74" x 5.59" x .39" (Heat Shrink Splice Sleeves Included)        | 445393   |
| T5PLS-24F  | 24-Fiber High Density, 4.5" x 7.63" x .43" (Heat Shrink Splice Sleeves Included) | 518183   |
| SPLMT-HKT  | Splice Tray Mounting Hardware Kit  | 527016   |

| <b>LEVITON FIBER OPTIC CONNECTORS</b> |   |          |
|---------------------------------------|---|----------|
| PART NO.                              | DESCRIPTION   | PART NO. |
| 49991-LLC                             | FastCam <sup>®</sup> Connector LC OM3/4                             | 395554   |
| 49991-LSC                             | FastCam <sup>®</sup> Connector SC OM3/4                             | 395555   |
| 49991-SLC                             | FastCam <sup>®</sup> Connector LC OS2                               | 483402   |
| 49991-SSC                             | FastCam <sup>®</sup> Connector SC OS2                               | 518109   |
| 49990-LL2                             | Fast-Cure <sup>®</sup> Connector LC OM3/4 (with 3mm boot)           | 593342   |
| 49990-LDL                             | Fast-Cure <sup>®</sup> Connector LC OM3/4 (with .9mm boot)          | 438470   |
| 49990-LSC                             | Fast-Cure <sup>®</sup> Connector SC OM3/4 (with 3mm and .9mm boots) | 518182   |
| 49990-SL2                             | Fast-Cure <sup>®</sup> Connector LC OS2 (with 3mm boot)             | 289766   |
| 49990-SDL                             | Fast-Cure <sup>®</sup> Connector LC OS2 (with .9mm boot)            | 414513   |
| 49990-SSC                             | Fast-Cure <sup>®</sup> Connector SC OS2 (with 3mm and .9mm boots)   | 247726   |

| LEVITON                                |   | ANIXTER  |
|--|---|----------|
| <b>1000i SDX RACK-MOUNT ENCLOSURES</b> |   |          |
| PART NO.                               | DESCRIPTION   | PART NO. |
| 5R1UM-F03                              | 1RU, empty, accepts 3 adapter plates                    | 447467   |
| 5R1UM-S03                              | 1RU, empty, with sliding tray, accepts 3 adapter plates | 447465   |
| 5R2UM-F06                              | 2RU, empty, accepts 6 adapter plates                    | 447468   |
| 5R2UM-S06                              | 2RU, empty, with sliding tray, accepts 6 adapter plates | 447466   |
| 5R2UM-S06                              | 3RU, empty, accepts 12 adapter plates                   | 447471   |
| 5R4UM-F12                              | 4RU, empty, accepts 12 adapter plates                   | 447473   |

| <b>SDX WALL-MOUNT ENCLOSURES</b> |   |          |
|----------------------------------|---|----------|
| PART NO.                         | DESCRIPTION   | PART NO. |
| 5WMNT-01C                        | Mini, empty, no lock, accepts 1 adapter plate                   | 923728   |
| 5WSML-02C                        | Small, empty with dual door, no lock, accepts 2 adapter plates  | 923730   |
| 5WMED-04C                        | Medium, empty with dual door, no lock, accepts 4 adapter plates | 923731   |
| 5WLRG-12C                        | Large, empty with dual door, no lock, accepts 12 adapter plates | 923732   |

| <b>ACCESSORIES</b> |  |          |
|--------------------|--|----------|
| PART NO.           | DESCRIPTION  | PART NO. |
| 5RCMP-KIT          | Universal Clamp Kit (for enclosure mounting), single cable grommet         | 455957   |
| 5RCMP-KT2          | Universal Clamp Kit (for enclosure mounting), multiple cable grommet       | 592879   |
| 5RCMR-KIT          | Universal Clamp Kit, Single and Multiple Cable Grommet (for rack mounting) | 592915   |
| 5R1UX-CMT          | 1RU Patch Cord Management Tray (includes ORU cable managers)               | 902903   |
| 5R2UX-CMT          | 2RU Patch Cord Management Tray (includes ORU cable managers)               | N/A*     |

| <b>LEVITON ECONOMY SERIES FIBER OPTIC DUPLEX PATCH CORDS</b> |                      |          |
|--|----------------------|----------|
| PART NO.   | DESCRIPTION          | PART NO. |
| 5LDLC-M01  | LC-LC, 1 meter, OM3  | 508807   |
| 5LDLC-M02  | LC-LC, 2 meter, OM3  | 508808   |
| 5LDLC-M03  | LC-LC, 3 meter, OM3  | 477050   |
| 5LDLC-M05  | LC-LC, 5 meter, OM3  | 592658   |
| 5LDLC-M10  | LC-LC, 10 meter, OM3 | 450999   |
| 5LDSC-M01  | SC-SC, 1 meter, OM3  | 570803   |
| 5LDSC-M02  | SC-SC, 2 meter, OM3  | 570804   |
| 5LDSC-M03  | SC-SC, 3 meter, OM3  | 570805   |
| 5LDSC-M05  | SC-SC, 5 meter, OM3  | N/A*     |
| 5LDSC-M10  | SC-SC, 10 meter, OM3 | N/A*     |
| 54DLC-M01  | LC-LC, 1 meter, OM4  | N/A*     |
| 54DLC-M02  | LC-LC, 2 meter, OM4  | N/A*     |
| 54DLC-M03  | LC-LC, 3 meter, OM4  | N/A*     |
| 54DLC-M05  | LC-LC, 5 meter, OM4  | N/A*     |
| 54DLC-M10  | LC-LC, 10 meter, OM4 | N/A*     |

\* Contact Anixter for part number creation

## LEVITON OPT-X® SDX PLATFORM | FIBER OPTIC ENCLOSURES, ADAPTER PLATES, AND ACCESSORIES

| LEVITON  |                      | ANIXTER  | LEVITON  |                      | ANIXTER  |
|--|----------------------|----------|--|----------------------|----------|
| LEVITON ECONOMY SERIES FIBER OPTIC DUPLEX PATCH CORDS (cont'd) |                      |          | LEVITON ECONOMY SERIES FIBER OPTIC DUPLEX PATCH CORDS (cont'd) |                      |          |
| PART NO.   | DESCRIPTION          | PART NO. | PART NO.   | DESCRIPTION          | PART NO. |
| 54DSC-M01  | SC-SC, 1 meter, OM4  | N/A*     | UPDLC-S05  | LC-LC, 5 meter, OS2  | 518187   |
| 54DSC-M02  | SC-SC, 2 meter, OM4  | N/A*     | UPDLC-S10  | LC-LC, 10 meter, OS2 | 592643   |
| 54DSC-M03  | SC-SC, 3 meter, OM4  | N/A*     | UPDSC-S01  | SC-SC, 1 meter, OS2  | 568467   |
| 54DSC-M05  | SC-SC, 5 meter, OM4  | N/A*     | UPDSC-S02  | SC-SC, 2 meter, OS2  | 592637   |
| 54DSC-M10  | SC-SC, 10 meter, OM4 | N/A*     | UPDSC-S03  | SC-SC, 3 meter, OS2  | 592636   |
| UPDLC-S01  | LC-LC, 1 meter, OS2  | 445401   | UPDSC-S05  | SC-SC, 5 meter, OS2  | 592635   |
| UPDLC-S02  | LC-LC, 2 meter, OS2  | 518119   | UPDSC-S10  | SC-SC, 10 meter, OS2 | 592638   |
| UPDLC-S03  | LC-LC, 3 meter, OS2  | 518174   |  |                      |          |

\* Contact Anixter for part number creation

## BERK-TEK FIBER OPTIC CABLES

| BERK-TEK   |  | ANIXTER           |
|--|--|-------------------|
| <b>OM3 PREMISES DISTRIBUTION INDOOR/OUTDOOR PLENUM CABLE</b> |  |                   |
| PART NO.   | DESCRIPTION  | PART NO.          |
| PDP006EB3010/25-I/O-C4(AQU)                                  | 6 Fiber, Tight Buffered, Plenum, 50 µm-OM3, Indoor/Outdoor, Aqua Jacket  | 373-BKTOM3-TBP-06 |
| PDP012EB3010/25-I/O-C4(AQU)                                  | 12 Fiber, Tight Buffered, Plenum, 50 µm-OM3, Indoor/Outdoor, Aqua Jacket | 373-BKTOM3-TBP-12 |
| PDP024EB3010/25-I/O-C4(AQU)                                  | 24 Fiber, Tight Buffered, Plenum, 50 µm-OM3, Indoor/Outdoor, Aqua Jacket | 373-BKTOM3-TBP-24 |

| <b>SINGLE-MODE PREMISES DISTRIBUTION INDOOR/OUTDOOR PLENUM CABLE</b> |  |                   |
|--|--|-------------------|
| PART NO.   | DESCRIPTION  | PART NO.          |
| PDP006AB0707-I/O-C4(YEL)   | 6 Fiber, Tight Buffered, Plenum, Single-Mode, Indoor/Outdoor, Yellow Jacket  | 373-BKTOS2-TBP-06 |
| PDP012AB0707-I/O-C4(YEL)   | 12 Fiber, Tight Buffered, Plenum, Single-Mode, Indoor/Outdoor, Yellow Jacket | 373-BKTOS2-TBP-12 |
| PDP024AB0707-I/O-C4(YEL)   | 24 Fiber, Tight Buffered, Plenum, Single-Mode, Indoor/Outdoor, Yellow Jacket | 373-BKTOS2-TBP-24 |

| <b>OM4 PREMISES DISTRIBUTION INDOOR/OUTDOOR PLENUM CABLE</b> |  |                   |
|--|--|-------------------|
| PART NO.   | DESCRIPTION  | PART NO.          |
| PDP006FB3010/F5-I/O-C4(AQU)                                  | 6 Fiber, Tight Buffered, Plenum, 50 µm-OM4, Indoor/Outdoor, Aqua Jacket  | 373-BKTOM4-TBP-06 |
| PDP012FB3010/F5-I/O-C4(AQU)                                  | 12 Fiber, Tight Buffered, Plenum, 50 µm-OM4, Indoor/Outdoor, Aqua Jacket | 373-BKTOM4-TBP-12 |
| PDP024FB3010/F5-I/O-C4(AQU)                                  | 24 Fiber, Tight Buffered, Plenum, 50 µm-OM4, Indoor/Outdoor, Aqua Jacket | 373-BKTOM4-TBP-24 |

| <b>OM3 PREMISES DISTRIBUTION INDOOR/OUTDOOR PLENUM CABLE WITH INTERLOCKING ARMOR</b> |  |                    |
|--|--|--------------------|
| PART NO.   | DESCRIPTION  | PART NO.           |
| PDPK006EB3010/25-I/O-C4C5(AQU)   | 6 Fiber Tight Buffered, Plenum, Interlock Armored, 50 µm-OM3, Indoor/Outdoor, Aqua Jacket  | 373-BKTOM3-TBPA-06 |
| PDPK012EB3010/25-I/O-C4C5(AQU)   | 12 Fiber Tight Buffered, Plenum, Interlock Armored, 50 µm-OM3, Indoor/Outdoor, Aqua Jacket | 373-BKTOM3-TBPA-12 |
| PDPK024EB3010/25-I/O-C4C5(AQU)   | 24 Fiber Tight Buffered, Plenum, Interlock Armored, 50 µm-OM3, Indoor/Outdoor, Aqua Jacket | 373-BKTOM3-TBPA-24 |

| <b>SINGLE-MODE PREMISES DISTRIBUTION INDOOR/OUTDOOR PLENUM CABLE WITH INTERLOCKING ARMOR</b> |  |                    |
|--|--|--------------------|
| PART NO.   | DESCRIPTION  | PART NO.           |
| PDPK006AB0707-I/O-C4C5(YEL)  | 6 Fiber Tight Buffered, Plenum, Interlock Armored, Single-Mode, Indoor/Outdoor, Yellow Jacket  | 373-BKTOS2-TBPA-06 |
| PDPK012AB0707-I/O-C4C5(YEL)  | 12 Fiber Tight Buffered, Plenum, Interlock Armored, Single-Mode, Indoor/Outdoor, Yellow Jacket | 373-BKTOS2-TBPA-12 |
| PDPK024AB0707-I/O-C4C5(YEL)  | 24 Fiber Tight Buffered, Plenum, Interlock Armored, Single-Mode, Indoor/Outdoor, Yellow Jacket | 373-BKTOS2-TBPA-24 |

| <b>OM4 PREMISES DISTRIBUTION INDOOR/OUTDOOR PLENUM CABLE WITH INTERLOCKING ARMOR</b> |  |                    |
|--|--|--------------------|
| PART NO.   | DESCRIPTION  | PART NO.           |
| PDPK006FB3010/F5-I/O-C4C5(AQU)   | 6 Fiber Tight Buffered, Plenum, Interlock Armored, 50 µm-OM4, Indoor/Outdoor, Aqua Jacket  | 373-BKTOM4-TBPA-06 |
| PDPK012FB3010/F5-I/O-C4C5(AQU)   | 12 Fiber Tight Buffered, Plenum, Interlock Armored, 50 µm-OM4, Indoor/Outdoor, Aqua Jacket | 373-BKTOM4-TBPA-12 |
| PDPK024FB3010/F5-I/O-C4C5(AQU)   | 24 Fiber Tight Buffered, Plenum, Interlock Armored, 50 µm-OM4, Indoor/Outdoor, Aqua Jacket | 373-BKTOM4-TBPA-24 |