

MPrint™

Mobile Printers

ULTRA-PORTABLE
MOBILE PRINTING SOLUTIONS

MPRINT™



These ultra-portable mobile printers fit in a pocket or hang on a belt, yet print high-resolution text, graphics and pictures on cut-sheet thermal paper in sizes from A7 (2.9" x 4.1") to A6 (4.1" x 5.8"). Their light weight, small size, and Bluetooth® technology interface make them ideal for printing documents such as e-citations, customer receipts and invoices, maintenance and repair reports, service records, and inspection certificates from handhelds and laptops practically anywhere.*

MW-120, MW-145BT & MW-260
Data Sheet

brother®
at your side



Technical Specifications			
	MW-120	MW-145BT	MW-260
Interface	USB, IrDA, Serial**	USB, Bluetooth®	USB, IrDA, Bluetooth®
Printing Method	Direct thermal printing with a line thermal print head		
Printing Speed	Up to 4 sheets/minute (standard text on A7 ThermalPlus® M paper with 7% coverage)		Up to 3 sheets/minute (standard text on A6 ThermalPlus® M paper with 7% coverage)
Printing Resolution	300 dpi x 300 dpi		
Paper Feed Method	Brother paper cassette, automatic feed mechanism		
Paper Size	Brother A7 paper (4.1" x 2.9")		Brother A6 paper (5.8" x 4.1")
Printable Area	3.9" x 2.7"		5.6" x 3.9"
External Dimensions	6.3" (L) x 3.9" (W) x 0.7" (H)		8.2" (L) x 5.2" (W) x 0.7" (H)
Weight (incl. battery and C-11 paper)	11 oz.		1.2 lbs.
Power Supply	Built-in rechargeable lithium ion battery with AC adapter for charging	Removable, rechargeable lithium ion battery with AC adapter for charging	Removable rechargeable lithium ion battery with AC adapter for charging
Number of Printable Pages	Up to 100 during continuous printing with a fully charged battery (based on 7% coverage and 25°C ambient temperature)		
Energy-Saving Feature	Auto power off (adjustable from 1 - 255 minutes)		
Operating Systems Supported	Windows® 7, Windows Vista, Windows XP, Windows 2000 Professional, Windows NT, Windows 98; PocketPC® 2002/2003/SE; Windows Mobile® 5/6; Android™ 2.2 or higher; BlackBerry® OS 4.2 or higher.	Windows® 7, Windows Vista, Windows XP, Windows 2000 Professional; Windows Mobile® 5/6; Android™ 2.2 or higher; BlackBerry® OS 4.2 or higher.	Windows® 7, Windows Vista, Windows XP, Windows 2000 Professional; Windows Mobile® 5/6; PocketPC® 2003/SE; Android™ 2.2 or higher; BlackBerry® OS 4.2 or higher.
Printing Software Included (on CD-Rom)	MPrint™ printer drivers		MPrint™ printer drivers, Brother MPrint™ printing software
Windows	Brother MPrint™ printing software and PrintPocketCE for Brother IrPrint™		
Pocket PC/Windows Mobile	Brother MPrint™ printing software		
Accessories/Supplies Included	1 USB cable, 1 AC adapter, 1 paper cassette containing 50 sheets of thermal paper		

Supplies: All Brother MPrint™ mobile printers use a paper cassette system that makes changing and loading the paper quick and easy. The paper cassettes are available in A7 size (2.9" x 4.1") for the MW-120 and MW-145BT series printers and A6 size (4.1" x 5.8") for the MW-260. Brother offers standard and fade-resistant (MW-260 only) paper.

ASK US ABOUT OUR OTHER PRODUCTS

PocketJet® 6 mobile printers

Full-page Mobile Printers

PocketJet® 6 Plus

- Up to 6ppm, at 300 dpi resolution
- Prints up to 8.5" wide on cut-sheet or continuous-roll thermal paper
- Stores downloaded templates
- Full-speed USB 2.0 and IrDA interfaces
- Optional Bluetooth® Version 2.0 plus EDR support available▼
- Optional Ni-MH battery or Li-ion battery available▼



PocketJet® 6

All the features of the PocketJet® 6 Plus, but with:

- Up to 6ppm, at 200 dpi resolution

▼ Requires additional purchase.



RuggedJet® mobile printers

Receipt & Label Mobile Printers

RuggedJet® RJ-4030

- Up to 5 ips, at industry-standard 203 dpi resolution
- IP54 certification to withstand dust and moisture
- 6 ft. drop protection
- Prints labels and receipts from 2" to 4" wide from convenient drop-in rolls
- Resident fonts
- USB 2.0, Serial and Bluetooth® technology interfaces
- Optional magnetic card reader available▼



RuggedJet® RJ-4040

All the features of the RuggedJet™ RJ-4030, but with:

- USB 2.0, Serial and Wi-Fi (802.11b/g/n) interfaces

▼ Requires additional purchase.



All specifications subject to change without notice.

BROTHER MOBILE SOLUTIONS, INC.

For more information, visit www.brothermobilesolutions.com
Call 1-800-543-6144 ext. 1601 for more information on our SDKs.

* MW-145BT and MW-260 only ** Additional purchase required for serial cable. MPrint™ printers include 50 sheets of thermal paper. Additional purchase required for all other paper supplies. Brother™ and the Brother logo are trademarks or registered trademarks of Brother Industries, Ltd. in the United States. The Bluetooth word mark and logos are owned by Bluetooth SIG, Inc. and any use of such marks by Brother International Corp. is under license. Windows® and Microsoft® are registered trademarks of Microsoft Corporation in the United States and other countries. The official name for Windows is the Microsoft Windows Operating System. PrintPocketCE for Brother by FieldSoftware Products. For additional Pocket PC printing utilities, visit www.fieldsoftware.com. Android is a trademark of Google Inc. Use of this trademark is a subject to Google permission. The company, product, and other names mentioned in this document are the trademarks or registered trademarks of each company. The RIM and Blackberry families of related marks, images and symbols are the exclusive properties and trademarks of Research In Motion Limited – used by permission.
© 2012 Brother Mobile Solutions, Inc.

brother
at your side

BMS 01-2012 009