

TD-4000 & TD-4100N

Desktop Barcode & Label Printers

LIGHT INDUSTRIAL THERMAL PRINTERS
FOR LABELS, RECEIPTS & TAGS



Brother™ TD Series desktop barcode and label printers come as complete solutions that include a 4" label printer, label design and print software, and labels to help you get started right out of the box – all this for the price of just the printer! Printing at 300 dpi resolution, up to 4.3ips print speed and featuring a built-in automatic cutter for cutting continuous thermal media to virtually any length on demand, these models deliver the highest performance at a low purchase price. Compatible with Windows® 7 or print from many legacy software applications using a variety of software development tools available from Brother.

TD-4000 & TD-4100N
Data Sheet

brother[®]
at your side



Technical Specifications		
	TD-4000	TD-4100N
Model Type	Desktop Barcode and Label Printer	Desktop Barcode and Label Printer (Network)
Maximum Media Width	4.16" (105.6 mm)	
Maximum Printing Speed	4.3 ips (110 mm/sec)	
Maximum Print Resolution	300 x 300 dpi (12 x 12 dots/mm)	
Printing Method	Direct Thermal	
Cutter	Automatic (Built-in)	
Media Sensor & Position	Fixed Transmissive, Edge	
Media Types	Drop-In Roll or Fanfold (rear slot) Continuous Label or Paper, Die Cut Labels, Tag Stock	
Maximum Roll Size (outside diameter)	4" (101.6 mm)	
Resident Fonts	Helsinki, Brussels, Letter Gothic, San Diego, Brougham	
Resident Barcodes	Linear: Code39, ITF (I-2/5), UPC-A, UPC-E, EAN8, EAN13, Codabar (NW-7), Code128, GS1-128 (UCC/EAN128), GS1 DataBar (RSS) 2-Dimensional: PDF417, QR Code, Data Matrix, Maxicode	
Software (included on CD-ROM)	P-touch® PT-Editor 5.0, Transfer Manager 2.1, Library 2.1	BRAdmin Light 1.14, P-touch® PT-Editor 5.0, Transfer Manager 2.1, Library 2.1
Database file compatibility	*.csv, *.txt, *.mdb, *.xls and Microsoft SQL Server	
Interface	USB (1.1 or 2.0), Serial (RS-232C)	USB (1.1 or 2.0), Serial (RS-232C), Ethernet (10/100 Base-TX)
Operating System	Windows® 7/XP/2000 Professional, Windows Vista®	Windows® 7/XP/2000 Professional, Windows Vista®, Windows Server® 2003/2008
Carton Contents	Printer, Power Cord, USB Cable, CD, RD Starter Roll - Continuous Length Label (2m or 6.56 ft.), RD Starter Roll - 2" x 1" Labels (60 labels), User Guide	
Power Supply	120VAC 60 Hz 1.8A	
EnergyStar	Yes	
Warranty	1 Year Limited Warranty	

ACCESSORIES*



For TD-4000 / TD-4100N

The RD label rolls are available in many standard die cut label sizes. Or choose the continuous label – Brother™ desktop label printers have a built-in cutter that will trim the label to virtually any length you need. Ask about new die cut label sizes, tags, receipt and other types of continuous media. Flood coat and preprinting services are also available.



RDS01U2	4in Wide Continuous Paper Label (145ft)
RDS02U1	4in x 6in Paper Label (281 labels/roll)
RDS03U1	4in x 2in Paper Label (814 labels/roll)
RDS04U1	3in x 1in Paper Label (1,544 labels/roll)
RDS05U1	2in x 1in Paper Label (1,544 labels/roll)

ASK US ABOUT OUR OTHER PRODUCTS

Desktop Barcode and Label Printers

PT-9700PC

Thermal transfer printer for tough and durable laminated labels



PT-9800PCN

Thermal transfer printer with built-in print server for tough and durable laminated labels



*Requires additional purchase. All specifications subject to change without notice.

BROTHER MOBILE SOLUTIONS, INC.

**For more information, call 1-800-543-6144,
or visit www.brothermobilesolutions.com**

Brother™ is a trademark or registered trademark of Brother Industries, Ltd. in the United States. Microsoft®, Windows® and Windows Vista® are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries. All other trademarks and registered trademarks are the properties of their respective companies.

© 2012 Brother Mobile Solutions, Inc., 100 Technology Drive, Suite 250A, Broomfield, CO 80021

brother
at your side

BMS 01-2012 004