


Everon™ Network Solutions

Fibre to the Edge Amusement Park (Wi-Fi, Audio, and Signaling [Light & Sound]) Scenario



TR Telecom Room



1. Closet Connector Housing
CCH-04U
Four rack units, holds 12 CCH connector panels
2. Power Supply Unit
CIP-16-56V or CIP-32-56V
16 or 32 channels, mountable, rack mountable
3. Media Converter
1LAN-FMC-10G
10G HPoE Media Converter, supports 90 W PoE++

CC Campus Cabling

4. ActiFi® Composite Cable
002ZTF-D1035M20
ActiFi® Composite Cable, Loose Tube, Outdoor, 2 F, 2 Cu Conductor, 16AWG

MC Edge Media Converter

3. Media Converter
1LAN-FMC-10G
10G HPoE Media Converter, supports 90 W PoE++, up to 10G, DIN rail mountable
5. Outdoor Enclosure
1LAN-D600-ENC-3
NEMA4 watertight enclosure
6. PoE Patch Copper Cord
CCAAGB-G2002-Ayyy-C0
yyy=length (010 for 1 metre, 020 2 metre etc)
Corning® Everon™ Copper Datacom Class EA Patch Cord, 2xRJ45, Cat.6A, S/FTP LSZH™ AWG26, blue



Security Room or Telecom Room

CCH-04U	Closet Connector Housing, four rack units, holds 12 CCH connector panels
CCH-02U	Closet Connector Housing, two rack units, holds 6 CCH connector panels
CCH-01U	Closet Connector Housing, one rack unit, holds 2 CCH connector panels
CCH-CS12-AE-P00RE	CCH Splice Module with pigtails, 12 F, LC UPC duplex shuttered, blue, single-mode (OS2)
CCH-CS24-AE-P00RE	CCH Splice Module with pigtails, 24 F, LC UPC duplex shuttered, blue, single-mode (OS2)
1LAN-D920CC-6	Panel for power supply, Keystone CCH panel, 6 position
1LAN-D600-CCP2-WH	Keystone Adapter, connector style
CIP-16-56V	Class 2 Power Supply, 56 VDC, 16 channels, 1.5RU
CIP-32-56V	Class 2 Power Supply, 56 VDC, 32 channels, 2RU
CIP-19SHELF-1.5U	19-in Rack Mount Shelf with 1.5U and 2U blank plates for CIP-16-56V and CIP-16-24V
CIP-19SHELF-2U	19-in Rack Mount Shelf with 1.5U and 2U blank plates for CIP-32-56V and CIP-32-24V
DE2-CCA-1PR18-2M	Single Cross-Connect Assembly with PHX connector, 18AWG, 2 m, 1 pair
1LAN-FMC-10G	10G HPoE Media Converter, supports 90W PoE++, up to 10G, DIN rail mountable
1LAN-SFPP-10LR	10 Gb/s SFP+ Transceiver Module, SMF, 1310 nm, 10 km
1LAN-FMC-DINBRACKET	Din Rail Accessory Bracket for FMC (48.8 x 32 x 9 mm)

LAN Cabling

002Z4U-22Z25M2G	ActiFi® Composite Cable, tight buffered, indoor, 2 F, 2 Cu Conductor, 20AWG, LSZH™, Cca
-----------------	-----------------------------------------------------------------------------------------

Campus Cabling

002ZTF-D1035M20	ActiFi Composite Cable, loose tube, outdoor, 2 F, 2 Cu Conductor, 16AWG
-----------------	-------------------------------------------------------------------------

Edge Media Conversion Point

1LAN-D600-ENC-3	NEMA4 Outdoor watertight enclosure
1LAN-D600-ENC-8	NEMA4 enclosure, contains DIN Rail for mounting 1LAN-FMC-10G
1LAN-D600-FMC-KIT	Mounting kit for 1LAN-FMC-10G into 1LAN-D600-ENC-3 outdoor enclosure
1LAN-FMC-10G	10G HPoE Media Converter, supports 90W PoE++, up to 10G, DIN rail mountable
1LAN-SFPP-10LR	10Gb/s SFP+ Transceiver Module, SMF, 1310 nm, 10 km
CAXISD-U0208-C002	Everon™ Copper Datacom IP67/65 Outlet for LANscape® jacks empty
CAXASM-00104-C001	Everon Copper Datacom S500 Jack Cat.6A, Shielded, LANscape Footprint
CCAAGB-G2002-Ayyy-CO	Everon Copper Datacom Class EA Patch Cord, 2xRJ45, Cat.6A, S/FTP LSZH AWG26, blue, yyy=length (010 for 1 metre, 020 2 metre etc)
CCAAGB-G1002-Ayyy-CC	Everon Copper Datacom Class EA Patch Cord, 2xRJ45, Cat.6A, S/FTP LSZH AWG26, Cca, grey, yyy=length (010 for 1 metre, 020 2 metre etc)

CORNING

Corning Optical Communications GmbH
& Co. KG • Leipziger Strasse 121
10117 Berlin, GERMANY
+00 800 2676 4641 • FAX: +49 30 5303
2335 • www.corning.com/opcomm/emea

Corning Optical Communications reserves the right to improve, enhance, and modify the features and specifications of Corning Optical Communications products without prior notification. A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2022 Corning Optical Communications. All rights reserved. LAN-3075-A4-BEN / November 2022