

**S500 Solution Cat6A & Cat7**

**Copper Cable**

<b>Anixter PN</b>	<b>Vendor PN</b>	<b>Description</b>	<b>Category</b>
CMZ-0423COR-ECF6R-06	CCXEDR-D0047-C003-L7	4P S/FTP 550MHZ 23 AWG CAT6A CABLE LSZH LOW FIRE RES BLUE 1000 MT REEL	Copper adder
CMZ-00423COR-F6AR-06	CCXEDR-D0047-C003-L6	FutureCom S/FTP 550MHz, 23AWG, 4-pair, Category 6A, LSZH/FRNC, Blue, 500 meters	Copper adder
CMZ-0423COR-CF6U-06	CCXEDR-D0047-C003-X2	S/FTP 550/23s Cat6A 4P Simplex Copper Cable, LSOH/LSZH, FRNC, 250m Reelex box	Copper adder
CMZ-00423COR-FF6A-06	CCXEDA-D0047-C001-L6	FutureCom F/FTP 550MHz, 23AWG, 4-pair, Category 6A, LSZH/FRNC, Blue, 500 meters	Copper adder
CMZ-00423COR-C6R-06	CCXEDB-D0047-C001-L7	S/FTP 550/23 Cat6A 4P Simplex Copper Cable, LSOH/LSZH, FRNC, 1.000m drum	Copper adder
CMZ-00423STP-6S-N	CCXEDB-F0047-C001-L7	CABLE, 23 AWG, 4 PAIR, CAT 6 SHIELDED FOIL TWISTED PAIR SOLID BARE COPPER CONDUCTOR POLYOLEFIN LOW SMOKE ZERO HALOGEN ICCS CABLE RATED 600MHZ	Copper adder
544157	CCXFCB-L0047-C001-L7	CABLE, 22 AWG, 4 PAIR, FOIL AND BRAID SHIELDED TWISTED PAIR 1200 FUTURECOM LOW SMOKE ZERO HALOGEN 1200MHZ COLOR BLUE CAT 7 1000 METER REELS	Copper adder
CM-00423COR-C7-06	CCXEDR-F0047-C001-L7	S/FTP 800/23s Cat7 4P Simplex Copper Cable, LSOH/LSZH, FRNC, 1.000m drum	Copper adder
CMZ-00422COR-CF7-06	CCXFCB-I0047-C001-L7	22-4PR FUTURECOM S/FTP LSOH PIMF 1000MHZ CAT7A SOL BLUE CCXFCB-I0047-C001-L7	Copper adder

**S500 Copper Jack**

<b>Anixter PN</b>	<b>Vendor PN</b>	<b>Description</b>	<b>Category</b>
-------------------	------------------	--------------------	-----------------

384029	CAXASM-00104-C001	FUTURECOM S500 CAT6A 1XRJ45 MOD SHIELED WITH DUST COVER CAXASM-00104-C001	Cat6A
386019	CAXBSM-00104-C001	FUTURECOM EA KEYSTONE S500 MOD RJ45 SHIEDED CAT6A WITH DUST COVER	Cat6A
386020	CAXASM-00104-C002	FUTURECOM EA S500 FLEX MOD RJ45 CAT6A FOR STRANDED CABLE W/DUST COVER	Cat6A
386021	CAXBSM-00104-C002	S500fx Keystone Cat.6A/Class EA Copper Jack with dust cap	Cat6A

### Copper Patch Cords

Anixter PN	Vendor PN	Description	Category
MM01M-CORC6A-06	CCAAGB-G2002-A010-c0	FUTURECOM EA PATCHCORD CAT6A RJ45/RJ45 S/FTP 4PR BLUE 1MT CCAAGBG2002A010	Cat6A
MM02M-CORC6A-06	CCAAGB-G2002-A020-c0	FUTURECOM EA PATCHCORD CAT6A RJ45/RJ45 S/FTP 4PR BLUE 2MT CCAAGBG2002A020	Cat6A
MM03M-CORC6A-06	CCAAGB-G2002-A030-c0	FUTURECOM EA PATCHCORD CAT6A RJ45/RJ45 S/FTP 4PR BLUE 3MT CCAAGBG2002A030	Cat6A
MM05M-CORC6A-06	CCAAGB-G2002-A050-c0	FUTURECOM EA PATCHCORD CAT6A RJ45/RJ45 S/FTP 4PR BLUE 5MT CCAAGBG2002A050	Cat6A
MM10M-CORC6A-06	CCAAGB-G2002-A100-c0	FUTURECOM EA PATCHCORD CAT6A RJ45/RJ45 S/FTP 4PR BLUE 10MT CCAAGBG2002A100	Cat6A
MM01M-CORC6A-09	CCAAGB-G1002-A010-c0	FUTURECOM EA PATCHCORD CAT6A RJ45/RJ45 S/FTP 4PR GREY 1 MT CCAAGBG1002A010	Cat6A
MM02M-CORC6A-09	CCAAGB-G1002-A020-c0	FUTURECOM EA PATCHCORD CAT6A S/FTP RJ45/RJ45 4PR GREY 2 MT CCAAGBG1002A020	Cat6A

MM03M-CORC6A-09	CCAAGB-G1002-A030-c0	FUTURECOM EA PATCHCORD CAT6A S/FTP RJ45/RJ45 4PR GREY 3 MT CCAAGBG1002A030	Cat6A
MM05M-CORC6A-09	CCAAGB-G1002-A050-c0	FUTURECOM EA PATCHCORD CAT6A S/FTP RJ45/RJ45 4PR GREY 5 MT CCAAGBG1002A050	Cat6A
MM10M-CORC6A-09	CCAAGB-G1002-A100-c0	FUTURECOM EA PATCHCORD CAT6A S/FTP RJ45/RJ45 4PR GREY 10 MT CCAAGBG1002A100	Cat6A