

Plug&Play Universal Modules LC-MTP

Anixter PN	Vendor PN	Description	Category
348949	CCH-UM12-04-89R	Plug & Play(tm) Universal Module, LC, 12 F, Shuttered LC to MTP, Single-mode (OS2)	Data Centre
327951	CCH-UM24-04-89R	24-FIBER MODULE LC DUP TO MTP 8.3/125 SM UNIVERSAL WIRING REDUCED DEPTH	Data Centre
415944	CCH-UM12-05-70T	Plug & Play(TM) Universal Module, LC, 12 fiber, Shuttered LC to MTP®, 50 µm multimode (OM3)	Data Centre
401471	CCH-UM24-05-70T	Plug & Play(TM) Universal Module, LC, 24 fiber, Shuttered LC to MTP®, 50 µm multimode (OM3)	Data Centre
366957	CCH-UM24-05-70Q	Plug & Play(TM) Universal Module, LC, 24 fiber, Shuttered LC to MTP®, 50 µm multimode (OM4)	Data Centre
401476	CCH-UM12-05-93T	Plug & Play(TM) Universal Module, LC, Low-Loss, 12 fiber, Shuttered LC to MTP®, 50 µm multimode (OM3)	Data Centre
401478	CCH-UM12-05-93Q	Plug & Play(TM) Universal Module, LC, Low-Loss, 12 fiber, Shuttered LC to MTP®, 50 µm multimode (OM4)	Data Centre
401477	CCH-UM24-05-93T	Plug & Play(TM) Universal Module, LC, Low-Loss, 24 fiber, Shuttered LC to MTP®, 50 µm multimode (OM3)	Data Centre
349192	CCH-UM24-05-93Q	Plug & Play(TM) Universal Module, LC, Low-Loss, 24 fiber, Shuttered LC to MTP®, 50 µm multimode (OM4)	Data Centre