

MM OM2 50/125 Fibre Optical Solution

Fibre Optical Cables

Multimode 50/125 OM2 Cable Indoor/Outdoor Loose Tube MPC with Rodent Protection

Anixter PN	Vendor PN	Description	Category
373-COR50CC-LTDCT-06	006TEU-13138A2G	6F MM 50/125 OM2 CLEARCURVE IN/OUT LSZH LT CT NON-MET/ROD LCXLM1-K0006-G700	OM2
373-COR50GF-LTDCT-12	012TEU-13138D2G	12F MM 50/125 OM2 CC FREEDM DRY MPC LT IN/OUT LSZH/FRNC 012TSZ-T2B31D20	OM2
373-COR50CC-LTDCT-24	024TEU-13138A2G	24F MM 50/125 OM2 CLEARCURVE L CT LSZH BLACK IN/OUT NON-MET/ LCXLM1-K0024-G700	OM2

Multimode 50/125 OM2 Cable Indoor Tight Buffer i-MIC

Anixter PN	Vendor PN	Description	Category
374-COR50CC-TBD-04	004T8Z-32138E2G	4F MM 50/125 OM2 CLEARCURVE TB I-MIC INDOOR LSZH/FRNC ORANGE LCXLI2-L5004-G700	OM2
374-COR50CC-TBD-12	012T8Z-32138E2G	12F MM 50/125 OM2 CLEARCURVE T I-MIC INDOOR LSZH/FRNC ORANGE LCXLI2-L5012-G700	OM2
374-COR50CC-TBD-24	024T8Z-32138E2G	24F MM 50/125 OM2 CLEARCURVE T I-MIC INDOOR LSZH/FRNC ORANGE LCXLI2-L5024-G700	OM2

UniCam Connectors Multimode OM2 50/125

Anixter PN	Vendor PN	Description	Category
278288	95-050-50	UniCam® Standard-Performance Connector, ST® Compatible, 50 µm multimode (OM2), ceramic ferrule, logo, single pack, amber housing, black boot	OM2

188883-NEW	95-050-51	UniCam® High-Performance Connector, ST® Compatible, 50 µm multimode (OM2), ceramic ferrule, logo, single pack, amber housing, black boot	OM2
278287	95-050-40	UniCam® Standard-Performance Connector, SC, 50 µm multimode (OM2), ceramic ferrule, logo, single pack, black housing, black boot	OM2
205644-NEW	95-050-41	UniCam® High-Performance Connector, SC, 50 µm multimode (OM2), ceramic ferrule, logo, single pack, black housing, black boot	OM2
280092-NEW	95-050-99	UniCam® High-Performance Connector, LC, 50 µm multimode (OM2), ceramic ferrule, logo, single pack, black housing, black boot	OM2
598639	95-050-90	LC UNICAM CONN 50/125 OM2 CER STD PERFORMANCE 0.3DB TYPICAL LOSS	OM2

Empty Panel

Anixter PN	Vendor PN	Description	Category
545410-V2	LANS-01U-B4	PULL OUT TRAY 19 INCH WIDE 1-U RACK MOUNT SPACE COLOR BLACK UP TO 24 SINGLE MODULE WITH HOLDER FOR UP TO 4 SPLICE TRAYS	Fibre&Copper Accy
454508-V2	LANS-02U-B8	PULL OUT TRAY 19 INCH WIDE 2-U RACK MOUNT SPACE COLOR BLACK UP TO 48 SINGLE MODULE WITH HOLDER FOR UP TO 4 SPLICE TRAYS	Fiber&Copper Accy
415633-EA	LANC-01U-B	1U fixed LANC Fibre Housing (24x LANscape), black	Fiber&Copper Accy

Modules LANC/LANS MM 50/125 OM2

Anixter PN	Vendor PN	Description	Category
415635-EA	LANC-MOD-P5-B	SC Duplex MM/OM2 Fibre Module, metal sleeve (2x LANscape), black socket	OM2

415634-EA	LANC-MOD-74-B	ST MM/OM2 Fibre Module, metal sleeve (1x LANscape), black socket	OM2
415639-EA	LANC-MOD-D2-B	LC Duplex MM/OM2 Fibre Module, metal sleeve (1x LANscape), black socket	OM2
415643	LANC-MOD-BLNK-B	BLANK MOD FOR LANC LINE BLACK 100 PCS/PK	OM2
545456	LANS-MOD-15-B	MODULE COLOR BLACK WITH 1 ST MULTIMODE FIBER ADAPTER (FEEDTHROUGH + ST) FOR USE WITH BLACK HARDWARE	OM2
429448	LANS-MOD-G7-B	LANS MOD MM 50/125 OM2 SC DUPX BLACK CER INSERT BLACK ADPT SINGLE PACKED	OM2
499267	LANS-MOD-AC-B	LANS MOD MM 50/125 OM2 LC DUPX BLACK CER INSERT BLACK ADPT SHUTTERED	OM2

LANC & LANS Splice Pack MM 50/125 OM2

Anixter PN	Vendor PN	Description	Category
415645-EA	SP12-50B-S8	STD SPLICE TRAY HEATSHRINK W/ 12 ST MM 50/125 OM2 PIGTAIL	OM2
415647-EA	SP12-39B-S8	SC MM/OM2 Universal Splice Pack (heat-shrink/crimp) incl. 12 pigtails and cover	OM2
415651-EA	SP12-03B-S8	LC MM/OM2 Universal Splice Pack (heat-shrink/crimp) incl. 12 pigtails and cover	OM2

Patchcords Multimode 50/125 OM2

Anixter PN	Vendor PN	Description	Category
------------	-----------	-------------	----------

412585	505002B5Z31003M	ST Compatible to ST Compatible patch cord on 2-fiber Zipcord cable, with 2.8 mm legs, and a low-smoke, zero-halogen sheath. 3 m	OM2
412589	575702B5Z31003M	SC Duplex to SC Duplex patch cord on 2-fiber Zipcord cable, with 2.8 mm legs, and a low-smoke, zero-halogen sheath. 3 m	OM2
412596	050502B5Z20003M	LC Duplex to LC Duplex patch cord on 2-fiber Zipcord cable, with 2 mm legs, and a low-smoke, zero-halogen sheath. 3 m	OM2
412604	505702B5Z31003M	2F JUMPER MM 50/125 OM2 CC ST/SC DUPX ORANGE LSZH ZIP 3M	OM2
412614	055702B5Z20003M	LC Duplex to SC Duplex patch cord on 2-fiber Zipcord cable, with 2 mm legs, and a low-smoke, zero-halogen sheath. 3 m	OM2
412609	055002B5Z20003M	LC Duplex to ST Compatible patch cord on 2-fiber Zipcord cable, with 2 mm legs, and a low-smoke, zero-halogen sheath. 3 m	OM2