

Hardware**UniCam Connector OM3/OM4 50/125**

Anixter PN	Vendor PN	Description	Category
308485	95-050-51-X	UniCam® High-Performance Connector, ST® Compatible, 50 µm multimode (OM3/OM4 compatible), ceramic ferrule, logo, single pack, amber housing, aqua boot	OM3/OM4
255259-NEW	95-050-41-X	UniCam® High-Performance Connector, SC, 50 µm multimode (OM3/OM4 compatible), ceramic ferrule, logo, single pack, black housing, aqua boot	OM3/OM4
280093-NEW	95-050-99-X	UniCam® High-Performance Connector, LC, 50 µm multimode (OM3/OM4 compatible), ceramic ferrule, logo, single pack, black housing, aqua boot	OM3/OM4

Empty Panel

Anixter PN	Vendor PN	Description	Category
545410-V2	LANS-01U-B4	PULL OUT TRAY 19 INCH WIDE 1-U RACK MOUNT SPACE COLOR BLACK UP TO 24 SINGLE MODULE WITH HOLDER FOR UP TO 4 SPLICE TRAYS	Fibre&Copper Accy
454508-V2	LANS-02U-B8	PULL OUT TRAY 19 INCH WIDE 2-U RACK MOUNT SPACE COLOR BLACK UP TO 48 SINGLE MODULE WITH HOLDER FOR UP TO 4 SPLICE TRAYS	Fibre&Copper Accy
415633-EA	LANC-01U-B	1U fixed LANC Fibre Housing (24x LANscape), black	Fibre&Copper Accy

LANC/LANS Module OM3/OM4 50/125

Anixter PN	Vendor PN	Description	Category
289655	LANS-MOD-E7-B	SC DUPX MOD MM ADAPTER OM3 COMP.HOUSING AQUA/CER.INSERT BLACK FEEDTHROUGH	OM3/OM4

545118	LANS-MOD-E5-B	LANS ADAPTER MODULE, ST COMPAT CERAMIC SLEEVE 50UM MM OM3/OM4 BLACK	OM3/OM4
499272	LANS-MOD-AD-B	LC Duplex MM/OM3+OM4 Shuttered Fibre Module, ceramic sleeve (1x LANscape), black socket	OM3/OM4
570704	LANS-MOD-AV-B	LC DUPLEX MM/OM4 FIBRE MODULE, SHUTTERED VIOLET ADAPT CERAMIC SLEEVE	OM3/OM4
415641-EA	LANC-MOD-H7-B	LC Duplex MM/OM3 Fibre Module, metal sleeve (1x LANscape), black socket	OM3/OM4
415637-EA	LANC-MOD-E8-B	SC Duplex MM/OM3 Fibre Module, metal sleeve (2x LANscape), black socket	OM3/OM4
415634-EA	LANC-MOD-74-B	ST MM/OM2 Fibre Module, metal sleeve (1x LANscape), black socket	OM3/OM4
415643	LANC-MOD-BLNK-B	BLANK MOD FOR LANC LINE BLACK 100 PCS/PK	OM3/OM4

LANC/LANS Splice-Pack OM3/OM4 50/125

Anixter PN	Vendor PN	Description	Category
415648-EA	SP12-39T-S8	SC MM/OM3 Universal Splice Pack (heat-shrink/crimp) incl. 12 pigtails and cover	OM3/OM4
415652-EA	SP12-03T-S8	LC MM/OM3 Universal Splice Pack (heat-shrink/crimp) incl. 12 pigtails and cover	OM3/OM4
476664	SP12-03Q-S8	LC MM/OM4 Universal Splice Pack (heat-shrink/crimp) incl. 12 pigtails and cover	OM3/OM4
TBD	SP12-50T-S8	SPLICE PACK 12XST MM OM3, HS/CRIMP	OM3/OM4

259639	HSP-60S100-1	Heat-shrink Protectors, 60mm (pack of 100)	OM3/OM4
--------	--------------	--	---------

Patchcords Multimode 50/125 OM4

Anixter PN	Vendor PN	Description	Category
412646	055702T5Z20003M	LC Duplex to SC Duplex patch cord on 2-fiber Zipcord cable, with 2 mm legs, and a low-smoke, zero-halogen sheath. 3 m	OM3/OM4
412622	575702T5Z80003M	SC Duplex to SC Duplex patch cord on 2-fiber Zipcord cable, with 2.8 mm legs, and a low-smoke, zero-halogen sheath. 3 m	OM3/OM4
412633	050502T5Z20003M	LC Duplex to LC Duplex Patch Cord on 2-fiber Zipcord Tight Buffered Cable, 50 Micron ClearCure Multimode, OM3, 2 mm Legs, LSZH, 3 Meters	OM3/OM4
412668	055702Q5Z20003M	LC Duplex to SC Duplex patch cord on 2-fiber Zipcord cable, with 2 mm legs, and a low-smoke, zero-halogen sheath. 3 m	OM3/OM4
412657	575702Q5Z80003M	SC Duplex to SC Duplex patch cord on 2-fiber Zipcord cable, with 2.8 mm legs, and a low-smoke, zero-halogen sheath. 3 m	OM3/OM4
408407	050502Q5Z20003M	LC Duplex to LC Duplex Patch Cord on 2-fiber Zipcord Cable, 50 Micron ClearCure Multimode, OM4, 2 mm Legs, LSZH, 3 Meters	OM3/OM4
449758	E797902TNZ20003M	Pretium EDGE Solutions Low loss Patchcord, LC duplex uniboot connectors, Clear Curve® Multimode 50/125µm OM3 Pretium 300 fibres, standard reverse fibre polarity, LSZH/FRNC jacket, aqua, 3 m	OM3/OM4
412451	E797902QNZ20003M	2F JUMPER EDGE MM 50/125 OM4 LC/LC DUPX REVERSE POLAR 3M E797902QNZ20003M	OM3/OM4
511004	577902TNZ20003M	3m LC Duplex UniBoot - SC Duplex MM/OM3 CC Fibre Patch Cord	OM3/OM4
520399	577902QNZ20003M	Interconnect Cable, LC Uniboot to SC Duplex, 2 F, Riser, FRNC, 50 µm multimode (OM4), 3 Meters	OM3/OM4