

# XTL™ 300

## 1" PC-Connected Handheld Industrial Label Maker

- Life-like on screen print preview and color display shows exactly how labels will look when applied to cables, pipes, panels, and more
- Built-in label applications make getting started from the home screen easy
- Pre-loaded label templates create labels 3x faster\* and ensure perfect formatting to save time
- Pre-set layouts for almost 100 patch panel models eliminate size and spacing guesswork
- Prints 1/4" up to 1" durable labels including continuous length tape, laminated wire/cable wraps, heat-shrink tubes and pre-sized labels
- Maximized print area helps reduce label waste
- PC-connectivity\*\* and free DYMO ID software for easy transfer of labels to and from the XTL 300 for jobsite editing and printing
- Durable built-in cutter for fast label production
- Impact-resistant rubber bumpers and wipe-clean keypad withstand harsh environments
- Handheld design and contoured finger grips for easy handling
- On-screen label indicator automatically detects and displays the loaded label



\*When compared to creating labels on an XTL label maker without templates

\*\* Works with Windows® 7 and later

### XTL 300 Single Unit Includes:

- DYMO XTL 300 Label Maker
- All-Purpose Vinyl Label Cartridge, Black on White, 1" x 23'
- AC Charging Adapter
- USB Cable
- Rechargeable Lithium Polymer Battery
- Lanyard
- Quick Start Guide
- Software Download Guide



### XTL 300 Kit Includes (everything in single unit as well as):

- Carrying Case
- Laminated Wire/Cable Wrap Cartridge, Black on White, 13/16" x 1 9/16"



### Quick Specs

Unit Dimensions (H x W x L)	2.7" x 4.7" x 10.4"
Weight (excluding battery)	2 lbs 5 oz
PC Compatible	Yes, via USB
Accepts Label Sizes	1/4", 3/8", 1/2", 3/4", or 1"
Tape Platform	XTL
Resolution	300 dpi
Printing System	Thermal Transfer
Barcodes	Code 128 (Auto), Code 39, Code 39 Mod 43, EAN 8, EAN 13, UPC-A, Codabar, PDF-417, QR Code
Cutter Type	Manual, Replaceable
Power Supply	Lithium Polymer Rechargeable Battery or AC Adapter
Memory	40 MB
Compatibility	Windows® 7 and later
Adapter	Yes
Networking	No
Warranty	3-Year Limited
Country of Origin	China

Item Number	Description	List Price (ea)	ECCN Number	ISV Playbook Merch Options		Length (in)	Width (in)	Height (in)	Weight (lbs)	QTY	Ti	Hi	UPC
1868813	XTL 300	\$349.99	EAR99	Requires Custom Display	Unit	7.56	3.19	11.54	4.17	1	-	-	071701000439
					Shelf	7.56	3.19	11.54	4.17	1	-	-	-
					Case	11.61	9.06	13.78	14.18	3	-	-	50071701000434
					Pallet	47.24	39.37	47.24	746.62	48	16	3	-
1868814	XTL 300 Kit	\$419.99	EAR99	Requires Custom Display	Unit	16.06	3.50	14.37	6.23	1	-	-	071701000545
					Shelf	16.06	3.50	14.37	6.23	1	-	-	-
					Case	17.32	11.81	15.75	20.67	3	-	-	50071701000540
					Pallet	47.24	39.37	53.15	620.51	24	8	3	-

## XTL 300 | Compatible Labels

### All-Purpose Vinyl

- Moisture, chemical and UV resistance makes vinyl ideal for indoor/outdoor use
- Wide range of colors that fit with OSHA, ANSI and ISO color standards to enhance workplace communication and safety
- UL recognized as a component to UL 969
- RoHS compliant
- Temperature rating: -40°F to 140°F

### Flexible Cable Wrap

- For labeling wires, cables and rounded surfaces, flexible nylon material is designed to conform and stick
- Tear-proof material resists damage when pulled through tight spaces or conduits
- UL recognized as a component to UL 969
- RoHS compliant
- Temperature rating: -40°F to 140°F

### Laminated Wire/Cable Wraps

- Pre-sized wire/cable wraps with laminated overwrap protect printed areas from oil, chemicals, moisture, abrasion and fading
- Also available in sheet label formats for high-volume installations
- UL recognized as a component to UL 969
- Temperature Rating: -40°F to 140°F

### Permanent Flat Surface

- For labeling panels, blocks, faceplates, shelves, bins, beams and more
- For labeling flat surfaces, a glossy finish leaves a professional look
- UL recognized as a component to UL 969
- Temperature rating: -40°F to 140°F
- RoHS compliant

### Heat-Shrink Tube (Continuous)

- Heat-Shrink Tubes provide insulation when shrunk down and ensure a secure fit on wires and cables with a 3:1 shrink ratio
- Meets MIL-M-81531, MIL-STD-202G, SAE-DTL- 23053/5 (Class 1 & 3)
- UL recognized as a component to UL 224
- RoHS compliant
- Temperature rating: Max 257°F

### Pre-Sized Labels

- Ideal for flat surface labeling like barcodes, faceplates, shelves, bins, beams and more
- Pre-Sized labels help facilitate batch label printing to improve productivity
- UL recognized as a component to UL 969
- Temperature rating: -40°F to 140°F

### XTL 300 Compatible Labels

Width	Length	List Price (ea)	A	A	A	A	A	A	A	A	A	A	A	A	A
<b>All-Purpose Vinyl</b>															
1/2"	23'	\$24.99	1868741	1868746	1868751	1868756	1868761	1868766	1868771	1868776	1868781	1868786	1868791	1868796	1868801
3/4"	23'	\$29.49	1868742	1868747	1868752	1868757	1868762	1868767	1868772	1868777	1868782	1868787	1868792	1868797	1868802
1"	23'	\$45.49	1868743	1868748	1868753	1868758	1868763	1868768	1868773	1868778	1868783	1868788	1868793	1868798	1868803
<b>Permanent Flat Surface</b>															
1/4"	29.8'	\$30.99	1868738	-	1868735	-	-	-	-	-	-	-	-	-	-
3/8"	29.8'	\$32.49	1868739	-	1868736	-	-	-	-	-	-	-	-	-	-
1/2"	29.8'	\$33.49	1868740	-	1868737	-	-	-	-	-	-	-	-	-	-
<b>Flexible Cable Wrap</b>															
1/2"	18'	\$24.99	-	-	1868806	-	-	-	-	-	-	-	-	-	-
3/4"	18'	\$28.49	-	-	1868807	-	-	-	-	-	-	-	-	-	-
1"	18'	\$32.99	-	-	1868808	-	-	-	-	-	-	-	-	-	-
<b>Heat-Shrink Tube (continuous)</b>															
1/4"	8.9'	\$63.59	-	-	1868809	-	-	-	-	-	-	-	-	-	-
1/2"	8.9'	\$76.79	-	-	1868810	-	-	-	-	-	-	-	-	-	-
1"	8.9'	\$109.20	-	-	1868811	-	-	-	-	-	-	-	-	-	-

### XTL 300 Compatible Pre-Sized Labels

SKU	List Price (ea)	Label Width	Label Length	Labels/Cartridge	Color
<b>Pre-Sized Labels</b>					
1868665	\$32.44	1/2"	1/2"	250	A
1868666	\$34.09	1/2"	1"	250	A
1868667	\$28.04	1/2"	1-1/2"	185	A
1868669	\$32.44	3/8"	1"	250	A
1868670	\$32.99	1/2"	3/4"	250	A
1868701	\$44.54	3/4"	1"	250	A
<b>Laminated Wire/Cable Wrap</b>					
1868704	\$51.69	13/16"	13/16"	250	A
1868705	\$37.39	13/16"	1-9/16"	150	A
1868706	\$45.09	13/16"	4"	75	A