

XTL™ 500

2" PC-Connected Touch Screen Industrial Label Maker

- Life-like on screen print preview and color display shows exactly how labels will look when applied to cables, pipes, panels and more
- Built-in label applications make getting started from the home screen easy
- Touch screen helps make label creation easier and faster
- Pre-loaded label templates create labels 3x faster* and ensure perfect formatting to save time
- Prints ¼" to 2" durable labels including continuous length tape, laminated wire/cable wraps, heat-shrink tubes and pre-sized labels
- Maximized print area helps reduce label waste
- Pre-set layouts for almost 100 patch panel models eliminate size and spacing guesswork
- Easily transfer labels to and from DYMO ID software and the PC-connected** XTL™ 500 for jobsite editing and printing
- Built-in auto-cutter for high volume label output
- Impact-resistant rubber bumpers and wipe-clean keypad withstands harsh environments
- Customizable printer settings eliminate unnecessary menus and steps
- On-screen label indicator automatically detects and displays the loaded label

*When compared to creating labels on an XTL label maker without templates

**Works with Windows® 7 and later



XTL 500 Case Kit Includes:

- DYMO XTL 500 Label Maker
- All-Purpose Vinyl Label Cartridge, Black on White, 1 ½" x 23'
- Laminated Wire/Cable Wrap, Black on White, 1 ½" x 1 9/16"
- Carrying Case
- AC Charging Adapter
- USB Cable
- Rechargeable Lithium Polymer Battery
- Quick Start Guide
- Software Download Card



Quick Specs

Unit Dimensions (H x W x L)	4.8" x 6.3" x 10.6"
Weight (excluding battery)	4lbs 4 oz
PC Compatible	Yes, via USB
Accepts Label Sizes	¼", ⅜", ½", ¾", 1", 1 ½", or 2"
Tape Platform	XTL
Resolution	300 dpi
Printing System	Thermal Transfer
Print Speed (average)	1.10 in/sec
Barcodes	Code 128 (Auto), Code 39, Code 39 Mod 43, EAN 8, EAN 13, UPC-A, Codabar, PDF-417, QR Code
Cutter Type	Auto, Replaceable
Power Supply	Lithium Polymer Rechargeable Battery or AC Adapter
Memory	40 MB
Compatibility	Windows® 7 and later
Adapter	Yes
Warranty	3-Year Limited
Networking	No
Country of Origin	China

Item Number	Description	List Price (ea)	ECCN Number	ISV Playbook Merch Options		Length (in)	Width (in)	Height (in)	Weight (lbs)	QTY	Ti	Hi	UPC
1868815	XTL 500	\$699.99	EAR99	Requires Custom Display	Unit	16.06	5.67	14.33	9.14	1	-	-	071701000552
					Shelf	16.06	5.67	14.33	9.14	1	-	-	-
					Case	17.32	12.60	15.75	20.26	2	-	-	50071701002056
					Pallet	47.24	39.37	53.15	648.52	24	8	3	-

XTL 500 | Compatible Labels

All-Purpose Vinyl

- Moisture, chemical and UV resistance makes vinyl ideal for indoor/outdoor use
- Wide range of colors that fit with OSHA, ANSI and ISO color standards to enhance workplace communication and safety
- UL recognized as a component to UL 969
- RoHS compliant
- Temperature rating: -40°F to 140°F

Flexible Cable Wrap

- For labeling wires, cables and rounded surfaces, flexible nylon material is designed to conform and stick
- Tear-proof material resists damage when pulled through tight spaces or conduits
- UL recognized as a component to UL 969
- RoHS compliant
- Temperature rating: -40°F to 140°F

Pre-Sized Safety Labels

- Specific labels with colored headers including labels pre-printed with DANGER and NOTICE headers for on-demand printing of small format safety signage
- UL recognized as a component to UL 969
- RoHS compliant
- Temperature rating: -40°F to 140°F

Laminated Wire/Cable Wraps

- Pre-sized wire/cable wraps with laminated overwrap protect printed areas from oil, chemicals, moisture, abrasion and fading
- Also available in sheet label formats for high-volume installations
- UL recognized as a component to UL 969
- Temperature Rating: -40°F to 140°F

Permanent Flat Surface

- For labeling panels, blocks, faceplates, shelves, bins, beams and more
- For labeling flat surfaces, a glossy finish leaves a professional look
- UL recognized as a component to UL 969
- Temperature rating: -40°F to 140°F
- RoHS compliant

Heat-Shrink Tube (Continuous & Pre-Sized)

- Heat-Shrink Tubes provide insulation when shrunk down and ensure a secure fit on wires and cables with a 3:1 shrink ratio
- Meets MIL-M-81531, MIL-STD-202G, SAE-DTL- 23053/5 (Class 1 & 3)
- UL recognized as a component to UL 224
- RoHS compliant
- Temperature rating: Max 257°F

Pre-Sized Labels

- Ideal for flat surface labeling like barcodes, faceplates, shelves, bins, beams and more
- Pre-Sized labels help facilitate batch label printing to improve productivity
- UL recognized as a component to UL 969
- Temperature rating: -40°F to 140°F

XTL 500 Compatible Labels

Width	Length	List Price (ea)	A	A	A	A	A	A	A	A	A	A	A	A	A
All-Purpose Vinyl															
½"	23'	\$24.99	1868741	1868746	1868751	1868756	1868761	1868766	1868771	1868776	1868781	1868786	1868791	1868796	1868801
¾"	23'	\$29.49	1868742	1868747	1868752	1868757	1868762	1868767	1868772	1868777	1868782	1868787	1868792	1868797	1868802
1"	23'	\$45.49	1868743	1868748	1868753	1868758	1868763	1868768	1868773	1868778	1868783	1868788	1868793	1868798	1868803
1-½"	23'	\$53.99	1868744	1868749	1868754	1868759	1868764	1868769	1868774	1868779	1868784	1868789	1868794	1868799	1868804
2"	23'	\$66.00	1868745	1868750	1868755	1868760	1868765	1868770	1868775	1868780	1868785	1868790	1868795	1868800	1868805
Permanent Flat Surface															
¼"	29.8'	\$30.99	1868738	-	1868735	-	-	-	-	-	-	-	-	-	-
¾"	29.8'	\$32.49	1868739	-	1868736	-	-	-	-	-	-	-	-	-	-
½"	29.8'	\$33.49	1868740	-	1868737	-	-	-	-	-	-	-	-	-	-
Flexible Cable Wrap															
½"	18'	\$24.99	-	-	1868806	-	-	-	-	-	-	-	-	-	-
½"	18'	\$28.49	-	-	1868807	-	-	-	-	-	-	-	-	-	-
1"	18'	\$32.99	-	-	1868808	-	-	-	-	-	-	-	-	-	-
Heat-Shrink Tube (continuous)															
¼"	8.9'	\$63.59	-	-	1868809	-	-	-	-	-	-	-	-	-	-
½"	8.9'	\$76.79	-	-	1868810	-	-	-	-	-	-	-	-	-	-
1"	8.9'	\$109.20	-	-	1868811	-	-	-	-	-	-	-	-	-	-
2"	5'	\$99.60	-	-	1868812	-	-	-	-	-	-	-	-	-	-

XTL 500 Compatible Pre-Sized Labels

SKU	List Price (ea)	Label Width	Label Length	Labels/Cartridge	Color
Pre-Sized Labels					
1868665	\$32.44	½"	½"	250	A
1868666	\$34.09	½"	1"	250	A
1868667	\$28.04	½"	1-½"	185	A
1868668	\$51.69	1"	1"	250	A
1868669	\$32.44	¾"	1"	250	A
1868670	\$32.99	½"	¾"	250	A
1868701	\$44.54	¾"	1"	250	A
1868702	\$46.19	1"	2"	100	A
1868703	\$48.39	2"	3"	100	A
Laminated Wire/Cable Wrap					
1868704	\$51.69	13/16"	13/16"	250	A
1868705	\$37.39	13/16"	1-9/16"	150	A
1868706	\$45.09	13/16"	4"	75	A
1868707	\$53.89	1-½"	13/16"	250	A
1868708	\$46.19	1-½"	1-9/16"	150	A
1868709	\$59.39	1-½"	4"	75	A
1868710	\$61.59	2"	13/16"	250	A
1868711	\$66.54	2"	1-9/16"	100	A
1868712	\$72.59	2"	4"	70	A





DISTRIBUTED BY:
DYMO, ATLANTA, GA 30328
800-426-7827: WWW.DYMO.COM

INTERNAL USE ONLY. NOT FOR DISTRIBUTION.



A *NewellRubbermaid* Brand

XTL 500 Compatible Pre-Sized Labels

SKU	List Price (ea)	Label Width	Label Length	Labels/Cartridge	Color
Pre-Sized Heat-Shrink Tube					
1868717	\$71.39	¼"	1-5/16"	81	A
1868718	\$60.59	½"	1-5/16"	65	A
1868719	\$107.40	1"	1-5/16"	60	A
1868720	\$61.79	2-½"	1-5/16"	25	A
1868731	\$68.39	¼"	1-7/8"	81	A
1868732	\$73.19	½"	1-7/8"	65	A
1868733	\$115.20	1"	1-7/8"	60	A
1868734	\$83.39	2-½"	1-7/8"	25	A
Pre-Sized Safety Labels (with colored headers)					
1868713	\$47.84	2"	4"	70	 A
1868714	\$47.84	2"	4"	70	 A
1868715	\$47.84	2"	4"	70	 A
1868716	\$47.84	2"	4"	70	 A