

# XTL™ Labels

## Permanent Flat Surface

- For labeling panels, blocks, faceplates, shelves, bins, beams and more
- Glossy finish that leaves your work looking professional
- Constructed polyester material and coated with industrial-grade adhesive
- Available in smaller widths down to ¼" to fit in tight spaces
- Easy-to-peel split back design makes applying labels quick and easy
- Durable thermal transfer printing technology – label text won't smear or fade
- RoHS compliant



### Quick Specs

Label Widths	¼", ⅜", ½"
Tape Platform	XTL
Printer Compatibility	XTL 300, XTL 500
Label Length	29.8'
Printing System	Thermal Transfer
Temperature Rating	-40°F to 140°F
UL Recognized	Component to UL 969
Country of Origin	Belgium
Material	Polyester

Item Number	Width	Color	List Price (ea)	ECCN Number		Length (in)	Width (in)	Height (in)	Weight (lbs)	QTY	Ti	Hi	UPC
1868735	¼"	A	\$30.99	EAR99	Unit	2.83	1.38	4.72	0.11	1	-	-	071701001146
					Shelf	8.46	2.99	4.96	0.78	6	-	-	30071701001147
					Case	15.75	9.06	5.71	4.56	30	-	-	50071701001141
					Pallet	48.03	40.16	51.57	456.71	88	11	8	-
1868738	¼"	A	\$30.99	EAR99	Unit	2.83	1.38	4.72	0.11	1	-	-	071701001177
					Shelf	8.46	2.99	4.96	0.78	6	-	-	30071701001178
					Case	15.75	9.06	5.71	4.56	30	-	-	50071701001172
					Pallet	48.03	40.16	51.57	456.71	88	11	8	-
1868736	⅜"	A	\$32.49	EAR99	Unit	2.83	1.38	4.72	0.12	1	-	-	071701001153
					Shelf	8.46	2.99	4.96	0.84	6	-	-	30071701001154
					Case	15.75	9.06	5.71	4.86	30	-	-	50071701001158
					Pallet	48.03	40.16	51.57	482.90	88	11	8	-

**DISTRIBUTED BY:**  
 DYMO, ATLANTA, GA 30328  
 800-426-7827: WWW.DYMO.COM

INTERNAL USE ONLY. NOT FOR DISTRIBUTION.



A *NewellRubbermaid* Brand

# XTL™ Labels



Item Number	Width	Color	List Price (ea)	ECCN Number		Length (in)	Width (in)	Height (in)	Weight (lbs)	QTY	Ti	Hi	UPC
1868739	¾"	A	\$32.49	EAR99	<b>Unit</b>	2.83	1.38	4.72	0.12	1	-	-	071701001184
					<b>Shelf</b>	8.46	2.99	4.96	0.84	6	-	-	30071701001185
					<b>Case</b>	15.75	9.06	5.71	4.86	30	-	-	50071701001189
					<b>Pallet</b>	48.03	40.16	51.57	482.90	88	11	8	-
1858737	½"	A	\$33.49	EAR99	<b>Unit</b>	2.83	1.38	4.72	0.13	1	-	-	071701001160
					<b>Shelf</b>	8.46	2.99	4.96	0.90	6	-	-	30071701001161
					<b>Case</b>	15.75	9.06	5.71	5.16	30	-	-	50071701001165
					<b>Pallet</b>	48.03	40.16	51.57	509.09	88	11	8	-
1868740	½"	A	\$33.49	EAR99	<b>Unit</b>	2.83	1.38	4.72	0.13	1	-	-	071701001191
					<b>Shelf</b>	8.46	2.99	4.96	0.90	6	-	-	30071701001192
					<b>Case</b>	15.75	9.06	5.71	5.16	30	-	-	50071701001196
					<b>Pallet</b>	48.03	40.16	51.57	509.09	88	11	8	-

**DISTRIBUTED BY:**  
 DYMO, ATLANTA, GA 30328  
 800-426-7827: WWW.DYMO.COM

INTERNAL USE ONLY. NOT FOR DISTRIBUTION.



150836

This information is being provided for general information purposes and the compliance standards and certifications referenced herein are based on current standards which are subject to change.



A *NewellRubbermaid* Brand

©2015 SANFORD, L.P.

A Newell Rubbermaid Company™	 <small>RMZ Millers Business Park          Campus - 2, 5th Floor          No. 143, DCM, S. R. Road          Kundranchal, Chennai 600 098 India          T: 91 44 4213 7777   www.schawki.com</small>		 Use the PANTONE MATCHING SYSTEM for accurate color reproduction	
	<b>VERSION</b>	JOB DESCRIPTION : NRM_Writing_Dymo Industrial_150836_WDY_XTL_SS_Product Fact Book FILE NAME : 150836_WDY_SS_RD_Permanent Flat Surface_v4.indd	<b>BRAND : DYMO</b>	
	<b>4</b> DATE : 06-11-2015 OPERATOR : RB	SCHAWKI JOB # : 341661H NRM JOB # : 150836 COMPONENT # : N/A	CATEGORY OF WORK : FLYER NO. OF PAGES# : 2 PAGES SIZE : A4	
	NOTE :			