























































Invest in Solid Engineering

NEMA

| AMP | VOLT | STRAIGHT-BLADE PLUG | STRAIGHT-BLADE RECEPTACLE | AMP | VOLT | STRAIGHT-BLADE PLUG | STRAIGHT-BLADE RECEPTACLE |
|-----|---------|---|--|-----|------------------|--|--|
| 15 | 125 | 5-15P  | 5-15R  | 20 | 250 | 6-20P  | 6-20R  |
| 20 | 125 | 5-20P  | 5-20R  | | | | |
| AMP | VOLT | TWIST-LOCK PLUG | TWIST-LOCK RECEPTACLE | AMP | VOLT | TWIST-LOCK PLUG | TWIST-LOCK RECEPTACLE |
| 15 | 125 | L5-15P  | L5-15R  | 20 | 120/208 x 3~ WYE | L21-20P  | L21-20R  |
| 20 | 125 | L5-20P  | L5-20R  | 20 | 230/400 x 3~ WYE | L22-20P  | L22-20R  |
| 30 | 125 | L5-30P  | L5-30R  | 30 | 120/208 x 3~ WYE | L21-30P  | L21-30R  |
| 20 | 250 | L6-20P  | L6-20R  | 30 | 230/400 x 3~ WYE | L22-30P  | L22-30R  |
| 30 | 250 | L6-30P  | L6-30R  | 30 | 250 x 3~ DELTA | L15-30P  | L15-30R  |
| 20 | 125/250 | L14-20P  | L14-20R  | AMP | VOLT | CALIFORNIA STYLE | |
| 30 | 125/250 | L14-30P  | L14-30R  | 50 | 250 | 2P, 3W  | 2P, 3W  |
| | | | | 50 | 250 x 3~ DELTA | 3P, 4W  | 3P, 4W  |

NEMA

IEC

| AMP | VOLT | POWER INLET | POWER RECEPTACLE | AMP | VOLT | POWER INLET | POWER RECEPTACLE |
|--------|------------|--|---|--------|-------------------|--|--|
| 15/10* | 125 or 250 | C-14  | C-13  | 20/16* | 125 or 250 | C-20  | C-19  |
| AMP | VOLT | PIN & SLEEVE | | AMP | VOLT | PIN & SLEEVE | |
| 20/16* | 250/230* | 2P, 3W  | 2P, 3W  | 60/63* | 250/230* | 2P, 3W  | 2P, 3W  |
| 20 | 250 | 3P, 4W  | 3P, 4W  | 60 | 250 | 3P, 4W  | 3P, 4W  |
| 30/32* | 250/320* | 2P, 3W  | 2P, 3W  | 20/16* | 230/400* x 3~ WYE | 4P, 5W  | 4P, 5W  |
| 30 | 250 | 3P, 4W  | 3P, 4W  | 30/32* | 230/400* x 3~ WYE | 4P, 5W  | 4P, 5W  |

IEC

*Rating for CE products