

# Jabra Engage 75 Engineered to be the world's most powerful professional wireless headsets\*

- Industry-leading wireless performance. Better customer connections.
- Crystal-clear calls. Enhance the customer experience.
- More talk time, less interruptions. Increase productivity.



## Specifications



Product name	Engage 75 Stereo	Engage 75 Mono	Engage 75 Convertible
<b>Audio</b>			
Speaker size	2pcs Ø 28 x 3.9mm	Ø 28 x 3.9mm	13 x 3.65mm
Speaker Max output power	<118 dB SPL(A)	<118 dB SPL(A)	<118 dB SPL(A)
Speaker frequency range	40Hz-16kHz	40Hz-16kHz	40Hz-16kHz
Speaker bandwidth music mode	40Hz-16kHz	40Hz-16kHz	40Hz-16kHz
Speaker bandwidth speak mode	150 - 6,800Hz	150 - 6,800Hz	150 - 6,800Hz
Microphone type	Dual Microphone - ECM Uni-Directional and Analog MEMS system	Dual Microphone - ECM Uni-Directional and Analog MEMS system	ECM Uni-Directional Microphone
Microphone frequency range	100Hz-10KHz	100Hz-10KHz	100Hz-10KHz
Certifications	CE, CB, FCC, IC, NOM, NTC, EAC, PSB, ICASA, TELEC, SIRIM, ACMA, NZ Telepermit, UL, Bluetooth®		
<b>Ease of use</b>			
Intuitive audio control	Answer/end call - reject call - volume control		
Voice/Mute	Yes		
Busylight	Integrated red light on the microphone tip and the headset, activated when on a call or manually by the user when busy, to act as a "do not disturb" signal (Convertible model has busylight on earcup only).		
<b>Fit &amp; comfort</b>			
Headset form factor	Headband	Headband (neckband accessory)	Earhook (headband & neckband accessory)
Earhook	N/A	N/A	2 sizes
EarGel™	N/A	N/A	2 EarGels™
Neckband	N/A	Included	Included
<b>Battery</b>			
Talk time (up to / hours) <sup>1</sup>	13	13	9
Standby time	52 (improves with use of power nap feature)	52 (improves with use of power nap feature)	32 (improves with use of power nap feature)
Charging time	90 min	90 min	75 min
AC power supply	Yes	Yes	Yes
Power consumption	7.5V/650mA	7.5V/650mA	7.5V/650mA
Battery status % after 30 min/60 min	40% after 30 min and 80% after 60 min	40% after 30 min and 80% after 60 min	40% after 30 min and 80% after 60 min
<b>Connectivity</b>			
Connectivity	Desk phone, USB desk phone, softphone, 2x mobile (Bluetooth®)	Desk phone, USB desk phone, softphone, 2x mobile (Bluetooth®)	Desk phone, USB desk phone, softphone, 2x mobile (Bluetooth®)
Connection (mini jack, USB, etc)	2pcs Micro USB, RJ-9 for handset, RJ-9 for desk phone audio, RJ-45 for AUX		
DECT device	Yes	Yes	Yes
NFC	Yes	Yes	Yes
Bluetooth® device	Yes, in base	Yes, in base	Yes, in base
Bluetooth® version	5.0	5.0	5.0
Supported Bluetooth® modes	SCO, eSCO, Sniff mode		
Supported Bluetooth® profiles	Headset, Hands-free and PBAB		
Pairing PIN	Bluetooth®: 0000		
Paired devices (up to)	2 Bluetooth® devices		
Operating range (up to)	150m/490ft		
Headset bandwidth	Narrowband and wideband. Optimized for music (when not in call)		

Jabra.com/Engage

## Specifications



Product name		Engage 75 Stereo	Engage 75 Mono	Engage 75 Convertible
<b>General</b>	Box content	Headset incl. padding, base, power supply, USB cable, desk phone cable, documentation, Quick start guide	Headset incl. padding, base, power supply, USB cable, desk phone cable, documentation, Quick start guide, neckband	Headset, earhook, base, power supply, USB cable, desk phone cable, documentation, Quick start guide, accessories: headband, earhook & eargel, neckband
	Packaging dimensions (L x W x H)	Unit box: 147 x 190 x 93mm	Unit box: 147 x 190 x 93mm	Unit box: 145 x 190 x 93mm
	Master carton dimensions (L x W x H)	395 x 300 x 206mm	395 x 300 x 206mm	395 x 300 x 206mm
	Main unit dimensions (W x D x H)	Base: 93 x 90 x 106mm Headset: 141 x 32 x 169mm	Base: 93 x 90 x 106mm Headset: 147 x 32 x 169mm	Base: 93 x 90 x 110mm Headset: 105 x 32 x 50mm
	Weight (incl. main wearing style)	Base: 218g Headset: 90g	Base: 218g Headset: 64g	Base: 218g Headset: 18g
	Battery included	Yes/exchangeable	Yes/exchangeable	Yes
	Security	DECT Security Step C & using FIPS approved algorithms for key generation, payload encryption and authentication		
	Warranty	North America: 1 year limited warranty Europe/APAC: 2 year limited warranty	North America: 1 year limited warranty Europe/APAC: 2 year limited warranty	North America: 1 year limited warranty Europe/APAC: 2 year limited warranty
	Operating temperature	-10°C to +55°C (non condensing)	-10°C to +55°C (non condensing)	-10°C to +55°C (non condensing)
	Storage temperature	-5°C to +45°C (non condensing)	-5°C to +45°C (non condensing)	-5°C to +45°C (non condensing)
	Charging plug dimensions	Ø 2.35mm	Ø 2.35mm	Ø 2.35mm

Region	SKU	Description	EAN	UPC
<b>EMEA</b>	9556-583-111	Jabra Engage 75 Mono	5706991019797	706487017363
	9555-583-111	Jabra Engage 75 Convertible	5706991019766	706487017332
	9559-583-111	Jabra Engage 75 Stereo	5706991019858	706487017424
<b>NA</b>	9556-583-125	Jabra Engage 75 Mono	5706991019810	706487017387
	9555-583-125	Jabra Engage 75 Convertible	5706991019780	706487017356
	9559-583-125	Jabra Engage 75 Stereo	5706991019872	706487017448
<b>UK/HK/ SG/AU/NZ</b>	9556-583-117	Jabra Engage 75 Mono	5706991019803	706487017370
	9555-583-117	Jabra Engage 75 Convertible	5706991019773	706487017349
	9559-583-117	Jabra Engage 75 Stereo	5706991019865	706487017431

Jabra.com/Engage