


















# Screen Surface Technology

		ALR	Digital Signage	Interactive/ Writable	Acoustically Transparent	Recommended for Edge Blending	Large Venue	Front Projection	Flexible Rear Projection	Recommended for Laser Projection	Suitable for Laser Projection	Lens - Ultra Short Throw (UST) (0.4:1 or less)	Lens - Short Throw (0.4-1.0:1)	Lens - Standard Throw (1.0:1 or greater)
HIGH RESOLUTION UP TO 16K	HD PROGRESSIVE 0.6					•	•	•		•		•	•	•
	HD PROGRESSIVE 0.9					•	•	•		•		•	•	•
	HD PROGRESSIVE 1.1					•	•	•		•		•	•	•
	HD PROGRESSIVE 1.1 CONTRAST					•	•	•		•		•	•	•
	HD PROGRESSIVE 1.3					•	•	•		•	•	•	•	•
	HD RENTAL					•	•	•		•		•	•	•
	DUAL VISION					•	•		•	•		•	•	•
	ULTRA WIDE ANGLE					•	•		•	•		•	•	•
HIGH RESOLUTION UP TO 4K	HD PROGRESSIVE 1.1 CONTRAST PERF				•			•		•		•	•	•
	HD PROGRESSIVE 1.1 PERF				•	•	•	•		•		•	•	•
	PARALLAX® PURE 0.8	•	•			•		•		•				•*
	PARALLAX PURE 2.3	•	•			•	•	•		•	•			•**
	PARALLAX PURE UST 0.45	•	•			•		•		•		•		
	PARALLAX STRATOS 1.0	•	•			•	•	•		•	•			•
	IDEA™ SCREEN			•				•		•		•		
STANDARD RESOLUTION	DA-MAT®					•	•	•		•		•	•	•
	DA-TEX®					•		•	•					•
	HIGH CONTRAST MATTE WHITE					•	•	•		•		•	•	•
	MATTE WHITE					•	•	•		•		•	•	•

\*1.5:1 or greater minimum throw distance  
 \*\*1.8:1 or greater minimum throw distance

FOR YOUR IMAGE™



	Electric Recessed	Electric Wall Mounted	Fixed Frame	Borderless	Manual	Portable	
High Definition	<b>Tensioned Advantage</b>  HD Progressive surfaces	<b>Tensioned Contour</b>  HD Progressive surfaces	<b>UTB Contour</b>  HD Progressive surfaces	<b>Cinema Contour</b>  HD Progressive surfaces	<b>FullVision</b>  HD Progressive surfaces	<b>Fast-Fold Deluxe</b>  HD Rental surface	
Ambient Light Rejection	<b>Tensioned Advantage</b>  Parallax surfaces	<b>Tensioned Contour</b>  Parallax surfaces	<b>Parallax</b>  Parallax surfaces	<b>Parallax Thin</b>  Parallax surfaces			
Standard Definition	<b>DescenderPro</b>  Matte White surface	<b>Contour</b>  Matte White surface	<b>Cinema Contour</b>  Da-Mat surface		<b>Model C with CSR</b>  Matte White surface	<b>Fast-Fold Deluxe</b>  Da-Mat surface	<b>Deluxe Insta-Theater</b>  Matte White surface
Interactive			<b>IDEA</b>  IDEA surface				

Popular screens and surfaces are listed above for reference. More options are available at [Legrandav.com](http://Legrandav.com).

5 Years Warranty  Custom Size Service  Indoor Air Quality Certified



FOR YOUR IMAGE | [legrandav.com](http://legrandav.com)

**USA** P +1 866 977 3901 E [av.support@legrand.com](mailto:av.support@legrand.com)  
**EMEA** P +31 495 580 840 E [av.emea.sales@legrand.com](mailto:av.emea.sales@legrand.com)  
**APAC** P +852 2145 4099 E [av.asia.sales@legrand.com](mailto:av.asia.sales@legrand.com)

