



Nothing but **HEAVY DUTY**.®

**FASTER.
MORE VERSATILE.
EASIER TO USE.**



2260-21

NEW!

**M12 160X120
THERMAL IMAGER**





Nothing but **HEAVY DUTY**®

M12™ 160X120 THERMAL IMAGER

- 1 Capture Thermal and Visual images on each trigger pull for enhanced reporting
- 2 Crisp, high resolution 160x120 pixel Thermal images for better definition and clarity
- 3 Broader temperature range (-10° to 350°C) to cover more applications
- 4 Built-In Visual camera and flashlight for improved analysis
- 5 Rugged over-mold protects the large LCD and camera lenses if dropped
- 6 M12™ REDLITHIUM™ batteries charge in 30 minutes, allowing for rapid field replacement. Compatible with 35+ tools
- 7 Simple screen layout allows you to focus on getting the best images
- 8 All Thermal and Visual images use standard JPEG format for use in any program
- 9 Media door seals the included 2GB SD card and USB connections
- 10 Included software allows you to quickly analyze images and build reports in user-friendly PDF file format



RESNET Compliant

SPECIFICATIONS

			
Brand	MILWAUKEE®	FLIR	FLUKE
Model #	2260-21	e30	Ti10
Resolution	160 x 120 Pixels	160 x 120 Pixels	160 x 120 Pixels
Temp Range	-10 – 350°C	-20 – 350°C	-20 – 250°C
Visual Camera	YES	Yes	Yes
Thermal / Visual Display	Thermal or Visual, Toggle Hot key	Thermal and Visual	Thermal, Picture-in-Picture
LED Flashlight	YES	Yes	No
Charger Type	External Battery	In-Camera Recharge	In-Camera Recharge
Removable Battery	YES	Yes	No
Battery Charge Time	30 minutes	4 Hours	2-1/2 Hours
Battery Life	> 4 Hours	4 Hours	3 – 4 hours
Storage Size / Type	2GB SD Card	2GB Micro SD Card	2GB SD Card
Tool Warranty	5 Year	2 Year	2 Years

For More Information or to Request a Demo Go To:
www.milwaukeetool.com/thermal-imaging