

NEC General IT Displays



NEC Model No.	MAP in US	LCD Size	Bezel	Native Resolution	Contrast Ratio (typical)	Response Time	Brightness (typical)	Low Blue Light	Flicker Free	Viewing Angle (CR>10)	Signal Input	Signal Output	Typical Power Consumption	Height Adjustability	USB Hub	>2000m Altitude/Tropical	Speakers	Warranty
SMB - AccuSync Series																		
AS173M-BK	\$159	17"	Standard	1280 x 1024	1000:1	5ms	250 cd/m2	Yes	Yes	170°/170°	DP, HDMI, VGA	-	12W	No	No	Yes/Yes	Integrated	3 years
AS194MI-BK	\$185	19"	Standard	1280 x 1024	1000:1	6ms	250 cd/m2	Yes	Yes	178°/178°	DP, HDMI, VGA	-	12W	No	No	Yes/Yes	Integrated	3 years
AS221F-BK	\$195	21"	Narrow	1920 x 1080	1000:1	6ms	250 cd/m2	Yes	Yes	178°/178°	DP, HDMI, VGA	-	13W	No	No	Yes/Yes	Integrated	3 years
AS241F-BK	\$195	24"	Narrow	1920 x 1080	1000:1	6ms	250 cd/m2	Yes	Yes	178°/178°	DP, HDMI, VGA	-	13W	No	No	Yes/Yes	Integrated	3 years
AS271F-BK	\$239	27"	Narrow	1920 x 1080	1000:1	6ms	250 cd/m2	Yes	Yes	178°/178°	DP, HDMI, VGA	-	14W	No	No	Yes/Yes	Integrated	3 years
ENTERPRISE - MultiSync E Series																		
E172M-BK	\$179	17"	Standard	1280x1024	1000:1	5ms	250 cd/m2	Yes	Yes	160°/170°	DVI-D, VGA	-	12W	Yes	No	No/Yes	Integrated	3 years
E221N-BK	\$215	22" wide	Narrow	1920 x 1080	1000:1	6ms	250 cd/m2	Yes	Yes	178°/178°	DP, HDMI, VGA	-	15W	Yes	No	No/Yes	Integrated	3 years
E233WMI-BK	\$259	23" wide	Standard	1920 x 1080	1000:1	5ms	250 cd/m2	Yes	Yes	178°/178°	DP, DVI-D, VGA	-	19W	Yes	No	No/Yes	Integrated	3 years
E242N-BK	\$229	24" wide	Narrow	1920 x 1080	1000:1	6ms	250 cd/m2	Yes	Yes	178°/178°	DP, HDMI, VGA	-	16W	Yes	Yes	No/Yes	Integrated	3 years
E243F-BK	\$299	24" wide	Narrow	1920 x 1080	5000:1	6ms	250 cd/m2	Yes	Yes	178°/178°	DP, HDMI, USB Type-C	-	15W	Yes	Yes	Yes/Yes	Integrated	3 years
E273F-BK	\$339	27" wide	Narrow	1920 x 1080	5000:1	6ms	250 cd/m2	Yes	Yes	178°/178°	DP, HDMI, USB Type-C	-	18W	Yes	Yes	Yes/Yes	Integrated	3 years
E271N-BK	\$305	27" wide	Narrow	1920 x 1080	1000:1	6ms	250 cd/m2	Yes	Yes	178°/178°	DP, HDMI, VGA	-	16W	Yes	No	No/Yes	Integrated	3 years
ENTERPRISE - MultiSync EA Series																		
EA193MI-BK	\$239	19"	Standard	1280 x 1024	1000:1	6ms	250 cd/m2	-	-	178°/178°	DP, DVI-D, VGA	-	18W	Yes	No	Yes/Yes	Integrated	3 years
EA224WMI-BK	\$239	22" wide	Standard	1920 x 1080	1000:1	6ms	250 cd/m2	-	-	178°/178°	HDMI, DP, DVI-D, VGA	-	26W	Yes	Yes	No/Yes	Integrated	3 years
EA234WMI-BK	\$299	23" wide	Standard	1920 x 1080	1000:1	6ms	250 cd/m2	-	-	178°/178°	HDMI, DP, DVI-D, VGA	-	27W	Yes	Yes	No/Yes	Integrated	3 years
EA245WMI-BK	\$425	24" wide	Narrow	1920 x 1200	1000:1	6ms	300 cd/m2	Yes	Yes	178°/178°	HDMI, DP, DVI-D, VGA	DP	22W	Yes	Yes	Yes/Yes	Integrated	3 years
EA231WU-BK	\$275	23" wide	Narrow	1920 x 1200	1000:1	5ms	250 cd/m2	Yes	Yes	178°/178°	HDMI, DP, DVI-D, VGA	-	15W	Yes	Yes	Yes/Yes	Integrated	3 years
EA231WU-H-BK	\$279	23" wide	Narrow	1920 x 1200	1000:1	5ms	250 cd/m2	Yes	Yes	178°/178°	HDMI, DP, DVI-D, VGA	-	15W	No	Yes	Yes/Yes	Integrated	3 years
EA241F-BK	\$259	24" wide	Narrow	1920 x 1080	1000:1	5ms	250 cd/m2	Yes	Yes	178°/178°	HDMI, DP, VGA, DVI-D	-	15W	Yes	Yes	Yes/Yes	Integrated	3 years
EA241F-H-BK	\$249	24" wide	Narrow	1920 x 1080	1000:1	5ms	250 cd/m2	Yes	Yes	178°/178°	HDMI, DP, VGA, DVI-D	-	15W	No	Yes	Yes/Yes	Integrated	3 years
EA242F-BK	\$339	24" wide	Narrow	1920 x 1080	1000:1	6ms	250 cd/m2	Yes	Yes	178°/178°	HDMI, DP, VGA, USB Type-C	DP	19W	Yes	Yes	Yes/Yes	Integrated	3 years
EA271F-BK	\$369	27" wide	Standard	1920 x 1080	1000:1	6ms	250 cd/m2	Yes	Yes	178°/178°	DP, HDMI, DVI-D, VGA	-	17W	Yes	Yes	Yes/Yes	Integrated	3 years
EA272F-BK	\$435	27" wide	Standard	1920 x 1080	1000:1	6ms	250 cd/m2	Yes	Yes	178°/178°	DP, HDMI, VGA, USB Type-C	DP	19W	Yes	Yes	Yes/Yes	Integrated	3 years
EA271Q-BK	\$565	27" wide	Narrow	2560 x 1440	1000:1	6ms	350 cd/m2	Yes	Yes	178°/178°	HDMI, DP, DVI-D, USB Type-C	DP	37W	Yes	Yes	Yes/Yes	Integrated	3 years
EA271U-BK	\$599	27" wide	Narrow	3840 x 2160	1000:1	5ms	350 cd/m2	Yes	Yes	178°/178°	HDMI, DP, DVI-D, USB Type-C	-	38W	Yes	Yes	Yes/Yes	Integrated	3 years
ENTERPRISE - MultiSync EX Series																		
EX241UN-BK	\$409	24" wide	Narrow	1920 x 1080	1000:1	6ms	250 cd/m2	Yes	Yes	178°/178°	HDMI, DP, DVI-D, VGA	DP	19W	Yes	Yes	Yes/Yes	Integrated	3 years
EX241UN-H-BK	\$409	24" wide	Narrow	1920 x 1080	1000:1	6ms	250 cd/m2	Yes	Yes	178°/178°	HDMI, DP, DVI-D, VGA	DP	19W	No	Yes	Yes/Yes	Integrated	3 years
EX241UN-PT-H	\$955	24" wide	Narrow	1920 x 1080	1000:1	6ms	250 cd/m2	Yes	Yes	178°/178°	HDMI, DP, DVI-D, VGA	DP	19W	No	Yes	Yes/Yes	Integrated	3 years
EX341R-BK	\$849	34" ultra wide	Narrow	3440 x 1440	3000:1	5ms	290 cd/m2	Yes	Yes	178°/178°	DP, HDMI (2)	DP	62W	Yes	Yes	Yes/Yes	Integrated	3 years
ENTERPRISE - SpectraView Series																		
EA231WU-BK-SV	\$429	23" wide	Narrow	1920 x 1200	1000:1	5ms	250 cd/m2	Yes	Yes	178°/178°	HDMI, DP, DVI-D, VGA	-	15W	Yes	Yes	Yes/Yes	Integrated	3 years
EA241F-BK-SV	\$409	24" wide	Narrow	1920 x 1080	1000:1	5ms	250 cd/m2	Yes	Yes	178°/178°	HDMI, DP, VGA, DVI-D, VGA	-	15W	Yes	Yes	Yes/Yes	Integrated	3 years
EA242F-BK-SV	\$489	24" wide	Narrow	1920 x 1080	1000:1	6ms	250 cd/m2	Yes	Yes	178°/178°	HDMI, DP, VGA, USB Type-C	DP	19W	Yes	Yes	Yes/Yes	Integrated	3 years
EA245WMI-BK-SV	\$575	24" wide	Standard	1920 x 1200	1000:1	6ms	300 cd/m2	Yes	Yes	178°/178°	HDMI, DP, DVI-D, VGA	DP	22W	Yes	Yes	Yes/Yes	Integrated	3 years
EA271F-BK-SV	\$519	27" wide	Standard	1920 x 1080	1000:1	6ms	250 cd/m2	Yes	Yes	178°/178°	DP, HDMI, DVI-D, VGA	-	17W	Yes	Yes	Yes/Yes	Integrated	3 years
EA272F-BK-SV	\$585	27" wide	Standard	1920 x 1080	1000:1	6ms	250 cd/m2	Yes	Yes	178°/178°	DP, HDMI, VGA, USB Type-C	DP	19W	Yes	Yes	Yes/Yes	Integrated	3 years
EA271Q-BK-SV	\$715	27" wide	Narrow	2560 x 1440	1000:1	6ms	350 cd/m2	Yes	Yes	178°/178°	HDMI, DP, DVI-D, USB Type-C	DP	37W	Yes	Yes	Yes/Yes	Integrated	3 years
EA271U-BK-SV	\$749	27" wide	Narrow	3840 x 2160	1000:1	5ms	350 cd/m2	Yes	Yes	178°/178°	HDMI, DP, DVI-D, USB Type-C	-	38W	Yes	Yes	Yes/Yes	Integrated	3 years
EX241UN-BK-SV	\$559	24" wide	Standard	1920 x 1080	1000:1	6ms	250 cd/m2	Yes	-	178°/178°	HDMI, DP, DVI-D, VGA	DP	19W	Yes	Yes	Yes/Yes	Integrated	3 years
EX341R-BK-SV	\$999	34" ultra wide	Standard	3440 x 1440	3000:1	5ms	290 cd/m2	Yes	Yes	178°/178°	DP, HDMI (2)	DP	62W	Yes	Yes	Yes/Yes	Integrated	3 years

NEC Professional Displays



NEC Model No.	MAP in US	LCD Size	Bezel	Native Resolution	Contrast Ratio (typical)	Response Time	Brightness (typical)	Low Blue Light	Flicker Free	Viewing Angle	Signal Input	USB Hub	>2000m Altitude/Tropical*	Speakers	Warranty
PROFESSIONAL/COLOR CRITICAL - MultiSync P/PA Series															
P243W-BK	\$725	24" wide	Standard	1920 x 1200	1000:1	8ms	350 cd/m2	Yes	Yes	178°/178°	HDMI, DP, DVI, VGA	USB 3.1, 3 up / 3 down	Yes/Yes	Integrated 2x1W	4 years
PA243W /-BK	NA / \$829	24" wide	Standard	1920 x 1200	1000:1	8ms	350 cd/m2	Yes	-	178°/178°	HDMI, DP, DVI, VGA	USB 3.0, 2 up / 3 down	Yes/Yes	Integrated 2x1W	4 years
PA271Q-BK	\$1,339	27" wide	Standard	2560 x 1440	1500:1	8ms	350 cd/m2	Yes	Yes	178°/178°	DP, mDP, HDMI (2), USB-C	USB 3.1, 3 up / 3 down	Yes/Yes	Integrated 2x1W	4 years
PA311D-BK	\$3,179	31" wide	Standard	4096 x 2160	1400:1	8ms	350 cd/m2	Yes	-	178°/178°	DP (2), HDMI	USB 3.1, 3 up / 3 down	Yes/Yes	Integrated 2x1W	4 years
PROFESSIONAL/COLOR CRITICAL - SpectraView_{II} Series															
P243W-BK-SV	\$975	24" wide	Standard	1920 x 1200	1000:1	8ms	360 cd/m2	Yes	Yes	178°/178°	HDMI, DP, DVI, VGA	USB 3.1, 3 up / 3 down	Yes/Yes	Integrated 2x1W	4 years
PA243W-BK-SV	NA / \$1,079	24" wide	Standard	1920 x 1200	1000:1	8ms	340 cd/m2	Yes	-	178°/178°	HDMI, DP, DVI, VGA	USB 3.0, 2 up / 3 down	Yes/Yes	Integrated 2x1W	4 years
PA271Q-BK-SV	\$1,589	27" wide	Standard	2560 x 1440	1500:1	8ms	350 cd/m2	Yes	Yes	178°/178°	DP, mDP, HDMI (2), USB-C	USB 3.1, 3 up / 3 down	Yes/Yes	Integrated 2x1W	4 years
PA311D-BK-SV	\$3,429	31" wide	Standard	4096 x 2160	1400:1	8ms	350 cd/m2	Yes	-	178°/178°	DP (2), HDMI	USB 3.1, 3 up / 3 down	Yes/Yes	Integrated 2x1W	4 years



ACCESSORIES	NEC Model No.	SVII-SOFT	MDSVSENSOR3	SVII-PRO-KIT	CC-SPYDER5	CC-I1PRO2	PA-MDP-CABL	CA-USBCDCS1
	Description		SpectraViewII software	NEC customized display calibration sensor for MD and SpectraViewII displays	Display calibration bundle with custom sensor and software for MultiSync 90, P and PA Series displays	Patented 7-color full spectrum sensor	X-Rite i1 Pro2 Spectrophotometer	Mini DisplayPort to DisplayPort cable

All displays feature LED backlights unless otherwise specified. *40° C and 93% humidity for 120 hours