

PROFICIENT®

Signature SERIES



Effortless Performance with Signature Subwoofers

Introducing the New Proficient® Signature In-wall Subwoofer, delivering the performance you expect from a Proficient speaker and the legendary heart and soul of a Sunfire® Subwoofer. This is our ultimate expression of science and technology. The Signature In-wall Subwoofer is designed to operate as a system with its dedicated rack mounted amplifier, the pair work harmoniously to reproduce heart-thumping bass for a transformative audio experience.

A 520 Watt vibration-free performance statement designed exclusively for In-Wall applications. Wrapped in a cabinet so thin and sophisticated that you can tap into all that power with virtually no mechanical vibration whatsoever. And bass performance that can play your movies, music and games with the kind of accurate reproduction that shows no favoritism.

This In-Wall Subwoofer has been created so that the subwoofer, the amplifier and even the remote control are purpose-built to work together harmoniously. Each component complements the other to provide the best performance characteristics possible.



With Custom Digital Audio Adjustment, you can create your perfect sound profile, with simple-to-use functions designed specifically to tailor the bass to the current mood.

Packed with proprietary features like StillBass that eliminates mechanical noises and Frequency Filtration Design (FFD) found in the dedicated matching amplifier. You will really be able to appreciate the sound quality as the Proficient In-Wall Subwoofer takes lows to an all-new high.

AMPLIFIER + IN-WALL SUBWOOFER

PROFICIENTSM SignatureSM SERIES

FEATURES

Two Active 8" High Back EMF Drivers - Delivering the most accurate bass made possible by this revolutionary driver design.

Custom Digital Audio Adjustment - The In-Wall Subwoofer System features professional-grade adjustments that are perfect for custom installers or audiophiles like yourself. Create your own sound profile.

Pre-Programmed Remote Control - Dial in the perfect sound from the comfort of your chair. With the single push of a button, you can switch sound modes from movie watching to music listening—automatically.

The HRSIW8AMP Subwoofer Amplifier is sold separately

Frequency Filtration Design - Proprietary FFD Technology is what makes the dedicated amplifier the perfect match for the prodigious bass capabilities of this subwoofer.

Vibration-Free StillBass Technology - Eliminate mechanical noises so you can turn the sound up and enjoy the incredible bass experience you've always craved. Clean, crisp and accurate bass that will give your music, movies and games a level of detail you won't get in any other product of its kind.



SPECIFICATIONS	HRSIW8AMP
Power (RMS)	520 Watts
Output Levels	> 106 dB Peak SPL
Signal Input	RCA Line Level, Balanced XLR
12 VDC Trigger Input	Input Voltage Range 2.2 -13 VDC
Crossover Filters	12 - 36 dB/Octave Adjustable Slope
Crossover Frequency	40 Hz - 160 Hz Adjustable, with LFE Bypass
Dimensions	1.75" (1U) x 19" x 11.2" (44.45 x 482.6 x 279.4 mm)
Weight	13.5 lb. / 6.12 kg
Warranty	1 Year

SPECIFICATIONS	PAS-HRSIW8-CAB
Woofers Size/Type	Dual 8" Woofers with Fiberglass Cones
Power	150-600 Watts
Frequency Response (-3dB)	33 Hz - 150 Hz
Cabinet Type	Sealed Cabinet, High Pressure Design
Grille Type	Paintable Magnet Grille with Thin Bezel
Complete Dimensions with Grille	24.61 x 12.05 x 3.74 (625 x 306 x 95 mm)
Cutout Dimensions	23.35" x 10.79" (593 x 274 mm)
Weight	32 lbs. / 14.51 kg
Warranty	5 Years

PROFICIENTSM

www.proficientaudio.com