



MIGHTY MO 10 TO MIGHTY MO 20 CROSS REFERENCE

MIGHTY MO 10 PART NO.	MIGHTY MO 20 EQUIVALENT PART NO.	MIGHTY MO 20 EQUIVALENT DESCRIPTION	MIGHTY MO 20 EQUIVALENT FEATURES AND BENEFITS	NOTES
OR-MM107SVR	OR-MM20730ADJ38-B	4-post adjustable rack 30"D, 7'	2000 lbs load rating, improved accessories (cable rings, larger capacity vertical managers, larger spools)	
OR-MM10716	OR-MM20716-B	Channel rack, 16.25" channel, 7'	2000 lbs load rating, improved accessories (cable rings, larger capacity vertical managers, larger spools, 180° cable trough, hex guard, increased airflow, zero U cable manager)	
OR-MM108SVR	OR-MM20830ADJ38-B	4-post adjustable rack 30"D, 8'	2000 lbs load rating, improved accessories (cable rings, larger capacity vertical managers, larger spools)	
OR-MM10816	OR-MM20816-B	Channel rack, 16.25" channel, 8'	2000 lbs load rating, improved accessories (cable rings, larger capacity vertical managers, larger spools, 180° cable trough, Hexguard, increased airflow, zero U cable manager)	
OR-MM10VMD712	OR-MM20VMD712-B*	Vertical cable management cage, 7'	Slam latch dual hinged door, single operation door, larger capacity, 180° bend limiting clips, aesthetic design	*Substitute for MM20 use only, MM10VMD712 still used for MM6
OR-MM10VMD716	OR-MM20VMD716-B	Vertical cable management cage, 7'	Slam latch dual hinged door, single operation door, larger capacity, 180° bend limiting clips, aesthetic design	No availability of 16" extrusions so use only MM20
OR-MM10VMD812	OR-MM20VMD812-B*	Vertical cable management cage, 8'	Slam latch dual hinged door, single operation door, larger capacity, 180° bend limiting clips, aesthetic design	*Substitute for MM20 use only, MM10VMD812 still used for MM6
OR-MM10VMD816	OR-MM20VMD816-B	Vertical cable management cage, 8'	Slam latch dual hinged door, single operation door, larger capacity, 180° bend limiting clips, aesthetic design	No availability of 16" extrusions, use only MM20
OR-MM10ABC1612	Not needed, part of ABL parts numbers	-	-	
OR-MM10ABL71612	OR-MM20ABL71612-B	Lightweight airflow baffle	Identical part	
OR-MM10ABL71616	OR-MM20ABL71616-B	Lightweight airflow baffle	Identical part	
OR-MM10ABL73012	OR-MM20ABL73012-B	Lightweight airflow baffle	Identical part	
OR-MM10ABL73016	OR-MM20ABL73016-B	Lightweight airflow baffle	Identical part	
OR-MM10ABL81612	OR-MM20ABL81612-B	Lightweight airflow baffle	Identical part	

MIGHTY MO 10 TO MIGHTY MO 20 CROSS REFERENCE

MIGHTY MO 10 PART NO.	MIGHTY MO 20 EQUIVALENT PART NO.	MIGHTY MO 20 EQUIVALENT DESCRIPTION	MIGHTY MO 20 EQUIVALENT FEATURES AND BENEFITS	NOTES
OR-MM10ABL81616	OR-MM20ABL81616-B	Lightweight airflow baffle	Identical part	
OR-MM10ABL83012	OR-MM20ABL83012-B	Lightweight airflow baffle	Identical part	
OR-MM10ABL83016	OR-MM20ABL83016-B	Lightweight airflow baffle	Identical part	
OR-MM10AB71616	OR-MM20ABL71616-B	Lightweight airflow baffle	Lightweight version made of PVC	
OR-MM10AB73012	OR-MM20ABL73012-B	Lightweight airflow baffle	Lightweight version made of PVC	
OR-MM10AB81612	OR-MM20ABL81612-B	Lightweight airflow baffle	Lightweight version made of PVC	
OR-MM10AB81616	OR-MM20ABL81616-B	Lightweight airflow baffle	Lightweight version made of PVC	
OR-MM10AB83012	OR-MM20ABL83012-B	Lightweight airflow baffle	Lightweight version made of PVC	
OR-MM10AB83016	OR-MM20ABL83016-B	Lightweight airflow baffle	Lightweight version made of PVC	
OR-MM10CRBRSVR	OR-MM20CRB4PRU-B	Bracket, cable runway	Identical part	
OR-MM10CRBSVR	OR-MM20CRB4PU-B	Bracket, cable runway	Identical part	
OR-MM10EPN730	OR-MM20EPN730-B	End panel, narrow, 30"	Identical part	
OR-MM10EPN830	OR-MM20EPN830-B	End panel, narrow, 30"	Identical part	
OR-MM10EPS	OR-MM20EPS-B	End panel support brace	Identical part	
OR-MM10SVRESB30	OR-MM20ESB30-B	Equipment support bracket 30"	Identical part	
OR-MM10WFE	OR-MM20WFE-B	Waterfall extension	Identical part	
OR-MM1024DMF-B	OR-MM2024DMFHD-B	Door mount front, 24"W	Improved locking mechanism, does not rotate on pin, heavy duty version	
OR-MM1024DMF-W	OR-MM2024DMFHD-W	Door mount front, 24"W	Improved locking mechanism, does not rotate on pin, heavy duty version	
OR-MM107SVRABR	OR-MM207ADJABR-B	4-post rack baffle rail, 7'	Identical part	
OR-MM10724PD-B	OR-MM20724PDHD-B	Perforated door, 7' heavy duty	Improved locking mechanism, does not rotate on pin, heavy duty version	
OR-MM10724PD-W	OR-OR-MM20724PDHD-W	Perforated door, 7' heavy duty	Improved locking mechanism, does not rotate on pin, heavy duty version	
OR-MM108SVRABR	OR-MM208ADJABR-B	4-post rack baffle rail, 8'	Identical part	
OR-MM10824PD-B	OR-MM20824PDHD-B	Perforated door, 8' heavy duty	Improved locking mechanism, does not rotate on pin, heavy duty version	
OR-MM10824PD-W	OR-MM20824PDHD-W	Perforated door, 8' heavy duty	Improved locking mechanism, does not rotate on pin, heavy duty version	
OR-MM1024DMFHD	OR-MM2024DMFHD-B	Door mount front, heavy duty	Improved locking mechanism, does not rotate on pin, heavy duty version	
OR-MM10VDA8244	no replacement	-	-	Now heavy duty version only
OR-MM10VDA8248	no replacement	-	-	Now heavy duty version only