

NEW!

## Mighty Mo® Wall Mount Cabinets

The Mighty Mo wall mount cabinets utilize advanced cable management to help secure, support and organize your network where floor space is limited. Providing capacity for both active and passive equipment, the cabinets feature one-rack unit finger style vertical managers to ensure proper cable management for maximum network performance. An optional rear horizontal mount bracket kit is designed to provide 2 additional fixed rack units on the rear wall for mounting fiber, equipment or power distribution units. In addition, the cabinet center section swings out from the wall to provide easy access to the equipment.

The front lockable wing turn latch allows you to completely close the door shut without having to lock the cabinet. This feature allows for easy access into the front of the cabinet when you are in a secure environment.

The Mighty Mo wall mount cabinets are also an ideal choice for mounting in an open office environment. The cabinet's heavy duty construction minimizes sagging under heavy loads and the optional 50cfm fan is 50% quieter than most other leading cabinets.



### FEATURES & BENEFITS

- Cable management to support and organize cables, ensuring proper cable management for minimum distortion and maximum network performance
- Choice of solid or plexiglas door
- The cabinet can be mounted to open left or right
- Locking center section swings out to provide easy access to the equipment
- Front and center sections are keyed alike
- Includes one pair of fully adjustable 12-24 EIA mounting rails for 20" deep cabinet
- Optional brush cable entries
- Cable knockouts and 3" removable cable access holes standard on top and bottom
- Vented sides for passive cooling of active equipment
- Optional 50cfm cooling fans are available to further protect active equipment
- Heavy duty 14 GA (.075") steel construction



## Ortronics

125 Eugene O'Neill Drive  
 New London, CT 06320  
 800.934.5432  
 860.445.3900 (sales)  
 860.405.2992 (fax)

[www.legrand.us/ortronics](http://www.legrand.us/ortronics)

REV. 10/09



## Mighty Mo® Wall Mount Cabinets

### ORDERING INFORMATION

#### Mighty Mo® wall mount cabinets

PART NO.	DESCRIPTION	WEIGHT CAPACITY
OR-MMW122420S-B	12U x 24"W x 20"D, Solid door, height is 23.50", Basic Black	150 lbs
OR-MMW122420P-B	12U x 24"W x 20"D, Plexiglass door, height is 23.50", Basic Black	150 lbs
OR-MMW192420S-B	19U x 24"W x 20"D, Solid door, height is 35.75", Basic Black	200 lbs
OR-MMW192420P-B	19U x 24"W x 20"D, Plexiglass door, height is 35.75", Basic Black	200 lbs
OR-MMW262420S-B	26U x 24"W x 20"D, Solid door, height is 48.00", Basic Black	300 lbs
OR-MMW262420P-B	26U x 24"W x 20"D, Plexiglass door, height is 48.00", Basic Black	300 lbs
OR-MMW122426S-B	12U x 24"W x 26"D, Solid door, height is 23.50", Basic Black	150 lbs
OR-MMW122426P-B	12U x 24"W x 26"D, Plexiglass door, height is 23.50", Basic Black	150 lbs
OR-MMW192426S-B	19U x 24"W x 26"D, Solid door, height is 35.75", Basic Black	200 lbs
OR-MMW192426P-B	19U x 24"W x 26"D, Plexiglass door, height is 35.75", Basic Black	200 lbs
OR-MMW262426S-B	26U x 24"W x 26"D, Solid door, height is 48.00", Basic Black	300 lbs
OR-MMW262426P-B	26U x 24"W x 26"D, Plexiglass door, height is 48.00", Basic Black	300 lbs

#### Mighty Mo® wall mount cabinet accessories

PART NO.	DESCRIPTION
OR-MMCFAN-4-50	Fan Kit, 4", 50cfm
OR-MMWHMBM12-B	Rear Horizontal Mount Bracket Kit
OR-MMWBPK	Brush Plate Kit
OR-MMW12M12-B	12U Mounting Rail, 12-24, 1-pair
OR-MMW19M12-B	19U Mounting Rail, 12-24, 1-pair
OR-MMW26M12-B	26U Mounting Rail, 12-24, 1-pair