

Choose from 12 of the most popular cabinet part numbers

- Quantities of 5 or less
- Ship from a USA warehouse



N-TYPE SWITCH CABINETS

- First choice for high density network, storage and compute applications
- Inset frame provides up to 10% more space for cable management and cooling airflow
- Innovative dual hinge door speeds deployments and moves, adds, and changes by 30%
- Open rail mounting creates more cable management space, equipment positioning flexibility, and allows installation of ducting solutions to optimize equipment efficiencies
- Vertical split side panels enable fast access to equipment
- Innovative leveling feet design reduces cabinet installation time by 80%
- Single point of bonding reduces deployment time
- 2 sets of high density cable management fingers included

S-TYPE SERVER CABINETS

- Designed to effectively manage space requirements and provide a complete, optimized physical infrastructure solution for all server and Top of Rack switch architectures
- Outset frame design maximizes RU utilization, saving as much as 15% of the floor space
- Outset cable entry allows equipment to be mounted at the top of the cabinet and improves floor space utilization by 5%
- Vertical split side panels enables fast access to equipment
- Innovative leveling feet design reduces cabinet installation time by 80%
- Single point of bonding reduces deployment time
- Vertical airdams, casters and PDU brackets pre-installed to speed deployment



See side 2 for part numbers

N-TYPE SWITCH CABINETS

Part Number	Width	Height	Depth	Side Panels	E-rails
N8212B	800mm	42 RU	1070mm	Included	Tapped
N8512B	800mm	45 RU	1070mm	Included	Tapped
N8512BC	800mm	45 RU	1070mm	Included	Cage Nut
N8519B	800mm	45 RU	1070mm	Not Included	Tapped
N8522B	800mm	45 RU	1200mm	Included	Tapped
N8522BC	800mm	45 RU	1200mm	Included	Cage Nut

Add accessories to maximize the functionality of the cabinet.



NVBP

Vertical blanking panels with pass-through holes for 42 RU through 48 RU cabinets. Color: Black



NCSTR4

Caster kit. 2 fixed casters for front of cabinet, 2 swivel casters for rear of cabinet, 4 mounting plates and 24 screws. Casters add 24mm (1") to height of cabinet. Color: Black



NVPDUB

PDU brackets. Sold in pairs. Color: Black

S-TYPE SERVER CABINETS

Part Number	Width	Height	Depth	Side Panels	E-rails
S6212B	600mm	42 RU	1070mm	Included	Cage Nut
S6522B	600mm	45 RU	1200mm	Included	Cage Nut
S7222B	700mm	42 RU	1200mm	Included	Cage Nut
S7522BF (includes vertical cable management fingers.)	700mm	45 RU	1200mm	Included	Cage Nut
S7529B	700mm	45 RU	1200mm	Not Included	Cage Nut
S8512BF (includes vertical cable management fingers.)	800mm	45 RU	1070mm	Included	Cage Nut

Add accessories to maximize the functionality of the cabinet.



S2BRK6

Combination PDU/cable management bracket, 152 mm (6") wide full length for 42 RU through 48 RU cabinet. Color: Black

SBRK12

Combination PDU/cable management bracket, 305mm (12") wide full length for 42 RU through 48 RU cabinet. Color: Black



S1LR



S1DR



S2LR



S2DR

D-Ring and L-Ring cable retainers, bag of 8 pcs., attaches to S2BRK6 and S2BRK12.