

Lighttogo



Things just got easier. Introducing our new lineup of lighting essentials – quick to order, easy on your wallet and simple to use.

Make your next outdoor lighting choice a brand you can trust. **Make it Philips Lighting.**

philips.com/Lighttogo



© 2019 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.

PLt-17101LL 02/19 philips.com/lighttogo

Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9

PHILIPS

Light to go

Downlighting



Real professionals choose Lighttogo

**REAL PROs
REAL QUALITY**



You've found your go to downlights, Philips Light to go downlights

Philips knows contractors look for dependability and ease of installation when choosing a downlight – and these lights were designed with that in mind. They are also versatile and suitable to be used in wet locations. Adding light where you need it has never been easier.

Philips Light to go downlights



Real professionals choose Lighttogo

Commercial retrofit downlight



- Adjustable lumen output switch allows you to make choices while you install or afterward.
- Great for different ceiling heights and different light level needs.
- Sturdy metal clips provide a solid fit and easy installation.
- Universal voltage 120-277V.
- Out-of-the-box pre-wired with flexible metal conduit and easy-twist quick connector.
- Lifetime >50,000 hours (L70).
- Backed by the Philips 5-year warranty.

Flat downlight - round & square



- Detachable electric box with remodel NEC clip.**
- 1" depth, low profile for non-intrusive install.
- Available in 4" & 6" sizes.
- Quick and easy installation without frame or reflector.
- LED technology featuring long lifetimes for reduced maintenance.
- IC-rated for direct contact with insulation.
- Through wiring capability.
- Lifetime >50,000 hours (L70).
- Mercury free and Wet location rated.
- Listings: ENERGY STAR®, Title 24 rated, UL 1598 wet location rated (in covered ceilings).

Surface mount



- One piece plastic flange. White matte finish.
- Available in 5" & 7" sizes.
- Diffused lens for smooth, comfortable light pattern.
- Power supply – Integral class 2 driver (see Electrical section for specifications).
- Utilizes edge lit LED technology.
- Lifetime L70 at 50,000 hours and backed by the Philips 5-year warranty.
- Compliance: Non-conductive fixture for shower light application.
- Support Wire: Support wire attached to the fixture to hook on the mounting bracket to hold the fixture.

Easy order. Budget friendly. Job ready.



Philips Catalog Code	Size	Max Lumens	Color Temp	Replaces
PCR4R10927UW	4"	1000	2700K	2x18W CFL
PCR4R10930UW	4"	1000	3000K	
PCR4R10935UW	4"	1000	3500K	
PCR4R10940UW	4"	1000	4000K	
PCR6R15927UW	6"	1500	2700K	2x26W CFL
PCR6R15930UW	6"	1500	3000K	
PCR6R15935UW	6"	1500	3500K	
PCR6R15940UW	6"	1500	4000K	
PCR8R23927UW	8"	2300	2700K	2x32W CFL
PCR8R23930UW	8"	2300	3000K	
PCR8R23935UW	8"	2300	3500K	
PCR8R23940UW	8"	2300	4000K	
PCR10R30927UW	10"	3000	2700K	2x38W CFL
PCR10R30930UW	10"	3000	3000K	
PCR10R30935UW	10"	3000	3500K	
PCR10R30940UW	10"	3000	4000K	

Philips Catalog Code	Size	Lumens	Color Temp	Dimming	Replaces
FDL4S07930TE1W	4"	700	3000K	ELV/TRIAC	50W PAR20
FDL6S09930TE1W	6"	900	3000K	ELV/TRIAC	65W PAR30
FDL4R07930TE1W	4"	700	3000K	ELV/TRIAC	50W PAR20
FDL6R09930TE1W	6"	900	3000K	ELV/TRIAC	65W PAR30

Accessories (order separately)
 FDLRN - Round new construction plate
 FDLN - Square new construction plate
 FDL06C - 6ft extension cable
 FDL20C - 20ft extension cable

Philips Catalog Code	Size	Lumens	Color Temp	Dimming	Replaces
PSD5R079301W	5"	600	3000K	ELV/TRIAC	65W PAR30
PSD7R099301W	7"	1000	3000K	ELV/TRIAC	75W PAR38

Please refer to the specification sheets for additional information and technical data, philips.com/Lighttogo

Mini downlight



- Detachable electric box with remodel NEC clip.**
- Quick and easy installation without frame or reflector.
- 550 Lumen output from the mini 1-1/4" aperture.
- LED technology featuring long lifetimes for reduced maintenance.
- 1" depth, low profile for non-intrusive install.
- IC-rated for direct contact with insulation.
- Lifetime >50,000 hours (L70).
- TRIAC dimming down to 10%.
- Listings: ENERGY STAR®, Title 24 (JA8-2016), ETL listed, damp location rated & AirSeal/IC.
- Backed by the Philips 5-year warranty.

Mini gimbal



- Detachable electric box with remodel NEC clip.**
- Quick and easy installation without frame or reflector.
- 550 Lumen output from the mini 1-1/2" aperture.
- LED technology featuring long lifetimes for reduced maintenance.
- 1" depth, low profile for non-intrusive install.
- IC-rated for direct contact with insulation.
- Lifetime >50,000 hours (L70).
- TRIAC dimming down to 10%.
- Listings: ENERGY STAR®, Title 24 (JA8-2016), ETL listed, damp location rated & AirSeal/IC.
- Backed by the Philips 5-year warranty.

Retrofit downlight



- Utilizes existing frames to make replacing old downlighting and upgrading to LED, a truly easy task.
- Available in 4" & 5/6" sizes.
- Flexible springs allow for installation without tools.
- Contemporary and simple design with baffle trim.
- Uniform LED light with glare-reduction filter, means a more comfortable space.
- Long lifetime will reduce your future maintenance (L70 at 42,000 hours).
- Backed by the Philips 5-year warranty.

Philips Catalog Code	Size	Lumens	Color Temp	Beam Spread	Replaces
PMD3R069301FW	3"	550	3000K	Flood	50W MR16

Accessories (order separately)
 PMDRN - Round new construction plate
 PMD06C - 6ft extension cable
 PMD20C - 20ft extension cable

Philips Catalog Code	Size	Lumens	Color Temp	Beam Spread	Replaces
PMG3R06930NF1W	3"	550	3000K	Narrow Flood	50W MR16

Accessories (order separately)
 PMDRN - Round new construction plate
 PMD06C - 6ft extension cable
 PMD20C - 20ft extension cable

Philips Catalog Code	Size	Lumens	Color Temp	Dimming	Replaces
PRD4R089301W	4"	900	3000K	ELV/TRIAC	50W PAR20
PRD5R129301W	5/6"	1400	3000K	ELV/TRIAC	65W PAR30