

Light to go



Philips Light to go luminaires



Philips knows you look for dependability and ease of installation when choosing your lighting – and these LED luminaires were designed with that in mind. Strong and long lasting with solid performance, adding light where you need it is quicker and easier than ever.

Easy landscape lighting solutions,

Look for Philips Light to go

Things just got easier. Introducing our new lineup of lighting essentials – quick to order, easy on your wallet and simple to use.

Make your next outdoor lighting choice a brand you can trust. **Make it Philips Lighting.**

philips.com/Lighttogo



© 2019 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify, Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.

PLT-18119LL 01/19 philips.com/Lighttogo

Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9

PHILIPS

Lighttogo

Landscape Luminaires



Real professionals choose Lighttogo

Real professionals choose Lighttogo



Commercial bollard



- Clean lines for a timeless, modern look.
- Rugged, aluminum construction and high quality finish.
- Simple installation.
- Ready-to-ship, in-stock product.
- Silicone gaskets protect internals from harsh elements.
- 50,000 hour rated life (L70).

LWL Wall light



- Ideal wall mount fixture for doorways, entryways and other poorly lit areas.
- Cost-effective enhanced LED performance means you won't have to sacrifice quality for your budget.
- Strong, one-piece, die-cast aluminum housing with a tough polycarbonate lens.
- Built-in photocell for automatic dusk to dawn lighting allow for even more cost-savings.
- Easy installation, the LWL Wall Light mounts to a standard 4" junction box with a galvanized mounting plate.
- 5 year limited warranty.

Commercial accent



- One all-encompassing landscape lighting solution is all you need.
- Narrow, medium and wide flood beam patterns, interchangeable via snap-on lenses.
- Standard 0-10V dimming.
- Five field adjustable lumen outputs.
- 3000K Color Temp.
- 5 year limited warranty.

General purpose floods



- Complete family of LED floodlights ideal to illuminate signs, building facades or other dark areas.
- Can be mounted on the ground, wall or pole-mounted.
- IP66 rated.
- Discreet, modern design.
- 4000K color temperature.
- All 5 sizes arrive fully assembled and ready to install. Three larger sizes have a trunion or slip fitter mount and the two smaller sizes have a knuckle mount.
- Fade-resistant, textured bronze finish with tempered glass lens that is heat and impact resistant.

Philips Catalog Code	Watts	Lumens	Voltage	Replaces
PBL25-NW-G1-5-8-BZ	26W	2508	120-277V	70W MH

Philips Catalog Code	Watts	Lumens	Voltage	Replaces
PLWLED1C5K120PCBBZ	12W	829	120V	100W INC

Philips Catalog Code	Wattage (Variable)	Color Temp	Lumens (Range)	Replaces
PB9DW-H	10W	3000K	932-995	35W MH
PB9DW-H	13W	3000K	1337-1427	50W MH
PB9DW-H	19W	3000K	1903-2031	70W MH
PB9DW-H	27W	3000K	2621-2797	70W MH
PB9DW-H	33W	3000K	3065-3271	70W MH

Philips Catalog Code	Watts	Lumens	Mounting	Replaces
PFL20-NW-G1-K-FL-8-BZ*	20W	2122	Knuckle Mount 1/2" NPS male	70W PSMH
PFL40-NW-G1-K-FL-8-BZ*	39W	4433	Knuckle Mount 1/2" NPS male	150W PSMH
PFL80-NW-G1-T-FL-8-BZ*	79W	8856	Trunion	250W PSMH
PFL80-NW-G1-S-FL-8-BZ	79W	8856	Slip Fitter	250W PSMH
PFL150-NW-G1-T-FL-8-BZ*	146W	16,325	Trunion	400W PSMH
PFL150-NW-G1-S-FL-8-BZ	146W	16,325	Slip Fitter	400W PSMH
PFL200-NW-G1-T-FL-8-BZ	197W	24,254	Trunion	400W PSMH
PFL200-NW-G1-S-FL-8-BZ	197W	24,254	Slip Fitter	400W PSMH
PFL300-NW-G1-T-FL-8-BZ	301W	34,025	Trunion	750W PSMH
PFL300-NW-G1-S-FL-8-BZ	301W	34,025	Slip Fitter	750W PSMH

*Also available with button photocell (PCB) option.

Please refer to the specification sheets for additional information and technical data, philips.com/Lighttogo

Low voltage accent



- Beam Adjustability: Lens zooms from narrow (15°) to medium (30°) beam, accessible after easy removal of twistoff shroud.
- Interchangeable flood (60°) lens included.
- Switchable Light Levels: Easy-access integral switch for 4 preset light outputs.
- Precise Aiming: Adjustable knuckle arm enables range of 150°. Vibration locking teeth secured by black SS screw.
- IP66 Rating: Dust tight and sealed against direct jets of water.
- Convenient Installation.

Low voltage inground



- Clean lines for a timeless, modern look
- Rugged construction and quality finish
- Ready-to-ship, in-stock products
- Ease of installation
- Flexibility to change light intensity in the field
- Countless lighting outcomes in a single luminaire save time and money
- Innovative zoomable LED Optics allow different beam patterns
- 50,000 hour rated life (L70)

Controller



- Manages up to 8 independent outdoor lighting groups at the touch of a finger.
- Easily group your lighting to instantly switch on and off or program your scenes to weekly schedules.
- Compatible with outdoor luminaires from other manufacturers.
- Install the Controller in under 10 minutes without any additional wires or adapter tools.
- Android or IOS compatible App with user-friendly interface to create and control lighting.
- 5 year limited warranty.

Power supply



- Control up to 300 Watts of luminaires.
- Housing is 304 brushed stainless steel case with stainless steel screws and lockable captive door.
- ETL Listed to U.S. safety standards for wet locations.
- cETL listed to Canadian safety standards for wet locations.
- 5 year limited warranty.

Easy order. Budget friendly. Job ready.

Philips Catalog Code	CCT	Watts Consumed	Lumens	Replaces
PBL9DW-HS7	Warm-3000K	2.0 W	230	20W MR16
PBL9DW-HS7	Warm-3000K	4.5 W	600	35W MR16
PBL9DW-HS7	Warm-3000K	8.6 W	1100	50W MR16
PBL9DW-HS7	Warm-3000K	10.7 W	1500	75W MR16

Philips Catalog Code	CCT	Watts Consumed	Lumens	Replaces
PIL9DW-A	Warm-3000K	2.0 W	230	20W MR16
PIL9DW-A	Warm-3000K	4.5 W	600	35W MR16
PIL9DW-A	Warm-3000K	8.6 W	1100	50W MR16
PIL9DW-A	Warm-3000K	10.7 W	1500	75W MR16

Landscape Controller Order Code	Max Consumption
PZoneScape1-A	Controls 300 Watts of Luminaires

Landscape Power Supply Order Code	Max Consumption
PTSS354-15	Will Power 300W Transformer

Please refer to the specification sheets for additional information and technical data, philips.com/Lighttogo