

## VM10LCD

### Features

- Professional TFT LCD for surveillance with multiple connections
- Picture-In-Picture feature that allows multi-picture display (in VGA mode)
- High brightness level and contrast ratio with super wide viewing angle
- Built-in 3D comb filter and 3D de-interlace for display picture performance
- Fast response time and refresh rate

### Specifications

- Panel Size ..... 10.4"
- Aspect Ratio ..... 4:3
- Resolution/Scan..... 640 x 480
- Brightness ..... 350 cd/m<sup>2</sup>
- Contract Ratio ..... 300:1
- Viewing Angle (H/V) ..... Left 70° / Right 70° / Up 40° / Down70°
- Response Time ..... 6ms (Typ.)
- Sync. Format ..... NTSC / PAL
- Frequency (Horizontal) ..... PC: 31.5K
- Frequency (Vertical) ..... PC: 60Hz - 75Hz, Video: 50 / 60Hz
- Video Interface ..... D-SUB 15IN x 1, Video In x 2 (BNC), Video Out x 2 (BNC), S-Video In x 1
- Audio Interface ..... In x 2, Audio Out x 2, PC-Audio In x 1
- Input Power ..... DC In x 1
- Termination ..... 75 Ohm (AutoTermination)
- Built-In Speakers ..... Yes (2pcs)
- Front Panel Button ..... Power, Source, Up, Down, Menu, Auto
- OSD Language ..... Multi Language
- VESA Mounting ..... VESA 75mm x 75mm
- Power Supply ..... 12VDC
- Power Consumption (max.) ..... 17.2W
- Operating Temperature/  
Humidity ..... 14° F - 122° F / RH 20% - 80%
- Dimensions ..... 10.3" (W) x 8.8" (H) x 2.5" (D)
- Weight (N.W. / G.W.) ..... 4 lbs. / 6.4 lbs.
- Included in Package ..... Power cord, user manual, remote control

