

CVC95AM 3.6mm wide angle lens, Horizontal 72° / Vertical 53°, BW

CVC695AM 3.6mm wide angle lens, Horizontal 72° / Vertical 53°, Color

Features

- Weather/tamper resistant cover
- Features a 3.6mm wide angle lens that views at a downward angle of 38°
- Includes tamper resistant screw for vandal resistant mounting
- 5 year warranty



Specifications

	CVC95AM
Image Sensor	1/3" BW CCD
Resolution.....	420 lines
Electronic Shutter	Auto: 1/60 sec. - 1/100,000 sec.
Minimum Illumination.....	0.02 lux
Video Output.....	1.0Vp.p - 75 Ohm
S/N Ratio	More than 50dB
Scanning Frequency.....	15.75kHz (H) / 60Hz (V)
Output.....	Video - BNC, Power -DC jack
Operating Temperature/	
Humidity.....	14° F - 122° F/ within 95% RH
Power Consumption	150mA
Power Supply	12VDC (UL and CSA listed power supply included)
Housing	18 gauge stainless steel
Dimensions.....	2.25" (W) x 2.75" (H) x 2.5" (L)
Weight	6.8 oz.

	CVC695AM
Image Sensor	1/4" color CCD
Resolution.....	420 lines
Electronic Shutter	Auto: 1/60 sec. - 1/100,000 sec.
Minimum Illumination.....	1.0 lux
Video Output.....	1.0Vp.p - 75 Ohm
S/N Ratio	More than 50dB
Scanning Frequency.....	15.75kHz (H) / 60Hz (V)
Output.....	Video - BNC, Power- DC jack
Operating Temperature/	
Humidity.....	14° F - 122° F/ within 95% RH
Power Consumption	210mA
Power Supply	12VDC (UL and CSA listed power supply included)
Housing	18 gauge stainless steel
Dimensions.....	2.25" (W) x 2.75" (H) x 2.5" (L)
Weight	6.8 oz.

Speco Technologies is constantly developing and improving products.

We reserve the right to modify product design and specifications without notice and without incurring any obligation.

Rev. 9/29/11

For more information contact Speco Technologies

200 New Highway, Amityville, NY 11701 • Toll Free: 1-800-645-5516 • Fax: 631-957-9142 or 631-957-3880
www.specotech.com