

Power & Connect the Classroom with Tripp Lite



Technology and remote learning have transformed traditional K-12 classrooms into network environments. Tripp Lite IT solutions support schools in their mission to serve students with modern, interactive instruction.

Charge Your Devices

A Charging Stations & Carts

Keep devices charged, organized and secure.

- Locking enclosures deter theft.
- USB models provide wired syncing; all models support wireless syncing.
- Cable management reduces cord clutter.
- Carts enable easy sharing between rooms.
- Towers save space in crowded rooms.

Reduce Your Risk

B Antimicrobial Products

Inhibit bacteria, viruses, mold and fungi for daily protection and peace of mind.

- Charging carts with UVC device sanitizing.
- Ethernet, AV and USB cables, including charging cables.
- Surge protectors and power strips.

Safe-IT
AntiMICROBIAL
PRODUCTS

Share Your Message

C Network Cables

Connect devices to high-speed networks with copper Ethernet cables.

D Audio/Video Solutions

Connect high-res AV sources to displays and projectors with cables, adapters and extenders. Options include HDMI, DisplayPort and USB-C.

E USB Solutions

Connect, adapt and charge USB-A and USB-C devices with cables, docks, hubs and adapters.

F Display Mounts & Mobile Stands

Mount TVs or monitors to save space, optimize viewing angles and move from place to place.

G Interactive Displays

Enrich in-person and remote collaboration with intelligent 4K interactive touchscreens. Available with or without built-in PC, mobile stand and lithium-ion battery system.

Power & Protect Equipment

H Desktop UPS Systems

Provide conditioned power and battery backup.

I Surge Protectors

Provide AC outlets and protect equipment from power surges. Optional USB charging.

J Wall-Mount Racks

Secure equipment in a locking steel cabinet.

K Power Distribution Units (PDUs)

Provide AC outlets without or without current meters, remote monitoring and outlet control.

L Network UPS Systems

Supply highly reliable power with battery backup and optional network management.

TRIPP-LITE

Powering and Connecting Your World

■ See Next Page for Top Solutions to Power and Connect the Classroom

Top Solutions to Power and Connect the Classroom

See 5,000+ products at tripplite.com, including CARES Act, CRRSA and E-Rate eligible options!

A Charging Stations & Carts

Charging Carts (Mobile Cabinets)	
Model	Description
CSC21AC	21-Device AC Charging Cart, Black
CSC27AC	27-Device AC Charging Cart, Black
CSC32AC	32-Device AC Charging Cart, Black
CSC32ACW	32-Device AC Charging Cart, White
CSC32USB	32-Device USB Charging Cart, Black
CSC36AC	36-Device Dual-Zone AC Charging Cart, Black
CSC42AC	42-Device Dual-Zone AC Charging Cart, Black
CSC45AC	45-Device Dual-Zone AC Charging Cart, Black
CSC48AC	48-Device Dual-Zone AC Charging Cart, Black

Charging Stations (Mountable Cabinets)	
Model	Description
CSC16AC	16-Device AC Charging Station, Black
CSC16ACW	16-Device AC Charging Station, White
CSC16USB	16-Device USB Charging Station, Black
CSC32AC	32-Device AC Charging Station, Black

Charging Towers (Space-Saving Open Frames)	
Model	Description
CST16AC	16-Device AC Charging Tower, White
CST32AC	32-Device AC Charging Tower, White

Desktop Charging Stations (CSD Models Secure Tablets)	
Model	Description
CSD1006AC	10-Device Desktop AC Charging Station
CSD1006USB	10-Device Desktop USB Charging Station
U280-010-ST	10-Device USB Charging Station

B Antimicrobial Products

Charging Carts (UVC Device Sanitizing)	
Model	Description
CSC32ACWVHG	32-Device AC Charging Cart with UVC, White
CSC32USBVHG	32-Device USB Charging Cart with UVC, White

Antibacterial Ethernet Cables (Cat6a 10G, Snagless, White)				
Length	UTP Cables	Slim UTP Cables	S/FTP Cables, PoE	
1 ft.	—	N261AB-S01-WH	—	—
2 ft.	—	N261AB-S02-WH	—	—
3 ft.	N261AB-003-WH	N261AB-S03-WH	N262AB-003-WH	—
5 ft.	N261AB-005-WH	N261AB-S05-WH	N262AB-005-WH	—
6 ft.	—	N261AB-S06-WH	—	—
7 ft.	N261AB-007-WH	N261AB-S07-WH	N262AB-007-WH	—
10 ft.	N261AB-010-WH	N261AB-S10-WH	N262AB-010-WH	—
14 ft.	N261AB-014-WH	—	N262AB-014-WH	—
15 ft.	—	N261AB-S15-WH	—	—
20 ft.	N261AB-020-WH	—	N262AB-020-WH	—
25 ft.	N261AB-025-WH	—	N262AB-025-WH	—

Antibacterial AV Cables (HDMI and DisplayPort)	
Model	Description
P568AB-006	High-Speed HDMI Cable, 4K, Black, 6 ft.
P569AB-006	High-Speed HDMI Cable with Ethernet, 4K, Black, 6 ft.
P580AB-006	High-Speed DisplayPort Cable, Latching, Black, 6 ft.

Antibacterial USB Cables	
Model	Description
M100AB-01M-WH	USB-A to Lightning Cable, MFi, White, 1 m
M100AB-02M-WH	USB-A to Lightning Cable, MFi, White, 2 m
M100AB-03M-WH	USB-A to Lightning Cable, MFi, White, 3 m
M101AB-004-LMCW	Universal USB-A to Lightning, USB-C and USB Micro-B Cable, MFi, White, 4 ft.
M102AB-01M-WH	USB-C to Lightning Cable, MFi, White, 1 m
M102AB-02M-WH	USB-C to Lightning Cable, MFi, White, 2 m
U024AB-006-WH	USB-A 2.0 Extension Cable, White, 6 ft.
U030AB-003-WH	USB-A to USB Mini-B Cable, White, 3 ft.
U050AB-003-WH	USB-A to USB Micro-B Cable, White, 3 ft.
U050AB-006-WH	USB-A to USB Micro-B Cable, White, 6 ft.

C Network Cables

Ethernet Patch Cables (UTP, Snagless, Blue)			
Length	Cat5e	Cat6	Slim Cat6a 10G
1 ft.	N001-001-BL	N201-001-BL	N261-S01-BL
3 ft.	N001-003-BL	N201-003-BL	N261-S03-BL
5 ft.	N001-005-BL	N201-005-BL	N261-S05-BL
7 ft.	N001-007-BL	N201-007-BL	—
10 ft.	N001-010-BL	N201-010-BL	N261-S10-BL
15 ft.	N001-015-BL	N201-015-BL	N261-S15-BL
25 ft.	N001-025-BL	N201-025-BL	N261-S25-BL
50 ft.	N001-050-BL	N201-050-BL	—

Bulk Ethernet Cabling	
Model	Description
N222-01K-BL	Cat6 Solid-Core UTP Bulk Cable, Blue, 1000 ft.
N224-01K-BL	Cat6 Solid-Core UTP Bulk Plenum Cable, Blue, 1000 ft.

D Audio/Video Solutions

Model	Description
B118-002-UHD	2-Port HDMI Splitter, 4K30, HDCP 1.3
B126-1A1	HDMI over Cat5/6 Extender Kit, 1080p, 150 ft.
B127A-1A1-BHPH	HDMI over Cat5/6 Extender Kit, 4K60, 230 ft.
P131-06N	HDMI to VGA with Audio Adapter Cable, 6 in.
P134-000	DisplayPort to DVI-I Adapter Cable, 6 in.
P134-06N-VGA	DisplayPort to VGA Adapter Cable, 6 in.
P568-006	High-Speed HDMI Cable, 4K60, 6 ft.
P580-006	DisplayPort Cable with Latches, 4K60, 6 ft.
P581-006	DisplayPort to DVI Adapter Cable, 1080p, 6 ft.
P582-006	DisplayPort to HDMI Adapter Cable, 1080p, 6 ft.

E USB Solutions

Model	Description
M100-003-WH	USB-A to Lightning Cable, MFi, White, 3 ft.
M100-006-WH	USB-A to Lightning Cable, MFi, White, 6 ft.
U022-015	USB-A to USB-B Cable, USB 2.0, Black, 15 ft.
U038-006	USB-A to USB-C Cable, USB 2.0, Black, 6 ft.
U360-004-SLIM	4-Port Ultra-Slim Portable USB 3.0 Hub, Black
U428-000-F	USB-C to USB-A Adapter, USB 3.1 Gen 1 (5 Gbps)
U442-DOCK4-S	USB-C Dock, 4K HDMI, VGA, DP, USB, GbE, 100W
U444-006-H	USB-C to HDMI Adapter Cable, 4K, Black, 6 ft.
U444-06N-H4GUBC	USB-C Mini-Dock, 4K HDMI, USB, GbE, 60W, Black
U444-06N-VGU-C	USB-C Mini-Dock, VGA, USB, GbE, 60W, White

F Display Mounts & Mobile Stands

Display Mounts (VESA Compliant)	
Model	Description
DDR1327SDD	Dual-Monitor Desktop Stand for 13 to 27 in. Displays
DWM1327SE	Swivel/Tilt Wall Mount for 13 to 27 in. Display
DWM1742MA	Swivel/Tilt Wall Mount for 17 to 42 in. Display, UL
DWM2655M	Swivel/Tilt Wall Mount for 26 to 55 in. Display
DWM3770X	Swivel/Tilt Wall Mount for 37 to 70 in. Display
DWM60100XX	Swivel/Tilt Wall Mount for 60 to 100 in. Display, UL

Mobile Stands (VESA Compliant)	
Model	Description
DMCS3270XP	Rolling TV/Monitor Cart/Stand for 32 to 70 in. Display
DMCS3770L	Rolling TV/Monitor Cart/Stand for 37 to 70 in. Display
DMCS60100XX	Rolling TV/Monitor Cart/Stand for 60 to 100 in. Display

G Interactive Displays

Model	Description
DMCSTP65CBP	Mobile Interactive Touchscreen Display with Rolling Stand, Lithium-Ion Battery System and PC, 4K, 65 in.
DMP650PS	Interactive Touchscreen Display with PC, 4K, 65 in.
DMP65NO	Interactive Touchscreen Display without PC, 4K, 65 in.

H Desktop UPS Systems

Internet Office® Standby UPS Systems	
Model	Description
INTERNET550U	550VA 300W Low-Profile UPS, 10 Outlets, USB
INTERNET600U	600VA 325W Low-Profile UPS, 10 Outlets, USB
INTERNET750U	750VA 450W Low-Profile UPS, 12 Outlets, USB

ECO UPS Systems with Energy-Saving Outlets	
Model	Description
ECO550UPS	550VA 300W Low-Profile UPS, 10 Outlets, USB
ECO750UPS	750VA 450W Low-Profile UPS, 12 Outlets, USB
ECO850LCD	850VA 425W Low-Profile UPS, 12 Outlets, USB, LCD
ECO1500LCD	1440VA 900W Tower UPS, 10 Outlets, USB, LCD

Line-Interactive UPS with Automatic Voltage Regulation (AVR)	
Model	Description
AVR750U	750VA 450W Low-Profile UPS, 12 Outlets, USB
OMNI900LCD	900VA 475W Tower UPS, 8 Outlets, USB, LCD
SMART1000LCD	1000VA 500W Tower UPS, 8 Outlets, USB, LCD
SMART1200LCD	1200VA 700W Tower/2U UPS, 8 Outlets, USB, LCD
SMART1500LCD	1500VA 900W Tower/2U UPS, 8 Outlets, USB, LCD
SMART1500CDT	1500VA 900W Tower UPS, 10 Outlets, USB, LCD

I Surge Protectors

Model	Description
ISOBAR8ULTRA	8 Outlets, 3840J, 12 ft. Cord, Metal, Premium, Lt. Gray
SS3612	12 Outlets, 1050J, 15 ft. Cord, Metal, Silver
SUPER7B	7 Outlets, 2160J, 7 ft. Cord, Black (Lt. Gray: SUPER7)
TLP606B	6 Outlets, 790J, 6 ft. Cord, Black (Lt. Gray: TLP606)
TLP615B	6 Outlets, 790J, 15 ft. Cord, Black (Lt. Gray: TLP615)
TLP6B	6 Outlets, 360J, 6 ft. Cord, Black
TLP712B	7 Outlets, 1080J, 12 ft. Cord, Black (Lt. Gray: TLP712)
TLP725	7 Outlets, 1080J, 25 ft. Cord, Lt. Gray
TLP808B	8 Outlets, 1440J, 8 ft. Cord, Black (Lt. Gray: TLP808)
TLP825	8 Outlets, 1440J, 25 ft. Cord, Lt. Gray
TLP88USBB	8 Outlets, 1200J, 8 ft. Cord, USB Charging, Black
ULTRABLOK	2 Outlets, 1410J, Direct Plug, Metal, Premium, Black

J Wall-Mount Racks

Model	Description
SRW6U	6U Wall-Mount Rack Enclosure, 16.5 in. Depth
SRW12US	12U Wall-Mount Rack Enclosure, 20.5 in. Depth
SRW12USDP	12U Wall-Mount Rack Enclosure, 24.5 in. Depth
SRW12USG	12U Wall-Mount Rack Enclosure, 20.5 in. Depth, Clear Acrylic Window
SRW15US	15U Wall-Mount Rack Enclosure, 20.5 in. Depth
SRW18US	18U Wall-Mount Rack Enclosure, 20.5 in. Depth
SRW18USDP	18U Wall-Mount Rack Enclosure, 24.5 in. Depth

K Power Distribution Units (PDUs)

Model	Description
PDU1215	1.8kW Basic PDU, (13) 5-15R Outlets, 15 ft. Cord, 1U
PDUMH15NET2LX	1.4kW Switched PDU, LX Platform Network Interface, (8) 5-15R Outlets, 12 ft. Cord, 1U, TAA

L Network UPS Systems

Model	Description
SMART500RT1U	500VA 300W 1U UPS, SNMP Slot, AVR
SMART1000RM1U	1000VA 800W 1U Sine Wave UPS, SNMP Slot, AVR
SMART1500RM2U	1500VA 1350W 2U Sine Wave UPS, SNMP Slot, AVR, LCD



Powering and Connecting Your World

Contact Tripp Lite for More Information:

773.869.1773 | presaleshelp@tripplite.com | tripplite.com/education