

Copper Certification*



Certifier10G™



Certifier40G™

Tier 1 and Tier 2 Fiber Certification*



SmartClass Fiber
OLTs-85



SmartClass Fiber
MPOLx



Certifier40G™



T-BERD/MTS-2000



T-BERD/MTS-4000

Essential Fiber Tools

Fiber Inspection



Probe microscope
P5000i



FiberChek™



FiberChek
Sidewinder™

VFL



Visual fault
locator
FFL-050

LFI



Live fiber
identifier
FI-60

Optical Power Measurement



Power meter
MP-60A



SmartPocket™



PowerChek™

**Ethernet Service Activation
and Maintenance**



SmartClass 4800



T-BERD/MTS-5800

Test and Certification Solutions for Enterprise & Data Center Contractors

Copper Certification

Feature	Certifier10G	Certifier40G
Up to Category 6A/Class EA channel and link certification	■	■
Up to Category 7A/Class FA channel and link certification		■
Up to Category 8 channel and link certification		■
Patch cord certification	■	■
Coax certification	■	■
Test result management and reporting	■	■

Ethernet Service Activation and Maintenance

Feature	SmartClass 4800	TBERD/MTS 5800
Commissioning Traffic Tests compliant with RFC 2544, Y1564, RFC 6349	■	■
Ethernet line rate capture/decode		■
OTN		■
CWDM/DWDM Testing		■
1G bandwidth testing	■	■
10G bandwidth testing		■
Dual port		■

Essential Fiber Tools

Optical Power Meters (OPM)

Feature	MP-60A	SmartPocket	PowerChek
Broadband optical power measurement	■	■	■
Absolute and reference-level measurement	■	■	■
On-board results storage		■	■
Optical source		■	■
Integrated display		■	■
In-bulkhead, non-contact test			■
Test result reporting	■	■	■

Live Fiber Identifier

Feature	FI-60A
Detect optical signals without having to disconnect the fiber	■
Ensure safe engagement with locking	■
Accepts multiple cable diameters (250 um to 3 mm jacketed fiber) without changing dies or inserts	■
Also functions as an optical power meter	■

Tier 1 and Tier 2 Fiber Certification

Feature	OLTS-85	MPOLx	Certifier40G	T-BERD/MTS-2000	T-BERD/MTS-4000
Fiber end-face inspection (with P5000i)	■	■	■	■	■
Dedicated fiber patch cord microscope	■	■			
Tier 1 fiber certification	■	■	■		
Encircled flux compliant	■	■	■		
Copper certification			■		
12 fiber MPO length/loss/polarity (multi-mode)		■	■		
Tier 2 fiber certification (OTDR)				■	■
Test result management and reporting	■	■	■	■	■
12 Fiber MPO Characterization & Troubleshooting (OTDR)				■	■
External MPO Switch				■	■
Internal/Integrated MPO switch					■

Essential Fiber Tools

Fiber Inspection

Feature	P5000i	FiberChek	FiberChek Sidewinder
Dual magnification inspection of fiber end faces	■	■	■
Pass/fail analysis to industry standards or custom requirements	■	■	■
Compatible with mobile devices	■	■	■
Auto-focus		■	■
On-board storage		■	■
Integrated display		■	■
Test result reporting	■	■	■
Wireless operation		■	■
MPO pass/fail analysis	1 test = 1 fiber	1 test = 1 fiber	1 test = all fibers

Visual Fault Locator

Feature	FFL-050
Locate sharp bends, breaks, and damages in fiber	■
Conduct end-to-end continuity tests	■
1 mW laser for single-mode and multimode applications	■



Contact Us **+1 844 GO VIAVI**
(+1 844 468 4284)

To reach the VIAVI office nearest you,
visit viasolutions.com/contacts.

© 2017 VIAVI Solutions Inc.
Product specifications and descriptions in this document are subject to change without notice.
enterprise-lc-net-tm-ae
30168203 908 0817

viasolutions.com