

Commercial Industrial Products



Manufacturing Capabilities

UL Types Available

TC	600 Volt Tray, Instrumentation Cable
MC	600 Volt Aluminum/Galvanized Steel Interlocked Armor Control and Instrumentation Cable
VFD	UL 2277 1KV Flexible Motor Lead Wire
PLTC, ITC	300 Volt Power Limited Tray Cable, Instrumentation Cable
Direct Burial	Direct Burial Rated
CSA / C (UL)	Cables are dual listed with Canadian Standards
Quad Rated	Cables Listed TC-ER, PLTC, NPLF, FPL
Sunlight Resistant	300V and 600V TC are UL Listed Sun Res
Limited Smoke	UL 1685 LS Rated
VW-1 Rated	UL 1581
ICEA-T-29-520	210,000 BTU/HR Flame Test, FT4, IEEE 1202
ER	Exposed Run
NFPA 130	

Product Types Available

Tray Cables 300V PLTC / 600V TC Rated, Control, Instrumentation, Power

PVC/PVC	HalGuard LSZH
PVC/Nylon	Thermoset Constructions
XLPE/PVC	XL-CPE
XLPE/CPE	XL-LSZH HalGuard <i>Plus</i>
TPE/TPE	
FEP/FEP	

Stocking programs

VFD
VNTC 600V Instrumentation

Utility Substation Cables 600V/1KV/2KV

20/10 - 30/15 Control Cable	HalGuard LSZH
XLPE/PVC	Thermoset Constructions
XLPE/CPE	XL-CPE
	XL-LSZH HalGuard <i>Plus</i>

Portable Cords

SE00W	ST00W
SJE00W	SJT00W

Specialty

VFD Cable
Teck 90 (HL)
IMSA Cable
Flexing Cables
XLPE-SIS VW-1, XHHW-2, RHH/RHW-2, USE-2
Thermocouple Extension Cable
Shipboard Cables
Type X Shipboard VFD
UL 1309
IEEE 1580 (IEEE45)
Profibus/Devicenet

Construction Specifications:

Gauge Size: 20AWG - 4/0 | Conductors: 2 - 50 conductors | Maximum OD Size: 2.1" | 1- 50 pairs

Shield Types:

Aluminum Mylar Shield | Braided Shield | Helically Applied Copper Tape Shield | Corrugated Copper Tape Shield

Armor Types:

Aluminum Interlock | Galvanized Steel Interlock | Aluminum Braid | Bronze Braid

Custom Capabilities:

Color Jackets | Custom Color Codes | Composite Cables | Extruded Stripes