

MORE+ WIRE AND CABLE: YOUR COMPLETE SOLUTION

Throughout the years, Liberty AV Solutions has served the AV industry by supporting the varying needs of integrators throughout the globe with an extensive offering of wire, cable, electronics, devices, custom products and managed-service offerings. Liberty's complete line of products and services enables integrators to offer total solutions by consolidating POs and efficiently kitting consumables for a streamlined deployment.

SERVICE AND SUPPORT: EVERY STEP OF THE WAY

The AV integration community has come to trust Liberty AV Solutions' knowledgeable service and support that begins before the project is quoted, through ordering, and beyond the installation. Every Liberty AV product is backed by industry-leading customer service, real technical support and a solid Liberty Edge Warranty.

Anixter Part Number	Liberty Part Number	Description
Conference Camera		
10103910	DL-WFH-CAM120	Webcam, Full HD @ 30fps, 120° Field of View, USB 2.0, Cable Included, Integrated Mic
10141549	DL-USB-PTZ10-W	Webcam, Full HD @30fps, 10X USB 2.0 PTZ, White. Includes Camera Wall Mount, IR Remote control, Control Cable, Power Supply and USB Cable
Speakerphone		
10136721	DL-USB-360SPKMIC	USB 2.0 Omnidirectional Speakerphone with a 5-8 meter pickup range with 360 ° sensitivity. 3-meter long attached USB-A cable
10115053	DL-USB-360MIC	USB 2.0 360° Omnidirectional Speakerphone, 4-meter pickup range, 5-meter long USB included, 1x Micro-USB port or 1x 3.5 mmj jack for connectivity
USB Extension		
10141618	INT-USB2-50C	USB 2.0 High speed extension with Isochronous data support up to 50m client side with 2 port USB-A hub
10141620	INT-USB2-50H	USB 2.0 High speed extension with Isochronous data support up to 50m - local only
10086749	INT-USB3.1CX	USB 3.1 100m extender set over category 6A / 7 backward compatible to 3.0, 2.0, 1.1 w/ 4 port hub on client side for multiple connected peripherals
10085869	DIGI-USB2	USB 2.0 High speed 1-Port 100m category 5e/6/6a/7 Extender Set with type B on Host and Type A on client w/ isochronous data support
10086587	DL-USB3.0	USB 3.0 DigitalLinx 15m Active Extension Cable. Powered through USB on-cable dongle for devices drawing > 2.5W, Locking USB 3.0 port per AIA USB3 Vision spec

Anixter Part Number	Liberty Part Number	Description
HDMI Extension		
10086537	DL-HDE100-H2	4K60 4:4:4 / HDR 18G 100m HDMI extender set with IR, RS232, ethernet pass through, 2-way flexible PoC
10086529	DL-HD50C	1080P HDMI extender set with IR over single category 5e/6a cable and HDMI loop out up to 70m
10086532	DL-HD70LSIR	4K60 4:2:0 10.2G 70m HDMI HDBaseT Extension set with IR and flexible 2-way PoC
Adapter Ring		
10016452	DL-AR	Universal HDMI Adapter Ring with 5 adapters, Micro HDMI "D" Male to HDMI "A" Female, DisplayPort Male to HDMI Female, Mini DisplayPort Male to HDMI Female for Thunderbolt, DVI Digital male to HDMI Female)
10085965	DL-AR2	HDMI Adapter Ring with Micro HDMI 'D' to HDMI 'A' Female, DisplayPort to HDMI Female, Mini HDMI 'C' Male to HDMI 'A' Female, Mini DisplayPort Male to HDMI Female for Thunderbolt
10086515	DL-ARDA	Apple-certified adapters - Lightning and Thunderbolt 3 (USB-C), Plus DisplayPort, Mini-DisplayPort, USB-C on 5" cables
10086514	DL-ARD	Universal Adapter with DisplayPort, Mini-Displayport, USB-C
10086516	DL-ARDD	Universal HDMI Adapter w/ 3 Cable Adapters
HDMI Cables		
10086592	E2-HDSEM-M-01	1M HDMI CABLE WITH ETHERNET
10086729	HDPMM03F	1M HIGH SPEED HDMI CABLE
10086596	E2-HDSEM-M-03	3M HDMI CABLE WITH ETHERNET
10086603	E2-HDSEM-M-15	15M HDMI CABLE WITH ETHERNET
10086604	E2-HDSEM-M-20	20M HDMI CABLE WITH ETHERNET
10086601	E2-HDSEM-M-10	10M HDMI CABLE WITH ETHERNET

Contact your salesperson to discuss solutions we can offer.

For more information, visit anixter.com/libertyav/emea.

About Anixter: anixter.com/aboutus/emea
Legal Statement: anixter.com/legalstatement

210069D002 © 2021 WESCO | Anixter 06/21

Anixter Inc. World Headquarters
 2301 Patriot Boulevard
 Glenview, Illinois 60026
 +1.224.521.8000

WESCO International
 225 West Station Square Drive, Suite 700
 Pittsburgh, PA 15219
 +1.412.454.2200

Anixter EMEA
 Inspired, Easthampstead Road
 Bracknell, Berkshire
 RG12 1YQ United Kingdom
 +44 (0)1344 388100