



Anixter has a broad infrastructure offering to fit your current and future data center needs.

Electrical Infrastructure

- 5–15 kV power cable (1)
- Building wire (2)
- Power whips (3)
- Low-voltage cable (4)
- Grounding and bonding (5)
- Flexible battery cable
- Innerduct and conduit
- Wire ties and labeling
- Lugs and connectors
- Bare copper

Network Infrastructure

- High-performance copper and fiber (6) cabling systems
- Racks and cabinets (7)
- Cable runway and raceway (8)
- Building entrance protection (BEP) (9)
- Wireless Ethernet (10)
- Switches and routers
- KVM solutions
- Media converters
- Power over Ethernet
- Power and asset management
- Transmission and access products
- Test equipment and tools
- Cable management
- Intelligent infrastructure management (IIM)

Security Solutions

- Access control (11)
- Asset tracking (12)
- Cabinet electronic locking (13)
- Video surveillance (14)
- Perimeter detection (15)
- Intercom, sound and paging
- Security consoles, racks and cabinets
- Video monitors

Power and Cooling Solutions

- High airflow dispersion floor tiles (16)
- Rack-mount power distribution (17)
- Uninterrupted power supplies (UPS) (18)
- Thermal management: passive, hot and cold aisle containment, in-row closed coupled and precision cooling solutions
- Network and environmental monitoring
- Power surge and transient voltage surge suppression (TVSS) protection