



Insta-reel

Reduce labour costs and the risk of injury to your employees with Insta-reel

Insta-reel is a standard wooden reel with oversized flanges attached to both sides. When chocked in place, the inner reel spins independently of the outer flanges creating a built-in payout stand for faster set up.

Insta-reels are pre-loaded with your required cable and are delivered completely assembled. After use, the empty reel is returned to Wesco Anixter, making it an eco-friendly and cost-efficient product.

By paralleling and phase taping multiple conductors on the same reel, you can reduce your labour costs and time. Additionally, pulling eyes can be installed on single-conductor cables to save time and decrease the risk of injury associated with on-site preparation.

Features and Benefits

- Can be pulled directly from the shipping cradle if desired
- Easily rolls into your pull position
- Multiple conductors can be paralleled onto the reel
- Pulling eyes can be installed on single-conductor cables
- Reduces the time and injury risk associated with locating and setting up jack stands
- Returnable, eliminating disposal costs and lessens the environmental impact of standard wooden reels
- Turns easily with independently spinning outer flanges

14ZC-Insta-1400-1120

Approx. Empty Weight – 250 kilos

Our 1400 mm high by 1120 mm wide reel is designed to handle many types of cable. It has a large barrel to allow for large minimum bending radii.

14ZC-Insta-1200-950W

Approx. Empty Weight – 150 kilos

The 1200 mm high by 950 mm wide reel for manoeuvring through standard doorways.

						14ZC-Insta-1400-1120-large(250)	14ZC-Insta-1200-950W-small(150)
Cable	Cores	Size (mm)	O/D (mm)	kg/km	B/R	Max length (m)	Max length (m)
AWA	1	50	17.5	800	110	1,173	659
AWA	1	70	20.2	940	130	880	495
AWA	1	95	22.3	1,220	140	722	406
AWA	1	120	24.2	1,490	150	613	345
AWA	1	150	27.4	1,870	170	478	269
AWA	1	185	30.0	2,290	180	399	224
AWA	1	240	32.8	2,880	200	334	NA
AWA	1	300	35.6	3,520	220	283	NA
AWA	1	400	40.5	4,500	250	219	NA
AWA	1	500	44.2	5,680	270	NA	NA
AWA	1	630	48.8	7,160	300	NA	NA
AWA	1	800	55.4	9,400	340	NA	NA
AWA	1	1,000	60.6	11,600	370	NA	NA
SWA	2	1.5	12.1	295	80	2,453	1,379
SWA	2	2.5	13.6	345	90	1,942	1,092
SWA	2	4	14.7	409	90	1,662	935
SWA	2	6	15.9	485	100	1,420	799
SWA	2	10	18	635	110	1,108	623
SWA	2	16	20.4	900	120	863	485
SWA	2	25	20.4	938	170	863	485
SWA	2	35	23.3	1,373	190	661	372
SWA	2	50	25.8	1,800	210	540	303
SWA	2	70	29.0	2,320	240	427	240
SWA	2	95	33.1	3,160	270	328	NA
SWA	2	120	36.1	3,790	290	276	NA
SWA	2	150	39.3	4,500	320	233	NA
SWA	2	185	44.7	5,820	360	NA	NA
SWA	2	240	49.0	7,220	400	NA	NA
SWA	2	300	53.5	8,710	430	NA	NA
SWA	2	400	59.0	11,100	480	NA	NA
SWA	3	1.5	12.6	330	80	2,262	1,272
SWA	3	2.5	14.1	390	90	1,806	1,016
SWA	3	4	15.3	470	100	1,534	863
SWA	3	6	16.6	570	100	1,303	733
SWA	3	10	19.5	880	120	944	531
SWA	3	16	21.6	1,070	130	770	433
SWA	3	25	26.7	1,550	170	504	283
SWA	3	35	29.4	1,940	180	415	234
SWA	3	50	28.5	2,360	230	442	249

						14ZC-Insta-1400-1120-large(250)	14ZC-Insta-1200-950W-small(150)
Cable	Cores	Size (mm)	O/D (mm)	kg/km	B/R	Max length (m)	Max length (m)
SWA	3	70	32.2	3,120	260	346	NA
SWA	3	95	37.0	4,310	300	262	NA
SWA	3	120	40.4	5,160	330	220	NA
SWA	3	150	45.5	6,610	370	NA	NA
SWA	3	185	49.8	7,920	400	NA	NA
SWA	3	240	55.1	9,930	450	NA	NA
SWA	3	300	60.2	11,970	490	NA	NA
SWA	3	400	66.6	14,770	540	NA	NA
SWA	4	1.5	13.3	380	90	2,030	1,142
SWA	4	2.5	15.0	450	90	1,596	898
SWA	4	4	16.4	560	100	1,335	751
SWA	4	6	18.7	790	120	1,027	578
SWA	4	10	21.1	1,040	130	807	454
SWA	4	16	23.4	1,300	140	656	369
SWA	4	25	28.9	1,880	180	430	242
SWA	4	35	31.9	2,350	200	353	198
SWA	4	50	32.0	2,950	260	351	NA
SWA	4	70	37.7	4,230	320	253	NA
SWA	4	95	41.7	5,390	340	207	NA
SWA	4	120	47.1	6,890	380	NA	NA
SWA	7	1.5	15.2	488	100	1,554	875
SWA	12	1.5	19.4	817	120	954	537
SWA	27	1.5	26.7	1,553	170	504	283
SWA	37	1.5	29.0	1,859	180	427	240
SWA	19	1.5	22.2	1,225	140	729	410
SWA	7	2.5	17.1	685	110	1,228	691
SWA	12	2.5	22.4	910	140	716	402
SWA	19	2.5	26.6	1,500	160	508	285
SWA	27	2.5	30.7	1,928	190	381	214
SWA	37	2.5	33.8	2,360	210	314	NA



14ZC-Insta-1400-1120
Approx. Empty Weight – 250 kilos



14ZC-Insta-1200-950W
Approx. Empty Weight – 150 kilos

From immediate needs to long-term goals, discover how we can help you drive productivity and progress.



Contact your Wesco Anixter sales representative for more information.



Wesco Anixter Regional Headquarters
Inspired, Easthampstead Road
Bracknell, Berkshire RG12 1YQ
United Kingdom
+44 (0) 1344 388100

Wesco World Headquarters
225 West Station Square Drive
Suite 700
Pittsburgh, PA 15219, USA

Wesco.com/emea
211032D002 © 2024 Wesco International