

Anixter stocks 133% 35kV medium-voltage cable in our Cranbury, New Jersey, location. Some of Anixter’s medium-voltage capabilities include:

- Installed pulling eyes
- Deadbreak elbows, arresters and additional terminations available in our Dulles, Virginia, location
- MV cables can ship on our INSTA-REELS, eliminating the need for jack stands and reducing on-site labor and risk of injury
- Cut to exact circuit length to reduce scrap and deliver just-in-time
- Both ends of the cables are always capped to prevent water from propagating into the cable ends
- Paralleled and phase-taped circuit lengths available

Reduce labor costs and the risk of injury to your staff by using the INSTA-REEL by Anixter.

The INSTA-REEL consists of a standard wooden reel that has oversized flanges attached to both sides and becomes a payout stand when chocked in place. The inner reel spins independently of the outer flanges, creating a reel with a built-in payout stand. Just roll the INSTA-REEL into place, chock the flanges and start pulling your cable. Available in two sizes for 35kV Installations.

Below you can find the applicable rubber parts for the MV cable. Please contact your local Anixter sales rep for additional information.



35kV Cable			Pulling Eye	ICEA Max Load	48W INSTA-REEL	60W INSTA-REEL
Gauge	Anixter Part #	Jacket OD	Kit Part #	Pulling Tension (lbs)	Fill Rate (ft)	Fill Rate (ft)
1/0	3DZ-1011	1.43	1049364	845	841	2,433
2/0	3DZ-2021	1.47	1049365	1065	795	2,303
4/0	3DZ-4041	1.57	1049366	1690	697	2,019
350 MCM	3DZ-3501	1.78	1049367	2800	0	1,570
500 MCM	3DZ-5001	1.90	1049369	4000	0	1,378
750 MCM	3DZ-7501	2.09	1049370	6000	0	1,139

About Anixter: anixter.com/aboutus
Legal Statement: anixter.com/legalstatement

19D0551NA © 2019 Anixter Inc. · 7/19

Anixter Inc. World Headquarters
 2301 Patriot Boulevard
 Glenview, Illinois 60026
 224.521.8000

1.800.ANIXTER | anixter.com

