makita®

# REFERENCE PRODUCT CATALOG

2016-17

**FEATURED TOOLS:** 18v LXT® High Torque 1/2" Wrench Kit (XWT08M, pg. 4), 18v X2 LXT® Brushless Recipro Saw Kit (XRJ06M, pg. 5)

makitatools.com

## 15 – 9-Piece Combo Kits

### XT1500

3.0Ah BATTERY

| | |
|---|---|
| XPH01Z | 1/2" Hammer Driver-Drill |
| XAD01Z | 3/8" Angle Drill |
| XDT04Z | Impact Driver |
| XWT05Z | 1/2" Impact Wrench |
| XWT04Z | 1/2" Impact Wrench |
| XSS02Z | 6-1/2" Circular Saw |
| XRJ03Z | Recipro Saw |
| XAG01Z | 4-1/2" Cut-off/Angle Grinder |
| XRH04Z | 7/8" Rotary Hammer |
| XSF01Z | Drywall Screwdriver |
| XSC01Z | 5-3/8" Metal Cutting Saw |
| DUB182Z | Blower |
| DML184 | Fluorescent/Incandescent Flashlight |
| DML185 | Xenon Flashlight |
| XRM02W | Compact Jobsite Radio |
| BL1830 | (4) 18v LXT® Lithium-Ion 3.0Ah Battery |
| DC18RC | (2) Rapid Optimum Charger |

### XT902

3.0Ah BATTERY

| | |
|---|---|
| XPH01Z | 1/2" Hammer Driver-Drill |
| XDT04Z | Impact Driver |
| XWT05Z | 1/2" Impact Wrench |
| XSS02Z | 6-1/2" Circular Saw |
| XRJ03Z | Recipro Saw |
| XRH04Z | 7/8" Rotary Hammer |
| XAG01Z | 4-1/2" Cut-off/Angle Grinder |
| DML185 | Xenon Flashlight |
| XRM02W | Compact Job Site Radio |
| BL1830 | (2) 18v LXT® Lithium-Ion 3.0Ah Battery |
| DC18RC | Rapid Optimum Charger |

## 7 – 4-Piece Combo Kits

### XT702

3.0Ah BATTERY

| | |
|---|---|
| XPH01Z | 1/2" Hammer Driver-Drill |
| XDT04Z | Impact Driver |
| XSS02Z | 6-1/2" Circular Saw |
| XRJ03Z | Recipro Saw |
| XAG01Z | 4-1/2" Cut-off/Angle Grinder |
| DML185 | Xenon Flashlight |
| XRM02W | Compact Jobsite Radio |
| BL1830 | (2) 18v LXT® Lithium-Ion 3.0Ah Battery |
| DC18RC | Rapid Optimum Charger |

### XT601

3.0Ah BATTERY

| | |
|---|---|
| XPH01Z | 1/2" Hammer Driver-Drill |
| XDT04Z | Impact Driver |
| XSS02Z | 6-1/2" Circular Saw |
| XRJ03Z | Recipro Saw |
| XAG01Z | 4-1/2" Cut-off/Angle Grinder |
| DML185 | Xenon Flashlight |
| BL1830 | (2) 18v LXT® Lithium-Ion 3.0Ah Battery |
| DC18RC | Rapid Optimum Charger |

### XT444MR

LXT BRUSHLESS

2.0Ah BATTERY 4.0Ah BATTERY

| | |
|---|---|
| XPH06Z | Brushless Hammer Driver-Drill |
| XDT08Z | Brushless Impact Driver |
| XRJ01Z | Recipro Saw |
| DML802 | L.E.D. Flashlight |
| BL1840B | 18v LXT® Lithium-Ion 4.0Ah Battery |
| BL1820B | 18v LXT® Lithium-Ion 2.0Ah Battery |
| DC18RC | Rapid Optimum Charger |

### XT405

3.0Ah BATTERY

| | |
|---|---|
| XPH01Z | 1/2" Hammer Driver-Drill |
| XDT04Z | Impact Driver |
| XSS02Z | 6-1/2" Circular Saw |
| DML185 | Xenon Flashlight |
| BL1830 | (2) 18v LXT® Lithium-Ion 3.0Ah Battery |
| DC18RC | Rapid Optimum Charger |

### XT406

3.0Ah BATTERY

| | |
|---|---|
| XPH01Z | 1/2" Hammer Driver-Drill |
| XSS02Z | 6-1/2" Circular Saw |
| XRJ03Z | Recipro Saw |
| DML185 | Xenon Flashlight |
| BL1830 | (2) 18v LXT® Lithium-Ion 3.0Ah Battery |
| DC18RC | Rapid Optimum Charger |

### XT407

3.0Ah BATTERY

| | |
|---|---|
| XPH01Z | 1/2" Hammer Driver-Drill |
| XDT04Z | Impact Driver |
| XRJ03Z | Recipro Saw |
| DML185 | Xenon Flashlight |
| BL1830 | (2) 18v LXT® Lithium-Ion 3.0Ah Battery |
| DC18RC | Rapid Optimum Charger |

### XT439PMB

LXT BRUSHLESS LXT X2 18v 18v 36v

4.0Ah BATTERY

| | |
|---|---|
| XPH07Z | Brushless 1/2" Hammer Driver-Drill |
| XDT04Z | Impact Driver |
| XSH01Z | X2 7-1/4" Circular Saw |
| DML802 | LED Flashlight |
| BL1840B | (3) 18v LXT® Lithium-Ion 4.0Ah Battery |
| DC18RD | Dual Port Rapid Optimum Charger |

## 2-Piece Trade Combo Kits

### XT259PMB

LXT X2 18v 18v 36v LXT BRUSHLESS

4.0Ah BATTERY

| | |
|---|---|
| XPH07Z | Brushless 1/2" Hammer Driver-Drill |
| XSH01Z | X2 7-1/4" Circular Saw |
| BL1840B | (3) 18v LXT® Lithium-Ion 4.0Ah Battery |
| DC18RD | Dual Port Rapid Optimum Charger |

### XT258PMB

LXT X2 18v 18v 36v LXT

4.0Ah BATTERY

| | |
|---|---|
| XDT11Z | Impact Driver |
| XRH05Z | X2 1" Rotary Hammer |
| BL1840B | (3) 18v LXT® Lithium-Ion 4.0Ah Battery |
| DC18RD | Dual Port Rapid Optimum Charger |

### XT255MB

LXT LXT BRUSHLESS

4.0Ah BATTERY

| | |
|---|---|
| XSF03Z | Brushless Drywall Screwdriver |
| XOC01Z | Cut-Out Tool |
| BL1840B | (2) 18v LXT® Lithium-Ion 4.0Ah Battery |
| DC18RC | Rapid Optimum Charger |

### XT256MB

LXT LXT BRUSHLESS

4.0Ah BATTERY

| | |
|---|---|
| XDT04Z | Impact Driver |
| XSF03Z | Brushless Drywall Screwdriver |
| BL1840B | (2) 18v LXT® Lithium-Ion 4.0Ah Battery |
| DC18RC | Rapid Optimum Charger |

## 2-3 Piece Combo Kits

LXT BRUSHLESS

**NEW XT268T** 5.0Ah BATTERY

XPH07Z Brushless 1/2" Hammer Driver-Drill
XDT14Z Brushless 3-Speed Impact Driver
BL1850B (2) 18v LXT® Lithium-Ion 5.0Ah Battery
DC18RC Rapid Optimum Charger

LXT BRUSHLESS

**NEW XT268M** 4.0Ah BATTERY

XPH07Z Brushless 1/2" Hammer Driver-Drill
XDT14Z Brushless 3-Speed Impact Driver
BL1840B (2) 18v LXT® Lithium-Ion 4.0Ah Battery
DC18RC Rapid Optimum Charger

LXT BRUSHLESS

**NEW XT267T** 5.0Ah BATTERY

XPH07Z Brushless 1/2" Hammer Driver-Drill
XDT13Z Brushless Impact Driver
BL1850B (2) 18v LXT® Lithium-Ion 5.0Ah Battery
DC18RC Rapid Optimum Charger

LXT BRUSHLESS

**NEW XT267M** 4.0Ah BATTERY

XPH07Z Brushless 1/2" Hammer Driver-Drill
XDT13Z Brushless Impact Driver
BL1840B (2) 18v LXT® Lithium-Ion 4.0Ah Battery
DC18RC Rapid Optimum Charger

LXT COMPACT BRUSHLESS

**NEW XT269M** 4.0Ah BATTERY

XPH12Z Brushless 1/2" Hammer Driver-Drill
XDT13Z Brushless Impact Driver
BL1840B (2) 18v LXT® Lithium-Ion 4.0Ah Battery
DC18RC Rapid Optimum Charger

LXT COMPACT BRUSHLESS

**NEW XT269R** 2.0Ah BATTERY

XPH12Z Brushless 1/2" Hammer Driver-Drill
XDT13Z Brushless Impact Driver
BL1820B (2)18v Compact Lithium-Ion 2.0Ah Battery
DC18RC Rapid Optimum Charger

LXT

**XT218MB** 4.0Ah BATTERY

XPH03Z 1/2" Hammer Driver Drill
XDT04Z Impact Driver
BL1840B (2) 18v LXT® Lithium-Ion 4.0Ah Battery
DC18RC Rapid Optimum Charger

LXT

**NEW XT261M** 4.0Ah BATTERY

XPH10Z 1/2" Hammer Driver-Drill
XDT11Z Impact Driver
BL1840B (2) 18v LXT® Lithium-Ion 4.0Ah Battery
DC18RC Rapid Optimum Charger

LXT COMPACT

**CT320R** 2.0Ah BATTERY

XFD10R 1/2" Driver-Drill
XDT11R Impact Driver
DML185W Flashlight
BL1820B (2)18v Compact Lithium-Ion 2.0Ah Battery
DC18RC Rapid Optimum Charger

LXT COMPACT

**NEW CT225R** 2.0Ah BATTERY

XFD10Z 1/2" Driver-Drill
XDT11Z Impact Driver
BL1820B (2)18v Compact Lithium-Ion 2.0Ah Battery
DC18RC Rapid Optimum Charger

## NEW CLASS

## LXT® SUB-COMPACT BRUSHLESS

**MOST COMPACT**
**LIGHTEST WEIGHT**
**18v COMPATABILITY**

**NEW CX200RB** 2.0Ah BATTERY

XFD11ZB Brushless 1/2" Driver-Drill
XDT15ZB Brushless Impact Driver
BL1820B (2)18v Compact Lithium-Ion 2.0Ah Battery
DC18RC Rapid Optimum Charger

## Hammer Driver-Drills

| | XPH07TB | XPH07MB | XPH03MB | XPH12M NEW | XPH12R NEW |
|---|---|---|---|---|---|
| | XPH07Z | XPH07Z | XPH03Z | XPH12Z | XPH12Z |
| | LXT BRUSHLESS **18v LXT® Brushless 1/2" Hammer Driver-Drill Kit** Delivers Up To 50% More Power | LXT BRUSHLESS **18v LXT® Brushless 1/2" Hammer Driver-Drill Kit** Delivers Up To 50% More Power | LXT **18v LXT® 1/2" Driver-Drill Kit** Makita-built 4-pole motor delivers a full 750 in.lbs. of max torque | LXT BRUSHLESS **18v LXT® 1/2" Brushless Hammer Driver-Drill Kit** All metal gear housing | LXT BRUSHLESS **18v LXT® 1/2" Brushless Hammer Driver-Drill Kit** All metal gear housing |
| Capacities (steel, wood, masonry) | 1/2", 3", 5/8" | 1/2", 3", 5/8" | 1/2", 3", (–) | 1/2", 1-1/2", 1/2" | 1/2", 1-1/2", 1/2" |
| No Load Speed (var. 2 spd) | 0-550 / 0-2,100 RPM | 0-550 / 0-2,100 RPM | 0-400 / 0-2,000 RPM | 0 - 500 / 0 - 2,000 RPM | 0 - 500 / 0 - 2,000 RPM |
| Maximum Torque (in.lbs./N•m) | 1,090 in.lbs./125N•m | 1,090 in.lbs./125N•m | 750 in.lbs. / 84 N•m | 530 in.lbs./45N•m | 530 in.lbs./45N•m |
| Battery | 18v LXT® Lithium-Ion (5.0Ah) | 18v LXT® Lithium-Ion (4.0Ah) | 18v LXT® Lithium-Ion (4.0Ah) | 18v LXT® Lithium-Ion (4.0Ah) | 18v LXT® Lithium-Ion (2.0Ah) |
| Net Weight (w/battery) | 5.9 lbs. | 5.9 lbs. | 5.1 lbs. | 4.2 lbs. | 3.6 lbs. |

## Hammer Driver-Drills/ Driver-Drills

| | XPH10R NEW | XFD07MB | XFD03 | XFD01 | XFD10R NEW |
|---|---|---|---|---|---|
| | XPH10Z | XFD07Z | XFD03Z | XFD01Z | XFD10Z |
| | LXT COMPACT **18v LXT® 1/2" Hammer Driver-Drill Kit** More Compact and 26% More RPM | LXT BRUSHLESS **18v LXT® Brushless 1/2" Driver-Drill Kit** 1,090 in.lbs. of Max Torque | LXT **18v LXT® 1/2" Driver-Drill Kit** 750 in.lbs. of Max Torque in a Compact Design | LXT **18v LXT® 1/2" Driver-Drill Kit** 480 in.lbs. of Max Torque in a Compact Design | LXT COMPACT **18v LXT® Compact 1/2" Driver-Drill Kit** Improved Preformance |
| Capacities (steel, wood, masonry) | 1/2", 1-1/2", 1/2" | 1/2", 3",(–) | 1/2", 3",(–) | 1/2", 1/2",(–) | 1/2", 1-1/2", 1/2" |
| No Load Speed | 0-600 / 0-1,900 RPM | 0-550 / 0-2,100 RPM | 0-400 / 0-2,000 RPM | 0-400, 0-1,500 RPM | 0-600 / 0-1,900 RPM |
| Maximum Torque | 480 in.lbs./54N•m | 1,090 in.lbs. / 125 N•m | 750 in.lbs. / 84 N•m | 480 in.lbs. / 54 N•m | 480 in.lbs./54N•m |
| Battery | 18v LXT® Lithium-Ion (2.0Ah) | 18v LXT® Lithium-Ion (4.0Ah) | 18v LXT® Lithium-Ion (3.0Ah) | 18v LXT® Lithium-Ion (3.0Ah) | 18v LXT® Compact Lithium-Ion (2.0Ah) |
| Net Weight (w/battery) | 3.4 lbs. | 5.9 lbs. | 5 lbs. | 3.3 lbs. | 5.9 lbs. |

## Driver-Drills

| | XFD11ZB NEW | XAD02 | XAD01 |
|---|---|---|---|
| | Tool only, battery & charger not included | XAD02Z | XAD01Z |
| | LXT SUB-COMPACT BRUSHLESS **18v LXT® Sub-Compact Brushless 1/2" Driver-Drill** Most Compact, Lightest Weight and 18v Compatability | LXT **18v LXT® 3/8" Angle Drill Kit** Close Quarters Drilling and Driving | LXT **18v LXT® 3/8" Angle Drill Kit** Close Quarters Drilling & Driving |
| Capacities (steel, wood) | 1/2", 1-7/16" | 3/8", 1" | 3/8", 1" |
| No Load Speed | 0 - 500 / 0 - 1,700 RPM | 0-1,800 RPM | 0-1,800 RPM |
| Maximum Torque | 350 in.lbs./40N•m | 121 in.lbs. / 14 N•m | 121 in.lbs. / 14 N•m |
| Battery | No Battery Included | 18v LXT® Lithium-Ion (3.0Ah) | 18v LXT® Lithium-Ion (3.0Ah) |
| Net Weight (w/battery) | 2.6 lbs. | 4.0 lbs. | 4.0 lbs. |

## Impact Drivers

| | XDT12M NEW |
|---|---|
| | XDT12Z |
| | LXT BRUSHLESS **18v LXT® Brushless 4-Speed Impact Driver Kit** Industry-Leading Performance |
| Drive | 1/4" (hex) |
| No Load Speed | 0-1,100/0-2,100/0-3,200/0-3,600 RPM |
| Maximum Torque | 1,550 in.lbs./175N•m |
| Battery | 18v LXT® Lithium-Ion (4.0Ah) |
| Net Weight (w/battery) | 3.3 lbs. |

## Impact Drivers

| | XDT14M NEW | XDT13M NEW | XDT11R NEW | XPT03 | XDT15ZB NEW |
|---|---|---|---|---|---|
| | XDT14Z XDT14R (w/2.0Ah Battery) | XDT13Z XDT13R (w/2.0Ah Battery) | XDT11Z | XPT03Z | Tool only, battery & charger not included |
| | LXT BRUSHLESS **18v LXT® Brushless 3-Speed Impact Driver Kit** High Speed in a More Compact Size | LXT BRUSHLESS **18v LXT® Brushless Impact Driver Kit** Brushless Motor Delivers 3,400 RPM | LXT COMPACT **18v LXT® Compact Impact Driver Kit** Makita 4-Pole Motor with 4-Brush Design Delivers 26% More RPM | LXT **18v LXT® Hybrid™ Impact Driver Kit** 4 Tools in 1 | LXT SUB-COMPACT BRUSHLESS **18v LXT® Sub-Compact Brushless Impact Driver** Assist Mode helps eliminate "screw cam-out" and "cross threading" |
| Drive | 1/4" (hex) | 1/4" (hex) | 1/4" (hex) | 1/4"(hex) | 1/4"(hex) |
| No Load Speed | 0 - 1,100 / 0 - 2,100 / 0 - 3,600 RPM | 0 - 3,400 RPM | 0-2,900 RPM | 0-700 / 0-2,300 RPM | 0 - 1,300 / 0 - 3,000 RPM |
| Maximum Torque | 1,550 in.lbs./175N•m | 1,500 in.lbs./170N•m | 1,460 in.lbs./165N•m | 1,240 in.lbs./140N•m | 1,240 in.lbs./140N•m |
| Battery | 18v LXT® Lithium-Ion (4.0Ah) | 18v LXT® Lithium-Ion (4.0Ah) | 18v LXT® Compact Lithium-Ion (2.0Ah) | 18v LXT® Lithium-Ion (3.0Ah) | No Battery Included |
| Net Weight (w/battery) | 3.3 lbs. | 3.3 lbs. | 2.8 lbs. | 4.1 lbs. | 2.6 lbs. |

## Impact Drivers

| | XST01M NEW | XLT01 |
|---|---|---|
| | XST01Z | XLT01Z |
| | LXT BRUSHLESS OIL IMPULSE **18v LXT® Brushless 3-Sp. Oil-Impulse Impact Driver Kit** Up to 30% Lower Noise In Low | LXT **18v LXT® Angle Impact Driver Kit** Ideal for Fastening in Close Quarters |
| Drive | 1/4"(hex) | 1/4" (hex) |
| No Load Speed | 0-3,200/0-2,000/0-1,200 RPM (3-Sp.) | 0-3,000 RPM |
| Maximum Torque | 1,240 in.lbs./140N•m | 530 in.lbs./60N•m |
| Battery | 18v LXT® Lithium-Ion (3.0Ah) | 18v LXT® Lithium-Ion (3.0Ah) |
| Net Weight (w/battery) | 4.1 lbs. | 3.9 lbs. |

## Impact Wrenches

| | XWT07M NEW | XWT08M NEW |
|---|---|---|
| | XWT07Z | XWT08Z |
| | LXT BRUSHLESS **18v LXT® Brushless High Torque 3/4" 3-Sp. Impact Wrench Kit** Delivers 1250 ft.lbs. of break away torque | LXT BRUSHLESS **18v LXT® Brushless High Torque 1/2" 3-Sp. Impact Wrench Kit** Perfect for High Torque Fastening |
| Drive | 3/4" (square) | 1/2" (square) |
| No Load Speed | 0-900 / 0-1,000 / 0-1,800 RPM (3-Sp.) | 0-900 / 0-1,000 / 0-1,800 RPM (3-Sp.) |
| Maximum Torque | 780 ft.lbs./1,057 N•m | 740 ft.lbs./1,003 N•m |
| Battery | 18v LXT® Lithium-Ion (4.0Ah) | 18v LXT® Lithium-Ion (4.0Ah) |
| Net Weight (w/battery) | 8.1 lbs. | 7.9 lbs. |

## Impact Wrenches

| | XWT04MB | XWT09T NEW | XWT01 | XWT02MB | XWT05 |
|---|---|---|---|---|---|
| | XWT04Z | XWT09Z | XWT01Z | XWT02Z | XWT05Z |
| | LXT **18v LXT® 1/2" Impact Wrench Kit** 1/2" Sq. Drive Designed for Faster and Convenient Fastening | LXT BRUSHLESS **18v LXT® Brushless High Torque 7/16" Hex 3-Sp. Impact Drill Kit** Perfect for High Torque Drilling | LXT **18v LXT® 7/16" Impact Drill Kit** Quick Change 7/16" Hex Chuck Designed for Utility Companiess | LXT BRUSHLESS **18v LXT® Brushless 3-Sp. 1/2" Impact Wrench Kit** Improved Fastening Control | LXT **18v LXT® 1/2" Impact Wrench Kit** Great for Mechanics, Installers & Builders |
| Drive | 1/2" (square) | 7/16" (hex) | 7/16" (hex) | 1/2" (square) | 1/2" (square) |
| No Load Speed | 1,600 RPM | 0-900 / 0-1,000 / 0-1,800 RPM (3-Sp.) | 1,900 RPM | 0-1,600 / 0-2,100 / 0-2,800 RPM | 0 - 2,100 RPM |
| Maximum Torque | 325 ft.lbs./440 N•m | 590 ft.lbs. | 325 ft.lbs./440 N•m | 210 ft.lbs./280 N•m | 170 ft.lbs./230 N•m |
| Battery | 18v LXT® Lithium-Ion (4.0Ah) | 18v LXT® Lithium-Ion (5.0Ah) | 18v LXT® Lithium-Ion (3.0Ah) | 18v LXT® Lithium-Ion (4.0Ah) | 18v LXT® Lithium-Ion (3.0Ah) |
| Net Weight (w/battery) | 7.5 lbs. | 8.1 lbs. | 7.8 lbs. | 3.8 lbs. | 3.8 lbs. |

## Impact Wrenches

| | XWT06 | XLT02 |
|---|---|---|
| | XWT06Z | XLT02Z |
| | LXT **18v LXT® 3/8" Impact Wrench Kit** Perfect for Automotive Mechanics | LXT **18v LXT® 3/8" Angle Impact Wrench Kit** For Work in Tight Spaces |
| Drive | 3/8" (square) | 3/8" (square) |
| No Load Speed | 0 - 2,100 RPM | 0 - 2,000 RPM |
| Maximum Torque | 155 ft.lbs./210 N•m | 44 ft.lbs./60 N•m |
| Battery | 18v LXT® Lithium-Ion (3.0Ah) | 18v LXT® Lithium-Ion (3.0Ah) |
| Net Weight (w/battery) | 3.4 lbs. | 3.3 lbs. |

## Recipro Saws

| | XRJ06M | XRJ05M |
|---|---|---|
| | XRJ06Z | XRJ05Z |
| | LXT X2 BRUSHLESS **18v X2 LXT® (36v) Brushless Recipro Saw Kit** Two 18V LXT® Batteries (36V) Deliver the Power of a Corded Recipro Saw | LXT BRUSHLESS **18v LXT® Brushless Recipro Saw Kit** BL™ Brushless Motor Runs Cooler and More Efficiently |
| Length of Stroke | 1-1/4" | 1-1/4" |
| Strokes Per Minute | 0-2,300 / 0 -3,000 SPM | 0-2,300 / 0 -3,000 SPM |
| Length | 17-3/4" | 17-1/4" |
| Battery | 2X 18v LXT® Lithium-Ion (4.0Ah) | 18v LXT® Lithium-Ion (4.0Ah) |
| Net Weight (w/battery) | 10.2 lbs. | 8.2 lbs. |

## Recipro Saws

| | XRJ04M | XRJ01 |
|---|---|---|
| | XRJ04 Z | XRJ01Z |
| | LXT **18v LXT® Recipro Saw Kit** Faster Cutting Speed | LXT **18v LXT® Compact Recipro Saw Kit** Compact for Close Quarter Cutting |
| Length of Stroke | 1-1/4" | 1/2" |
| Strokes Per Minute | 0-2,800 SPM | 0-3,000 SPM |
| Length | 19-1/8" | 15-5/8" |
| Battery | 18v LXT® Lithium-Ion (4.0Ah) | 18v LXT® Lithium-Ion (3.0Ah) |
| Net Weight (w/battery) | 8.3 lbs. | 3.9 lbs. |

## Saws

| | XSH01X | XSH03MB |
|---|---|---|
| | XSH01Z | XSH03Z |
| | LXT X2 36V **18v X2 LXT® (36v) 7-1/4" Circular Saw Kit** Two 18v LXT® Batteries Deliver the Cutting Performance of a Corded Saw | LXT BRUSHLESS AUTOMATIC SPEED CHANGE **18V LXT® Brushless 6-1/2" Circular Saw Kit** BL™ Motor Delivers 5,000 RPM |
| Blade Diameter | 7-1/4" | 6-1/2" |
| Arbor | 5/8" | 5/8" |
| No Load Speed | 4,800 RPM | 5,000 RPM |
| Battery | 2X 18v LXT® Lithium-Ion (3.0Ah) | 18v LXT® Lithium-Ion (4.0Ah) |
| Net Weight (w/battery) | 10.1 lbs. | 7.3 lbs. |

## Saws

| | XSS01 | XSS02Z | XSS03 |
|---|---|---|---|
| | XSS01Z | Tool only, battery & charger not included | XSS03Z |
| | LXT **18v LXT® 6-1/2" Circular Saw Kit** Cuts 2X Material at 45° | LXT **18v LXT® 6-1/2" Circular Saw** 2-1/4" Maximum Cutting Capacity | LXT **18v LXT® 5-3/8" Circular Trim Saw Kit** Weighs Only 6.0 lbs. |
| Blade Diameter | 6-1/2" | 6-1/2" | 5-3/8" |
| Arbor | 5/8" | 5/8" | 5/8" |
| No Load Speed | 3,700 RPM | 3,700 RPM | 3,600 RPM |
| Battery | 18v LXT® Lithium-Ion (3.0Ah) | No Battery Included | 18v LXT® Lithium-Ion (3.0Ah) |
| Net Weight (w/battery) | 7.6 lbs. | 7.3 lbs. | 6.0 lbs. |

## Jig Saws

| | XVJ02Z |
|---|---|
| | Tool only, battery & charger not included |
| | LXT BRUSHLESS **18v LXT® Brushless Jig Saw** Up To 45% Faster Cutting |
| Length of Stroke | 1" |
| Strokes Per Minute | 800 - 3,500 SPM |
| Blade Shank | "T" Tang |
| Battery | No battery Included |
| Net Weight (w/battery) | 5.8 lbs. |

## Jig Saws

| | XVJ03 |
|---|---|
| | XVJ03Z |
| | LXT **18v LXT® Jig Saw Kit** Custom Cutting Without a Cord |
| Length of Stroke | 1" |
| Strokes Per Minute | 0 - 2,600 SPM |
| Blade Shank | "T" Tang |
| Battery | 18v LXT® Lithium-Ion (3.0Ah) |
| Net Weight (w/battery) | 14.7 lbs. |

## Adhesive Guns

| | XGC011 | XGC011B | XGC01M1C NEW |
|---|---|---|---|
| | XGC01Z | XGC01ZB | XGC01ZC |
| | LXT **18v LXT® 10 oz. Caulk/Adhesive Gun Kit** Delivers an Industry-Leading 1,100 lbs. of Dispensing Force | LXT **18v LXT® 20 oz. Caulk Gun Kit** Delivers up to 2.5X More Dispensing Speed | LXT **18v LXT® 29 oz. Caulk and Adhesive Gun Kit** Delivers 1,100 lbs. of Dispensing Force |
| Capacity | 10 oz. | 20 oz. | 29 oz. |
| Dispense Force | 1,100 lbs. | 1,100 lbs. | 1,100 lbs. |
| Inches Per Minute | 0 - 66 IPM | 0 - 66 IPM | 0 - 66 IPM |
| Battery | 18v LXT® Lithium-Ion (3.0Ah) | 18v LXT® Lithium-Ion (3.0Ah) | 18v LXT® Lithium-Ion (4.0Ah) |
| Net Weight (w/battery) | 5.1 lbs. | 6 lbs. | 5.9 lbs. |

## Rotary Hammers

| | HRH01 | XRH05Z | XRH011X | XRH01Z | XRH04 |
|---|---|---|---|---|---|
| | Tool only, battery & charger not included | | XRH01ZVX DX01 | Tool only, battery & charger not included | XRH04Z |
| | 36v LXT® 1" Rotary Hammer Kit<br>Corded Speed & Power Without the Cord | 18v X2 LXT® 1" Rotary Hammer<br>18 Volt Solution for Corded Power Demands | 18v LXT® Brushless 1" Rotary Hammer Kit<br>Built-on HEPA Vacuum | 18v LXT® Brushless 1" Rotary Hammer<br>Efficient BL™ Brushless Motor | 18v LXT® 7/8" Rotary Hammer Kit<br>Compact D-Handle Grip Design |
| No Load Speed | 0 - 1,200 RPM | 0 - 1,250 RPM | 0 - 4,700 RPM | 0 - 950 RPM | 0 - 1,100 RPM |
| Blows Per Minute | 0 - 4,800 BPM | 0 - 5,000 BPM | 0 - 4,700 BPM | 0 - 4,700 BPM | 0 - 4,000 BPM |
| Impact Energy | 2.2 ft.lbs. | 2.2 ft.lbs. | 1.7 ft.lbs. | 1.7 ft.lbs. | 1.4 ft.lbs. |
| Battery | 36v LXT® Lithium-Ion (2.6Ah) | No Battery Included | 18v LXT® Lithium-Ion (3.0Ah) | No Battery Included | 18v LXT® Lithium-Ion (3.0Ah) |
| Net Weight ( w/battery) | 7.7 lbs. | 9.3 lbs. | 10.2 lbs. | 7.2 lbs. | 7.7 lbs. |

## Rotary Hammer

| | XRH03 |
|---|---|
| | XRH03Z |
| | 18v LXT® 7/8" Rotary Hammer Kit<br>Erganomic Handle Design |
| No Load Speed | 0 - 1,100 RPM |
| Blows Per Minute | 0 - 4,000 BPM |
| Impact Energy | 1.4 ft.lbs. |
| Battery | 18v LXT® Lithium-Ion (3.0Ah) |
| Net Weight (w/battery) | 7.7 lbs. |

## Concrete Vibrators and Rebar Cutter

| | XRV01 | XRV02 | XCS01Z |
|---|---|---|---|
| | XRV01Z | XRV02Z | |
| | 18v LXT® 4' Concrete Vibrator Kit<br>Only 7.7 lbs. for Comfortable Operation | 18v LXT® 8' Concrete Vibrator Kit<br>Dual Switch for Operation in Any Orientation | 18v LXT® Rebar Cutter<br>Up To 75 Cuts Of #6 3/4" Rebar with A 3.0Ah LXT Battery; 4000 Per Blade |
| No Load Vibrations/Min | 13,000 | 12,500 | Capacity: 1/8"- 3/4" |
| Vibrator Diameter | 1" | 1" | 4,000 Cuts Per Blade |
| Length | 58-1/2" | 105-1/2" | 16-1/2" |
| Battery | 18v LXT® Lithium-Ion (3.0Ah) | 18v LXT® Lithium-Ion (3.0Ah) | No Battery Included |
| Net Weight (w/battery) | 7.7 lbs. | 11.4 lbs. | 24.3 lbs. |

## Woodworking

| | XSL02Z | XSL01 NEW | X0B01 | XPK01 | XJP03Z |
|---|---|---|---|---|---|
| | | XSL01Z | X0B01Z | XPK01Z | |
| | 18v X2 LXT® Brushless 7-1/2" Compound Miter Saw<br>Powerful BL™ Motor delivers 5,700 RPM for Faster Cutting | 18v LXT® 7-1/2" Compound Miter Saw Kit<br>Cutting Capacity up to 2-1/16"and 11-3/4" Crosscuts at 90° | 18v LXT® 5" Random Orbit Sander Kit<br>Corded Performance without the Cord | 18v LXT® 3-1/4" Planer Kit<br>Planes Up to 3-1/4" Wide and 5/64" Deep in a Single Pass | 18v LXT® Plate Joiner<br>Delivers up to 300 Cuts for #0 Biscuits on a Single Charge |
| Blade Diameter | 7-1/2" | 7-1/2" | Pad Size (round): 4-7/8" | Planing Width: 3-1/4" | Blade Diameter: 4" |
| Capacity (90° Miter) | 2-1/16"x11-3/4" | 2-1/16"x11-3/4" | Abrasive Disc Size: 5" | Planing Depth: 5/64" | Cutting Capacity (depth): 3/4" |
| No Load Speed | 5,700 RPM | 2,200 RPM | Battery: 18v LXT® Lithium-Ion (3.0Ah) | Battery: 18v LXT® Lithium-Ion (3.0Ah) | No Battery Included |
| Battery | No Battery Included | 18v LXT® Lithium-Ion (3.0Ah) | Orbit Diameter: 1/8" | No Load Speed: 14,000 RPM | No Load Speed: 6,500 RPM |
| Net Weight (w/battery) | 28.9 lbs. | 27.3 lbs. | Net Weight (w/battery): 3.6 lbs. | Net Weight (w/battery): 7.4 lbs. | Net Weight (w/battery): 6.7 lbs. |

## Multi-Tool

| | XMT035 |
|---|---|
| | XMT035Z |
| | 18v LXT® Multi-Tool Kit<br>"Tool-less" Clamp System for Fast Accessory Installation |
| Oscillations Per Minute | 6,000 - 20,000 OPM |
| Oscillation Angle | 3.2° |
| Battery | 18v LXT® Lithium-Ion (3.0Ah) |
| Overall Length | 13-3/8" |
| Net Weight (w/battery) | 4.9 lbs. |

## Nailers

| | XTS01 | XTP01Z NEW | XNB01Z NEW |
|---|---|---|---|
| | XTS01Z | Tool only, battery & charger not included | Tool only, battery & charger not included |
| | 18v LXT® 3/8" Crown Stapler Kit<br>Contact Actuation for Production Environments | 18v LXT® Pin Nailer, 23 Ga.<br>Drives up to 3,000 Nails using 3.0Ah 18v LXT Battery BL1830 | 18v LXT® 2" Brad Nailer, 18 Ga.<br>Drives 1000 Nails using 3.0Ah LXT Battery BL1830 |
| Capacity | 98 Staples | 130 Pin Nails | 110 Brads |
| Leg Length | 1/4" to 7/8" | 11/16" - 1 3-8" | 5/8" to 2" (18 ga.) |
| Overall Length | 9-7/8" | 9-3/4" | 11-5/8" |
| Battery | 18v LXT® Lithium-Ion (3.0Ah) | No Battery Included | No Battery Included |
| Net Weight | 5.3 lbs. | 4.6 lbs. | 7.7 lbs. |

## Fastening

| | XSF03MB | XRF02 NEW | XRF01 |
|---|---|---|---|
| | XSF03Z | XRF02Z Screws not included | XRF01Z Screws not included |
| | 18v LXT® Brushless Drywall Screwdriver Kit<br>Drives 1,860 Screws with Push Drive™ | 18v LXT® Autofeed Screwdriver Kit<br>Ideal for Hanging Drywall | 18v LXT® Autofeed Screwdriver Kit<br>Ideal for Decking and Sub-Floors |
| Bit Type | 1/4" Hex | 1/4" Hex | 1/4" Hex |
| No Load Speed (variable speed) | 0 - 4,000 RPM | 4,000 RPM | 4,000 RPM |
| Overall Length | 9-7/8" | 16-3/4" | 16-3/4" |
| Battery | 18v LXT® Lithium-Ion (4.0Ah) | 18v LXT® Lithium-Ion (3.0Ah) | 18v LXT® Lithium-Ion (3.0Ah) |
| Net Weight (w/battery) | 3.8 lbs. | 5.1 lbs. | 5.1 lbs. |

## Cut-Out Tool

| | XOC01MB |
|---|---|
| | XOC01Z |
| | 18v LXT® Cut-Out Tool Kit<br>Slim Body Design (2-1/4") for Comfort and Control |
| Collet Capacity | 1/8", 1/4" |
| No Load Speed | 30,000 RPM |
| Overall Length | 12-3/8" |
| Battery | 18v LXT® Lithium-Ion (4.0Ah) |
| Net Weight (w/battery) | 3.7 lbs. |

## Metalworking

| | XAG10M | XAG06MB NEW | XAG03MB | XAG01 | XDG01 |
|---|---|---|---|---|---|
| | XAG10Z | XAG06Z | XAG03Z | XAG01Z | XDG01Z |
| | LXT BRUSHLESS | LXT BRUSHLESS AUTOMATIC SPEED CHANGE | LXT BRUSHLESS AUTOMATIC SPEED CHANGE | LXT | LXT |
| | **18v LXT® Brushless 4-1/2" Cut-Off/Angle Grinder Kit** Electric Brake and Paddle Switch | **18v LXT® Brushless 4-1/2" Cut-Off/Angle Grinder** Large Flush-Mount Paddle Switch | **18v LXT® Brushless 4-1/2" Cut-Off/Angle Grinder Kit** Slide Switch For User Convenience | **18v LXT® 4-1/2" Cut-off/Angle Grinder Kit** Compact Barrel Grip for Easy Handling | **18v LXT® 1/4" Die Grinder Kit** Delivers 25,000 RPM for Faster Grinding |
| Grinding Wheel | 4-1/2" | 4-1/2" | 4-1/2" | 4-1/2" | Collet Capacity: 1/4" |
| No Load Speed | 8,500 RPM | 8,500 RPM | 8,500 RPM | 10,000 RPM | No Load Speed: 25,000 RPM |
| Battery | 18v LXT® Lithium-Ion (4.0Ah) | 18v LXT® Lithium-Ion (4.0Ah) | 18v LXT® Lithium-Ion (4.0Ah) | 18v LXT® Lithium-Ion (3.0Ah) | Overall Length: 15-3/4" |
| Overall Length | 14-1/4" | 14-1/4" | 14-1/4" | 12-1/2" | Battery: 18v LXT® Lithium-Ion (3.0Ah) |
| Net Weight (w/battery) | 5.6 lbs. | 5.6 lbs. | 5.5 lbs. | 5 lbs. | Net Weight (w/battery): 4.4 lbs. |

## Metalworking

| | XSC02M | XSC01MB NEW | XBP02 | XBP01 |
|---|---|---|---|---|
| | XSC02Z | XSC01Z | XBP02Z | XBP01Z |
| | LXT BRUSHLESS AUTOMATIC SPEED CHANGE | LXT | LXT | LXT |
| | **18v LXT® Brushless 5-7/8" Metal Cutting Saw Kit** Cuts 2" Conduit in a Single Pass | **18v LXT® 5-3/8" Metal Cutting Saw Kit** Cuts a Wide Range of Metal Material | **18v LXT® Portable Band Saw Kit** 4-3/4" x 4-3/4" Cutting Capacity | **18v LXT® Compact Band Saw Kit** 2-1/2" x 2-1/2" Cutting Capacity |
| Cutting Capacity | 2-1/4" | 2" | 4-3/4" x 4-3/4" | 2-1/2" x 2-1/2" |
| No Load Speed | 3,900 RPM | 3,600 RPM | 275 - 530 ft./min. | 630 - ft./min. |
| Overall Length | 13-1/8" | 13-3/4" | 20-5/8" | 18-1/2" |
| Battery | 18v LXT® Lithium-Ion (3.0Ah) | 18v LXT® Lithium-Ion (3.0Ah) | 18v LXT® Lithium-Ion (3.0Ah) | 18v LXT® Lithium-Ion (3.0Ah) |
| Net Weight (w/battery) | 6.4 lbs. | 5.7 lbs. | 14.3 lbs. | 7.5 lbs. |

**GET REGISTERED**

Register your products and keep them in one safe place, your own Tool Box. It is where you can go to obtain your tool model numbers and serial numbers in the event your tool is stolen or needs service.

makitatools.com/ **product registration**

## Metalworking

| | XSJ01 | XNJ01 |
|---|---|---|
| | XSJ01Z | XNJ01Z |
| | LXT | LXT |
| | **18v LXT® 18 Gauge Straight Shear Kit** Swivel Shear Head Rotates 360° | **18v LXT® 16 Gauge Nibbler Kit** Powerful, Versatile and Cordless |
| Cutting Capacity | Mild steel 18 ga. | 2" |
| Strokes Per Minute | 3,000 SPM | 0-1,900SPM |
| Overall Length | 13-3/4" | 18v LXT® Lithium-Ion (3.0Ah) |
| Battery | 18v LXT® Lithium-Ion (3.0Ah) | 12-3/8" |
| Net Weight (w/battery) | 5.3 lbs. | 4.8 lbs. |

## Hedge Trimmers

| | XHU04Z | XHU02Z |
|---|---|---|
| | Tool only, battery & charger not included | Tool only, battery & charger not included |
| | LXT X2 18V+18V 36V | LXT |
| | **18v X2 LXT® Hedge Trimmer** Two 18v LXT Lithium-Ion Batteries Deliver the Performance of a Trimmer | **18v LXT® Hedge Trimmer** Up to 75 Minutes of Run Time with 3.0Ah Battery on Lowest Setting |
| Blade Length | 25-1/2" | 22" |
| Strokes Per Minute | 1,800 SPM | 1,350 SPM |
| Overall Length | 48-3/4" | 38" |
| Battery | No Battery Included | No Battery Included |
| Net Weight (w/battery) | 13.3 lbs. | 7.4 lbs. |

## String Trimmers

| | XRU07Z NEW | XRU04Z | XRU08Z NEW | XRU02Z |
|---|---|---|---|---|
| | Tool only, battery & charger not included | Tool only, battery & charger not included | Tool only, battery & charger not included | Tool only, battery & charger not included |
| | LXT X2 18V+18V 36V BRUSHLESS | LXT BRUSHLESS | LXT BRUSHLESS | LXT |
| | **18v X2 LXT® (36v) Brushless String Trimmer** Zero Emissions and Reduced Maintenance; No Need for Gas or oil | **18v LXT® Brushless String Trimmer** Up to 60 Min. of Run Time with 3.0Ah Battery | **18v LXT® Brushless Curved Shaft String Trimmer** Up to 44 Minutes of Run Time Under Load | **18v LXT® String Trimmer** Up to 45 Minutes of Run Time with 3.0Ah Battery Under No Load |
| Cutting Capacity | 13-3/4" | 11-3/4" | 11-3/4" | 10-1/4" |
| No Load Speed | 5,000/6,500 RPM | 3,500/6,000 RPM | 5,000-6,000 RPM | 7,800 RPM |
| Overall Length | 69" | 72-1/2" | 64-1/2" | 10-1/4" |
| Battery | No Battery Included | No Battery Included | No Battery Included | No Battery Included |
| Net Weight (w/battery) | 9.9 lbs. | 8.6 lbs. | 7.9 lbs. | 6.9 lbs. |

LXT

See pages 11 & 26 for more information on batteries, charge times, and battery accessories

## Chain Saws

| | HCU02C1 | XCU02Z | XCU01Z |
|---|---|---|---|
| | | Tool only, battery & charger not included | Tool only, battery & charger not included |
| | 36v SYNCHRO-CUT | LXT X2 18V+18V 36V | LXT |
| | **36v LXT® Chain Saw Kit** Zero Emissions and up to 40% Quieter Than Gas | **18v X2 LXT® (36v) Chain Saw** Powered by Two 18v LXT Lithium-Ion Batteries | **18v LXT® 4-1/2" Chain Saw** The Perfect Chain Saw for Limbing, Powered by 18v LXT |
| Guide Bar Length | 12" | 12" | 4-1/2" |
| Chain Speed | 1,650 FPM | 1,650 FPM | 980 FPM |
| Overall Length | 24-5/8" | 24-5/8" | 16-5/8" |
| Battery | 36v LXT® Lithium-Ion (2.2Ah) | No Battery Included | No Battery Included |
| Net Weight (w/battery) | 10.1 lbs. | 11.2 lbs. | 5.4 lbs. |

## Grass Shear

| | XMU02Z |
|---|---|
| | Tool only, battery & charger not included |
| | LXT |
| | **18v LXT® Grass Shear** Up to 125 Minutes of Run Time with 3.0Ah battery Under No Load |
| Guide Bar Length | 6-5/16" |
| Chain Speed | 1,250 SPM |
| Overall Length | 13-7/8" |
| Battery | No Battery Included |
| Net Weight (w/battery) | 3.6 lbs. |

## Blowers & Vacuums

| | UB360DWB | XBU02Z NEW | XBU01Z | DUB182 | DCL500Z |
|---|---|---|---|---|---|
| | 36v LXT® Blower Kit<br>Delivers up to 14 Minutes of Run Time with 36v Battery Under No Load on Highest Setting | Tool only, battery & charger not included<br>18v X2 LXT® (36v) Brushless Blower<br>Up to 29 min. of Run Time | Tool only, battery & charger not included<br>18v X2 LXT® (36v) Blower<br>Makita-built Motor Produces a Maximum Air Volume of 155 CFM | DUB182Z<br>18v LXT® Blower Kit<br>179 MPH for Fast Clean-Ups | Tool only, battery & charger not included<br>18v LXT® Cyclonic Canister Vacuum<br>Long Lasting Powerful Suction |
| Max. Air Volume | 155 CFM | 473 CFM | 155 CFM | 91 CFM | **Capacity (pint):** .53 |
| Max. Air Velocity | 208 MPH | 120 MPH | 208 MPH | 179 MPH | **Overall Length:** 13-7/8" |
| No Load Speed | 0 - 10,000 / 0 - 17,000 RPM | 11,400 - 21,500 RPM | 0 - 10,000 / 0 - 17,000 RPM | 0 - 18,000 RPM | **Continuous Use:** 49 min. |
| Battery | 36v LXT® Lithium-Ion (2.2Ah) | No Battery Included | No Battery Included | 18v LXT® Lithium-Ion (3.0Ah) | No Battery Included |
| Net Weight (w/battery) | 6.8 lbs. | 9.9 lbs. | 8 lbs. | 3.7 lbs. | 9.4 lbs. |

## Vacuums & Fans

| | XCV04Z NEW | XCV05Z NEW | XLC02RB1W | DCF300Z | BCF201Z |
|---|---|---|---|---|---|
| | Tool only, battery & charger not included<br>18v X2 LXT® (36v) 2.1 Gallon HEPA Filter Dry Vacuum<br>Cordless/Corded Power Option for Versatility and Convenience | Tool only, battery & charger not included<br>18v X2 LXT® (36v) Brushless HEPA Filter Backpack Vacuum<br>Powerful Suction Power in a Light and Comfortable Design | XLC02ZW<br>18v LXT® Compact Vacuum Kit<br>Strong Suction Power for Fast Cleaning with More Run Time | Tool only, battery & charger not included<br>18v LXT® 13" Job site Fan<br>Up to 5.7 Hours of Continuous Run-Time\ on a Single BL1850 | Tool only, battery & charger not included<br>18v LXT® Job Site Fan<br>Up to 5.5 Hours of Continuous Run Time on a Single BL1850 |
| Air Flow Rate | 127 CFM | 53 CFM | **Capacity (pint):** 1.3 pint | **Voltage:** 18v | **Voltage:** 14.4-18v |
| Static Water Lift | 96" | 28.5" | **Overall Length:** 18-3/4" | **AC Adapter:** Yes | **AC Adapter:** Yes |
| Continuous Use | 65 min. | 60 min. | 15 min. | 5.7 Hours | 5.5 Hours |
| Battery | No Battery Included | No Battery Included | 18v LXT® Compact Lithium-Ion (2.0Ah) | No Battery Included | No Battery Included |
| Net Weight (with battery) | 21.8 lbs. | 9.4 lbs. | 2.7 lbs. | 10.4 lbs. | 7.1 lbs. |

## L.E.D. Lights

| | DML805 NEW | DML802 | DML801 | DML807 NEW | DML806 NEW |
|---|---|---|---|---|---|
| | Shown with optional tripod lightstand (GM00001381)<br>18v LXT® Cordless/Corded L.E.D. Flood Light<br>L.E.D. Lights Deliver Bright and Even Lighting For Large Workspaces | 18v LXT® L.E.D. Flashlight<br>Up to 21 Hours of Illumination with 5.0Ah LXT Battery | 18v LXT® 12 L.E.D. Flashlight<br>Extra Bright 12 L.E.D. Flashlight Provides 240 Lumens | 18v LXT® L.E.D. Lantern / Flashlight<br>Built-in USB Port | 18v LXT® L.E.D. Lantern / Flashlight<br>Dual Purpose; Use as a Lantern or Flashlight |
| Run Time (max in hours) | 17 | 21 | 40 | 36 | 59 |
| Lumens | 750 | 200 | 240 | 300 | 240 |
| Battery | No Battery Included | No Battery Included | No Battery Included | No Battery Included | No Battery Included |
| Overall Length | 8-3/8" | 10-3/4" | 15" | 14-1/4" | 14-3/8" |
| Net Weight (w/battery) | 6.1 lbs. | 2.1 lbs. | 2.1 lbs. | 1.36 lbs. | 2.1 lbs. |

## Lights

| | DML184 | DML185 | LXLM01 |
|---|---|---|---|
| | 18v LXT® Fluorescent/ Incandescent Flashlight<br>Two Modes: Fluorescent or Incandescent | Also Available LXT® Compact model DML185W<br>18v LXT® Xenon Flashlight<br>Up to 7.5 Hours of Illumination with 5.0Ah LXT Battery | Also Available LXT® Compact model DML186W<br>18v LXT® L.E.D. Flashlight<br>Flashlight Illuminates The Job site |
| Run Time (max in hours) | 20 | 7.5 | 82.5 |
| Lumens | 15 | 180 | 500 |
| Battery | No Battery Included | No Battery Included | No Battery Included |
| Overall Length | 17-3/4" | 11-1/8" | 5-7/8" |
| Net Weight (w/battery) | 2.2 lbs. | 2.1 lbs. | .5 lbs. |

## Power Source

| | ADP05 NEW |
|---|---|
| | 18v LXT® USB Power Source<br>Charges up to 2 USB compatible devices where AC power is not available |
| No. of USB Ports | 2 |
| Output | 2.1A / 4.2 A (with both USB Ports) |
| Battery | No Battery Included |
| Overall Length | 2.5" |
| Net Weight (w/battery) | .4 lbs. |

## Radios

| | XRM04B | XRM03 | XRM02W |
|---|---|---|---|
| | Tool only, battery & charger not included<br>18v LXT® Bluetooth® Job Site Radio<br>Bluetooth® and MP3 Compatible | Tool only, battery & charger not included<br>iPod® not included<br>18v LXT® Jobsite Radio<br>iPod® Docking Station, MP3 Compatible | Tool only, battery & charger not included<br>18v LXT® Compact Job Site Radio<br>MP3 Compatible for iPod® and MP3 players |
| Voltage | 7.2-18v | 7.2-18v | 7.2-18v |
| Digital Tuner | FM/AM | FM/AM | FM/AM |
| Backlit LCD Display | Yes | Yes | Yes |
| iPod® Dock | No | Yes | No |
| AC Adaptor | Yes | Yes | Yes |

## Coffee Maker

| | DCM500Z NEW |
|---|---|
| | Tool only, battery & charger not included<br>18v LXT® Coffee Maker<br>Auto Drip Brewing |
| Battery | No Battery Included |
| Overall Length | 8-3/8" |
| Net Weight (w/battery) | 3.7 lbs. |
| Shipping Weight | 4.4 lbs. |

## Jackets & Vest

### 18v LXT® Heated Jacket

Jacket Only, Battery & Charger Not Included

| | |
|---|---|
| DCJ200ZS | SMALL |
| DCJ200ZM | MEDIUM |
| DCJ200ZL | LARGE |
| DCJ200ZXL | X-LARGE |
| DCJ200Z2XL | 2X-LARGE |
| DCJ200Z3XL | 3X-LARGE |

| | |
|---|---|
| Heat Settings | High-Medium-Low |
| Number of Pockets | 5 (including battery pocket) |
| Battery | No Battery Included |
| Overall Length | 12-7/8" |
| Net Weight (with battery) | 3.8 lbs. |

### 18v LXT® Mossy Oak® Heated Jacket

Jacket Only, Battery & Charger Not Included

| | |
|---|---|
| DCJ201ZS | SMALL |
| DCJ201ZM | MEDIUM |
| DCJ201ZL | LARGE |
| DCJ201ZXL | X-LARGE |
| DCJ201Z2XL | 2X-LARGE |
| DCJ201Z3XL | 3X-LARGE |

| | |
|---|---|
| Heat Settings | High-Medium-Low |
| Number of Pockets | 5 (including battery pocket) |
| Battery | No Battery Included |
| Overall Length | 12-7/8" |
| Net Weight (with battery) | 3.8 lbs. |

### NEW 18v LXT® Heated Vest

Vest Only, Battery & Charger Not Included

| | |
|---|---|
| DCV200ZM | MEDIUM |
| DCV200ZL | LARGE |
| DCV200ZXL | X-LARGE |
| DCV200Z2XL | 2X-LARGE |
| DCV200Z3XL | 3X-LARGE |

| | |
|---|---|
| Heat Settings | High-Medium-Low |
| Number of Pockets | 5 (including battery pocket) |
| Battery | No Battery Included |
| Overall Length | 12-7/8" |
| Net Weight (with battery) | 3.8 lbs. |

### NEW 18v LXT® Fan Jacket

Jacket Only, Battery & Charger Not Included

| | |
|---|---|
| DFJ201ZM | MEDIUM |
| DFJ201ZL | LARGE |
| DFJ201ZXL | X-LARGE |
| DFJ201Z2XL | 2X-LARGE |
| DFJ201Z3XL | 3X-LARGE |

| | |
|---|---|
| Fan Settings | High-Medium-Low |
| Number of Pockets | 3 |
| Battery | No Battery Included |
| Overall Length | 12-7/8" |
| Net Weight (with battery) | 3.2 lbs. |

## 12v max CXT™ 2–Piece Combo Kits

### NEW CT226RX

| | |
|---|---|
| FD05Z | 3/8" Driver-Drill |
| DT03Z | Impact Driver |
| BL1021B | (2) 12v max CXT™ Lithium-Ion Battery |
| DC10WD | CXT™ Lithium-Ion Charger |

### NEW CT226

| | |
|---|---|
| FD05Z | 3/8" Driver-Drill |
| DT03Z | Impact Driver |
| BL1021B | (2) 12v max CXT™ Lithium-Ion Battery |
| DC10WD | CXT™ Lithium-Ion Charger |

### NEW CT229R

| | |
|---|---|
| FD05Z | 3/8" Driver-Drill |
| RJ03Z | Recipro Saw |
| BL1021B | (2) 12v max CXT™ Lithium-Ion Battery |
| DC10WD | CXT™ Lithium-Ion Charger |

### NEW CT227R

| | |
|---|---|
| FD05Z | 3/8" Driver-Drill |
| SH02Z | 3-3/8" Circular Saw |
| BL1021B | (2) 12v max CXT™ Lithium-Ion Battery |
| DC10WD | CXT™ Lithium-Ion Charger |

## 12v max Drills

| | PH05R1 NEW | PH04R1 NEW | FD07R1 NEW | FD05R1 NEW | FD06R1 NEW |
|---|---|---|---|---|---|
| | PH05Z | PH04Z | FD07Z | FD05Z | FD06Z |
| | **12v max CXT™ Brushless 3/8" Hammer Driver-Drill Kit** Compact Brushless and Ergonomic Design | **12v max CXT™ 3/8" Hammer Driver-Drill Kit** Slide Style Battery and Improved Ergonomic Grip | **12v max CXT™ Brushless 3/8" Driver-Drill Kit** Compact Brushless and Ergonomic Design | **12v max CXT™ 3/8" Driver-Drill Kit** Slide Style Battery and Improved Ergonomic Grip | **12v max CXT™ 1/4" Hex Driver-Drill Kit** Slide Style Battery and Improved Ergonomic Grip |
| Capacities (Steel) (Wood) (Masory) | (3/8")(1-1/8")(5/16") | (3/8")(13/16")(5/16") | (3/8")(1-1/8")(–) | (3/8")(13/16")(–) | (3/8")(13/16")(–) |
| Maximum Torque (in.lbs./N•m) | 280 in.lbs. | 250 in.lbs. | 280 in.lbs. | 250 in.lbs. | 250 in.lbs. |
| Overall Length | 6-5/8" | 7-7/8" | 6-1/16" | 7-7/16" | 6-3/16" |
| Battery | 12v max CXT™ Lithium-Ion (2.0ah) | 12v max CXT™ Lithium-Ion (2.0ah) | 12v max CXT™ Lithium-Ion (2.0ah) | 12v max CXT™ Lithium-Ion (2.0Ah) | 12v max CXT™ Lithium-Ion (2.0Ah) |
| Net Weight (w/battery) | 2.4 lbs. | 2.5 lbs. | 2.3 lbs. | 2.2 lbs. | 2.1 lbs. |

## 12v max Impact Driver

| | DT03R1 NEW |
|---|---|
| | DT03Z |
| | **12v max CXT™ Impact Driver Kit** Slide Style Battery and Improved Ergonomic Grip |
| Drive | 1/4" (hex) |
| No Load Speed | 0 - 2,600 RPM |
| Maximum Torque (in.lbs./N•m) | 970 in.lbs./110N•m |
| Overall Length | 6" |
| Net Weight (w/battery) | 2.3 lbs. |

## 12v max Saws

| | RJ03R1 NEW | SH02R1 NEW | VJ04R1 NEW |
|---|---|---|---|
| | RJ03Z | SH02Z | VJ04Z |
| | **12v max CXT™ Recipro Saw Kit** Slide Style Battery and Improved Ergonomic Grip | **12v max CXT™ 3-3/8" Circular Saw Kit** High Cutting Efficiency | **12v max CXT™Jig Saw Kit** Improved Cutting Efficiency and Performance |
| Length of Stroke | 1/2" | Blade Diameter: 3-3/8" | 11/16" |
| Strokes Per Minute | 0 - 3,300 SPM | **No Load Speed:** 1,500 RPM | 2,900 SPM |
| Battery | 12v max CXT™ Lithium-Ion (2.0ah) | 12v max CXT™ Lithium-Ion (2.0ah) | 12v max CXT™ Lithium-Ion (2.0ah) |
| Overall Length | 14-3/4" | 12-3/8" | 9-1/8" |
| Net Weight (w/battery) | 3 lbs. | 3.5 lbs. | 3.8 lbs. |

## 12v max Saw and Multi-Tool

| | CC02R1 NEW | MT01R1 NEW |
|---|---|---|
| | CC02Z | MT01Z |
| | **12v max CXT™ 3-3/8" Tile/Glass Saw Kit** Smooth and Powerful Cutting | **12v max CXT™ Multi-Tool Kit** Compact Barrel Grip Design |
| Blade Diameter | 3-3/8" | **Oscillations Per Minute:** 6,000 - 20,000 |
| No Load Speed | 1,600 RPM | **Oscillation Angle:** 3.2° |
| Battery | 12v max CXT™ Lithium-Ion | **Battery:** 12v max CXT™ Lithium-Ion |
| Overall Length | 12-3/8" | **Overall Length:** 10-7/8" |
| Net Weight (w/battery) | 4.2 lbs. | **Net Weight (w/battery):** 2.4 lbs. |

## 12v max Flashlight & Power Source

| | ML103 NEW | ADP06 NEW |
|---|---|---|
| | | |
| | **12v max CXT™ L.E.D. Flashlight** Compact for Convenient Illumination | **12v max CXT™ USB Power Source** Charges 1 USB compatible electronic device where AC power is not available |
| Run Time | (max. in hours) : 28 | No. of USB Ports : 1 |
| Lumens | 100 | Output: 2.1 |
| Battery | No Battery Included | No Battery Included |
| Overall Length | 3" | 3.2" |
| Net Weight (w/battery) | .6 lbs. | .6 lbs. |

## 12v max 3 & 2 – Piece Combo Kits

### LCT309W

| | |
|---|---|
| FD02ZW | 3/8" Driver-Drill |
| WT01ZW | 3/8" Impact Wrench |
| LM01W | L.E.D. Flashlight |
| BL1014 | (2) 12v max Lithium-Ion Battery |
| DC10WB | Lithium-Ion Charger |

### LCT314W

| | |
|---|---|
| FD02ZW | 3/8" Driver-Drill |
| DT01ZW | Impact Driver |
| LM01W | L.E.D. Flashlight |
| BL1014 | (2)12v max Lithium-Ion Battery |
| DC10WB | Lithium-Ion Charger |

### LCT209W

| | |
|---|---|
| FD02ZW | 3/8" Driver-Drill |
| DT01ZW | Impact Driver |
| BL1014 | (2) 12v max Lithium-Ion Battery |
| DC10WB | Lithium-Ion Charger |

### LCT212W

| | |
|---|---|
| FD02ZW | 3/8" Driver-Drill |
| RJ01ZW | Recipro Saw |
| BL1014 | (2) 12v max Lithium-Ion Battery |
| DC10WB | Lithium-Ion Charger |

### LCT208W

| | |
|---|---|
| FD02ZW | 3/8" Driver-Drill |
| SH01ZW | 3-3/8" Circular Saw |
| BL1014 | (2) 12V max Lithium-Ion Battery |
| DC10WB | Lithium-Ion Charger |

## 12v max Drills and Impacts

| | FD02W | AD02W | FD01W | DT01W | WT01W |
|---|---|---|---|---|---|
| | FD02ZW | AD02ZW | FD01Z | DT01ZW | WT01ZW |
| | **12v max 3/8" Driver-Drill Kit** Makita-Built Motor Delivers 200 in.lbs. of Max Torque | **12v max 3/8" Right Angle Drill Kit** Close Quarters Drilling and Driving | **12v max 1/4" Hex Driver-Drill Kit** Ultra-Compact Design | **12v max Impact Driver Kit** 800 in.lbs. of Max Torque in an Ultra-Compact Size | **12v max 3/8" Impact Wrench Kit** Makita-Built Motor Delivers 1,000 in.lbs. of Max Torque |
| Capacities: (Steel, Wood) | 3/8", 13/16" | 3/8", 1/2" | **Hex Shank:** 1/4" | **Hex Shank:** 1/4" | **Square Drive:** 3/8" |
| No Load Speed | 0 - 350 / 0 - 1,300 RPM | 800 RPM | 0 - 350 / 0 - 1,300 RPM | 2,400 RPM | 2,400 RPM |
| Battery | 12v max Lithium-Ion | 12v max Lithium-Ion | 12v max Lithium-Ion | 12v max Lithium-Ion | 12v max Lithium-Ion |
| Overall Length | 7-7/16" | 12-1/4" | 6-3/16" | 6-3/8" | 6-3/8" |
| Net Weight (w/battery) | 2.2 lbs. | 2.5 lbs. | 2 lbs. | 2.1 lbs. | 2.1 lbs. |

## 12v Saws

| | SH01W | CC01W | RJ01W | VJ01W |
|---|---|---|---|---|
| | SH01ZW | CC01ZW | RJ01ZW | VJ01ZW |
| | **12v max 3-3/8" Circular Saw** Up to 70 Cuts of 1/2" x 12" Plywood Per Charge | **12v max 3-3/8" Tile/Glass Saw Kit** Up to 70 Cuts on a Single Charge | **12v max Recipro Saw Kit** 25% Faster Cutting Speed on 1-1/2" PVC Pipe | **12v max Jig Saw Kit** Fast Cutting, Weighs Only 3.7 lbs. |
| No Load Speed | 1,400 RPM | 1,400 RPM | **Strokes Per Minute:** 0-3,300 | **Strokes Per Minute:** 0-2,400 |
| Battery | 12v max Lithium-Ion | 12v max Lithium-Ion | 12v max Lithium-Ion | 12v max Lithium-Ion |
| Overall Length | 11-3/4" | 11-3/4" | 14" | 9-1/8" |
| Net Weight (w/battery) | 3.3 lbs. | 3.7 lbs. | 2.6 lbs. | 3.7 lbs. |
| Shipping Weight | 5.61 lbs. | 6.5 lbs. | 4.65 lbs. | 10.4 lbs. |

## Vacuums and Flashlight

| | LC01Z | LC05 |
|---|---|---|
| | Tool only, battery & charger not included | Includes built-in battery with A/C charger cord |
| | **12v max Vacuum** Quick Clean-Ups with Strong Suction Power | **12v max Vacuum, Built-in Battery** Strong Suction Power |
| Capacity | 1.25 pint | **Capacity:** 1.05 pint |
| Battery | No Battery Included | **Continuous Use:** 12 min. |
| Overall Length | 17-7/8" | **Overall Length:** 38-5/8" |
| Net Weight (w/battery) | 4 lbs. | **Net Weight (w/battery):** 1.9 lbs. |
| | | **Shipping Weight:** 4.3 lbs. |

## 12v max Light

| | ML102 |
|---|---|
| | **12v max L.E.D. Lantern/Flashlight** Ultra-Compact L.E.D. Lantern/Flashlight Runs up to 8 Hours Per Charge |
| Bulb | 1 LED |
| Brightness | 800 lux |
| Battery Charge Time | 60 min |
| Overall Length | 4-3/4" |
| Net Weight | .55 lbs. |

**GET REGISTERED**

Register your products and keep them in one safe place, your own Tool Box. It is where you can go to obtain your tool model numbers and serial numbers in the event your tool is stolen or needs service.

**makitatools.com/account/login/**

## 7.2v Lithium-Ion

| | TD021DSE NEW | DF010DSE |
|---|---|---|
| | **7.2v Lithium-Ion 1/4" Hex Impact Driver Kit** Variable Speed for Controlled Operation | **7.2v Lithium-Ion Driver-Drill** Auto-Stop Clutch Delivers Exact Torque Control |
| Drive | 1/4" (hex) | 1/4" (hex) |
| No Load Speed | 0/2,300 RPM | 200/650 RPM |
| Battery | 7.2v Lithium-Ion | 7.2v Lithium-Ion |
| Overall Length | 11" | 11" |
| Net Weight (w/battery) | 1.2 lbs. | 1.2 lbs. |

**Impact GOLD** Xtreme Torsion Technology

### B-52370 NEW

IMPACT GOLD® 38 PC. TORSION BIT SET

Designed Exclusively for High-Torque Impact Drivers

- Impact GOLD® insert bits last up to 60X longer than standard insert bits
- Double Ended Power Bits feature one bit with two magnetic tips for quick bit changes
- Xtreme Torsion Technology is engineered to allow the torsion section of the bit and bit holder to flex under load, taking pressure off of the bit tip

## 18v Lithium-Ion

**UPGRADED**
NEW L.E.D. BATTERY CHARGE INDICATOR
LXT®

### 18v LXT® LITHIUM-ION 6.0Ah BATTERY
Reaches Full Charge in 55 Minutes or Less

| | | |
|---|---|---|
| BL1860B | (1-Pack) | 6.0Ah BATTERY |
| BL1860B-2 | (2-Pack) | |

NEW — 55 Minute Charge Time

### 18v LXT® LITHIUM-ION 5.0Ah BATTERY
Reaches Full Charge in 45 Minutes or Less

| | | |
|---|---|---|
| BL1850B | (1-Pack) | 5.0Ah BATTERY |
| BL1850B-2 | (2-Pack) | |

NEW — 45 Minute Charge Time

### 18v LXT® LITHIUM-ION 4.0Ah BATTERY
Reaches Full Charge in 40 Minutes or Less

| | | |
|---|---|---|
| BL1840B | (1-Pack) | 4.0Ah BATTERY |
| BL1840B-2 | (2-Pack) | |

NEW — 40 Minute Charge Time

### 18v LXT® LITHIUM-ION 3.0Ah BATTERY
Reaches Full Charge in 30 Minutes or Less

| | | |
|---|---|---|
| BL1830 | (1-Pack) | 3.0Ah BATTERY |
| BL1830-2 | (2-Pack) | |
| BL1830-10 | (10-Pack) | |

30 Minute Charge Time

### 18v LXT® COMPACT LITHIUM-ION 2.0Ah BATTERY
Reaches Full Charge in 25 Minutes or Less

| | | |
|---|---|---|
| BL1820B | (1-Pack) | 2.0Ah BATTERY |
| BL1820B-2 | (2-Pack) | |

NEW — 25 Minute Charge Time

### 18v LITHIUM-ION RAPID OPTIMUM CHARGER
Rapid Charging
**DC18RC**

### 18v LITHIUM-ION DUAL PORT RAPID OPTIMUM CHARGER
Charges 2 Batteries Simultaneously
**DC18RD**

### 18v LITHIUM-ION 4-PORT CHARGER
Will Accommodate Up To 4 Makita® 18v LXT® Batteries
**DC18SF**
- Charges 4 batteries at a time

### 18v LITHIUM-ION OPTIMUM AUTOMOTIVE CHARGER[1]
Charge 18v LXT® Batteries in Your Auto or Truck
**DC18SE**

[1] Not a rapid charger

## 36v Lithium-Ion

### 36v LITHIUM-ION BATTERY
30 Minute Charge Time[2]
**BL3626** — 2.6Ah BATTERY

30 Minute Charge Time

### 36v LITHIUM-ION BATTERY
60 Minute Charge Time[2]
**BL3622A** — 2.2Ah BATTERY

60 Minute Charge Time

[2] When used with Makita's Rapid Optimum Charger (DC36WA)

### 36v CHARGER
Charges Makita 36v Lithium-Ion Battery (BL3622A) in 60 Minutes
**DC36WA**

Battery BL3622A must only be used with 36v Optimum Charger (DC36WA)

## 14.4v Lithium-Ion

### 14.4v LITHIUM-ION BATTERY
22 Minutes Fast Charging
**BL1430**

22 Minute Charge Time

**DC18RC** Rapid Optimum Charger

**DC18SF** Rapid Optimum 4-Port Charger

**DC18RD** Rapid Optimum Dual Port Charger

## 12v max Lithium-Ion

### 12v max CXT™ LITHIUM-ION 4.0Ah BATTERY
NEW
Slide-Style Battery
**BL1041B** — 4.0Ah BATTERY

### 12v max CXT™ LITHIUM-ION CHARGER
NEW
Charges 12v max CXT™ Slide-Style Batteries
**DC10WD**

### 12v max CXT™ LITHIUM-ION 2.0Ah BATTERY
NEW
Slide-Style Battery
**BL1021B** — 2.0Ah BATTERY

### 12v max LITHIUM-ION BATTERY
Pod-Style Battery
**BL1014**

50 Minute Charge Time

### LITHIUM-ION CHARGER
Charges 7.2v to12v max Batteries
**DC10WB**
- Also charges 10.8V Lithium-Ion batteries

## 7.2v Lithium-Ion

### 7.2v LITHIUM-ION BATTERY
60 Minute Charge Time
**BL7010**

60 Minute Charge Time

### LITHIUM-ION CHARGER
Charges 7.2v to 12v max Batteries
**DC10WB**
- Also charges 10.8V Lithium-Ion batteries

## Lasers

| | SK103PZ NEW | SK104Z NEW | LD080P NEW | LD050P NEW |
|---|---|---|---|---|
| | | | |  |
| | **Self-Leveling Combination Cross-Line/Point Laser**<br>All-In-One Solution: Combination Laser | **Self-Leveling Horizontal / Vertical Cross-Line Laser**<br>Cross-Line Horizontal/Vertical Reference Line Solution | **Laser Distance Measure, 262'**<br>Measuring Accuracy and Productivity | **Laser Distance Measure, 164'**<br>Measuring Accuracy and Productivity |
| Laser Diode | 635nm, class II | 635nm, class II | 635nm, class II | 635nm, class II |
| Working Range | Line (50'), Point (100') | 50' | 262' | 164' |
| Line accuracy (at 30') | +/- 1/8" | +/- 1/8" | +/- 1/16" | +/- 5/64" |
| Power Supply | 3 AA Batteries | 3 AA Batteries | 2 AA Batteries | 2 AA Batteries |
| Net Weight | 1.04 lbs. | 1.04 lbs. | .3 lbs. | .22 lbs. |

**CARBIDE & DEMOLITION STEEL**

SDS-PLUS — 1-1/8" Hex

SDS-MAX — 3/4" Hex

SPLINE shank

## Demolition Hammers

| | HM1812X3 | HM1810X3 | HM1317CB | HM1500B | HM1307CB |
|---|---|---|---|---|---|
| | Bit Type 1-1/8" Hex<br> | Bit Type 1-1/8" Hex<br> | Bit Type 1-1/8" Hex<br> | Bit Type 1-1/8" Hex<br> | Bit Type 1-1/8" Hex<br> |
| | **70 lb. Advanced AVT® Breaker Hammer**<br>Hits Like Air Without the Vibration | **70 lb. AVT® Breaker Hammer**<br>Anti-Vibration Technology for 2X Less Vibration | **42 lb. AVT® Demolition Hammer**<br>Anti-Vibration Technology for 2X Less Vibration | **42 lb. Demolition Hammer**<br>Rugged All Metal Housing for Longer Tool Life | **35 lb. Demolition Hammer**<br>Electronic Controller for Operator Convenience |
| Blows Per Minute | 870 BPM | 1,100 BPM | 730 - 1,450 BPM | 1,300 BPM | 730 - 1,450 BPM |
| Impact Energy | 53.9 ft.lbs. | 46.5 ft.lbs. | 25.7 ft.lbs. | 18.4 ft.lbs. | 25.7 ft.lbs. |
| AMPS | 15 | 15 | 14 | 13.5 | 14 |
| Noise Level | 106 dB | 107 dB | 101 dB | 101 dB | 101 dB |
| Net Weight | 69.1 lbs. | 71.3 lbs. | 41.9 lbs. | 44.1 lbs. | 38.2 lbs. |

## Demolition Hammers

| | HM1214C | HM1203C | HM1211B | HM1111C | HM0870C |
|---|---|---|---|---|---|
| | Bit Type Accepts SDS-MAX<br> | Bit Type Accepts SDS-MAX<br> | Bit Type 3/4" Hex - 21/31" Round<br> | Bit Type Accepts SDS-MAX<br> | Bit Type Accepts SDS-MAX<br> |
| | **27 lb. AVT® Demolition Hammer**<br>Anti-Vibration Technology for 2X Less Vibration | **20 lb. Demolition Hammer**<br>Compact Power with Less Weight | **20 lb. Demolition Hammer**<br>Close Quarters Drilling & Driving | **17 lb. AVT® Demolition Hammer**<br>Anti-Vibration Technology for 2X Less Vibration | **11 lb. Demolition Hammer**<br>Compact Power with Less Weight |
| Blows Per Minute | 950 - 1,900 BPM | 950 - 1,900 BPM | 2,000 BPM | 1,100 - 2,650 BPM | 1,100 - 2,650 BPM |
| Impact Energy | 19 ft.lbs. | 18.8 ft.lbs. | 10.5 ft.lbs. | 12.7 ft.lbs. | 8.4 ft.lbs. |
| AMPS | 14 | 14 | 10 | 14 | 10 |
| Overall Length | 27-1/2" | 22-3/4" | 19-5/16" | 20-3/4" | 17-3/4" |
| Net Weight | 27.1 lbs. | 20.3 lbs. | 20.7 lbs. | 17.7 lbs. | 11.1 lbs. |

## Demolition Hammers

| | HM0810B | HK1810 |
|---|---|---|
| | Bit Type 3/4" Hex - 21/31" Round<br> | Bit Type Makita Small<br> |
| | **11 lb. Demolition Hammer**<br>Ideal for Light Chiseling, Chipping and Scaling | **Power Scraper**<br>Versatile Tool for Scraping and Tile Removal |
| Blows Per Minute | 2,900 BPM | 0 - 3,200 BPM |
| Impact Energy | 5.6 ft.lbs. | 2.9 ft.lbs. |
| AMPS | 8.3 | 4.5 |
| Overall Length | 16-5/8" | 12-3/8" |
| Net Weight | 12.8 lbs. | 7.1 lbs. |

## Rotary Hammers

| | HR5212C | HR4510C |
|---|---|---|
| | Bit Type Accepts SDS-MAX<br> | Bit Type Accepts SDS-MAX<br> |
| | **2" Advanced AVT® Rotary Hammer**<br>Advanced AVT for Significantly Less Vibration | **1-3/4" AVT® Rotary Hammer**<br>Anti-Vibration Technology for 2X Less Vibration |
| Blows Per Minute | 1,100 - 2,250 BPM | 1/4" |
| Impact Energy | 14 ft.lbs. | 9.2 ft.lbs. |
| AMPS | 15 | 13.5 |
| Overall Length | 23-1/2" | 18" |
| Net Weight | 26.2 lbs. | 4.1 lbs. |

## Rotary Hammers

| | HR4013C | HR4002 | HR5000 | HR4041C | HR3210C |
|---|---|---|---|---|---|
| | Bit Type Accepts SDS-MAX<br> | Bit Type Accepts SDS-MAX<br> | Bit Type Accepts Spline Shank<br> | Bit Type Accepts Spline Shank<br> | Bit Type Accepts SDS-PLUS<br> |
| | **1-9/16" Advanced AVT® Rotary Hammer**<br>Advanced AVT for Significantly Less Vibration | **1-9/16" Rotary Hammer**<br>Sequential Impact Timing for up to 50% Faster Drilling | **2" Rotary Hammer**<br>Air Cushion Design for Hard Hitting Action | **9/16" Rotary Hammer**<br>Electronic Controller for Operator Convenience | **1-1/4" AVT® Rotary Hammer**<br>Anti-Vibration Technology for 2X Less Vibration |
| Blows Per Minute | 1,450 - 2,900 BPM | 2,500 BPM | 2,100 BPM | 1,300 - 2,600 BPM | 1,650 - 3,300 BPM |
| Impact Energy | 8.4 ft.lbs. | 4.6 ft.lbs. | 8.7 ft.lbs. | 6.8 ft.lbs. | 4.1 ft.lbs. |
| AMPS | 11 | 10 | 11 | 12 | 8.2 |
| Overall Length | 18-11/16" | 18" | 18-3/4" | 16-7/8" | 15-5/8" |
| Net Weight | 15.1 lbs. | 14.6 lbs. | 21.8 lbs. | 14.8 lbs. | 11.4 lbs. |

## Rotary Hammers

| | HR2811F | HR2641 | HR2475 | HR2611F | HR1830F |
|---|---|---|---|---|---|
| | Bit Type Accepts SDS-PLUS | Bit Type Accepts SDS-PLUS, AVT Anti Vibration Technology | Bit Type Accepts SDS-PLUS | Bit Type Accepts SDS-PLUS, AVT Anti Vibration Technology | Bit Type Accepts SDS-PLUS |
| | **1-1/8" Rotary Hammer** Torque Limiting Clutch Engineered to Prevent Gear Damage | **1" AVT® Rotary Hammer** Anti-Vibration Technology for 2X Less Vibration | **1" Rotary Hammer** Torque Limiting Clutch Engineered to Prevent Gear Damage | **1" AVT® Rotary Hammer** Anti-Vibration Technology for 2X Less Vibration | **11/16" Rotary Hammer** Compact with Less Weight (4.2 lbs.) |
| Blows Per Minute | 0 - 4,500 BPM | 0 - 4,500 BPM | 0 - 4,500 BPM | 0 - 4,600 BPM | 0 - 5,000 BPM |
| Impact Energy | 2.1 ft.lbs. | 2.1 ft.lbs. | 2 ft.lbs. | 2.1 ft.lbs. | .9 ft.lbs. |
| AMPS | 7 | 8 | 7 | 7 | 4.2 |
| Overall Length | 12-5/8" | 16-5/8" | 16-7/8" | 15-1/8" | 10-7/8" |
| Net Weight | 7.7 lbs. | 7.1 lbs. | 6.6 lbs. | 6.6 lbs. | 4.2 lbs. |

## Cordless Rotary Hammers

| | HRH01 | XRH05Z | XRH011X | XRH01Z | XRH04 |
|---|---|---|---|---|---|
| | Bit Type Accepts SDS-PLUS, 36V LITHIUM-ION | Bit Type Accepts SDS-PLUS, Tool only, battery & charger not included, LXT X2 18V 36V | Bit Type Accepts SDS-PLUS, BARE TOOL AVAILABLE XRH01ZVX, DX01, LXT BRUSHLESS | Bit Type Accepts SDS-PLUS, Tool only, battery & charger not included, LXT BRUSHLESS | Bit Type Accepts SDS-PLUS, BARE TOOL AVAILABLE XRH04Z, LXT |
| | **36v LXT® 1" Rotary Hammer Kit** Corded Speed & Power Without the Cord | **18v X2 LXT® (36v) 1" Rotary Hammer** 18 Volt Solution for Corded Power Demands | **18v LXT® Brushless 1" Rotary Hammer Kit** Built-on HEPA Vacuum | **18v LXT® Brushless 1" Rotary Hammer** Efficient BL™ Brushless Motor | **18v LXT® 7/8" Rotary Hammer Kit** Compact D-Handle Grip Design |
| No Load Speed | 0 - 1,200 RPM | 0 - 1,250 RPM | 0 - 4,700 RPM | 0 - 950 RPM | 0 - 1,100 RPM |
| Blows Per Minute | 0 - 4,800 BPM | 0 - 5,000 BPM | 0 - 4,700 BPM | 0 - 4,700 BPM | 0 - 4,000 BPM |
| Impact Energy | 2.2 ft.lbs. | 2.2 ft.lbs. | 1.7 ft.lbs. | 1.7 ft.lbs. | 1.4 ft.lbs. |
| Battery | 36v LXT® Lithium-Ion (2.6Ah) | No Battery Included | 18v LXT® Lithium-Ion (3.0Ah) | No Battery Included | 18v LXT® Lithium-Ion (3.0Ah) |
| Net Weight ( w/battery) | 7.7 lbs. | 9.3 lbs. | 10.2 lbs. | 7.2 lbs. | 7.7 lbs. |

## Cordless Rotary Hammers

| | XRH03 |
|---|---|
| | Bit Type Accepts SDS-PLUS, BARE TOOL AVAILABLE XRH04Z, LXT |
| | **18v LXT® 7/8" Rotary Hammer Kit** Ergonomic Handle Design |
| Blows Per Minute | 0 - 4,000 BPM |
| Impact Energy | 1.4 ft.lbs. |
| Battery | 14 |
| Overall Length | 18v LXT® Lithium-Ion (3.0Ah) |
| Net Weight ( w/battery) | 7.7 lbs. |

## Hammer Drills

| | HP2070F | HP2050F | HP2050 |
|---|---|---|---|
| | **3/4" Hammer Drill** "Hammering with Rotation" or "Rotation Only" | **3/4" Hammer Drill** L.E.D. Light illuminates the Work Area | **3/4" Hammer Drill** "Hammering with Rotation" or "Rotation Only" |
| No Load Speed | 0 - 1,200 / 0 - 2,900 RPM | 0 - 1,200 / 0 - 2,900 RPM | 0 - 1,200 / 0 - 2,900 RPM |
| Blows Per Minute | 0 - 24,000 / 0 - 58,000 BPM | 0 - 24,000 / 0 - 58,000 BPM | 0 - 24,000 / 0 - 58,000 BPM |
| AMPS | 8.2 | 6.6 | 6.6 |
| Overall Length | 14-1/4" | 14-1/4" | 14-1/4" |
| Net Weight ( w/battery) | 5.3 lbs. | 5.6 lbs. | 5.6 lbs. |

## Hammer Drills

| | HP2010N | HP1641K | HP1640 |
|---|---|---|---|
| | **3/4" Hammer Drill Kit** Industrial Metal Gear Housing for Durability | **5/8" Hammer Drill, with Keyless Chuck** Industrial Keyless Chuck; includes Tool Case | **5/8" Hammer Drill** Lightweight (4.4 lbs.) with Large Drilling Capacity |
| No Load Speed | 0 - 900 / 0 - 2,300 RPM | 0 - 2,800 RPM | 0 - 2,800 RPM |
| Blows Per Minute | 0 - 18,000 / 0 - 46,000 BPM | 0 - 44,800BPM | 0 - 44,800BPM |
| AMPS | 6 | 6 | 6 |
| Overall Length | 13-3/4" | 11-7/8" | 11-7/8" |
| Net Weight ( w/battery) | 6.4 lbs. | 6 lbs. | 4.4 lbs. |

## Angle Cutter

| | 4114 |
|---|---|
| | **14" SJS™ Angle Cutter** Built in Dust Port for Reduced Dust and Debris when Connected to a Vacuum |
| No Load Speed | 3,800 RPM |
| Arbor | 1" |
| AMPS | 15 |
| Max Cutting Depth | 5" |
| Net Weight | 23.8 lbs. |

## Power Cutters

| | EK8100 | EK7651H | EK7301 | EK6101 | DT4000 / DT2010 |
|---|---|---|---|---|---|
| | **16" 81 cc Power Cutter** Capacity Performance 16" Power Cutter with 5.6 HP/81 cc Engine | **14" 76 cc MM4® 4-Stroke Power Cutter** No Oil Mixing Prevents Piston Seizure Due to Improper Mixing | **14" 73 cc Power Cutter** Powerful Performance with 5.1 HP/73 cc. Engine | **14" 61 cc Power Cutter** Compact Performance at Only 19.6 lbs with 4.4 HP/61 cc Engine | DT4000 Shown **Power Cutter Dolly** "Tool-less" Attatchment from power cutter to dolly |
| Engine Displacement (cu.in. / cc) | 4.9 cu.in. / 81 cc | 4.61 cu.in. / 75.6 cc | 4.5 cu.in. / 73 cc | 3.7 cu.in. / 61 cc | DT4000 for model EK7651H Includes: Dolly and gravity feed tank |
| Engine ( Max Power) | 5.6 HP/4.2 kW | 4.1 HP/3 kW | 5.1 HP/3.8 kW | 4.4 HP/3.2 kW | |
| No Load Speed / Max Spindle Speed | 9,350 / 3,820 RPM | 9,100 / 4,300 RPM | 9,350 / 4,300 RPM | 9,850 / 4,400 RPM | |
| Max Cutting Depth | 5-3/4" | 4-13/16" | 4-13/16" | 5-1/8" | DT2010 for models EK7301, EK8100 Includes: Dolly and gravity feed tank |
| Dry Weight | 23.3 lbs. | 35.2 lbs. | 22 lbs. | 19.6 lbs. | |

## Masonry Saws

| | 4101RH | 4100NH | GA5040X1 | GA5042CX1 | A-96017 |
|---|---|---|---|---|---|
| | **5" Masonry Saw** For Wet Cutting of Tile, Masonry, Concrete and More | **4-3/8" Masonry Saw** Powerful Cutting in Stone, Masonry, Tile & Concrete | SJSII **5" SJS™II Angle Grinder with Tuck Point Guard** 5" Dust Extraction Tuck Point Guard | SJSII **5" SJS™II High-Power Grinder with Tuck Point Guard** 5" Dust Extraction Tuck Point Guard | **5" DUAL SANDWICH TUCKPOINT BLADE** |
| Wheel Diameter | 5" | 4-3/8" | 5" | 5" | |
| No Load Speed | 13,800 RPM | 14,500 RPM | 11,000 RPM | 2,800 - 11,000 RPM | |
| AMPS | 7.9 | 12 | 10 | 12 | |
| Cutting Capacity | 1-5/8" | 1-3/8" | 1" | 1" | |
| Net Weight | 6.5 lbs. | 6.5 lbs. | 5.4 lbs. | 5.4 lbs. | |

## Concrete Planers

| | PC5000C | PC5001C |
|---|---|---|
| | **5" Concrete Planer** Electronic Controller for Operator Convenience | **5" Concrete Planer** Adjustable Front Roller for Consistent Planing Depth |
| Wheel Diameter | 5" | 5" |
| No Load Speed | 10,000 RPM | 2,800 - 11,000 RPM |
| AMPS | 10 | 10 |
| Overall Length | 11-7/8" | 18-13/16" |
| Net Weight | 8.9 lbs. | 11.2 lbs. |

## Fans

| | DCF300Z | BCF201Z |
|---|---|---|
| | Tool only, battery & charger not included LXT **18v LXT® 13" Job Site Fan** Up to 5.7 Hours of Continuous Run-Time on a Single Charge | Tool only, battery & charger not included LXT **18v LXT® Job Site Fan** Up to 5.5 Hours of Continuous Run Time on a Single Charge |
| Voltage | 18v | 14.4-18v |
| AC Adapter | Yes | Yes |
| Run Time | 5.7 Hours | 5.5 Hours |
| Battery | No Battery Included | No Battery Included |
| Net Weight (w/battery) | 10.4 lbs. | 7.1 lbs. |

## Vacuums

| | VC4710 | XCV04Z NEW | XCV05Z NEW | DCL500Z | XLC02RB1W |
|---|---|---|---|---|---|
| | Xtract Vac **12 Gallon Wet/Dry Vacuum** Long Lasting Powerful Suction | LXT X2 18V (36V) **18v X2 LXT® (36v) 2.1 Gallon HEPA Filter Dry Vacuum** Cordless/Corded Power Option for Versatility and Convenience | Tool only, battery & charger not included LXT X2 18V (36V) **18v X2 LXT® (36v) Brushless HEPA Filter Backpack Vacuum** Powerful Suction Power in a Light and Comfortable Design | Tool only, battery & charger not included LXT **18v LXT® Cyclonic Canister Vacuum** Long Lasting Powerful Suction | BARE TOOL AVAILABLE XLC02ZW LXT COMPACT **18v LXT® Compact Vacuum Kit** Strong Suction Power for Fast Cleaning with More Run Time |
| Air Flow Rate | 135 CFM | 127 CFM | 53 CFM | .53 pint | **Capacity (pint):** 1.3 pint |
| Static Water Lift | 8 gal. | 96" | 28.5" | 13-7/8" | **Overall Length:** 18-3/4" |
| AMPS | 12 | **Continuous Use:** 65 min. | **Continuous Use:** 60 min. | **Continuous Use:** 49 min. | 15 min. |
| Power Consumption | 840/0 watts | No Battery Included | No Battery Included | No Battery Included | 18v LXT® Compact Lithium-Ion (2.0Ah) |
| Peak Horsepower | 4 HP | 21.8 lbs. | 9.4 lbs. | 9.4 lbs. | 2.7 lbs. |

## Vacuums

| | LC01Z | LC05 |
|---|---|---|
| | Tool only, battery & charger not included 12V max CXT LITHIUM-ION **12v max Vacuum** Quick Clean-Ups with Strong Suction Power | Includes built-in battery with A/C charger cord 12V max CXT LITHIUM-ION **12v max Vacuum, Built-in Battery** Strong Suction Power |
| Air Flow Rate | 1.25 pint | 1.05 pint |
| Static Water Lift | 17-7/8" | 38-5/8" |
| Continuous Use | 12 min. | 12 min. |
| Battery | No Battery Included | **Built-In Battery:** 12v max Lithium-Ion |
| Net Weight (with battery) | 2.7 lbs. | 1.9 lbs. |

## Drills

| | 6407 | 6408 / 6408K |
|---|---|---|
| | **3/8" Drill** Low Decibel Rating (79dB) for Quieter Operation | **3/8" Drill** For Drilling in a Wide Variety of Materials |
| Capacities | Steel (3/8") / Wood (1") | Steel (3/8") / Wood (1") |
| No Load Speed | 0 - 2,500 RPM | 0 - 2,500 RPM |
| AMPS | 4.9 | 4.9 |
| Overall Length | 10-9/32" | 10-9/32" |
| Net Weight | 3.1 lbs. | 3.1 lbs. |

## Drills

| | 6302H | DP4000 / DP4002 | DS4011 | DS4012 | DS4000 |
|---|---|---|---|---|---|
| | **1/2" Drill** Industrial Metal Gear Housing for Durability | **1/2" Drill** Lightweight Aluminum Gear Housing for Durability; 0-950 RPM | **1/2" Spade Handle Drill** Powerful 8.5 AMP Motor with Variable Speed for Improved Mixing and Drilling Performance | **1/2" Spade Handle Drill** Powerful 8.5 AMP Motor with Variable Speed for Improved Mixing and Drilling Performance | **1/2" Spade Handle Drill** Faster 500 RPM and More Powerful 9.0 AMPS |
| Capacities | Steel (1/2") / Wood (1-3/8") | Steel (1/2") / Wood (1-1/2") | Steel (1/2") / Wood (1-1/2") | Steel (1/2") / Wood (1-1/2") | Steel (1/2") / Wood (1-1/2") |
| No Load Speed | 0 - 550 RPM | 0 - 950 RPM | 0 - 600 RPM | 0 - 600 RPM | 500 RPM |
| AMPS | 6.5 | 7 | 8.5 | 8.5 | 9 |
| Overall Length | 11-1/4" | 12" | 13-3/8" | 13-3/8" | 14-1/4" |
| Net Weight | 4.8 lbs. | 4.8 lbs. / 4.9 lbs. | 6.3 lbs. | 6.2 lbs. | 8.8 lbs. |

## Angle Drills

| | DA4000LR | DA3010F | DA4031 | DA6301 |
|---|---|---|---|---|
| | **1/2" Angle Drill** 360º Angle Attachment for Drilling in Any Position | **3/8" Angle Drill** Light Up Your Drilling Surface with L.E.D. Power | **1/2" Angle Drill** Sidewinder Handle Rotates 90º Left or Right | **1/2" Angle Drill** 360º Angle Attachment for Drilling in Any Position |
| Capacities: (Steel) (Wood) (Masory) | (1/2") (1-1/2")(–) | (3/8")(13/16")(–) | (3/8")(13/16")(–) | (1/2")(1-1/2")(–) |
| No Load Speed | 400/900 RPM | 0 - 2,400 RPM | 300/1,200 RPM | 300/1,200 RPM |
| AMPS | 7.5 | 4 | 10 | 7.5 |
| Overall Length | 16-1/4" | 10-5/8" | 18-1/4" | 16-1/8" |
| Net Weight | 8.1 lbs. | 3.5 lbs. | 12.3 lbs. | 9.5 lbs. |

**Impact GOLD**

**1" Phillips Insert Bits**

| Desc. | Qty./Pkg. | Part # |
|---|---|---|
| #1 | 4 | B-34936 |
| #2 | 4 | B-34942 |
| #2 | 15 | B-34958 |
| #2 | 100 | B-42569 |
| #3 | 4 | B-34964 |

See pg. 27 for more Impact Gold®

## Screwdrivers

| | FS6200 / FS6200TP | FS4200 | FS4200A | FS4200TP | XSF03MB |
|---|---|---|---|---|---|
| | 6,000RPM **6,000 RPM Drywall Screwdriver** Precision Balance With Less Weight | 4,000RPM **4,000 RPM Drywall Screwdriver** Features 8.2' Cord | 4,000RPM **4,000 RPM Drywall Screwdriver** Features 50' Cord | 4,000RPM **4,000 RPM Drywall Screwdriver** Features 50' Cord w/TL | XSF03Z; LXT BRUSHLESS PUSH DRIVE **18v LXT® Brushless Drywall Screwdriver Kit** Drives 1,860 Screws with Push Drive™ |
| Drive | 1/4" (hex) | 1/4" (hex) | 1/4" (hex) | 1/4"(hex) | 1/4" (hex) |
| No Load Speed | 0 - 6,000 RPM | 0 - 4,000 RPM | 0 - 4,000 RPM | 0 - 4,000 RPM | 0 - 4,000 RPM |
| AMPS / Battery | 6 | 6 | 6 | 6 | 18v LXT® Lithium-Ion (4.0Ah) |
| Overall Length | 11-1/8" | 11-1/8" | 11-1/8" | 11-1/8" | 9-7/8" |
| Net Weight | 3 lbs. | 3 lbs. | 3 lbs. | 3 lbs. | 3.8 lbs. |

## Screwdrivers

| | FS2200 | FS2500 | FS2701 | 6844 | XRF02 NEW |
|---|---|---|---|---|---|
| | 2,500RPM **2,500 RPM Drywall Screwdriver** Precision Balance With Less Weight | 2,500RPM **2,500 RPM Screwdriver** Precision Balance With Less Weight | 2,500RPM **2,500 RPM Screwdriver** 6-Stage Torque Adjustment | **Autofeed Screwdriver** "Tool-less" Screw Depth Adjustment | XRF02Z; LXT **18v LXT® Autofeed Screwdriver Kit** Ideal for Hanging Drywall |
| Drive | 1/4" (hex) | 1/4" (hex) | 1/4" (hex) | 1/4" (hex) | 1/4" (hex) |
| No Load Speed | 0 - 2,500 RPM | 0 - 2,500 RPM | 0 - 2,500 RPM | 3,000 RPM | 4,000 RPM |
| AMPS / Battery | 6 | 6 | 6 | 4.3 | 18v LXT® Lithium-Ion (3.0Ah) |
| Overall Length | 11-1/8" | 11" | 11-1/8" | 17-1/4" | 16-3/4" |
| Net Weight | 3.5 lbs. | 3.4 lbs. | 4 lbs. | 4.5 lbs. | 5.1 lbs. |

## Cut-Out Tools

| | 3706 | XOC01MB |
|---|---|---|
| | **Drywall Cut-Out Tool** Slim Body Design (2-1/4'') for Comfort and Control | XOC01Z; LXT **18v LXT® Cut-Out Tool Kit** Slim Body Design (2-1/4") for Comfort and Control |
| Collet Capacity | 1/4" , 1/8" | 1/4" , 1/8" |
| No Load Speed | 32,000 RPM | 30,000 RPM |
| AMPS / Battery | 5 | 18v LXT® Lithium-Ion (3.0Ah) |
| Overall Length | 9-7/8" | 12-3/8" |
| Net Weight | 2.4 lbs. | 3.7 lbs. |

## Impact Wrenches

| | 6952 | 6953 |
|---|---|---|
| | **1/4" Impact Driver** Fast 0-3,200 RPM and High Torque of 88.5 ft.lbs. | **1/2" Impact Wrench w/ Detent Pin Anvil** Max Torque of 110 ft.lbs. |
| Drive | 1/4" (hex) | 1/2" (square) |
| No Load Speed | 0 - 3,200 RPM | 0 - 3,000 RPM |
| Maximum Torque | 120 ft.lbs./162 N•m | 110 ft.lbs./150 N•m |
| AMPS | 2.3 | 2.5 |
| Net Weight (w/battery) | 3.1 lbs. | 3.3 lbs. |

## Impact Wrenches

| | TW0200 | TW0350 | 6906 | TW1000 | 6922NB |
|---|---|---|---|---|---|
| | **1/2" Impact Wrench w/ Detent Pin Anvil** Max Torque of 150 ft.lbs. | **1/2" Impact Wrench w/ Detent Pin Anvil** Max Torque of 258 ft.lbs. | **3/4" Impact Wrench w/ Friction Ring Anvil** Max Torque of 433 ft.lbs. | **1" Impact Wrench w/ Friction Ring Anvil** Max torque of 738 ft.lbs. | **3/4" Shear Wrench** Compact and Lightweight Yet Powerful |
| Drive | 1/2" (square) | 1/2" (square) | 1/2" (square) | 1" (square) | Bolt Drive (5/8", 3/4", 7/8") |
| No Load Speed | 0 - 2,200 RPM | 0 - 2,000 RPM | 0 - 2,000 RPM | 1,400 RPM | 18 RPM |
| Maximum Torque | 150 ft.lbs./200 N•m | 258 ft.lbs./350 N•m | 258 ft.lbs./350 N•m | 738 ft.lbs./1,000 N•m | 593 ft.lbs./804 N•m |
| AMPS | 3.3 | 3.5 | 3.5 | 12 | – |
| Net Weight (w/battery) | 4.9 lbs. | 12.3 lbs. | 12.3 lbs. | 19 lbs. | 10.6 lbs. |

## Impact Wrenches

| | XWT07M NEW | XWT08M NEW | XWT09T NEW | XWT02MB |
|---|---|---|---|---|
| | XWT07Z | XWT08Z | XWT09Z | XWT02Z |
| | LXT BRUSHLESS<br>**18v LXT® Brushless High Torque 3/4" Impact Wrench Kit**<br>Delivers 1250 ft.lbs. of break away torque | LXT BRUSHLESS<br>**18v LXT® Brushless High Torque 1/2" Impact Wrench Kit**<br>Perfect for High Torque Fastening | LXT BRUSHLESS<br>**18v LXT® Brushless High Torque 7/16" Hex Impact Drill Kit**<br>Perfect for High Torque Drilling | LXT BRUSHLESS<br>**18v LXT® Brushless 3-Speed 1/2" Impact Wrench Kit**<br>Improved Fastening Control |
| Drive | 3/4" (square) | 1/2" (square) | 7/16" (hex) | 1/2" (square) |
| No Load Speed | 0-900 / 0-1,000 / 0-1,800 RPM | 0-900 / 0-1,000 / 0-1,800 RPM | 0-900 / 0-1,000 / 0-1,800 RPM | 0-1,600 / 0-2,100 / 0-2,800 RPM |
| Maximum Torque | 780 ft.lbs./1,057 N•m | 740 ft.lbs./1,003 N•m | 590 ft.lbs. | 210 ft.lbs./280 N•m |
| Battery | 18v LXT® Lithium-Ion (4.0Ah) | 18v LXT® Lithium-Ion (4.0Ah) | 18v LXT® Lithium-Ion (5.0Ah) | 18v LXT® Lithium-Ion (4.0Ah) |
| Net Weight (w/battery) | 8.1 lbs. | 7.9 lbs. | 8.1 lbs. | 3.8 lbs. |

**SJS™II**
**SUPER JOINT SYSTEM®**

SJS™II provides a leaf spring and cam gear drive mechanism that is engineered to reduce vibration for increased operator comfort during extended use.

## Angle Grinders

| | GA4030 / GA4030K | GA4530 | GA4534 | 9557NB | 9557PB |
|---|---|---|---|---|---|
| | | | | | |
| | **4" Angle Grinder**<br>Small Diameter Barrel Grip (only 2-1/4") | **4-1/2" Angle Grinder**<br>Small Diameter Barrel Grip (only 2-1/4") | **4-1/2" Paddle Switch Angle Grinder**<br>Small Diameter Barrel Grip (only 2-1/4") | **4-1/2" Angle Grinder**<br>AC/DC Switch for Use with Alternative Power Source | **4-1/2" Paddle Switch Angle Grinder**<br>Large Flush-Mount Paddle Switch |
| Wheel Diameter | 4" | 4-1/2" | 4-1/2" | 4-1/2" | 4-1/2" |
| AMPS | 6 | 6 | 6 | 7.5 | 7.5 |
| No Load Speed | 11,000 RPM | 11,000 RPM | 11,000 RPM | 10,000 RPM | 11,000 RPM |
| Overall Length | 10-1/2" | 10-1/2" | 10-3/8" | 10-5/8" | 10-3/4" |
| Net Weight | 3.7 lbs. | 4 lbs. | 4.2 lbs. | 4.5 lbs. | 4.5 lbs. |

## Angle Grinders

| | 9564P | 9558PB | 9565PCV | 9565PC / 9564PC | 9565CV / 9564CV |
|---|---|---|---|---|---|
| | | | | | |
| | **4-1/2" SJS™ Paddle Switch Angle Grinder**<br>SJS™ Clutch System Helps Prevent Motor Damage | **5" Paddle Switch Angle Grinder**<br>Large Flush-Mount Paddle Switch for Comfortable Operation | **5" SJS™ High-Power Paddle Switch Angle Grinder**<br>Paddle Switch and Variable Speed Dial | **5" SJS™ Paddle Switch Angle Grinder**<br>SJS™ Clutch System Helps Prevent Motor Damage | **5" SJS™ Angle Grinder**<br>Electronic Controller for Increased Durability |
| Wheel Diameter | 4-1/2" | 5" | 5" | 9565PC (5"), 9564PC (4-1/2") | 9565CV (5"), 9564CV (4-1/2") |
| AMPS | 10 | 7.5 | 13 | 13 | 12 |
| No Load Speed | 10,5000 RPM | 10,000 RPM | 2,800 RPM | 10,500 RPM | 2,800 - 10,500 RPM |
| Overall Length | 12-1/8" | 10-3/4" | 12-1/8" | 12-1/8" | 11-3/4" |
| Net Weight | 5.1 lbs. | 4.6 lbs. | 4.2 lbs. | 5.3 lbs. / 5.3 lbs | 5.2 lbs. / 5.3 lbs. |

## Angle Grinders

| | 9005B / 9005BZ | XAG10M NEW | XAG06MB | XAG03MB | GA5042C / GA4542C |
|---|---|---|---|---|---|
| | | XAG10Z | XAG06Z | XAG03Z | |
| | **5" Angle Grinder**<br>Job Site Proven for Over 20 Years | LXT BRUSHLESS<br>**18v LXT® Brushless 4-1/2" Cut-Off/Angle Grinder Kit**<br>Electric Brake and Paddle Switch | LXT BRUSHLESS AUTOMATIC SPEED CHANGE<br>**18v LXT® Brushless 4-1/2" Cut-Off/Angle Grinder**<br>Large Flush-Mount Paddle Switch | LXT BRUSHLESS AUTOMATIC SPEED CHANGE<br>**18v LXT® Brushless 4-1/2" Cut-Off/Angle GrinderKit**<br>Slide Switch For User Convenience | **5" SJS™II Angle Grinder**<br>SJS™II Technology Reduces Vibration for User Comfort |
| Wheel Diameter | 5" | 4-1/2" | 4-1/2" | 4-1/2" | GA5042C (5"), GA4542C (4-1/2") |
| No Load Speed | 10,000 RPM | 8,500 RPM | 8,500 RPM | 8,500 RPM | 2,800 - 11,000 RPM |
| AMPS / Battery | 9 | 18v LXT® Lithium-Ion (4.0Ah) | 18v LXT® Lithium-Ion (4.0Ah) | 18v LXT® Lithium-Ion (4.0Ah) | 12 |
| Overall Length | 14" | 14-1/4" | 14-1/4" | 14-1/4" | 11-7/8" |
| Net Weight | 6.6 lbs. | 5.6 lbs. | 5.6 lbs. | 5.5 lbs. | 5.4 lbs. |

## Angle Grinders

| | GA5040X1 | GA5042CX1 | GA5020 | GA5020Y | GA5010Z |
|---|---|---|---|---|---|
| | | | | | |
| | **5" SJS™II Angle Grinder with Tuck Point Guard**<br>5" Dust Extraction Tuck Point Guard | **5" SJS™II High-Power Grinder with Tuck Point Guard**<br>5" Dust Extraction Tuck Point Guard | **5" SJS™ Angle Grinder**<br>Electric Brake for Maximum Productivity | **5" SJS™ Angle Grinder**<br>Electric Brake for Maximum Productivity | **5" Angle Grinder**<br>10.5 AMP Motor and Labyrinth Construction |
| Wheel Diameter | 5" | 5" | 5" | 5" | 5" |
| No Load Speed | 11,000 RPM | 2,800 - 11,000 RPM | 11,000 RPM | 11,000 RPM | 11,000 RPM |
| AMPS / Battery | 10 | 12 | 10.5 | 10.5 | 10.5 |
| Overall Length | 11-7/8" | 11-7/8" | 14" | 14" | 14" |
| Net Weight | 5.4 lbs. | 5.4 lbs. | 5.9 lbs. | 5.9 lbs. | 5.8 lbs. |

## Angle Grinders

| | 9566PC / 9566PCX1 | 9566CV | GA6020YX1 | GA6020 | GA6010Z |
|---|---|---|---|---|---|
| | 9566PCX1 Shown | | | | |
| | **6" SJS™ Paddle Switch Cut-Off/Angle Grinder** SJS™ Clutch System Helps Prevent Motor Damage | **6" SJS™ Cut-Off/ Angle Grinder** Electronic Controller for Increased Durability | **6" SJS™ Cut-Off/ Angle Grinder** Electric Brake for Maximum Productivity | **6" SJS™ Cut-Off/ Angle Grinder** Electric Brake for Maximum Productivity | **6" Cut-Off/Angle Grinder** AC/DC Switch for Use with Alternative Power Source |
| Wheel Diameter | 6" | 6" | 6" | 6" | 6" |
| No Load Speed | 9,000 RPM | 4,000 - 9,000 RPM | 10,000 RPM | 10,000 RPM | 10,000 RPM |
| AMPS | 13 | 12 | 10.5 | 10.5 | 10.5 |
| Overall Length | 12-1/8" | 11-3/4" | 14" | 14" | 14" |
| Net Weight | 5.5 lbs. | 5.3 lbs. | 6.7 lbs. | 6.7 lbs. | 5.9 lbs. |

## Angle Grinders

| | GA7011C | GA7020 | GA7021 | GA7040S | GA7031Y |
|---|---|---|---|---|---|
| | | | | | |
| | **7" Angle Grinder** Electronic Controller for Increased Durability | **7" Angle Grinder** Powerful 15.0 AMP Motor Delivers 8,500 RPM | **7" Angle Grinder** Powerful 15.0 AMP Motor Delivers 6,000 RPM | **7" Angle Grinder** Powerful 15.0 AMP Motor Delivers 6,000 RPM | **7" Angle Grinder** Rear Handle Rotates With Just the Push of a Button |
| Wheel Diameter | 7" | 7" | 7" | 7" | 7" |
| No Load Speed | 6,000 RPM | 8,500 RPM | 6,000 RPM | 8,000 RPM | 8,500 RPM |
| AMPS | 10.5 | 10.5 | 10.5 | 10.5 | 10.5 |
| Overall Length | 17-7/8" | 18-5/8" | 18-5/8" | 20-1/8" | 19-7/8" |
| Net Weight | 5.3 lbs. | 12.2 lbs. | 12.2 lbs. | 14.2 lbs. | 13.5 lbs. |

## Angle Grinders & Sanders

| | GA7001L | GA7911 | GA9020 | GA9031Y | GA9040S |
|---|---|---|---|---|---|
| | | | | | |
| | **7" Angle Grinder** Rugged All Metal Housing for Longer Tool Life | **Angle Sander** Rugged All Metal Housing for Longer Tool Life | **9" Angle Grinder** AC/DC Switch for Use with Alternative Power Sources | **9" Angle Grinder** Rear Handle Rotates With Just the Push of a Button | **9" Angle Grinder** Soft Start Suppresses Start-Up Reaction |
| Wheel Diameter | 7" | 7" or 9" | 9" | 9" | 9" |
| No Load Speed | 6,000 RPM | 6,000 RPM | 6,000 RPM | 6,000 RPM | 6,000 RPM |
| Spindle Thread | 10.5 | 15 | 10.5 | 10.5 | 10.5 |
| Overall Length | 16-1/4" | 16-1/4" | 18-5/8" | 19-7/8" | 20-1/8" |
| Net Weight | 12.6 lbs. | 12.2 lbs. | 12.9 lbs. | 14 lbs. | 14.8 lbs. |

## Die Grinders

| | XDG01 | GD0801C | GD0800C | GD0600 | GD0601 |
|---|---|---|---|---|---|
| | XDG01Z | | | | |
| | **18V LXT® 1/4" Die Grinder Kit** Delivers 25,000 RPM for Faster Grinding | **1/4" SJS™ Paddle Switch Die Grinder** Electronic Controller for Convenience | **1/4" SJS™ Die Grinder** Electronic Controller | **1/4" Paddle Switch Die Grinder** Large Flush-Mount Paddle Switch for Easy Operation | **1/4" Die Grinder** Side Switch for Operator Convenience |
| Max. Wheel Diameter | 1-1/2" | 2" | 2" | 2" | 1-1/2" |
| No Load Speed | 25,000 RPM | 7,000 - 28,000 RPM | 7,000 - 28,000 RPM | 25,000 RPM | 25,000 RPM |
| AMPS / Battery | 18v LXT® Lithium-Ion | 6.6 | 6.6 | 3.5 | 3.5 |
| Overall Length | 15-3/4" | 14-3/8" | 14-5/8" | 14-1/8" | 14-1/8" |
| Net Weight | 4.4 lbs. | 4.2 lbs. | 3.7 lbs. | 3.7 lbs. | 3.7 lbs. |

## Grinders

| | GS5000 |
|---|---|
| | |
| | **5" Straight Grinder** Powerful 7.0 AMP Motor Delivers More Output and 5,600 RPM |
| Wheel Diameter | 5" |
| No Load Speed | 5,600 RPM |
| Battery | 7 |
| Overall Length | 22-1/4" |
| Net Weight | 11.1 lbs. |

## Sanders

| | GV5010 | 9218SB | GV7000C |
|---|---|---|---|
| | | | |
| | **5" Disc Sander** Compact Design at Only 2.6 lbs. | **7" Disc Sander** Motor-Over-Pad Design for Balance and Control | **7" Disc Sander** Lightweight (4.6 lbs.) for Comfort and Control |
| Sanding Disc | 5" | 7" | 7" |
| No Load Speed | 4,500 RPM | 4,500 RPM | 2,500 - 4,700 RPM |
| AMPS | 4.2 | 5.2 | 7.9 |
| Overall Length | 7-1/8" | 8-7/8" | 8-1/4" |
| Net Weight | 2.6 lbs. | 6.3 lbs. | 4.6 lbs. |

## Polishers

| | PV7001C | PK5011CX1 | PW5001C | 9237C | 9227C |
|---|---|---|---|---|---|
| | **7" Vertical Polisher** High Power-to-Weight Ratio | **5" Electronic Stone Polisher** Powerful Stone Edge Work With Water Feed and Splash Guard | **4" Electronic Stone Polisher** Precision Engineered for a Professional Finish | **7" Polisher** Electronic Controller for Operator Convenience | **7" Polisher** Fast and Powerful Polishing for Clearcoat Finishes |
| Disc Size | 7" | 5" | 4" | 7" | 7" |
| No Load Speed | 600 RPM | 2,000 - 5,500 RPM | 2,000 - 4,000 RPM | 0 - 3,000 RPM | 0 - 3,000 RPM |
| Spindle Thread | 5/8" - 11 UNC | 5/8" - 11 UNC | 5/8" - 11 UNC | 5/8" - 11 UNC | 5/8" - 11 UNC |
| AMPS | 7.9 | 11 | 7.9 | 10 | 10 |
| Net Weight | 4.8 lbs. | 8.4 lbs. | 5.1 lbs. | 7 lbs. | 6.9 lbs. |

## Nibblers

| | XNJ01 | JN3201 | JN1601 |
|---|---|---|---|
| | XNJ01Z **18v LXT® 16 Gauge Nibbler Kit** Powerful, Versatile and Cordless | **10 Gauge Nibbler** Powerful 6.2 AMP Motor; 1,300 SPM for the Most Demanding Applications | **16 Gauge Nibbler** Handles 16 Ga. Mild Steel and 18 Ga. Stainless |
| Strokes Per Minute | 0 - 1,900 SPM | 1,300 SPM | 2,200 SPM |
| AMPS / Battery | 18v LXT® Lithium-Ion | 6.2 | 5 |
| Overall Length | 12-3/8" | 8-1/2" | 10-1/4" |
| Net Weight | 4.8 lbs. | 7.5 lbs. | 3.6 lbs. |
| Shipping Weight | 13.3 lbs. | 8.8 lbs. | 5.28 lbs. |

FIND MORE BLADES AND ACCESSORIES ON pg. 27

## Shears

| | XSJ01 | JS1300 | JS1602 | JS3201 | JS8000 |
|---|---|---|---|---|---|
| | XSJ01Z **18v LXT® 18 Gauge Straight Shear Kit** Swivel Shear Head Rotates 360° | **18 Gauge Straight Shear** Powerful 6.5 AMP Motor for Continuous Operation | **16 Gauge Shear** Cuts 16 Ga. Mild Steel and 18 Ga. Stainless | **10 Gauge Shear** Powerful 6.2 AMP Motor; 1,600 SPM for the Most Demanding Applications | **Fiber Cement Shear** Cuts Quickly While Producing Less Dust |
| Strokes Per Minute | 0 - 2,500 SPM | 0 - 2,500 SPM | 1,300 SPM | 2,200 SPM | 0 - 2,500 SPM |
| AMPS / Battery | 18v LXT® Lithium-Ion | 6.5 | 6.2 | 5 | 6.5 |
| Overall Length | 13-5/8" | 11-7/8" | 8-1/2" | 10-1/4" | 13-5/8" |
| Net Weight | 4.8 lbs. | 3.9 lbs. | 7.5 lbs. | 3.6 lbs. | 4.8 lbs. |
| Shipping Weight | 8.5 lbs. | 5.28 lbs. | 8.8 lbs. | 5.28 lbs. | 8.5 lbs. |

## Metalworking Saws

| | XSC02M NEW | 4131 | 2107FZ / 2107FZK | XBP02 | XBP01 |
|---|---|---|---|---|---|
| | XSC02Z **18v LXT® Brushless 5-i7/8" Metal Cutting Saw Kit** Cuts 2" Conduit in a Single Pass | **7-1/4" Metal Cutting Saw** Faster, Cleaner and More Efficient Metal Cutting | 2107FZK Includes Case **Portable Band Saw** No lock-on feature; saw turns off when the switch is released | XBP02Z **18v LXT® Portable Band Saw Kit** 4-3/4" x 4-3/4" Cutting Capacity | XBP01Z **18v LXT® Compact Band Saw Kit** 2-1/2" x 2-1/2" Cutting Capacity |
| Blade Diameter | 5-7/8" with 3/8" Arbor | 7-1/4" with 3/8" Arbor | 4-3/4" x 4-3/4" | 4-3/4" x 4-3/4" | 2-1/2" x 2-1/2" |
| AMPS / Battery | 18v LXT® Lithium-Ion (4.0Ah) | 13 | 6.5 | 18v LXT® Lithium-Ion (3.0Ah) | 18v LXT® Lithium-Ion (3.0Ah) |
| No Load Speed | 3,900 RPM | 3,500 RPM | 200 - 350 ft./min. | 275 - 530 ft./min. | 630 ft./min. |
| Overall Length | 13-1/8" | 14-1/8" | 20-5/8" | 20-5/8" | 18-1/2" |
| Net Weight | 6.4 lbs. | 10.6 lbs. | 13.1 lbs. | 14.3 lbs. | 7.5 lbs. |

## Metalworking Saws

| | LW1400 NEW | LW1401 NEW | 2414NB / 2414DB | LC1230 | 4114 |
|---|---|---|---|---|---|
| | **14" Cut-Off Saw with Tool-Less Wheel Change** "Tool-less" Adjustments for Easy Operation and Increased Productivity | **14" Cut-Off Saw** Large Cutting Capacity; Cuts up to 5" Round and 4" x 7-5/8" Rectangular | **14" Cut-Off Saw** AC/DC only on 2414DB | **12" Metal Cutting Saw** For Cutting in Pipe, Angle Iron, Conduit and More | **14" SJS™ Angle Cutter** Built in Dust Port for Reduced Dust and Debris when Connected to a Vacuum |
| Blade Diameter | 14" | 14" | 14" | 12" | 14" |
| Arbor | 1 | 1" | 1" | 1" | 1" |
| AMPS | 15 | 15 | 15 | 15 | 15 |
| Overall Length | 20-7/8" | 19-3/4" | 19-3/4" | 20-1/4" | 26-1/2" |
| Net Weight | 37.9 lbs. | 37 lbs. | 40.6 lbs. / 37.1 lbs. | 42.5 lbs. | 23.8 lbs. |

## Circular Saws

| | 5007MG | 5007MGA | 5007F | 5007FA | XSH01X |
|---|---|---|---|---|---|
| | MAGNESIUM™ **7-1/4" Magnesium Circular Saw** Most Refined Saw with Magnesium Components | MAGNESIUM™ **7-1/4" Magnesium Circular Saw** More Refined Saw with Magnesium Components and an Electric Brake | **7-1/4" Circular Saw** #1 Contractor Circular Saw Preferred by Professional Contractors | **7-1/4" Circular Saw** With Electric Brake | XSH01Z BARE TOOL AVAILABLE LXT BRUSHLESS **18v X2 LXT® (36v) 7-1/4" Circular Saw Kit** Cutting Performance of a Corded Saw |
| Blade Diameter | 7-1/4" | 7-1/4" | 7-1/4" | 7-1/4" | 7-1/4" |
| Arbor | 5/8" | 5/8" | 5/8" | 5/8" | 5/8" |
| No Load Speed | 5,800 RPM | 5,800 RPM | 5,800 RPM | 5,800 RPM | 4,800 RPM |
| AMPS / Battery | 15 | 15 | 15 | 15 | 2X 18v LXT® Lithium-Ion (3.0 Ah) |
| Net Weight | 10.6 lbs. | 10.6 lbs. | 11.1 lbs. | 11.1 lbs. | 10.1 lbs. |

## Circular Saws

| | HS7600 | 5007NK | 5057KB NEW | 5377MG | 5477NB |
|---|---|---|---|---|---|
| | **7-1/4" Circular Saw** Well-balanced and Lightweight (8.6 lbs.) | **7-1/4" Circular Saw** Improved Design for Increased Performance | **7-1/4" Circular Saw, w/ Dust Collector** Designed for Cutting Fiber-Cement | MAGNESIUM™ **7-1/4" Magnesium Hypoid Saw** Hypoid Gears Deliver More Power to the Blade for More Efficient Cutting | **7-1/4" Hypoid Saw** Heat-Treated Hypoid Gears are Designed for Less Maintenance |
| Blade Diameter | 7-1/4" | 7-1/4" | 7-1/4" | 7-1/4" | 7-1/4" |
| Arbor | 5/8" | 5/8" | 5/8" | 5/8" | 5/8" |
| No Load Speed | 5,200 RPM | 5,800 RPM | 5,800 RPM | 4,500 RPM | 4,500 RPM |
| AMPS | 10.5 | 15 | 13 | 15 | 15 |
| Net Weight | 8.6 lbs. | 11 lbs. | 11.8 lbs. | 13.2 lbs. | 14.3 lbs. |

## Circular Saws

| | XSH03MB | 5005BA | 4101RH | 4100NH | SP6000J / SP6000J1 |
|---|---|---|---|---|---|
| | XSH03Z BARE TOOL AVAILABLE LXT BRUSHLESS AUTOMATIC SPEED CHANGE **18v LXT® Brushless 6-1/2" Circular Saw Kit** Automatic Speed Change™ Technology | **5-1/2" Circular Saw** Cuts 2x Lumber at 90° | **5" Masonry Saw** For Wet Cutting of Tile, Masonry, Concrete and More | **4-3/8" Masonry Saw** Powerful Cutting in Stone, Masonry, Tile & Concrete | **6-1/2" Plunge Circular Saw** Delivers Splinter-Free Cuts |
| Blade Diameter | 6 1/2" | 5-1/2" | 5" | 4-3/8" | 6-1/2" |
| Arbor | 5/8" | 5/8" | 3/4" | 3/4" | 20mm |
| No Load Speed | 5,000 RPM | 8,000 RPM | 13,800 RPM | 14,500 RPM | 2,000 - 5,200 RPM |
| AMPS / Battery | 18V LXT® Lithium-Ion (4.0Ah) | 8 | 7.9 | 12 | 12 |
| Net Weight | 7.3 lbs. | 6.2 lbs. | 6.5 lbs. | 6.5 lbs. | 9.7lbs. / 16.5lbs. |

## Circular Saws

| | 5008MGA | 5104 | 5402NA |
|---|---|---|---|
| | MAGNESIUM™ **8-1/4" Magnesium Circular Saw** Largest Cutting Capacity in its Class | **10 1/4" Circular Saw** Cuts 4x Lumber in a Single Pass | **16-5/16" Circular Saw** Large Cutting Capacity for Beams and Timber |
| Blade Diameter | 8-1/4" | 10-1/4" | 16-5/16" |
| Arbor | 5/8" | 5/8" | 1" |
| No Load Speed | 5,200 RPM | 3,800 RPM | 2,200 RPM |
| AMPS | 15 | 14 | 15 |
| Net Weight | 11.4 lbs. | 20.3 lbs. | 32.1 lbs. |

**GET SERVICE**

Go online to makitatools.com and download parts breakdowns and owner manuals for your tools.

**makitatools.com**

## Recipro Saws

| | JR3070CT | JR3070CTZ | JR3050T | JR3050TZ |
|---|---|---|---|---|
| | AVT® Anti Vibration Technology **AVT® Recipro Saw - 15 AMP** Anti-Vibration Technology for 2X Less Vibration (Lock On) | AVT® Anti Vibration Technology **AVT® Recipro Saw - 15 AMP** Anti-Vibration Technology for 2X Less Vibration (No Lock On) | **Recipro Saw - 11 AMP** Powerful Motor for improved performance (Lock On) | **Recipro Saw - 11 AMP** Powerful Motor for improved performance (No Lock On) |
| Length of Stroke | 1-1/4" | 1-1/4" | 1-1/8" | 1-1/8" |
| Strokes Per Minute | 0 - 2,800 SPM | 0 - 2,800 SPM | 0 - 2,800 SPM | 0 - 2,800 SPM |
| AMPS | 15 | 15 | 11 | 11 |
| Overall Length | 19-1/8" | 19-1/8" | 17-3/4" | 17-3/4" |
| Net Weight | 10 lbs. | 9.6 lbs. | 7.3 lbs. | 7.3 lbs. |

**AVT® Anti Vibration Technology**

**Up to 60% Less Vibration***

*When compared to Makita hammers without AVT® Anti Vibration Technology

## Jig Saws

| | 4350FCT | 4351FCT | JV0600K | 4329K | XVJ02Z |
|---|---|---|---|---|---|
| | **Top Handle Jig Saw** Precision Engineering Delivers Best-in-Class Cutting | **Barrel Grip Jig Saw** Barrel Grip Design is Closer to the Work Surface for More Precise Cuts | **Top Handle Jig Saw** Powerful 6.5 AMP Motor | **Top Handle Jig Saw** 3 Orbital Settings Plus Straight Cutting | Tool only, battery & charger not included LXT BRUSHLESS **18v LXT® Brushless Jig Saw** Up To 45% Faster Cutting |
| Length of Stroke | 1" | 1" | 7/8" | 11/16" | 1" |
| Strokes Per Minute | 800 - 2,800 SPM | 800 - 2,800 SPM | 500 - 3,100 SPM | 500 - 3,100 SPM | 800 - 3,500 SPM |
| Blade Shank | "T" Tang | "T" Tang | "T" Tang | "T" Tang | "T" Tang |
| AMPS / Battery | 6.3 | 6.3 | 6.5 | 3.9 | No Battery Included |
| Net Weight | 5.7 lbs. | 5.5 lbs. | 5.2 lbs. | 4.2 lbs. | 5.8 lbs. |

## Jig Saws / Miter Saws

| | XVJ03 | LS1216L | LS1216LX4 | LS1016L |
|---|---|---|---|---|
| | XVJ03Z LXT **18v LXT® Jig Saw** Custom Cutting Without a Cord | DXT LASER **12" Dual Slide Compound Miter Saw** Cuts Up to 8" Crown and 15" at 90° | DXT LASER **12" Dual Slide Compound Miter Saw** Cuts Up to 8" Crown and 15" at 90° | DXT LASER **10" Dual Slide Compound Miter Saw** Largest Crown Molding Cutting Capacity |
| Length of Stroke | 1" | Blade Diameter | 12" | 12" | 10" |
| Strokes Per Minute | 0 - 2,600 SPM | Arbor | 1" | 1" | 5/8" |
| Blade Shank | "T" Tang | Capacities (90°)( 45°) | (3-5/8"x15")( 3-5/8"x10-1/2") | (3-5/8"x15")( 3-5/8"x10-1/2") | (2-13/16"x12")( 2-13/16"x8-1/2") |
| Battery | 18v LXT® Lithium-Ion (3.0Ah) | No Load Speed | 3,200 RPM | 3,200 RPM | 3,200 RPM |
| Net Weight | 5.8 lbs. | Net Weight | 58.6 lbs. | 116.2 lbs. | 53.3 lbs. |

## Miter Saws

| | LS1016 | LS1016LX5 | LS1018 | LS0815F | XSL01 NEW |
|---|---|---|---|---|---|
| | DXT **10" Dual Slide Compound Miter Saw** Largest Crown Molding Cutting Capacity | DXT LASER **10" Dual Slide Compound Miter Saw** Largest Crown Molding Cutting Capacity | **10" Dual Slide Compound Miter Saw** Compact Design with Less Weight | **8-1/2" Slide Compound Miter Saw** Job Site Portability | XSL01Z LXT **18v LXT® 7-1/2" Compound Miter Saw Kit** Large Cutting Capacity |
| Blade Diameter | 10" | 10" | 10" | 8-1/2" | 7-1/2" |
| Arbor | 5/8" | 5/8" | 5/8" | 5/8" | 5/8" |
| Capacities (90°)( 45°) | (2-13/16"x12")( 2-13/16"x8-1/2") | (2-13/16"x12")( 2-13/16"x8-1/2") | (3-5/8" x 12")( 3-5/8" x 8-1/2") | (2-9/16"x12")( 2-9/16"x8-1/2") | (2-1/16"x11-3/4")( 2 1/16"x8 3/8") |
| No Load Speed | 3,200 RPM | 3,200 RPM | 4,300 RPM | 5,000 RPM | 2,200 RPM |
| Net Weight | 53.1 lbs. | 110.2 lbs. | 43.7 lbs. | 31.1 lbs. | 27.5 lbs. |

## Miter Saws & Stands

| | XSL02Z | LS1221 | LS1040 | 195083-4 | WST05 |
|---|---|---|---|---|---|
| | Tool only, battery & charger not included LXT BRUSHLESS AUTOMATIC SPEED CHANGE **18v X2 LXT® Brushless 7-1/2" Compound Miter Saw** Powerful BL™ Brushless Motor | **12" Compound Miter Saw** Consistently Precise Cutting Performance | **10" Compound Miter Saw** Pivoting Fence for Supporting Larger Material | **Jobsite Miter Saw Stands** Ideal for Jobsite Use | **Jobsite Miter Saw Stands** Large Solid Rubber Wheels for Easier Jobsite Portability |
| Blade Diameter | 7-1/2" | 12" | 10" | Material Support Extensions: 9' | Material Support Extensions: 9' |
| Arbor | 5/8" | 5/8" | 5/8" | In Feed Roller: Yes | In Feed Roller: Yes |
| Capacities bevel miter (90°)( 45°) | (2-1/16"x11-3/4")( 2-1/16"x8-3/8") | (3-7/8"x6")( 2-3/4"x5-7/8") | (2-3/4"x5-1/8")( 1-3/8"x3-5/8") | Material Stop: Yes | Material Stop: Yes |
| No Load Speed | 5,700 RPM | 4,000 RPM | 4,600 RPM | Folded Dimensions: 50-1/2" | Folded Dimensions: 46" |
| Net Weight | 28.9 lbs. | 37 lbs. | 27.3 lbs. | Net Weight: 79 lbs. | Net Weight: 58 lbs. |

## Table Saws & Stands / Planer

| | 2705 | 2705X1 | 194093-8 | 2012NB |
|---|---|---|---|---|
| | **10" Table Saw** Precision Machined Table Top for Accurate Cuts | **10" Contractor Table Saw with Stand** Precision Machined Table Top | **Portable Table Saw Stand** Mobility Simplified | **12" Portable Planer** Automated Head Clamp Eliminates Snipe |
| Blade Diameter | 10" | 10" | - | No. of Knives | 2 |
| Arbor | 5/8" | 5/8" | - | Table Size | (WxL)12" x 30-3/8" |
| No Load Speed | 4,800 RPM | 4,800 RPM | - | AMPS | 15 |
| Net Weight | 65.5 lbs. | 114.7 lbs. | - | Net Weight | 61.9 lbs. |
| Shipping Weight | 82 lbs. | 171 lbs. | - | Shipping Weight | 67.6 lbs. |

## Routers

| | RP2301FC | RP1800 | RP0900K | RF1101KIT2 | RF1101 |
|---|---|---|---|---|---|
| | **3-1/4 HP* Plunge Router** Delivers Power and Precision | **3-1/4 HP* Plunge Router** Deep 2-3/4" Depth Capacity Delivers Performance | **1-1/4 HP* Plunge Router** Powerful 8 AMP Motor Delivers 27,000 RPM | **2-1/4 HP* Router Kit, with Plunge Base** Includes the Most Popular Accessories | **2-1/4 HP* Router** Quietest and Lowest Vibration Router in its Class |
| Collet Capacity | 1/2", 1/4" | 1/2", 1/4" | 1/4" | 1/2", 1/4" | 1/2", 1/4" |
| AMPS | 15 | 15 | 8 | 11 | 11 |
| Plunge Capacity | 2-3/4" | 2-3/4" | 1-3/8" | **Max. Horsepower:** 2-1/4 HP | **Max. Horsepower:** 2-1/4 HP |
| No Load Speed | 9,000 - 22,000 RPM | 22,000 RPM | 27,000 RPM | 8,000 - 24,000 RPM | 8,000 - 24,000 RPM |
| Net Weight | 13.4 lbs. | 13.4 lbs. | 6 lbs. | 7.2 lbs. | 7.2 lbs. |

## Routers

| | RD1101 | RT0701CX3 | RT0701CX7 | RT0701C | 3709 |
|---|---|---|---|---|---|
| | **2-1/4 HP* Router** Variable Speed (8,000-24,000 RPM) | **1-1/4 HP* Compact Router Kit** Powerful 1-1/4 HP* Motor for Improved Performance | **1-1/4 HP* Compact Router Kit** Powerful 1-1/4 HP* Motor Delivers Improved Performance | **1-1/4 HP* Compact Router** Powerful 1-1/4 HP* Motor Delivers Performance and Accuracy | **1/4" Fixed Base Laminate Trimmer** Rack-and-Pinion Depth Adjustments |
| Collet Capacity | 1/2", 1/4" | 1/4" | 1/4" | 1/4" | 1/4" |
| AMPS | 11 | 6.5 | 6.5 | 6.5 | 4 |
| No Load Speed | 8,000 - 24,000 RPM | 10,000 - 30,000 RPM | 10,000 - 30,000 RPM | 10,000 - 30,000 RPM | 30,000 RPM |
| Max. Horsepower | 2-1/4 HP | 1-1/4 HP | 1-1/4 HP | 1-1/4 HP | Overall Length: 7-7/8" |
| Net Weight | 7.9 lbs. | 3.9 lbs. | 3.9 lbs. | 3.9 lbs. | 3.3 lbs. |

## Sanders

| | B05030 / B05030K | B05031K | B05041 / B05041K | B06050J NEW | B06030 |
|---|---|---|---|---|---|
| | **5" Random Orbit Sander** Rubberized Grip for Increased Comfort | **5" Random Orbit Sander, with Case** 3.0 AMP Motor; Includes Tool Case | **5" Random Orbit Sander, with Variable Speed** More Power for Faster Sanding | **6" Random Orbit Sander** Fine or Fast Finish with 2-Mode Selection | **6" Random Orbit Sander** 30% Less Vibration than the Nearest Competitor |
| Pad Size | 4-13/16" | 4-13/16" | 4-13/16" | 6" | 6" |
| AMPS | 3 | 3 | 3 | 6.6 | 2.7 |
| Orbit Diameter | 1/8" | 1/8" | 1/8" | 7/32" | 1/8" |
| Orbits Per Minute | 12,000 OPM | 4,000-12,000 OPM | 4,000 - 12,000 OPM | 1,600 - 6,800 OPM | 4,000 - 10,000 OPM |
| Net Weight | 2.9 lbs. | 3 lbs. | 3.5 lbs. | 5.7 lbs. | 5.2 lbs. |

## Sanders

| | X0B01 | B04556 / B04556K | B03710 | B04900V | 9032 |
|---|---|---|---|---|---|
| | BARE TOOL AVAILABLE X0B01Z LXT **18v LXT® 5" Random Orbit Sander Kit** Corded Performance without the Cord | **Finishing Sander** 14,000 OPM for Fast and Smooth Finish Sanding | **1/3 Sheet Finishing Sander** Lower Vibration and Smooth Finish | **1/2 Sheet Finishing Sander** Through-the-Pad Dust Collection System | **3/8" x 21" Belt Sander** Compact Design for Sanding in Close Quarters |
| Pad Size | 4-7/8" | 4-1/2" x 4" | 3-5/8" x 7-1/4" | 4-1/2" x 9" | Belt Size: 3/8" x 21" |
| AMPS / Battery | 18v LXT® Lithium-Ion (3.0Ah) | 2 | 1.7 | 2.9 | 4.4 |
| Orbits Per Minute | 7,000, 9,500, 11,000 OPM | 14,000 OPM | 11,000 OPM | 4,000 - 10,000 OPM | **Belt Speed:** 980 - 5,600 ft./min. |
| Overall Length | 6-7/8" | 5-1/8" | 10 | 11-3/8" | 16-1/2" |
| Net Weight | 3.6 lbs. | 2.5 lbs. | 3.5 lbs. | 6 lbs. | 3.5 lbs. |

## Sanders

| | 9031 | 9903 | 9920 | 9924DB | 9404 |
|---|---|---|---|---|---|
| | **1-1/8" x 21" Belt Sander** Variable Speed Control Dial | **3" x 21" Belt Sander** Powerful 8.8 AMP Motor; only 85dB | **3" x 24" Belt Sander** Powerful 8.8 AMP Motor; Only 84dB | **3" x 24" Belt Sander** Low Profile Balanced Design | **4" x 24" Belt Sander** Variable Speed Control Dial |
| Belt Size | 1-1/8" x 21" | 3" x 21" | 3" x 24" | 3" x 24" | 4" x 24" |
| AMPS | 5 | 8.8 | 8.8 | 7.8 | 8.8 |
| Belt Speed | 656 - 3,280 ft./min. | 690 - 1,440 ft./min. | 690 - 1,440 ft./min. | 1,300 ft./min. | 690 - 1,440 ft./min. |
| Overall Length | 15" | 11-5/8" | 13-1/8" | 14" | 13-1/8" |
| Net Weight | 4.6 lbs. | 9.5 lbs. | 9.9 lbs. | 10.6 lbs. | 10.3 lbs. |

*Maximum horsepower

## Sanders

| | 9403 | 9741 |
|---|---|---|
| | **4" x 24" Belt Sander** Powerful 11 AMP Motor for High Production Use | **Wheel Sander** Unique Design for More Controlled Operation |
| Belt Size | 4" x 24" | Wheel Size 4-3/4" x 4" |
| Belt Speed | 1,640 ft./min. | 3,500 RPM |
| AMPS | 11 | 7.8 |
| Overall Length | 13-7/8" | 12-1/4" |
| Net Weight | 12.6 lbs. | 9.3 lbs. |

## Multi-Tools

| | TM3010CX1 | XMT035 |
|---|---|---|
| | **Multi-Tool Kit** "Tool-less" Clamp System for Fast Accessory Installation | XMT035Z LXT **18v LXT® Multi-Tool Kit** "Tool-less" Clamp System for Fast Accessory Installation |
| Oscillations Per Minute | 6,000 - 20,000 OPM | 6,000 - 20,000 OPM |
| Oscillation Angle | 3.2° | 3.2° |
| AMPS / Battery | 3 | 18v LXT® Lithium-Ion (3.0Ah) |
| Overall Length | 11-1/8" | 13-3/8" |
| Net Weight | 3.5 lbs. | 4.9 lbs. |

## Planers

| | KP0800K | KP0810 | XPK01 | 1002BA | 1912B |
|---|---|---|---|---|---|
| | **3-1/4" Planer, with Tool Case** High Power-to-Weight Ratio; Weighs Only 5.7 lbs. | **3-1/4" Planer Kit** Powerful with Less Weight (7.5 AMP Motor; 7.3 lbs.) | XPK01Z LXT **18v LXT® 3-1/4" Planer Kit** Planes Up to 3-1/4" Wide and 5/64" Deep in a Single Pass | **4-3/8" Curved Base Planer** Large Planing Width Engineered for an Even Cut | **4-3/8" Planer** Planes up to 4-3/8" Wide and 1/16" Deep |
| Planing Width | 3-1/4" | 3-1/4" | 3-1/4" | 4-3/8" | 4-3/8" |
| Planing Depth | 3/32" | 5/32" | 5/64" | 3/16" | 1/16" |
| No Load Speed | 17,000 RPM | 16,000 RPM | 14,000 RPM | 15,000 RPM | 16,000 RPM |
| AMPS | 6.5 | 7.5 | 18v LXT® Lithium-Ion (3.0Ah) | 9.6 | 7.5 |
| Net Weight | 5.7 lbs. | 7.3 lbs. | 7.4 lbs. | 11.4 lbs. | 9.3 lbs. |

## Planers

| | 1806B | KP312 |
|---|---|---|
| | **6-3/4" Planer** Unrivaled for Shear Power and Performance | **12-1/4" Planer** Precision Engineered for an Even Cut Every Time |
| Planing Width | 6-3/4" | 12-1/4" |
| Planing Depth | 1/16" | 1/8" |
| No Load Speed | 15,000 RPM | 12,000 RPM |
| AMPS/Battery | 10.9 | 15 |
| Net Weight | 19.8 lbs. | 40.6 lbs. |

## Plate Joiner

| | PJ7000 | XJP03Z |
|---|---|---|
| | **Plate Joiner** Rack-and-Pinion Vertical Fence Adjustments | XJP03Z LXT **18V LXT® Plate Joiner** Delivers up to 300 Cuts for #0 Biscuits on a Single Charge |
| Blade Diameter | 4" | 4" |
| Max. Cutting Depth | 3/4" | 3/4" |
| No Load Speed | 11,000 RPM | 6,500 RPM |
| AMPS/Battery | 5.6 | No Battery Included |
| Net Weight | 5.5 lbs. | 6.7 lbs. |

## Blade Sharpener

| | 98202 |
|---|---|
| | **Blade Sharpener** Precision Sharpening of Planer Blades and More |
| Wheel Size | 7-7/8" |
| No Load Speed | 560 RPM |
| AMPS | 1.1 |
| Overall Length | 15-3/8" |
| Net Weight | 24.3 lbs. |

## Chain Mortiser

| | 7104L |
|---|---|
| | **Chain Mortiser** Ideal for Timber Framing or Log Home Building |
| Max. Hole Width (longitudinal) | 5-1/8" |
| Max. Hole Width (transverse) | 1-1/4" |
| Max. Hole Depth | 6-1/8" |
| No Load Speed | 3,200 RPM |
| Chain Speed | 1,000 FPM |

## Blower

| | UB1103 |
|---|---|
| | **Blower** Delivers a Maximum Air Speed of 203 MPH for Faster Job Site Clean Up |
| AMPS | 6.8 |
| Max. Air Volume | 145 CFM |
| Max. Air Velocity | 203 MPH |
| No Load Speed | 0 - 16,000 RPM |
| Overall Length | 18-7/8" |

## Heat Gun

| | HG551V |
|---|---|
| | **Heat Gun** Low Vibration and Noise, Ideal for Indoor Applications |
| Air Temperature | 180° - 1,020° F |
| Air Volume | 8.8 and 16 CFM |
| AMPS | 12 |
| Watts (AC only) | 1,400 |
| Overall Length | 9" |

**STAR PROTECTION COMPUTER CONTROLS™** OVERLOAD OVER-DISCHARGE OVERHEAT WITH BATTERY & TOOL

The demanding applications you take on every day are also demanding on your cordless tools and batteries. You rely on your tools, so Makita created STAR Protection Computer Controls™. STAR Protection is communication technology that allows the tool and battery to monitor conditions and exchange data in real time to protect against Overloading, Over-Discharging and Over-heating.

## Nailers

| | AN930H | AN610H | AN923 | AN902 | AN611 |
|---|---|---|---|---|---|
| | **3-1/2" High Pressure Framing Coil Nailer** Superior Power-to-Weight Ratio | **2-1/2" High Pressure Siding Coil Nailer** Delivers Precise Flush Nailing | **3-1/2" Framing Nailer** Drives up to 3-1/2" x .162" (16d) nails | **3-1/2" Framing Coil Nailer** More Power and Less Weight for Increased Versatility | **2-1/2" Siding Coil Nailer** "Tool-less" Depth Adjustment with 9 Settings |
| Operating Air Pressure | 170 - 320 PSI | 140 - 320 PSI | 65 - 120 PSI | 60 - 120 PSI | 65 - 120 PSI |
| Nail Size (in., ga.) | 1-3/4" to 3-1/2" ( ga.) | 1-1/4"-2-1/2".080"-.113" | 2" - 3-1/2" .113" - .162" | 1-3/4" - 3-1/2" .099" - .148" | 1-1/4" - 2-1/2" .080" - .099" |
| Magazine Capacity (range) | 150 - 300 | 200 - 400 | 64 - 74 | 150 - 300 | 200 - 400 |
| Dimensions (LxWxH) | 11-1/4" x 5" x 13" | 11-1/8" x 5-3/8" x 10-7/8" | 22" x 4-1/4" x 13-11/16" | 12-1/2" x 5" x 14-7/8" | 13-1/16" x 5" x 12-1/2" |
| Net Weight | 5.7 lbs. | 4.2 lbs. | 8.7 lbs. | 7.7 lbs. | 5.1 lbs. |

## Nailers

| | AN453 | AF635 NEW | AF601 NEW | AF505N | AF353 NEW |
|---|---|---|---|---|---|
| | **1-3/4" Roofing Coil Nailer** Easy-Loading Adjustable Canister | **2-1/2" Angled Finish Nailer, 15 Ga.** Feature Rich for Professional Performance | **2-1/2" Straight Finish Nailer, 16 Ga.** Engineered for More Precise Finish | **2" Brad Nailer, 18Ga.** Narrow nose design allows easy nailing access in confined areas | **1-3/8" Pin Nailer, 23 Ga.** Beauty and Convenience of Minimal Nail Holes |
| Operating Air Pressure | 65 - 120 PSI | 70 - 120 PSI | 70 - 120 PSI | 60 - 115 PSI | 65 - 100 PSI |
| Nail Size (in., ga.) | 3/4" - 1-3/4" | 1-1/4" to 2-1/2" (15 Ga.) | 1 - 2-1/2" (16 Ga.) | 5/8" to 2" (18 ga.) | 5/8" to 1-3/8" (23 Ga.) |
| Magazine Capacity (range) | 150 - 300 | 100 | 100 | 100 | 130 |
| Dimensions (LxWxH) | 10-3/8" x 4-5/8" x 10-5/8" | 13-3/8" x 3-15/16" x 12-1/8" | 12" x 3-3/4" x 11-3/4" | 10-1/4" x 2-1/2" x 9-3/8" | 8-3/16" x 2-5/8" x 7-1/2" |
| Net Weight | 5.2 lbs. | 4 lbs. | 3.8 lbs. | 3 lbs. | 2 lbs. |

## Nailers

| | AT2550A | AT1150A | AT638A |
|---|---|---|---|
| | **1" Wide Crown Stapler** Lightweight Design for Comfort and Control | **7/16" Medium Crown Stapler** Clear Jammed Nails Easily with Cam-Lock | **1/4" Narrow Crown Stapler, 18 Ga.** Designed for a Variety of Applications |
| Operating Air Pressure | 65 - 120 PSI | 65 - 120 PSI | 70 - 120 PSI |
| Staple Length (in.) | 1" to 2" | 1" to 2" | 1/2" to 1-1/2" |
| Magazine Capacity (range) | 140 | 140 | 100 |
| Dimensions (LxWxH) | 14-1/2" x 3" x 10-1/4" | 14-1/2" x 3-7/16" x 11-3/8" | 9" x 2-15/16" x 9-7/8" |
| Net Weight | 5.1 lbs. | 4.9 lbs. | 2.7 lbs. |

## Compressors

| | AC310H |
|---|---|
| | **2.5 HP* High Pressure Air Compressor** Technology Delivers 400 PSI Capacity |
| Maximum Horsepower | 2-1/2 HP |
| Running Horsepower | 1.9 HP |
| Tank | 1.6 gal. |
| Maximum Pressure | 400 PSI |
| Net Weight | 79.4 lbs. |

## Compressors

| | MAC5501G | MAC5200 | MAC2400 | MAC700 | AC001 |
|---|---|---|---|---|---|
| | BIG BORE™ **5.5 HP* Big Bore™ Gas Air Compressor** Provides 12.5 CFM at 100 PSI | BIG BORE™ **3.0 HP* Big Bore™ Air Compressor** Powerful For Two Framing Nailers | BIG BORE™ **2.5 HP* Big Bore™ Air Compressor** Pump Runs at Lower RPM Resulting in Lower Noise (79dB) | BIG BORE™ **2.0 HP* Big Bore™ Air Compressor** With Low Noise and High Draw Output | **Compact Air Compressor** Low Noise and Less Weight |
| Maximum Horsepower | 5.5 HP | 3 HP | 2.5 HP | 2 HP | 1/6 HP |
| Running Horsepower | 5.5 HP | 2.1 HP | 2.1 HP | 1.7 HP | 1/6 HP |
| Tank | 10 gal. | 5.2 gal. | 4.2 gal. | 2.6 gal. | 1 gal. |
| Maximum Pressure | 135 PSI | 140 PSI | 130 PSI | 130 PSI | 125 PSI |
| Net Weight | 190 lbs. | 88 lbs. | 77 lbs. | 52 lbs. | 23.1 lbs. |

## ADVANTAGES OF MAKITA HIGH PRESSURE PNEUMATICS

**MORE POWER -** High pressure compressor technology delivers 400 PSI

**LESS WEIGHT -** Nailers are up to 30% less weight than conventional nailers

**BETTER PERFORMANCE -** Dual-head (2-stage) pump compressor provides faster recovery time

HIGH PRESSURE TECHNOLOGY

Drives Nails into OSB, LVL & Gluelam

**INCREASED EFFICIENCY**
Low amp draw reduces tripped breakers and voltage drop during start-ups

## Blowers

| | EB7650TH | EB7650WH | BBX7600N | BHX2500CA | PM7650H |
|---|---|---|---|---|---|
| | MM4 4-STROKE ENGINE<br>**75.6 cc MM4® Backpack Blower**<br>High Air Volume (670 CFM) and Air Speed (200 MPH) | MM4 4-STROKE ENGINE<br>**75.6 cc MM4® Hip Throttle Backpack Blower**<br>High Air Volume (670 CFM) and Air Speed (200 MPH) for Commercial Duty Performance | MM4 4-STROKE ENGINE<br>**75.6 cc MM4® Backpack Blower**<br>Efficient 4-Stroke Engine, No Fuel Mix Required | MM4 4-STROKE ENGINE<br>**24.5 cc MM4® Blower**<br>No Fuel Mix Required, Lower Emissions | MM4 4-STROKE ENGINE<br>**75.6 cc MM4® Mist Blower**<br>Efficient 4-Stroke Engine, No Fuel Mix Required |
| Engine Displacement (cc) | 75.6 cc | 75.6 cc | 75.6 cc | 24.5 cc | 75.6 cc |
| Engine (HP) | 3.8 HP | 3.8 HP | 3.8 HP | 1.1 HP | 3.67 HP |
| Max Air Volume | 670 CFM | 670 CFM | 526 CFM | 356 CFM | 496 CFM |
| Max. Air Velocity | 200 MPH | 200 MPH | 195 MPH | 145 MPH | Tank: 3.9 gal. |
| Fuel Type | Unleaded gas | Unleaded gas | Unleaded gas | Unleaded gas | Unleaded gas |

## Blowers

| | UB360DWB | XBU02Z | XBU01Z |
|---|---|---|---|
| | 36V BATTERY POWERED<br>**36v Blower Kit**<br>Delivers up to 14 Minutes of Run Time with 36v Battery Under No Load on Highest Setting | Tool only, battery & charger not included<br>LXT BRUSHLESS<br>**18v X2 LXT® (36v) Brushless Blower**<br>Makita-built BL™ Brushless Motor Produces a Maximum 473 CFM | Tool only, battery & charger not included<br>LXT X2 18V (36V)<br>**18v X2 LXT® (36v) Blower**<br>Makita-built Motor Produces a Maximum Air Volume of 155 CFM |
| Max Air Volume | 155 CFM | 473 CFM | 155 CFM |
| Max. Air Velocity | 208 MPH | 120 MPH | 208 MPH |
| No Load Speed (variable speed) | 0 - 10,000 / 0 - 17,000 RPM | 11,400 - 21,500 RPM | 0 - 10,000 / 0 - 17,000 RPM |
| Battery | 36v LXT® Lithium-Ion (2.2Ah) | No Battery Included | No Battery Included |
| Net Weight (with battery) | 6.8 lbs. | 9.9 lbs. | 8 lbs. |

## Grass Shear

| | XMU02Z |
|---|---|
| | Tool only, battery & charger not included<br>LXT<br>**18v LXT® Grass Shear**<br>Up to 125 Minutes of Run Time with 3.0Ah battery Under No Load |
| Cutting Capacity (width) | 6-5/16" |
| Depth Adjustment Range | 3/8", 13/16", 1-3/16" |
| No Load Speed | 1,250 RPM |
| Battery | No Battery Included |
| Net Weight (with battery) | 3.6 lbs. |

## Pruners, Edgers, & Trimmers

| | EY2650H25H | EE2650H | EN7350SH | EN5950SH | EN49515SH |
|---|---|---|---|---|---|
| | MM4 4-STROKE ENGINE<br>**25.4 cc MM4® Telescoping Pole Pruner**<br>Powerful MM4 Engine, No Fuel Mix Required, Lower Emissions | MM4 4-STROKE ENGINE<br>**25.4 cc MM4® Edger**<br>No Fuel Mix Required, Lower Emissions | MM4 4-STROKE ENGINE<br>**30" 25.4 cc MM4® Single-Sided Hedge Trimmer**<br>30" Single-Sided Blade with High Blade Speed (4,200 SPM) for Efficient Cutting | MM4 4-STROKE ENGINE<br>**24" 25.4 cc MM4® Double-Sided Hedge Trimmer**<br>24" Double-Sided Blade with High Blade Speed (4,200 SPM) for Efficient Cutting | MM4 4-STROKE ENGINE<br>**24" 25.4 cc MM4® Double-Sided Hedge Trimmer**<br>24" Double-Sided Blade with High Blade Speed (4,200 SPM) for Efficient Cutting |
| Engine Displacement (cc) | 25.4 cc | 25.4 cc | 25.4 cc | 25.1 cc | 25.1 cc |
| Engine (HP) | 1.1 HP | 1.1 HP | 1.1 HP | 1.1 HP | 1.1 HP |
| Overall Length | 154-1/2" | 154-1/2" | **Blade Length:** 30" | **Blade Length:** 24" | **Blade Length:** 24" |
| Guide Bar Length | 10" | 10" | **Blade Speed:** 4,200 SPM | **Blade Speed:** 4,200 SPM | **Blade Speed:** 4,200 SPM |
| Fuel Type | Unleaded gas | Unleaded gas | Unleaded gas | Unleaded gas | Unleaded gas |

## Pruners, Edgers, & Trimmers

| | EN4950H | EM2652LHN | EM2650LH | EM2650UH | XRU07Z NEW |
|---|---|---|---|---|---|
| | MM4 4-STROKE ENGINE<br>**20" 25.4 cc MM4® Articulating Hedge Trimmer**<br>13 Angle Settings for Efficient Trimming of Overhead And Low-Lying Hedges | MM4 4-STROKE ENGINE<br>**25.4 cc MM4® High Torque String Trimmer**<br>High Torque Gear Case For Improved Cutting Performance | MM4 4-STROKE ENGINE<br>**25.4 cc MM4® High Torque String Trimmer**<br>Powerful Multi-Position 4-Stroke Engine | MM4 4-STROKE ENGINE<br>**25.4cc MM4® Brush Cutter**<br>Powerful Multi-Position 4-Stroke Engine | Tool only, battery & charger not included<br>LXT X2 18V (36V) BRUSHLESS<br>**18v X2 LXT® (36v) Brushless String Trimmer**<br>Zero Emissions and Reduced Maintenance; No Need for Gas or oil |
| Engine Displacement (cc) | 25.4 cc | 25.4 cc | 25.4 cc | 25.4 cc | **Cutting Capacity (diameter):** 13-3/4" |
| Engine (HP) | 1.1 HP | 1.1 HP | 1.1 HP | 1.1 HP | **No Load Speed (2 spd):** 5,000/6,500 RPM |
| Overall Length | 154-1/2" | 69-1/2" | 69-1/2" | 69-1/2" | **Overall Length:** 69" |
| Guide Bar Length | 10" | **Fuel Tank Capacity:** 20.3 oz. | **Fuel Tank Capacity:** 20.3 oz. | **Fuel Tank Capacity:** 20.3 oz. | **Battery:** No Battery Included |
| Fuel Type | Unleaded gas | Unleaded gas | Unleaded gas | Unleaded gas | **Net Weight (w/battery):** 9.9 lbs. |

## Pruners, Edgers, & Trimmers

| | XRU04Z | XRU02Z |
|---|---|---|
| | Tool only, battery & charger not included<br>LXT<br>**18v LXT® Brushless String Trimmer**<br>Up to 60 Minutes of Run Time with 3.0Ah Battery under No Load on the Lowest Setting | Tool only, battery & charger not included<br>LXT<br>**18v LXT® String Trimmer**<br>Up to 45 Minutes of Run Time with 3.0Ah Battery Under No Load |
| Cutting Capacity (diameter) | 11-3/4" | 10-1/4" |
| No Load Speed | 3,500/6,000 RPM | 7,800 RPM |
| Battery | No Battery Included | No Battery Included |
| Overall Length | 72-1/2" | 10-1/4" |
| Net Weight (w/battery) | 8.6 lbs. | 6.9 lbs. |

## Chainsaws

| | DCS642120 | EA6100P53G NEW |
|---|---|---|
| | MM2 4-STROKE ENGINE<br>**20" 64 cc Chain Saw**<br>4.7 HP Professional Chain Saw | MM2 4-STROKE ENGINE<br>**20" 64 cc Chain Saw**<br>4.6 HP Professional Chain Saw |
| Engine Displacement(cu.in./cc) | 3.9 cu.in. (64 cc) | 3.7 cu.in. (61 cc) |
| Power Rating | 4.7 HP/3.5 kW | 4.6 HP/3.4 kW |
| Fuel Tank Capacity | 24.5 oz. | 27 oz. |
| Oil Tank Capacity | 14.2 oz. | 16 oz. |
| Net Weight (w/o bar & chain) | 13.9 lbs. | 13.2 lbs. |

## Chainsaws

| | EA5000P53G | DCS5121 | EA4300F40B | EA3601F40B NEW | EA3201S35B |
|---|---|---|---|---|---|
| | | | | | |
| | **20" 50 cc Chain Saw**<br>3.9 HP Professional Chain Saw | **18" 50 cc Chain Saw**<br>Easy Start, Spring-Assisted Starter for Quick Starting with Less Force | **16" 42 cc Chain Saw**<br>High Power-to-Weight Ratio 3.0 HP Engine | **16" 35 cc Chain Saw**<br>Easy Start, Spring-Assisted for Quick Starting with Less Force | **14" 32 cc Chain Saw**<br>Easy Start, Spring-Assisted for Quick Starting with Less Force |
| Engine Displacement(cu.in./cc) | 3.1 cu.in. (50 cc) | 3.1 cu.in. (50 cc) | 42 cu.in. (2.6 cc) | 2.1 cu. in. (35.2 cc) | 2 cu.in. (32 cc) |
| Power Rating | 3.9 HP/2.9 kW | 3.3 HP/2.5 kW | 3 HP/2.2 kW | 2.4 HP/1.8kW | 1.8 HP/1.3 kW |
| Fuel Tank Capacity | 15.9 oz. | 15.9 oz. | 16.2 oz. | 10.5 oz. | 13.5 oz. |
| Oil Tank Capacity | 9.1 oz. | 9.1 oz. | 9.5 oz. | 8.8 oz. | 9.5 oz. |
| Net Weight (w/o bar & chain) | 11.9 lbs. | 12.3 lbs. | 10.8 lbs. | 9.3 lbs. | 9.4 lbs. |

## Chainsaws

| | HCU02C1 | XCU02Z | XCU01Z | UC4051A | UC3551A |
|---|---|---|---|---|---|
| | | Tool only, battery & charger not included | Tool only, battery & charger not included | | |
| | **36v LXT® Chain Saw Kit**<br>Zero Emmissions and up to 40% Quieter Than Gas | **18v X2 LXT® (36v) Chain Saw**<br>Powered by Two 18v LXT® Lithium-Ion Batteries | **18v LXT® 4-1/2" Chain Saw**<br>The Perfect Chain Saw for Limbing, Powered by 18v LXT | **16" Electric Chain Saw**<br>Heavy-Duty for Fast and Efficient Cutting | **14" Electric Chain Saw**<br>Heavy-Duty for Fast and Efficient Cutting |
| Guide Bar Length | 12" | 12" | 4-1/2" | 16" | 14" |
| Chain Speed | 1,650 FPM | 1,650 FPM | 980 FPM | 2,900 FPM | 2,900 FPM |
| Overall Length | 24-5/8" | 24-5/8" | 16-5/8" | **Chain Gauge:** .050" | **Chain Gauge:** .050" |
| Battery | 36v LXT® Lithium-Ion | No Battery Included | No Battery Included | **Oil Tank Capacity:** 6.8 oz. | **Oil Tank Capacity:** 6.8 oz. |
| Net Weight (w/battery) | 10.1 lbs | 8.2 lbs. | 5.4 lbs. | **Overall Length:** 19-7/8" | **Overall Length:** 19-7/8" |

## Chainsaws

| | 5012B |
|---|---|
| | |
| | **11-3/4" Electric Chain Saw**<br>Compact and Lightweight (9.5 lbs.) |
| Guide Bar Length | 11-3/4" |
| Chain Speed | 5,500 FPM |
| Chain Gauge | .050" |
| AMPS | 11.5 |
| Overall Length | 22" |

## 18v X2 TECHNOLOGY

# NO LIMITS

POWER & SPEED TO UNPLUG THE CORD

**36v POWER**

(2) 18v BATTERIES

## Hedge Trimmers

| | UH6570 | UH5570 | HHU01C1 | XHU04Z | XHU02Z |
|---|---|---|---|---|---|
| | | | | Tool only, battery & charger not included | Tool only, battery & charger not included |
| | **25" Electric Hedge Trimmer**<br>Large Cutting Capacity and High Performance | **22" Electric Hedge Trimmer**<br>Large Cutting Capacity and High Performance | **36v LXT® Hedge Trimmer Kit**<br>36v Lithium-ion Battery Delivers the Cutting Performance of a Corded Trimmer | **18v X2 LXT® Hedge Trimmer**<br>Two 18v LXT® Lithium-Ion Batteries Deliver the Cutting Performance of a Corded Trimmer | **18v LXT® Hedge Trimmer**<br>Up to 75 Minutes of Run Time with 3.0Ah Battery on Lowest Setting |
| Capacities: (Diameter) (Length) | 1/2", 25-1/2" | 1/2", 21-5/8" | 25-1/2" | 25-1/2" | 22" |
| Blade Speed | 1,600 SPM | 1,600 SPM | 1,800 SPM | 1,800 SPM | 1,350 SPM |
| AMPS | 4.8 | 4.8 | 36v LXT® Lithium-Ion (2.2Ah) | No Battery Included | No Battery Included |
| Overall Length | 44-3/4" | 40-1/2" | 48-3/4" | 48-3/4" | 38" |
| Net Weight | 8.2 lbs. | 7.9 lbs. | 11.7 lbs. | 11.7 lbs. | 7.4 lbs. |

## EASY START TECHNOLOGY

# EASY START

**Spring-assisted starter** combined with a **low-spark ignition coil** to significantly reduce pull-starting force for easier starts

- Reduces pull-rope resistance by more than 30%
- More dependable starting
- Smoother ignitions
- Lower mechanical wear to starter assembly

## Batteries & Chargers

### 18v Lithium-Ion

**18v LXT® 6.0Ah Lithium-Ion Battery***

6.0Ah BATTERY — 55 Minute Charge Time

NEW **BL1860B (1-Pack)**
**BL1860B-2 (2-Pack)**

**18v LXT® 5.0Ah Lithium-Ion Battery***

5.0Ah BATTERY — 45 Minute Charge Time

NEW **BL1850B (1-Pack)**
**BL1850B-2 (2-Pack)**

**18v LXT® 4.0Ah Lithium-Ion Battery***

4.0Ah BATTERY — 40 Minute Charge Time

NEW **BL1840B (1-Pack)**
**BL1840B-2 (2-Pack)**

**18v LXT® 3.0Ah Lithium-Ion Battery***

3.0Ah BATTERY — 30 Minute Charge Time

**BL1830 (1-Pack)**
**BL1830-2 (2-Pack)**
**BL1830-10 (10-Pack)**

**18v Compact 2.0Ah Lithium-Ion Battery**

2.0Ah BATTERY — 25 Minute Charge Time

NEW **BL1820B (1-Pack)**
**BL1820B-2 (2-Pack)**

**18v Rapid Optimum Charger**

**DC18RC**

| Charge Time | |
|---|---|
| BL1830 | 30 Minute Charge Time |
| BL1820B | 25 Minute Charge Time |

Also charges 14.4v Lithium-Ion batteries

**18v Rapid Optimum 4-Port Charger**

**DC18SF**

| Charge Time - 2 Batteries | |
|---|---|
| BL1830 | 60 Minute Charge Time |
| BL1820B | 50 Minute Charge Time |

Also charges 14.4v Lithium-Ion batteries

**18v Dual-Port Rapid Optimum Charger**

**DC18RD** with USB

| Charge Time | |
|---|---|
| BL1830 | 30 Minute Charge Time |
| BL1820B | 25 Minute Charge Time |

Also charges 14.4v Lithium-Ion batteries

**18v Automotive Charger**

**DC18SE**

| Charge Time | |
|---|---|
| BL1830 | 60 Minute Charge Time |
| BL1820B | 50 Minute Charge Time |

Also charges 14.4v Lithium-Ion batteries

### 36v Lithium-Ion

**36v Lithium-Ion Battery**

**BL3626**

**BL3622A**

**36V Rapid Optimum Charger**

**DC36RA**

| Charge Time | |
|---|---|
| BL3626 | 30 Minute Charge Time |
| BL3622A | 60 Minute Charge Time |

Battery BL3622A must only be used with 36v Optimum Charger (DC36WA)

### 14.4v Lithium-Ion

**14.4v Lithium-Ion Battery**

**BL1430**

**Rapid Optimum Charger**

- DC18RC — Rapid Optimum Charger
- DC18SF — Rapid Optimum 4-Port Charger
- DC18RA — Rapid Optimum Charger
- DC18SE — Automotive Charger

### 12v max Lithium-Ion

**12V max Lithium-Ion Battery**

**BL1014**

**Lithium-Ion Charger**

**DC10WB**

| Charge Time | |
|---|---|
| BL1014 | 60 Minute Charge Time |

Also charges 7.2v and 10.8v Lithium-Ion batteries

### 7.2v Lithium-Ion

**7.2v Lithium-Ion Battery**

**BL7010**

**Lithium-Ion Charger**

**DC10WB**

| Charge Time | |
|---|---|
| BL7010 | 60 Minute Charge Time |

## Carbide Bits

**SDS-MAX**

- 4-Cutter technology for reduced friction and rapid dust removal
- Centering tip features a more aggressive design for faster hole starting
- Central guiding action for accurate holes
- Aggressive head geometry in primary cutter engineered for use in reinforced concrete
- Engineered for reduced vibration
- Wear marking on primary cutter indicates bit wear

| Diameter | Usable Length | Overall Length | Part # |
|---|---|---|---|
| 1/2" | 8" | 13" | T-00256* |
| 1/2" | 16" | 21" | T-00262* |
| 9/16" | 16" | 21" | T-00278* |
| 5/8" | 8" | 13" | T-00284 |
| 5/8" | 16" | 21" | T-00290 |
| 5/8" | 31" | 36" | T-00309 |
| 3/4" | 8" | 13" | T-00315 |
| 3/4" | 16" | 21" | T-00321 |
| 3/4" | 31" | 36" | T-00337 |
| 7/8" | 8" | 13" | T-00359 |

*2-Cutter Design

**SDS-PLUS**

- Thruster® Style carbide tip penetrates on contact and plows through rebar
- Reinforced flute engineered for reduced vibration and faster dust removal
- Dynamic chisel shaped head engineered to keep bit in contact with the material during drilling for faster penetration
- Rebar chamfers help keep carbide from chipping
- Self-centering tip is ideal for spot drilling

| Diameter | Usable Length | Overall Length | Part # |
|---|---|---|---|
| 5/32" | 4" | 6-1/4" | 711227-A |
| 3/16" | 4" | 6-1/4" | 711229-A |
| 3/16" | 6" | 8-1/4" | 711230-A |
| 1/4" | 2" | 4-1/2" | 711235-A |
| 1/4" | 4" | 6-1/4" | 711236-A |
| 1/4" | 6" | 8-1/4" | 711237-A |
| 5/16" | 4" | 6-1/4" | 711240-A |
| 5/16" | 10" | 12" | 711241-A |
| 3/8" | 4" | 6-1/4" | 711242-A |
| 3/8" | 10" | 12-1/4" | 711243-A |

## Demolition Steel

**1-1/8" Hex**

- Manufactured using state-of-the-art technology
- Clear-coated to prevent rust build-up and premature wear
- Shot peened for added strength and surface hardness
- CNC machined and forged from a tough alloy material for increased durability and product longevity

Self-Sharpening Bull Point

| Description | Size | Part # |
|---|---|---|
| Self-Sharpening Bull Point | 16" | B-45559 |
| Bull Point | 20-1/2" | D-21353* |
| Flat Chisel | 20-1/2" | D-21369* |
| Scaling Chisel | 3" x 20-1/2" | D-21347* |
| Superkut Chisel | 20-1/2" | 751222-A |
| One Piece Bushing Tool | 1-3/4" x 14-3/4" | 751717-A |
| Asphalt Cutter | 5" x 17-1/2" | 751620-A |

*Also fits air tools

| Description | Size | Part # |
|---|---|---|
| Digging Chisel | 3" x 22-1/2" | 751621-A |
| Clay Spade | 5-1/2" x 20" | 751622-A |
| Ground Rod Driver | 1" I.D. x 2-1/4" x 16" | 751102-A |
| Spike / Pin Driver | 1-3/4" I.D. x 14-1/2" | 751101-A |
| Tamper Shank | 15-1/2" | 751103-A |
| Tamper Plate | 6" x 6" Square<br>8" x 8" Square | 751710-A<br>751711-A |

**SDS-MAX**

| Description | Size | Part # |
|---|---|---|
| Bull Point | 12"<br>18" | 751421-A<br>751424-A |
| Flat Chisel | 1" x 12"<br>1" x 18" | 751228-A<br>751231-A |
| Scaling Chisel | 1-1/2" x 12"<br>2" x 12"<br>3" x 12" | 751235-A<br>751229-A<br>751230-A |
| Scraping Chisel | 2" x 12" | 751232-A |
| One Piece Bushing Tool | 1-3/4" x 10" | 751715-A |
| Floor Scraper | 6" x 25" | T-02593 |
| Clay Spade | 4-1/2" x 17" | 751626-A |
| Ground Rod Driver | 3/4" I.D. x 2-3/4" x 10" | 751108-A |

# Impact GOLD® THE GOLD STANDARD IN IMPACT DRIVING

Xtreme Torsion Technology

## Nutsetters

| Description | Length | Qty./Pkg. | Part # |
|---|---|---|---|
| 5/16" Nutsetter | 1-7/8" | 1 | B-35047 |
| 5/16" Nutsetter | 1-7/8" | 10 | B-42684 |
| 3/8" Nutsetter | 1-7/8" | 1 | B-35053 |
| 3/8" Nutsetter | 1-7/8" | 10 | B-42690 |
| 7/16" Nutsetter | 1-7/8" | 1 | B-35069 |
| 7/16" Nutsetter | 1-7/8" | 10 | B-42709 |

## Socket Sets

**9 Pc. 3/8" 6-Point Impact Socket Set**

**B-34833**

## Magnetic Drive Bit Sets

**7 Pc. Doubled Ended Power Bits with Mag Boost**

**B-44987**

**Impact GOLD® 26 Pc. Torsion Bit Set**

**B-46919**

**Impact GOLD® 38 Pc. Torsion Bit Set**

**B-52370**

## Carbide-Tipped Saw Blades

| Diameter | Blade Type | No. Teeth | Model | Part # |
|---|---|---|---|---|
| 7-1/4" | General Contractor | 16T | 5007F, 5007FA, 5007MG, 5007MGA, 5377MG, HS7600, 5477NB, XSH01 | A-90009-B-10 (10/pk) |
| 7-1/4" | General Contractor | 24T | | D-45989-10 (10/pk) |
| 7-1/4" | Framing | 24T | | A-94839-10 (10/pk) |
| 7-1/4" | Ultra-Coated Framing | 24T | | A-94530-10 (10/pk) |
| 7-1/4" | FMF® Ultra-Coated Framing | 24T | | A-95298-10 (10/pk) |
| 7-1/4" | Fine Crosscutting | 40T | | 721251-A |
| 8-1/4" | Framing | 24T | 5008MGA | D-21521 |
| 8-1/4" | Fine Crosscutting | 40T | | 792377-A |
| 10-1/4" | Framing | 24T | 5104 | A-94910 |
| 16-5/16" | Beam & Timber | 32T | 5402NA | A-90956 |
| 16-5/16" | Beam & Timber | 60T | | 792118-8 |

## Diamond Blades

### Ultra Premium Diamond Blade NEW

- Each diamond is placed in an even 3 dimensional pattern for unparalleled performance in lifetime and speed
- Noise reduction technology utilizes laminate blades which reduce resonance and run significantly quieter

| Diameter | Material | Part # |
|---|---|---|
| 14" | Cured Concrete, Green Concrete, Asphalt, Block, Brick, Granite | T-02537 |

### Segmented and Turbo Rim

| Description | Diameter | Material | Part # |
|---|---|---|---|
| Segmented Rim | 4" | General Purpose | A-94677 |
| | 4-1/2" | General Purpose | A-94683 |
| | 7" | General Purpose | A-94714 |
| | 10" | Dual Purpose | T-01258 |
| | 12" | Dual Purpose | T-01264 |
| | 14" | Dual Purpose | T-01270 |
| | 16" | Dual Purpose | T-01286 |
| Turbo Rim | 4" | General Purpose | A-94546 |
| | 4-1/2" | General Purpose | A-94552 |
| | 7" | General Purpose | A-94574 |

### Dual Sandwich Tuck Point Blades

- Dual sandwich design for faster more efficient removal of material
- Less dust than solid tuck point blades

| Diameter | Size | Part # |
|---|---|---|
| 4" | 1/4" | A-95906 |
| 4-1/2" | 1/4" | A-95912 |
| 5" | 1/4" | A-96017 |

## Carbide Metal Cutting Blades

### Ferrous Metal

**BURR-FREE CUTTING. Cool to the Touch and Less Cost Per Cut.**

Number of Cuts

Cutting Speed in Seconds
Cutting test performed in 2" x 2" x 1/4" angle iron

| Diameter | Blade Type | No. Teeth | Model | Part # |
|---|---|---|---|---|
| 5-3/8" | Ferrous Metal | 30T | XSC01 | A-95037 |
| 5-3/8" | Ferrous Metal - Thin Gauge | 50T | | A-94524 |
| 5-7/8" | Ferrous Metal | 32T | XSC02 | A-96095 |
| 5-7/8" | Ferrous Metal - Thin Gauge | 52T | | A-96104 |
| 7-1/4" | Ferrous Metal | 38T | 4131 | A-93821 |
| 7-1/4" | Ferrous Metal | 48T | | A-93837 |
| 7-1/4" | Ferrous Metal - Thin Gauge | 70T | | A-93843 |
| 12" | Ferrous Metal | 60T | LC1230 | A-90532 |
| 12" | Ferrous Metal | 60T | | A-90722* |
| 12" | Ferrous Metal - Thin Gauge | 78T | | A-90875 |

*Quiet cutting

| Diameter | Blade Type | No. Teeth | Model | Part # |
|---|---|---|---|---|
| 5-3/8" | Aluminum | 50T | XSC01 | A-95940 |
| 5-7/8" | Aluminum | 52T | XSC02 | A-96126 |

### Stainless Steel

Special alloy tip for longer cutting life in stainless steel

Ultra-thin kerf for faster more efficient cutting

Special geometry for increased cutting efficiency

| Diameter | Blade Type | No. Teeth | Model | Part # |
|---|---|---|---|---|
| 5-3/8" | Stainless Steel - Thin Gauge | 56T | XSC01 | A-95794 |
| 5-7/8" | Stainless Steel – Thin Gauge | 60T | XSC02 | A-96110 |
| 7-1/4" | Stainless Steel - Thin Gauge | 64T | 4131 | A-95875 |
| 12" | Stainless Steel | 76T | LC1230 | A-91039 |
| 12" | Stainless Steel - Thin Gauge | 100T | | A-95803 |

### Industrial Carbide-Tipped Hole Saws

- Lasts 15X longer and drills 2.6X faster than Bi-M hole saws
- Specially designed carbide tips for cutting clean holes
- Max. cutting depth of 1/8" with 2-1/2" overall length

| Diameter | Size | Center Bits Type C Part # |
|---|---|---|
| 5/8" | 714070-A | 714086-A |
| 3/4" | 714071-A | |
| 7/8" | 714073-A | |
| 1" | 714074-A | |
| 1-1/8" | 714075-A | |
| 1-1/4" | 714077-A | |
| 1-3/8" | 714078-A | |
| 1-1/2" | 714079-A | |
| 1-3/4" | 714080-A | |
| 2" | 714081-A | |
| 2-1/8" | 714092-A | |
| 2-1/4" | 714082-A | |

## INOX Grinding Wheels

- Aggressive composition for faster material removal
- Innovative design for reduced noise
- Reduced vibration for superior user experience

| Diameter | Thickness | Arbor | Model | 1/Pkg. Part# | 5/Pkg. Part# | 25/Pkg. Part# |
|---|---|---|---|---|---|---|
| 4-1/2" | 1/4" | 7/8" | 9557NB/PB, 9564CV/PC/P, GA4530, GA4534, XAG01, XAG03, XAG06 | A-95956 | A-95956-5 | A-95956-25 |
| 5" | 1/4" | 7/8" | 9005B/BZ, 9558PB, 9565CV/PC, GA5010Z, GA5020/Y | A-95962 | A-95962-5 | A-95962-25 |
| 6" | 1/4" | 7/8" | 9566CV/PC, GA6010Z, GA6020 | A-95978 | A-95978-5 | A-95978-25 |
| 4-1/2" | 1/4" | 5/8"-11 | 9557NB/PB, 9564CV/PC/P, GA4530, GA4534, XAG01, XAG03, XAG06 | A-95984 | A-95984-5 | A-95984-25 |
| 5" | 1/4" | 5/8"-11 | 9005B/BZ, 9558PB, 9565CV/PC, GA5010Z, GA5020/Y | A-95990 | A-95990-5 | A-95990-25 |
| 6" | 1/4" | 5/8"-11 | 9566CV/PC, GA6010Z, GA6020 | A-96001 | A-96001-5 | A-96001-25 |

## Ultra Thin Cut-Off Wheels

- .032" thick for faster cutting and reduced material waste
- For making cuts in metal and stainless steel pipes, sheet, and channel

| Diameter | Thickness | Arbor | Model | 1/Pkg. Part # | 25/Pkg. Part # |
|---|---|---|---|---|---|
| 4" | .032" | 5/8" | GA4030 | B-46143 | B-46143-25 |
| 4-1/2" | .032" | 7/8" | 9557NB/PB, 9564CV/PC/P, GA4530, GA4534, XAG01, XAG03, XAG06 | B-46159 | B-46159-25 |
| 5" | .032" | 7/8" | 9005B/BZ, 9558PB, 9565CV/PC, GA5010Z, GA5020/Y | B-46165 | B-46165-25 |

## Premium Hammer Cart

| Description | Part # |
|---|---|
| • Conveniently transports breaker hammers and bits on the job site | T-02892 |

makita®

AVT Advanced ANTI VIBRATION TECHNOLOGY™

HM1812X3

## 70 lb. Advanced AVT® Breaker Hammer

with 4-Pc. Steel Set & Hammer Cart, accepts 1-1/8" Hex bits

**Powerful 15AMP Motor**
with improved hammer mechanism delivers over 50 ft. lbs. (68 Joules) of impact energy

**Mechanical Counterbalance System**
greatly reduces vibration and directs more impact energy to the work surface

**Vibration Absorbing Housing**
moves independently of the motor and hammer mechanism effectively isolating more vibration away from the user

**Integrated Cord Guide**
helps position 16'4" power cord away from working area

**Fixed Movement Handles**
for more control and greater accuracy

MM4®
4-STROKE ENGINE

EK7651H
**14" MM4® Power Cutter**
shown with optional premium diamond blade (T-02537)

The MAKITA TEAL COLOR is the trade dress of Makita® Corporation and is protected under common law and registered with the U.S. Patent and Trademark Office. Printed in U.S.A. **999CAT12** GC-0816-30M MA-1835-16

makitatools.com