

3M

DBI
SALA

Fall Protection



Support at every level.

3M™ DBI-SALA® ExoFit™ XE Series Harnesses

XE100

3M™ DBI-SALA® ExoFit™ XE100 Safety Harness

Designed with high-quality components

Created for enhanced harness safety, fit and the comfort of your team whilst working at heights.

Built with durable 26kN polyester webbing and alloy steel hardware, the 3M™ DBI-SALA® ExoFit™ XE100 Safety Harness features nylon/polyester hybrid comfort padding with added air channels for comfort alongside reflective 3M™ Scotchlite™ panels. The back D-ring plate designed with pSRL tunnel allows quick and easy connection of Personal Self-Retracting Lifelines (pSRLs). XE100 harness features revolving torso-adjustment and quick-connect buckles for a quick, safe and comfortable harness fit. This harness is compatible with variety of 3M Fall Protection for Tools accessories. All models are equipped with low-profile suspension trauma relief straps.

Steel hardware alloy steel

3M™ Scotchlite™ reflective panels for enhanced visibility in low-light environments.

Integrated pSRL tunnel for quick and easy connection/disconnection of personal SRLs.

Cross Chest Buckle assembly (patent pending) Central front fall arrest attachment point, optimized position on body for climbing with vertical fall arrest systems.

Revolving torso adjuster (patented) for quick and easy harness fit adjustment.

Low-profile suspension trauma relief straps (patented)

Hybrid comfort padding with breathable mesh under-side for enhanced thermal comfort and ergonomics.

3M™ Connected Safety ID integrated RFID for simplified inventory, inspection and record management.

3M | Fall Protection

Registered Offices:
Capital Safety (Northern Europe) Limited
3M Centre, Cain Road, Bracknell,
Berkshire, RG12 8HT, UK

Capital Safety Group (EMEA)
Le Broc Center, Bâtiment A, Z.1. 1re Avenue
- BP15, 06511 Carros Le Broc, Cedex, FRANCE

Phone: +33 (0)4 83 58 08 08
Email: informationfallprotection@mmm.com
Web: 3M.com/FallProtection

3M, DBI-SALA, ExoFit and Nano-Lok are trademarks of 3M Company and its affiliates. ©3M 2022. All rights reserved

*XE100 models are available as well in belted version.

Important notice

The mounting and use of the product described within this document assumes that the user has previous experience of this type of product and that it will be assembled by a competent professional according to product documentation. Before any use of this product it is recommended to complete some trials to validate the performance of the product within its expected application. All information and specification details contained within this document are inherent to this specific 3M product and would not be applied to other products or environment. Any action or usage of this product made in violation of this document is at the risk of the user. Compliance to the information and specification relative to the product contained within this document does not exempt the user from compliance with additional guidelines (safety rules, procedures). Compliance to operational requirements especially in respect to the environment and usage of tools with this product must be observed. 3M and its affiliates (who cannot verify or control these elements) would not be held responsible for the consequences of any violation of these rules which remain external to its decision and control. Warranty conditions for products are determined with the sales contract documents and with the mandatory and applicable law, excluding any other warranty or compensation.

GLOBAL PRODUCT WARRANTY, LIMITED REMEDY AND LIMITATION OF LIABILITY WARRANTY: THE FOLLOWING IS MADE IN LIEU OF ALL WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OR CONDITIONS OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Unless otherwise provided by local laws, 3M fall protection products are warranted against factory defects in workmanship and materials for a period of one year from the date of installation or first use by the original owner. LIMITED REMEDY: Upon written notice to 3M, 3M will repair or replace any product determined by 3M to have a factory defect in workmanship or materials. 3M reserves the right to require product be returned to its facility for evaluation of warranty claims. This warranty does not cover product damage due to wear, abuse, misuse, damage in transit, failure to maintain the product or other damage beyond 3M's control. 3M will be the sole judge of product condition and warranty options. This warranty applies only to the original purchaser and is the only warranty applicable to 3M's fall protection products. Please contact 3M's customer service department in your region for assistance. LIMITATION OF LIABILITY: TO THE EXTENT PERMITTED BY LOCAL LAWS, 3M IS NOT LIABLE FOR ANY INDIRECT, INCIDENTAL, SPECIAL OR CONSEQUENTIAL DAMAGES INCLUDING, BUT NOT LIMITED TO LOSS OF PROFITS, IN ANY WAY RELATED TO THE PRODUCTS REGARDLESS OF THE LEGAL THEORY ASSERTED.