

PT-18RKT

Compact Rechargeable Label Printer

VERSATILE PORTABLE LABELING SYSTEM

P-touch®
ELECTRONIC LABELING SYSTEM

The PT-18RKT blends performance and portability to help save you time printing labels and solving complicated labeling problems. Use it as a compact standalone labeling system or as a portable label printer - either way, it works the way you do. Simply place the PT-18RKT in its cradle to keep the battery fully charged - then grab and go. It's a complete labeling system that also includes two full-length laminated TZe tapes, rechargeable battery and a carry case.



PT-18RKT
Data Sheet

brother®
at your side

Technical Specifications

Tape Line	HG / HGe, TZe (laminated)
Tape Width	6mm, 9mm, 12mm, 18mm
Max. Print Resolution	180 dpi
Max. Print Height	15.8mm
Display	15 Character x 2 Line
Tape Cutter	Automatic
Power Source: Batteries AC Adapter	Rechargeable (BA-18R) AD-18 (both included)
Number of Lines	5 [▲]
Keyboard	QWERTY
Rotate Printing	Yes
Fonts	4 [▲]
Type Sizes	7 [▲]
Type Styles	12 [▲]
Auto Formats	Yes
Number of Symbols	103 [▲]
Bar Codes	9 [▲]
Repeat Printing	up to 99 copies [▲]
Auto Numbering	1-99, A-Z, a-z [▲]
Auto Incrementation	Yes
Text Insert	Yes
Memory	10 files or 459 characters
Label Length Setting	Yes
Horizontal Alignment	Left, Center, Right
Mirror Printing	Yes
Vertical Printing	Yes
(PC) Connectivity	Yes
Operating Systems*	Windows® 7*, Windows Vista®, Windows® XP, 2000, 98, 98SE, Me
Package Contents	One 9mm x 8m Black on White Extra-Strength Adhesive Laminated TZe Tape, One 18mm x 8m Black on White Flexible ID Laminated TZe Tape, Cradle (Charging), Ni-MH Rechargeable Battery, Power Adapter, Custom Carrying Case, USB Cable, CD
Unit Weight	1.3 lbs. [§]
UPC Code	0 12502 63245 0
Warranty	1 Year Limited Exchange [○]

*See system requirements on www.brother.com. *The drivers for Windows® Vista® and Windows® 7 may require a download from <http://solutions.brother.com>. ▲When operating in stand-alone mode. Also connects to PC. §Without tape and battery.
○Visit www.brother.com for complete details.

ASK US ABOUT OUR OTHER LABELING PRODUCTS

P-touch EDGE® Series

Rugged handheld labelers that produce durable laminated labels up to 24mm wide



TD Series Desktop Barcode and Label Printers

Light, industrial thermal printers for labels, receipts and tags up to 4" wide from continuous and die cut paper media on convenient drop-in rolls



PT-9700PC and PT-9800PCN Label Printers

Thermal transfer printers for tough and durable laminated labels up to 36mm wide



BROTHER MOBILE SOLUTIONS, INC.

For more information, call 1-800-543-6144,
or visit www.brothermobilesolutions.com

brother
at your side

Brother™ is a trademark or registered trademark of Brother Industries, Ltd. in the United States. Microsoft®, Windows® and Windows Vista® are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries. All other trademarks and registered trademarks are the properties of their respective companies.

© 2012 Brother Mobile Solutions, Inc., 100 Technology Drive, Suite 250A, Broomfield, CO 80021

BMS 05-2012 008



HG/HGe tapes are designed for commercial and industrial labeling applications, and are compatible with the PT-18RKT, PT-9700PC and PT-9800PCN. All individual tapes are 8m (26.2 ft) long.

6mm (0.23 in) 9mm (0.35 in) 12mm (0.47 in) 18mm (0.7 in)

HGe Extra-Strength Adhesive Tapes - 5 piece bulk packaging, designed for use on plastics, textured and hard to stick surfaces

BLACK ON WHITE	c	RU	US	HGeS2115PK	HGeS2215PK	HGeS2315PK	HGeS2415PK
BLACK ON YELLOW	c	RU	US		HGeS6215PK	HGeS6315PK	HGeS6415PK
BLACK ON MATTE SILVER	c	RU	US				HGeS9415PK
BLACK ON CLEAR	c	RU	US		HGeS1215PK	HGeS1315PK	HGeS1415PK

HG Standard Adhesive Tapes - 5 piece bulk packaging, designed for use on smooth and flat surfaces

BLACK ON WHITE			HG2215PK	HG2315PK	HG2415PK
BLACK ON YELLOW					HG6415PK
BLACK ON MATTE SILVER					HGM9415PK
BLACK ON CLEAR					HG1415PK



TZe tapes feature the same laminated structure and durability of HG tapes. TZe tapes are compatible with the PT-18RKT, as well as all other P-touch® TZ and TZe compatible labelers. All individual tapes are 8m (26.2 ft) long, unless otherwise noted.

6mm (0.23 in) 9mm (0.35 in) 12mm (0.47 in) 18mm (0.7 in)

Flexible ID Tapes - Individual tapes designed for wrapping around and adhesive-to-adhesive flag labels

BLACK ON WHITE	c	RU	US		TZeFX231	TZeFX241
BLACK ON YELLOW	c	RU	US		TZeFX631	

Extra-Strength Adhesive Tapes - Individual tapes designed for plastics and textured surfaces

BLACK ON WHITE	c	RU	US	TZeS211	TZeS221	TZeS231	TZeS241
BLACK ON CLEAR	c	RU	US		TZeS121	TZeS131	TZeS141
BLACK ON YELLOW	c	RU	US		TZeS621	TZeS631	TZeS641
WHITE ON CLEAR	c	RU	US			TZeS135	
BLACK ON MATTE SILVER	c	RU	US				TZeS941

Standard Adhesive Tapes - Individual tapes designed for use on smooth and flat surfaces

BLACK ON WHITE		TZe211	TZe221	TZe231	TZe241
BLACK ON CLEAR		TZe111	TZe121	TZe131	TZe141
BLACK ON RED			TZe421		TZe441
BLACK ON YELLOW				TZe631	TZe641
BLACK ON GREEN					TZe741
BLACK ON BLUE					TZe541
BLACK ON FL. ORANGE					TZe841 ¹
WHITE ON BLACK		TZe315	TZe325	TZe335	TZe345
WHITE ON CLEAR				TZe135	TZe145
RED ON WHITE				TZe232	TZe242
BLUE ON WHITE					TZe243
GOLD ON BLACK				TZe334	TZe344

¹5m long

Tamper Evident Tapes - Individual tapes designed to reveal a security pattern when the label is removed or disturbed

BLACK ON WHITE	c	RU	US		TZeSE4
----------------	---	----	----	--	--------

Stencil Tapes - Non-adhesive tape designed to mask ink or special fluids for direct part marking

STENCIL TAPE					STe141
--------------	--	--	--	--	--------