

S250 Solution Cat6**Copper Cable**

Anixter PN	Vendor PN	Description	Category
CMZ-00423COR-CF6R-06	CCXERA-B0047-C001-L7	Indoor Copper Cable, FutureCom, Category 6, LSZH, 23 AWG, 4-Pair, 250 MHz, U/FTP, Fuild, 1000 Meters	Copper adder
CMZ-00423COR-CF6RB06	CCXERA-B0047-C001-X1	Indoor Copper Cable, FutureCom, Category 6, LSZH, 23 AWG, 4-Pair, 250 MHz, U/FTP, Fuild, 305MT Reelex Box	Copper adder
544315	CCXDDA-D0047-C001-L7	F/FTP450 23AWG 4 PR FUTURECOME LSZH 450 MHZ BLUE CAT.6 IN SPOOLS OF 1000 MT	Copper adder
400021	CCXDDA-D0047-C001-X2	F/FTP 450/23 Cat6 4P Simplex Copper Cable, LS0H/LSZH, FRNC, 250m Reelex box	Copper adder
CMZ-00423COR-CF6-06	CCXDDA-D0047-C001-L6	F/FTP 450/23 Cat6 4P Simplex Copper Cable, LS0H/LSZH, FRNC, 500m drum	Copper adder

S250 Copper Jack

Anixter PN	Vendor PN	Description	Category
542951	CAXESM-00100-C001	S250 MODULE, RJ45, SHIELDED, CAT 6, WITH CONDUCTING TAPE TO MOUNT IN OUTLETS	Cat6

Copper Patch Cords

Anixter PN	Vendor PN	Description	Category
MM01M-CORE6-02	CCAIEA-DP002-A010-C0	1 Meter Indoor Patch Cord, FutureCom E, FRNC, RJ45 - RJ45 Connector, U/FTP, Category 6, 4-Pair, 26AWG, Black Jacket With Grey Boots	Cat6

MM02M-CORE6-02	CCAEIA-DP002-A020-C0	2 Meter Indoor Patch Cord, FutureCom E, FRNC, RJ45 - RJ45 Connector, U/FTP, Category 6, 4-Pair, 26AWG, Black Jacket With Grey Boots	Cat6
MM03M-CORE6-02	CCAEIA-DP002-A030-C0	3 Meter Indoor Patch Cord, FutureCom E, FRNC, RJ45 - RJ45 Connector, U/FTP, Category 6, 4-Pair, 26AWG, Black Jacket With Grey Boots	Cat6
MM05M-CORE6-02	CCAEIA-DP002-A050-C0	5 Meter Indoor Patch Cord, FutureCom E, FRNC, RJ45 - RJ45 Connector, U/FTP, Category 6, 4-Pair, 26AWG, Black Jacket With Grey Boots	Cat6
MM01M-COREC6-02	CCAEIA-DQ002-A010-C0	1 Meter Indoor Patch Cord, FutureCom E, FRNC, RJ45 - RJ45 Connector, U/FTP, Category 6, 4-Pair, 26AWG, Black Jacket With Blue Boot	Cat6
MM02M-COREC6-02	CCAEIA-DQ002-A020-C0	2 Meter Indoor Patch Cord, FutureCom E, FRNC, RJ45 - RJ45 Connector, U/FTP, Category 6, 4-Pair, 26AWG, Black Jacket With Blue Boot	Cat6
MM03M-COREC6-02	CCAEIA-DQ002-A030-C0	3 Meter Indoor Patch Cord, FutureCom E, FRNC, RJ45 - RJ45 Connector, U/FTP, Category 6, 4-Pair, 26AWG, Black Jacket With Blue Boot	Cat6
MM05M-COREC6-02	CCAEIA-DQ002-A050-C0	5 Meter Indoor Patch Cord, FutureCom E, FRNC, RJ45 - RJ45 Connector, U/FTP, Category 6, 4-Pair, 26AWG, Black Jacket With Blue Boot	Cat6
MM10M-COREC6-02	CCAEIA-DQ002-A100-C0	10 Meter Indoor Patch Cord, FutureCom E, FRNC, RJ45 - RJ45 Connector, U/FTP, Category 6, 4-Pair, 26AWG, Black Jacket With Blue Boot	Cat6