

**CCH Rack-Mountable solution****Empty housing**

<b>Anixter PN</b>	<b>Vendor PN</b>	<b>Description</b>	<b>Category</b>
180626	CCH-01U	Closet Connector Housing (CCH), 1 rack unit, holds 2 CCH connector panels	Fibre&Copper Accy
180627	CCH-02U	Closet Connector Housing (CCH), 2 rack units, holds 4 CCH connector panels	Fibre&Copper Accy
180628	CCH-03U	Closet Connector Housing (CCH), 3 rack units, holds 6 CCH connector panels	Fibre&Copper Accy
180420	CCH-04U	Closet Connector Housing (CCH), 4 rack units, holds 12 CCH connector panels	Fibre&Copper Accy

**Loaded Panels for CCH LC duplex**

<b>Anixter PN</b>	<b>Vendor PN</b>	<b>Description</b>	<b>Category</b>
590570	CCHE-CP12-AD	CONN.PANEL W/6 LC DUPX ADPT MM OM3 SHUTTERED CERAMIC INSERT LOADED(CCH&WCHE)	OM3/OM4
289681	CCHE-CP12-D3	CONN.PANEL W/6 LC DUPX ADPT MM 50/125 CER.INSERT/COMP.HOUSING LOADED(CCH&WCHE)	OM2
289682	CCHE-CP12-E4	CONN.PANEL W/6 LC DUPX ADPT MM OM3 CER.INSERT/COMP.HOUSING LOADED(CCH&WCHE)	OM3/OM4
289679	CCHE-CP12-05	CONN.PANEL W/6 LC DUPX ADPT MM 62.5 CER.INSERT/COMP.HOUSING LOADED(CCH&WCHE)	OM1
423958	CCHE-CP24-AD	24 Fibre, 12 shuttered LC Duplex MM/OM3+OM4 CCH Adapter Panel, ceramic sleeve	OM3/OM4
289686	CCHE-CP24-D3	24 Fibre, 12 LC Duplex MM/OM2 CCH Adapter Panel, ceramic sleeve	OM2

289687	CCHE-CP24-E4	CONN.PANEL W/12 LC DUPX ADPT MM OM3 CER.INSERT/COMP.HOUS. LOADED(CCH&WCHE)	OM3/OM4
289684	CCHE-CP24-05	CONN.PANEL W/12 LC DUPX ADPT MM 62.5 CER.INSERT/COMP.HOUS. LOADED(CCH&WCHE)	OM1
548816	CCHE-CP24-AE	CCHE Panel, black, 24 LC duplex, turquoise OM3, shuttered	OM3/OM4
539596	CCHE-CP24-L4	CONN.PANEL W/12 LC DUPX ADPT SM OS2 CER.INSERT/COMP. LOADED(CCH&WCHE)	OS2
289664	CCHE-CP06-D3	CONN.PANEL W/3 LC DUPX ADPT MM 50/125 CER.INSERT/COMP.HOUSING LOADED(CCH&WCHE)	OM2
289665	CCHE-CP06-E4	CONN.PANEL W/3 LC DUPX ADPT MM OM3 CER.INSERT/COMP.HOUSING LOADED(CCH&WCHE)	OM3/OM4
289662	CCHE-CP06-05	CONN.PANEL W/3 LC DUPX ADPT MM 62.5 CER.INSERT/COMP.HOUSING LOADED(CCH&WCHE)	OM1
564708	CCHE-CP24-AV	24 Fibre, 12 shuttered Violet LC Duplex MM/OM3+OM4 CCH Adapter Panel, ceramic sleeve	OM3/OM4
289680	CCHE-CP12-04	CONN.PANEL W/6 LC DUPX ADPT SM CER.INSERT/COMP.HOUSING LOADED (CCH&WCHE)	OS2
289685	CCHE-CP24-04	24 Fibre, 12 LC Duplex SM/OS2 UPC CCH Adapter Panel, ceramic sleeve	OS2
289663	CCHE-CP06-04	CONN.PANEL W/3 LC DUPX ADPT SM CER.INSERT/COMP.HOUSING LOADED (CCH&WCHE)	OS2

**Loaded Panels for CCH SC duplex**

Anixter PN	Vendor PN	Description	Category
------------	-----------	-------------	----------

426643	CCHE-CP06-57	CONN.PANEL W/3 SC DUPX ADPT.MM 62.5 CERAMIC INSERT COMP.HOUSI LOADED(CCH&WCHE)	OM1
--------	--------------	---	-----

289661	CCHE-CP06-E7	CONN.PANEL W/3 SC DUPX ADPT MM OM3 CER.INSERT/COMP.HOUSING LOADED(CCH&WCHE)	OM3/OM4
289669	CCHE-CP08-G7	CONN.PANEL W/4 SC DUPX ADPT MM 50/125 CER.INSERT/COMP.HOUSING LOADED(CCH&WCHE)	OM2
315652	CCHE-CP12-57	CONN.PANEL W/6 SC DUPX ADPT MM 62.5/125 CER.INSERT BEIGE LOADED(CCH&WCHE)	OM1
289675	CCHE-CP12-72	12 Fibre, 6 SC Duplex SM/OS2 UPC CCH Adapter Panel, ceramic sleeve	OS2
456605	CCHE-CP12-D9	12F CONN PANEL SM 9/125 OS2 W/ 6 SC-APC DUPLX ADPT FOR CCH WCH & PCH	OS2
289678	CCHE-CP12-E7	12 Fibre, 6 SC Duplex MM/OM3+OM4 CCH Adapter Panel, ceramic sleeve	OM3/OM4
289677	CCHE-CP12-G7	12 Fibre, 6 SC Duplex MM/OM2 CCH Adapter Panel, ceramic sleeve	OM2

**Loaded Panels for CCH ST**

<b>Anixter PN</b>	<b>Vendor PN</b>	<b>Description</b>	<b>Category</b>
289657	CCHE-CP06-15	CCH PANEL W/6 THREADED ST ADPT MM 62.5&50 CER. INSERT COMP. HOUSING LOADED	OM1
353629	CCHE-CP06-19	CONN PANEL W/6 ST ADPT OS1 SM 9/125 CER INSERT/COMP HOUSING CCH, PCH & WCHE	OS2
289666	CCHE-CP08-15	CONN.PANEL W/8 THREADED ST ADP MM 62.5&50 CER.INSERT/COMP. HOUSING LOADED (CCH)	OM2
506809	CCHE-CP08-19	CONN.PANEL W/8 THREADED ST ADP MM 62.5&50 CER.INSERT,W/BLUE RING, CCH	OM2
289683	CCHE-CP12-15	12 Fibre, 12 ST MM/OM2 CCH Adapter Panel, ceramic sleeve	OM2

353628	CCHE-CP12-19	12 Fibre, 12 ST SM/OS2 UPC CCH Adapter Panel, ceramic sleeve	OS2
488764	CCHE-CP12-25	CONN PANEL W/6 ST COMP. ADPT 12F MM OM1 OR OM2. FITS IN ALL LANSCAPE SOLUTIONS	OM2

**CCH Pigtailed Splice Cassette & empty one**

Anixter PN	Vendor PN	Description	Category
474219	CCH-CS12-59-P00RE	CCH Splice Cassette, 12 fiber, SC, UPC, Duplex, Single-mode (OS2), Single-Fiber (250 µm)	OS2
474221	CCH-CS12-6T-P00RE	CCH Splice Cassette, 12 fiber, ST® Compatible, UPC, Simplex, Single-mode (OS2), Single-Fiber (250 µm)	OS2
474222	CCH-CS12-A9-P00RE	CCH Splice Cassette, 12 fiber, LC, UPC, Duplex, Single-mode (OS2), Single-Fiber (250 µm)	OS2
463218	CCH-CS12-E4-P00TE	CCH Splice Cassette, 12 fiber, LC, PC, Duplex, 50 µm (OM3), Single-Fiber (250 µm)	OM3/OM4
511017	CCH-CS12-E7-P00TE	12 Fibre, 6 SC Duplex MM/OM3 pigtailed CCH Splice Module (heat-shrink protection), ceramic sleeve	OM3/OM4
564711	CCH-CS12-G5-P00BE	CCH Splice Cassette, 12 fiber, ST Compatible, UPC, Simplex, Multimode (OM2), Single-Fiber (250 µm)	OM2
564703	CCH-CS12-G7-P00BE	CCH Pigtailed Splice Cassette, 12 F, SC UPC duplex, black, OM2	OM2
474223	CCH-CS24-A9-P00RE	CCH Splice Cassette, 24 fiber, LC, UPC, Duplex, Single-mode (OS2), Single-Fiber (250 µm)	OS2
549849	CCH-CS24-AD-P00QE	24F CCH PIGTAIL SPLICE CASSETT OM4 LOADED LC-DUPLEX SHUTTER CCH-CS24-AD-P00QE	OM3/OM4
522152	CCH-CS24-AD-P00TE	CCH Pigtailed Splice Cassette, 24 F, LC duplex shuttered, turquoise, OM3	OM3/OM4

550914	CCH-CS24-AE-P00RE	CCH Pigtailed Splice Cassette, Loaded, 24-Fibers, OS2 Singlemode, Blue, LC UPC Duplex Shuttered, Wall- or Rack-mount	OS2
564704	CCH-CS24-D3-P00BE	CCH Pigtailed Splice Cassette, 24 F, LC duplex, black, OM2	OM2
564701	CCH-CS24-E4-P00QE	CCH Splice Cassette, 24 fiber, LC, PC, Duplex, 50 µm (OM4)	OM3/OM4
474218	CCH-CS24-E4-P00TE	CCH Splice Cassette, 24 fiber, LC, PC, Duplex, 50 µm (OM3), Single-Fiber (250 µm)	OM3/OM4
459349	CCH-CS	CCH Cassette, Splicing, empty, for 1 CCH panel	Fibre&Copper Accy