

Hardware

UniCam Connector OM1 62.5/125

| Anixter PN | Vendor PN | Description | Category |
|------------|-----------|--|----------|
| 170002-NEW | 95-000-50 | UniCam® Standard-Performance Connector, ST® Compatible, 62.5 µm multimode (OM1), ceramic ferrule, logo, single pack, amber housing, beige boot | OM1 |
| 170001-NEW | 95-000-51 | UniCam® High-Performance Connector, ST® Compatible, 62.5 µm multimode (OM1), ceramic ferrule, logo, single pack, amber housing, beige boot | OM1 |
| 169224-NEW | 95-000-40 | UniCam® Standard-Performance Connector, SC, 62.5 µm multimode (OM1), ceramic ferrule, logo, single pack, beige housing, beige boot | OM1 |
| 205644-NEW | 95-050-41 | UniCam® High-Performance Connector, SC, 50 µm multimode (OM2), ceramic ferrule, logo, single pack, black housing, black boot | OM1 |
| 280091-NEW | 95-000-99 | UniCam® High-Performance Connector, LC, 62.5 µm multimode (OM1), ceramic ferrule, logo, single pack, beige housing, beige boot | OM1 |

Empty Panel - LANC & LANS

| Anixter PN | Vendor PN | Description | Category |
|------------|-------------|---|----------------------|
| 545410-V2 | LANS-01U-B4 | PULL OUT TRAY 19 INCH WIDE 1-U RACK MOUNT SPACE COLOR BLACK UP TO 24 SINGLE MODULE WITH HOLDER FOR UP TO 4 SPLICE TRAYS | Fibre&Copper Accy |
| 454508-V2 | LANS-02U-B8 | PULL OUT TRAY 19 INCH WIDE 2-U RACK MOUNT SPACE COLOR BLACK UP TO 48 SINGLE MODULE WITH HOLDER FOR UP TO 4 SPLICE TRAYS | Fibre&Copper Accy |
| 415633-EA | LANC-01U-B | 1U fixed LANC Fibre Housing (24x LANscape), black | Fibre&Copper Accy |

LANC & LANS Modules

| Anixter PN | Vendor PN | Description | Category |
|-------------------|------------------|--|-----------------|
| 415636-EA | LANC-MOD-P8-B | SC-DUPX MOD FOR LANC LINE MM 62.5/125 OM1 BLACK METAL | OM1 |
| 415634-EA | LANC-MOD-74-B | ST MM/OM2 Fibre Module, metal sleeve (1x LANScape), black socket | OM1 |
| 415640-EA | LANC-MOD-A7-B | LC-DUPX MOD FOR LANC LINE MM 62.5/125 OM1 BLACK METAL | OM1 |
| 415643 | LANC-MOD-BLNK-B | BLANK MOD FOR LANC LINE BLACK 100 PCS/PK | OM1 |
| 545456 | LANS-MOD-15-B | MODULE COLOR BLACK WITH 1 ST MULTIMODE FIBER ADAPTER (FEEDTHROUGH + ST) FOR USE WITH BLACK HARDWARE | OM1 |
| 545457 | LANS-MOD-57-B | MODULE COLOR BLACK WITH 1 SC DUPLEX MULTIMODE FIBER ADAPTER (FEEDTHROUGH + FOR USE WITH SC DUPLEX) FOR USE WITH BLACK HARDWARE | OM1 |
| 499263 | LANS-MOD-AB-B | LANS MOD BEIGE LC DUPLEX MM 62.5/125 OM1 CER SHUTTERED BLACK | OM1 |

Splice Pack

| Anixter PN | Vendor PN | Description | Category |
|-------------------|------------------|---|-----------------|
| 415644-EA | SP12-50K-S8 | STD SPLICE TRAY HEATSHRINK W/ 12 ST MM 62.5/125 OM1 PIGTAIL | OM1 |

| | | | |
|-----------|-------------|---|-----|
| 415646-EA | SP12-39K-S8 | STD SPLICE TRAY HEATSHRINK W/ 12 SC MM 62.5/125 OM1 PIGTAIL | OM1 |
| 415650-EA | SP12-03K-S8 | STD SPLICE TRAY HEATSHRINK W/ 12 LC MM 62.5/125 OM1 PIGTAIL | OM1 |

Patchcords

| Anixter PN | Vendor PN | Description | Category |
|------------|-----------------|--|----------|
| 521427 | 505002K5Z41003M | ST Compatible to ST Compatible patch cord on 2-fiber Zipcord cable, with 2.8 mm legs, and a low-smoke, zero-halogen sheath. 3 m | OM1 |
| 544637 | 575702K5Z41003M | SC Duplex to SC Duplex patch cord on 2-fiber Zipcord cable, with 2.8 mm legs, and a low-smoke, zero-halogen sheath. 3 m | OM1 |
| 261976 | 050502K5Z20003M | LC Duplex to LC Duplex patch cord on 2-fiber Zipcord cable, with 2 mm legs, and a low-smoke, zero-halogen sheath. 3 m | OM1 |
| 525145 | 505702K5Z41003M | DUPLEX PATCH CORD FIBER OPTIC CONNECTOR JUMPER 62.5/125 MULTIMODE FIBER ST/ST TO SC-DUPLEX 3 METER LOW SMOKE ZERO HALOGEN COLOR ORANGE | OM1 |
| 261987 | 055702K5Z20003M | LC Duplex to SC Duplex patch cord on 2-fiber Zipcord cable, with 2 mm legs, and a low-smoke, zero-halogen sheath. 3 m | OM1 |
| 412585 | 505002B5Z31003M | ST Compatible to ST Compatible patch cord on 2-fiber Zipcord cable, with 2.8 mm legs, and a low-smoke, zero-halogen sheath. 3 m | OM1 |
| 412589 | 575702B5Z31003M | SC Duplex to SC Duplex patch cord on 2-fiber Zipcord cable, with 2.8 mm legs, and a low-smoke, zero-halogen sheath. 3 m | OM1 |
| 412596 | 050502B5Z20003M | LC Duplex to LC Duplex patch cord on 2-fiber Zipcord cable, with 2 mm legs, and a low-smoke, zero-halogen sheath. 3 m | OM1 |

| | | | |
|--------|-----------------|--|-----|
| 412604 | 505702B5Z31003M | 2F JUMPER MM 50/125 OM2 CC ST/SC DUPX ORANGE LSZH ZIP 3M | OM1 |
| 412614 | 055702B5Z20003M | LC Duplex to SC Duplex patch cord on 2-fiber Zipcord cable, with 2 mm legs, and a low-smoke, zero-halogen sheath. 3 m | OM1 |