


CMRX



Waterfall Bracket

Integrated radius on brackets provide a smooth transition for cables from rack to overhead runway

Vertical Cable Manager

Optional front only or front and rear VCMs are fully assembled and install with just 2 bolts

Channel Pattern

Circles on staggered centers provide unlimited cable attachment points for cable bundles

FMP Mounting

Flexible Mounting Profile along the channel allows optional finger and accessory installation without occupying RMU

"D" Rings

¼ turn "D" rings can be mounted in any of the square hole patterns along the channel

POWERLOK

Machine soldered connections create a unit that is 3x more reliable than other industry units; bundle a CMRX and Quick Ship PDU model for 24-48 hour shipping

PDU Brackets


Optional, 2 or 3 position brackets attach to the side of the channel for button mounting PDUs

Part No.	RMU	H"	W" (19" EIA)	W" (23" EIA)	Channel Depth"	Overall Depth"*	Rail Rating (lbs.)
CMRX-45U10	45	84	24	28	10.5	14.1	2500
CMRX-45U16	45	84	24	28	16.25	19.85	2500
CMRX-45U24	45	84	24	28	24	27.6	2500
CMRX-45U30	45	84	24	28	30	33.6	2500
CMRX-45U36	45	84	24	28	36	39.6	2500
CMRX-52U10	52	96.25	24	28	10.5	14.1	2500
CMRX-52U16	52	96.25	24	28	16.25	19.85	2500
CMRX-52U24	52	96.25	24	28	24	27.6	2500
CMRX-52U30	52	96.25	24	28	30	33.6	2500
CMRX-52U36	52	96.25	24	28	36	39.6	2500
CMRX-59U10	59	108.5	24	28	10.5	14.1	2500
CMRX-59U16	59	108.5	24	28	16.25	19.85	2500
CMRX-59U24	59	108.5	24	28	24	27.6	2500
CMRX-59U30	59	108.5	24	28	30	33.6	2500
CMRX-59U36	59	108.5	24	28	36	39.6	2500

*Overall depth is with toe-out footprint

EXCEPTIONAL CABLE MANAGEMENT SUPPORT IN A SINGLE RACK

- #12-24 tapped channels (with RMU markings) for 19" and 23" mounting
- For 3/8" sq. (M6) channels, add 'M6' to end of part number
- Cable management pattern of 2.75" circles on 3.25" staggered centers allows for unlimited cable attachment points; square hole pattern between centers accept ¼ turn "D" rings; 20 rings included, 3.5" x 5"
- Square hole pattern and FMP pattern along the front and rear face of channels accept "D" rings and fingers for horizontal cable support
- Four top waterfall brackets with 3" bend radius; two fixed, two adjustable
- Cable runway or basket tray can rest directly on top of the rack or can be supported by optional ladder rack brackets
- Self squaring assembly with toe-in or toe-out orientation (Overall depth listed below is with toe-out footprint)
- Color: Black, Winter White
- Standards: UL2416, RoHS II



View the complete Great Lakes Rack collection:
GreatCabinets.com/racks