

FIRST AID & EMERGENCY EYEWASH



First Aid

Our enhanced custom first-aid program offers a new, broad portfolio of products, increased flexibility and improved turn-around times for custom quotations. Select one of the standard kits and add or subtract items you desire, or we can completely customize kits to meet your specific needs. You may also choose one of the many customization options to promote your company or your customer's organization.

- Customize the front cover label and/or refill label
- Choose between a label or printed option
- Utilize a Rapid label for a semi-custom look
- Receive your custom quote within 48 hours
- Three different Custom Imprint options available

Eyewash

Honeywell is the well-respected market leader in portable eyewash stations and is recognized for its wide range of emergency eyewash products, including the first 100% sterile sealed-fluid cartridge and 100% sterile delivery station, the first self-contained gravity-fed station, the first heated self-contained gravity-fed station and the first heated sterile eyewash station. The need for immediate flushing requires the installation of emergency eyewash devices in accessible locations that require no more than 10 SECONDS to reach. For a strong acid or strong caustic, the eyewash should be immediately adjacent to the hazard. Honeywell self-contained, portable eyewash stations require no plumbing for easy and affordable placement near any workplace hazard, and deliver a sterile or buffered saline solution superior to tap water for emergency eye care. Ordinary tap water, used in plumbed or some tank-type eyewash devices, may contain harmful bacteria or contaminants that can cause additional eye damage. A sterile or buffered saline solution is the most effective flushing fluid for emergency first aid.

NORTH





FAK75PL-CLSA

North® Bulk Plastic and Steel First Aid Kits

- The most economical option to be prepared
- Ideal for both work and home settings
- ANSI Z308.1-2015 compliant

| SKU | Description |
|---------------|---|
| FAK25PL-CLSA | 25 Person First Aid Kit, Plastic, Class A |
| FAK25STL-CLSA | 25 Person First Aid Kit, Steel, Class A |
| FAK50PL-CLSA | 50 Person First Aid Kit, Plastic, Class A |
| FAK50STL-CLSA | 50 Person First Aid Kit, Steel, Class A |
| FAK75PL-CLSA | 75 Person First Aid Kit, Plastic, Class A |
| FAK75STL-CLSA | 75 Person First Aid Kit, Steel, Class A |



FAK100CAB-CLSB

North® Steel First Aid Stations

- Contain a large assortment of first aid and medical supplies
- Ideal for large office or manufacturing settings – all stations are ANSI Z308.1-2015 compliant
- Rugged steel cabinets available in an assortment of sizes

| SKU | Description |
|----------------|---|
| FAK100CAB-CLSB | 100 Person First Aid Kit, Steel, Class B |
| FAK150CAB-CLSB | 150 Person First Aid Kit, Steel, Class B |
| FAK200CAB-CLSB | 200 Person First Aid Kit, Steel, Class B |
| FAK3SHLF-CLSB | 3-Shelf First Aid Kit, Steel, Class B, w/ Liner |
| FAK4SHLF-CLSB | 4-Shelf First Aid Kit, Steel, Class B, w/ Liner |



FRKSOFPAK-CLSB

North® First Responder Softpack First Aid Kits

- Soft kits are lightweight and neatly organized for easy access and inventory
- Wide variety of supplies to treat a wide variety of injuries
- Rugged nylon bags are easy to carry to the scene of the emergency

| SKU | Description |
|----------------|---|
| FRKSOFPAK-CLSB | First Responder First Aid Kit, Soft Carrier, ANSI 2015, Class B |
| 018501-4221 | 4221 Soft Pack Medium North |
| 018502-4220 | 4220 Soft Pack Small North |
| 346200 | XL First Responder Emergency Kit |



019744-0031

North® Specialty First Aid Kits

- Specially designed to treat injuries common to a particular work place

| SKU | Description |
|--------------|--|
| 019737-0024L | Truckers First Aid Kit, Steel, 10 Unit |
| 019744-0031L | Construction Bulk First Aid Kit, 50 Person Plastic |
| 019729-0016L | Construction Bulk First Aid Kit, 10 Unit Steel |
| 019730-0017L | Construction Bulk First Aid Kit, 16 Unit Steel |



FIRST AID KITS



049056

North® Burn Care Soft Pack First Aid Kits

- Gel-soaked burn care that relieves pain
- Gel is water soluble to be easily rinsed for further medical treatment
- Prevents infection by protecting against airborne contamination

| SKU | Description |
|--------|---------------------------------------|
| 049020 | Water-Jel Fire Blanket Canister 6'x5' |
| 049056 | Large Soft Burn Kit Water-Jel |
| 049055 | Small Soft Burn Kit Water-Jel |



552001

North® Personal Protection Soft Pack First Aid Kits

- Complete kits with the necessary supplies to clean a spill that contains the risk of blood-borne pathogens
- Necessary for OSHA 1910.130 compliance

| SKU | Description |
|--------------|--------------------------------|
| 019749-0032L | 16U Plastic North Response Kit |
| 552001 | Body Fluid Clean Up Kit Bag |

EMERGENCY EYEWASH – PRIMARY DEVICES



Honeywell Fendall Pure Flow 1000® Mounted Eyewash Station

- Easy installation. No plumbing required.
- Factory-sealed fluid cartridges eliminate mixing and measuring.
- Easy-to-activate sure-grip handle provides instant, simple activation.
- Unique nozzle design delivers a soft “ribbon” of our buffered saline solution.
- Permits thorough flushing with a constant flow rate and stream height that provides 0.4 gpm for entire 15-minute cycle.
- Captures waste fluid to eliminate spill hazards and simplify fluid disposal
- Integral valve at bottom of unit allows easy draining of reservoir after use.
- 24-month cartridge life*
- Cartridges remain sealed until activated.
- Made in the USA

| SKU | Description |
|----------------|----------------------------------|
| 32-001000-0000 | Pure Flow 1000 Station |
| 32-001050-0000 | Pure Flow 1000 Cartridge |
| 32-ST1050-0000 | Sterile Pure Flow 1000 Cartridge |

*Shelf life determined by date of manufacture. Always check product expiration date.





Honeywell Fendall 2000® Sterile Delivery Eyewash Station

- Delivers 100% sterile saline from a 100% sterile delivery system
- 24-month cartridge life*
- Built-in alarm system that sounds when the unit has been activated and again when the injured individual has completed the required 15-minute flush
- Deactivation button that allows for fast and easy maintenance without false activation
- Arm/headrest provides user comfort, enabling better compliance
- Integrated waste containment to prevent spills and is easily emptied
- Sleek assembly that fits in most locations
- Self-contained, with no plumbing required, makes this highly portable
- Easy-view side windows to check sterile solution expiration date and key contact information
- Meets ANSI Z358.1 15-minute flush requirement for primary eyewash stations
- Sterile Solution Made in the USA

| SKU | Description |
|----------------|--------------------------------|
| 32-002000-0000 | Fendall 2000 Station |
| 32-ST2050-0000 | Sterile Fendall 2000 Cartridge |

*Shelf life determined by date of manufacture. Always check product expiration date.





32-000462-0000



32-000465-0000

Wall Stations

- Sealed, sterile bottles contain Honeywell Saline – a buffered, saline solution superior to tap water for emergency eye care
- Blow-fill-seal bottles are tamper resistant, yet easily removed in an emergency
- Extended flow opening provides longer flow rate than conventional bottles
- Durable, open face design holds bottles firmly in place with easy access to bottles in an emergency
- Mounts to wall with provided screws
- Durable plastic is easy to clean
- Simple, highly visible operating instructions are provided on each unit – 16- and 32-oz. bottles feature trilingual instructions
- Ensured quality and lasting value with FDA-grade polyethylene bottles featuring lot numbers and expiration dates
- Does not meet ANSI Z358.1 15-minute flushing requirement
- Made in the USA

| SKU | Description |
|----------------|----------------------------|
| 32-000462-0000 | 32-oz. Double Wall Station |
| 32-000465-0000 | 16-oz. Double Wall Station |
| 32-000461-0000 | 32-oz. Single Wall Station |
| 32-000460-0000 | 16-oz. Single Wall Station |





32-001065-0000

Universal Eyewash Stand

- Inexpensive alternative to wall mounting
- Versatile stand can be mounted to a floor or be used free standing
- Compact and easy to assemble (assembly time – 5 minutes or less)
- All assembly parts are included
- Lightweight, sturdy steel tubing design (25 lbs.)

| SKU | Description |
|----------------|---|
| 32-001065-0000 | Eyewash Stand for Use with Fendall 2000, Fendall Pure Flow 1000, and Fendall Porta Stream I, II and III |



32-001060-0000

Universal Eyewash Cart

- Provides quick, easy portability for self-contained, gravity-fed emergency eyewash devices
- Reliable design ensures durability
- Uses mounting bracket supplied with eyewash station

| SKU | Description |
|----------------|--|
| 32-001060-0000 | Eyewash Cart for Use with All Portable Devices |



32-002001-0000

Heated Fendall 2000™ Accessory

- For use both indoors and outdoors for the greatest flexibility
- Tested and approved for temperatures as low as -40°, making emergency eyewash available to workers even in extreme cold environments
- Powered by a built-in 110 volt, UL/ CSA-certified, GFCI-protected heater for the highest levels of safety. Utilizes environmentally friendly heat-spreading technology for efficient heat distribution and minimized energy requirements

Perfect for:

- Outdoor worksites during cold weather months
- Low-temperature work areas, such as freezers

| SKU | Description |
|----------------|-------------------------------|
| 32-002001-0000 | Fendall 2000 Heated Accessory |

