

Parallax & Parallax Thin

with Ambient Light Rejecting Technology

FOR YOUR IMAGE™




Parallax™

Finally. An ambient light-rejecting technology worthy of Pro AV. Introducing the latest surfaces from Da-Lite, which feature an advanced optical lens system that rejects light. This new technology mimics the look of a television when it is on and when it is off, but without the glare from windows or lighting fixtures.

Parallax 0.8 and Parallax UST 0.45

- Parallax 0.8 for standard throw projectors (1.5:1 throw or greater)
 - 96% blocked ambient light*
 - 85 degree wide viewing half angle*
- Parallax UST 0.45 for ultra short-throw projectors
 - 95% blocked ambient light*
 - 80 degree wide viewing half angle*



Features

- Unassembled shipping and easy installation
- Pro-Trim® finish to absorb light surrounding the viewing area
- Easy to assemble 2½" frame

Parallax Sizes

HDTV (16:9) Format				Wide (16:10) Format				Cinemascope (2.35:1) Format			
VIEWING AREA (H X W)		NOMINAL DIAGONAL		VIEWING AREA (H X W)		NOMINAL DIAGONAL		VIEWING AREA (H X W)		NOMINAL DIAGONAL	
in.	cm	in.	cm	in.	cm	in.	cm	in.	cm	in.	cm
37½" x 67"	95 x 170	77"	196	44½" x 71½"	113 x 182	84"	213	37½" x 88"	95 x 224	96"	244
40½" x 72"	103 x 183	82"	208	50" x 80"	127 x 203	94"	239	40½" x 95"	103 x 241	103"	262
45" x 80"	114 x 203	92"	234	57½" x 92"	146 x 234	109"	277	45" x 106"	114 x 269	115"	292
49" x 87"	124 x 221	100"	254					49" x 115"	124 x 292	125"	318
52" x 92"	132 x 234	106"	269					52" x 122"	132 x 310	133"	338
54" x 96"	137 x 244	110"	279					54" x 126"	137 x 320	138"	351
59" x 104½"	150 x 265	120"	305					58" x 136½"	147 x 347	148"	376

Parallax Surfaces

Da-Lite's Parallax surfaces are made up of lens-like, micro-layers to achieve optimal ambient light rejection for a glare-free and speckle-free image.




Parallax 0.8
Horizontal Half Angle: 85°
Vertical Half Angle: 17°
Gain: 0.8



Parallax UST 0.45
Horizontal Half Angle: 80°
Vertical Half Angle: 55°
Gain: 0.45

Parallax Thin

- Parallax 0.8 surface for standard throw projectors (1.5:1 or greater)
- Thin 3/8" bezel aluminum frame
- 1" depth
- Ships fully assembled



Parallax Thin Sizes

HDTV (16:9) Format

VIEWING AREA (H X W)		NOMINAL DIAGONAL	
in.	cm	in.	cm
45" x 80"	114 x 203	92"	234
49" x 87"	124 x 221	100"	254
52" x 92"	132 x 234	106"	269
54" x 96"	137 x 244	110"	279
59" x 104½"	150 x 265	120"	305

Wide (16:10) Format

VIEWING AREA (H X W)		NOMINAL DIAGONAL	
in.	cm	in.	cm
50" x 80"	127 x 203	94"	239
57½" x 92"	146 x 234	109"	277



A BRAND OF MILESTONE AV TECHNOLOGIES | www.milestone.com

P 800.622.3737 / 574.267.8101 **F** 877.325.4832 / 574.267.7804

E info@da-lite.com

In British Columbia, Milestone AV Technologies ULC carries on business as MAVT Milestone AV Technologies ULC.

©2016 Milestone AV Technologies. DL-0617 0216.

Da-Lite is a registered trademarks of Milestone AV Technologies. All other brand names or marks are used for identification purposes and are trademarks of their respective owners. All patents are protected under existing designations. Other patents pending.

milestone

Milestone AV Technologies is home of Chief, Da-Lite, Sanus and Projecta. Across these brands, Milestone produces a wide range of innovative audiovisual solutions.