

XTL™ Labels

Heat-Shrink Tube (Continuous)

- DYMO XTL™ label makers print directly on continuous Heat-Shrink Tubes
- Heat-Shrink Tubes provide insulation when shrunk down and ensure a secure fit on wires and cables with a 3:1 shrink ratio
- Constructed of flame-retardant polyolefin sleeves and tested to industry standards
- Meets MIL-M-81531, MIL-STD-202G, SAE-DTL-23053/5 (Class 1 & 3)
- Easy-to-peel split back design makes applying labels quick and easy
- Durable thermal transfer printing technology – label text won't smear or fade
- RoHS compliant



Quick Specs

Label Widths	¼", ½", 1", 2"
Tape Platform	XTL
Printer Compatibility	XTL 300: Up to 1" wide XTL 500: Up to 2" wide
Label Length	8.9' (¼", ½", 1" width) 5.9' (2" width)
Printing System	Thermal Transfer
Temperature Rating	Max 257°F
UL Recognized	Yes, component to UL 224
Country of Origin	Belgium
Material	Heat Shrink

Item Number	Width	Color	List Price (ea)	ECCN Number		Length (in)	Width (in)	Height (in)	Weight (lbs)	QTY	Ti	Hi	UPC
1868809	¼"	A	\$63.59	EAR99	Unit	2.83	1.38	4.72	0.11	1	-	-	071701001887
					Shelf	8.46	2.99	4.96	0.73	6	-	-	30071701001888
					Case	15.75	9.06	5.71	4.30	30	-	-	50071701001882
					Pallet	48.03	40.16	51.57	433.43	88	11	8	-
1868810	½"	A	\$76.79	EAR99	Unit	2.83	1.38	4.72	0.13	1	-	-	071701001894
					Shelf	8.46	2.99	4.96	0.85	6	-	-	30071701001895
					Case	15.75	9.06	5.71	4.93	30	-	-	50071701001899
					Pallet	48.03	40.16	51.57	488.72	88	11	8	-

DISTRIBUTED BY:
DYMO, ATLANTA, GA 30328
800-426-7827: WWW.DYMO.COM

INTERNAL USE ONLY. NOT FOR DISTRIBUTION.



A *NewellRubbermaid* Brand

©2015 SANFORD, L.P.

XXXXXX

This information is being provided for general information purposes and the compliance standards and certifications referenced herein are based on current standards which are subject to change.

XTL™ Labels



Item Number	Width	Color	List Price (ea)	ECCN Number		Length (in)	Width (in)	Height (in)	Weight (lbs)	QTY	Ti	Hi	UPC
1868811	1"	A	\$109.20	EAR99	Unit	2.83	1.38	4.72	0.19	1	-	-	071701001900
					Shelf	8.46	2.99	4.96	1.22	6	-	-	30071701001901
					Case	15.75	9.06	5.71	6.75	30	-	-	50071701001905
					Pallet	48.03	40.16	51.57	648.78	88	11	8	-
1868812	2"	A	\$99.60	EAR99	Unit	2.83	2.56	4.72	0.32	1	-	-	071701001917
					Shelf	8.46	2.99	4.96	1.04	3	-	-	30071701001918
					Case	15.75	9.06	5.71	5.89	15	-	-	50071701001912
					Pallet	48.03	40.16	51.57	573.11	88	11	8	-

DISTRIBUTED BY:
 DYMO, ATLANTA, GA 30328
 800-426-7827: WWW.DYMO.COM

INTERNAL USE ONLY. NOT FOR DISTRIBUTION.



XXXXXX

This information is being provided for general information purposes and the compliance standards and certifications referenced herein are based on current standards which are subject to change.



A *NewellRubbermaid* Brand

©2015 SANFORD, L.P.

A Newell Rubbermaid Company™				
	<small>RMZ Millenia Business Park Campus - 2, 5th Floor No. 143, DCM, S. R. Road Kondachawall, Chennai 600 096 India T: 91 44 4213 7777 www.schawki.com</small>			
	Use the PANTONE MATCHING SYSTEM for accurate color reproduction			
	VERSION	JOB DESCRIPTION : NRM_Writing_Dymo Industrial_150836_WDY_XTL_SS_Product Fact Book FILE NAME : 150836_WDY_SS_RD_Heat Shrink Tube_Continuous_v2.indd	BRAND : DYMO	
2 DATE : 05-25-2015 OPERATOR : PS	SCHAWKI JOB # : 341661D NRM JOB # : 150836 COMPONENT # : N/A	CATEGORY OF WORK : FLYER NO. OF PAGES# : 2 PAGES SIZE : A4		
NOTE :				