

XTL™ Labels

Heat-Shrink Tube (Pre-Sized)

- DYMO XTL™ label makers print directly on Heat-Shrink Tubes
- Heat-Shrink Tubes provide insulation when shrunk down and ensure a secure fit on wires and cables with a 3:1 shrink ratio
- Constructed of flame-retardant polyolefin sleeves and tested to industry standards
- Meets MIL-M-81531, MIL-STD-202G, SAE-DTL-23053/5 (Class 1 & 3)
- Durable thermal transfer printing technology – label text won't smear or fade
- RoHS compliant



Quick Specs

Label Widths	¼", ½", 1", 2-1/8"
Tape Platform	XTL
Printer Compatibility	XTL 500
Printing System	Thermal Transfer
Temperature Rating	Max 257°F
UL Recognized	Component to UL 224
Country of Origin	Belgium
Material	Heat-Shrink

Item Number	Width (in)	Length (in)	List Price (ea)	Color	Quantity of Pre-Sized Labels	ECCN Number	Unit	Length (in)	Width (in)	Height (in)	Weight (lbs)	QTY	Ti	Hi	UPC
1868717	¼"	1-5/16"	\$71.39	A	81	EAR99	Unit	2.83	2.56	4.72	0.27	1	-	-	071701000798
							Shelf	8.46	2.99	4.96	0.91	3	-	-	30071701000799
							Case	15.75	9.06	5.71	5.22	15	-	-	50071701000793
							Pallet	48.03	40.16	51.57	514.91	88	11	8	-
1868718	½"	1-5/16"	\$60.59	A	65	EAR99	Unit	2.83	2.56	4.72	0.27	1	-	-	071701000804
							Shelf	8.46	2.99	4.96	0.91	3	-	-	30071701000805
							Case	15.75	9.06	5.71	5.22	15	-	-	50071701000809
							Pallet	48.03	40.16	51.57	514.91	88	11	8	-
1868719	1"	1-5/16"	\$107.40	A	60	EAR99	Unit	2.83	2.56	4.72	0.27	1	-	-	071701000811
							Shelf	8.46	2.99	4.96	0.91	3	-	-	30071701000812
							Case	15.75	9.06	5.71	5.22	15	-	-	50071701000816
							Pallet	48.03	40.16	51.57	514.91	88	11	8	-

DISTRIBUTED BY:
DYMO, ATLANTA, GA 30328
800-426-7827: WWW.DYMO.COM

INTERNAL USE ONLY. NOT FOR DISTRIBUTION.



A *NewellRubbermaid* Brand



©2015 SANFORD, L.P.

XTL™ Labels

Item Number	Width	Length	List	Color	Quantity of Pre-Sized Labels	ECCN Number		Length (in)	Width (in)	Height (in)	Weight (lbs)	QTY	Ti	Hi	UPC
1868720	2-1/8"	1-5/16"	\$61.79	A	25	EAR99	Unit	2.83	2.56	4.72	0.27	1	-	-	071701001092
							Shelf	8.46	2.99	4.96	0.91	3	-	-	30071701001093
							Case	15.75	9.06	5.71	5.22	15	-	-	50071701001097
							Pallet	48.03	40.16	51.57	514.91	88	11	8	-
1868731	¼"	1-7/8"	\$68.39	A	81	EAR99	Unit	2.83	2.56	4.72	0.27	1	-	-	071701001108
							Shelf	8.46	2.99	4.96	0.91	3	-	-	30071701001109
							Case	15.75	9.06	5.71	5.22	15	-	-	50071701001103
							Pallet	48.03	40.16	51.57	573.11	88	11	8	-
1868732	½"	1-7/8"	\$73.19	A	65	EAR99	Unit	2.83	2.56	4.72	0.32	1	-	-	071701001115
							Shelf	8.46	2.99	4.96	1.04	3	-	-	30071701001116
							Case	15.75	9.06	5.71	5.89	15	-	-	50071701001110
							Pallet	48.03	40.16	51.57	573.11	88	11	8	-
1868733	1"	1-7/8"	\$115.20	A	60	EAR99	Unit	2.83	2.56	4.72	0.32	1	-	-	071701001122
							Shelf	8.46	2.99	4.96	1.04	3	-	-	30071701001123
							Case	15.75	9.06	5.71	5.89	15	-	-	50071701001127
							Pallet	48.03	40.16	51.57	573.11	88	11	8	-
1868734	2-1/8"	1-7/8"	\$83.39	A	25	EAR99	Unit	2.83	2.56	4.72	0.32	1	-	-	071701001139
							Shelf	8.46	2.99	4.96	1.04	3	-	-	30071701001130
							Case	15.75	9.06	5.71	5.89	15	-	-	50071701001134
							Pallet	48.03	40.16	51.57	573.11	88	11	8	-

DISTRIBUTED BY:
 DYMO, ATLANTA, GA 30328
 800-426-7827: WWW.DYMO.COM

INTERNAL USE ONLY. NOT FOR DISTRIBUTION.

A Newell Rubbermaid Company™				
	<small>RMZ Millenia Business Park Campus - 2, 5th Floor No. 143, DCM, S, R, Road Kondachawall, Chennai 600 096 India T: 91 44 4233 7777 www.schawk.com</small>			
	Use the PANTONE MATCHING SYSTEM for accurate color reproduction			
	VERSION	JOB DESCRIPTION : NRM_Writing_Dymo Industrial_150836_WDY_XTL_SS_Product Fact Book FILE NAME : 150836_WDY_SS_RD_Heat_Shrink_Tube_Pre-Sized_v3.indd	BRAND : DYMO	
3 DATE : 06-03-2015 OPERATOR : SUN	SCHAWK JOB # : 341661E NRM JOB # : 150836 COMPONENT # : N/A	CATEGORY OF WORK : FLYER NO. OF PAGES# : 2 PAGES SIZE : A4		
NOTE:				