

Commercial QuickPort® Patch Panels (empty)

	Flat							Angled						
	Standard				High Density	Diecast	High Density	Standard				High Density		
	49255-H24	49255-L24	49255-H48	49255-L48	49255-Q48	49255-D48	49255-D72	49256-H24	49256-L24	49256-H48	49256-L48	49256-D48	49256-D72	
RU	1RU		2RU		1RU		2RU	1RU		2RU		1RU	2RU	
Ports	24		48		48		72	24		48		72		
Labeling	Silk-Screened Blocks	Mag Lens	Silk-Screened Blocks	Mag Lens	Silk-Screened Numbering	Mag Lens	Silk-Screened Numbering	Silk-Screened Blocks	Mag Lens	Silk-Screened Blocks	Mag Lens	Silk-Screened Numbering		
Cable Mgt.	Included				Sold Separately (P/N 49005-DMB)		Included		Sold Separately (P/N 49006-AMB)					
Country of Origin	Taiwan	Mexico	Taiwan	USA				Mexico		Taiwan	USA	Mexico		

Released May 2018 7216 / E18



49255-H24



49255-Q48



49256-L48

Commercial Patch Panels

Cat 5e							
	Flat		Angled		Composite Flat	Flat QuickPort Panel Kit [^]	
	5G596-U**	5G596-C48	5G596-L**	5G597-U**	5G597-L**	C1586-U48	5G270-U**
RU	1RU (12, 24 Port) 2RU (48 Port) 4RU (96 Port)	2RU	1RU (24 Port) 2RU (48 Port)	1RU (24 Port) 2RU (48 Port)		2RU	1RU (24 Port) 2RU (48 Port)
Ports	12, 24, 48, 96	48	24, 48	24, 48		48	24, 48
Labeling	Standard Color Coded	Central Labeling Color Coded	Magnifying Lens Color Coded	Standard Color Coded	Magnifying Lens Color Coded	Customizable [†]	White Blocks
PoE Rating	Up to 60W						
Primary Construction	Metal				40% Glass-Filled Polymer Composite		Metal
Color	Black For custom colors, contact Leviton Inside Sales at 800.722.2082				Custom		Black
Rear Cable Mgt. Bar	Included			Sold Separately (P/N 49006-AMB)		Included	
Country of Origin	USA						
Applications	All			<ul style="list-style-type: none"> • Racks w/ vertical cable management • Free standing racks • Applications with minimal clearance in front of mounting surface 		Showroom for Data Centers/TRS	All

* Port Size [^]Kitted with eXtreme Connectors [†] Customize composite patch panels with any design, color, or logo

Released May 2018 7216 / E18



5G596-L24



5G596-U48

Commercial Patch Panels

Cat 6							
Flat			Angled		Composite Flat	Flat QuickPort Panel Kit [^]	
	69586-U**	69586-C48	69586-L**	69587-U**	69587-L**	C1686-U48	69270-U**
RU	1RU (12, 24 Port) 2RU (48 Port) 4RU (96 Port)	2RU	1RU (24 Port) 2RU (48 Port)	1RU (24 Port) 2RU (48 Port)		2RU	1RU (24 Port) 2RU (48 Port)
Ports	12, 24, 48, 96	48	24, 48	24, 48		48	24, 48
Labeling	Standard Color Coded	Central Labeling Color Coded	Magnifying Lens Color Coded	Standard Color Coded	Magnifying Lens Color Coded	Customizable [†]	White Blocks
PoE Rating	Up to 100W						
Primary Construction	Metal				40% Glass-Filled Poly. Composite	Metal	
Color	Black For custom colors, contact Leviton Inside Sales at 800.722.2082				Custom	Black	
Rear Cable Mgt. Bar	Included			Sold Separately (P/N 49006-AMB)		Included	
Country of Origin	USA						
Applications	All			<ul style="list-style-type: none"> Racks w/ vertical cable mgt. Free standing racks Applications with minimal clearance in front of mounting surface 		Showroom for DCs/TRs	All

* Port Size ^Kitted with eXtreme Connectors † Customize composite patch panels with any design, color, or logo



69587-U48



C1686-U48

Cat 6A		
Flat	Angled	Flat QuickPort Panel Kit [^]
6A586-U**	6A587-U**	6910G-U**
1RU (24 Port) 2RU (48 Port)		
24, 48		
Magnifying Lens Color Coded		White Blocks
Up to 100W		
Metal		
Black For custom colors, contact Inside Sales at 800.722.2082		
Included	Sold Separately (P/N 49006-AMB)	Included
USA		
All	<ul style="list-style-type: none"> Racks w/ vertical cable mgt. Free standing racks Applications with minimal clearance in front of mounting surface 	All

Released May 2018 7216 / E18



6910G-U24

Commercial QuickPort® Patch Panels (empty)

	Composite, e2XHD, Recessed & Recessed-Angled					Shielded						
	Composite	e2XHD Flat and Angled	Vertigo	Recessed	Recessed Angled		Flat Standard		Flat High Density	Angled Standard		Angled High Density
	C1255-H48	E2X1 [^] -S48	49280-QP*	49255-R24	4W256-H24	4W256-H48	4S255-S24	4S255-S48	4S255-D48	4S256-S24	4S256-S48	4S256-D48
RU	2RU	1RU	0RU	1RU		1RU		2RU	1RU	2RU	1RU	1RU
Ports	48		12	24		48	24	48		24	48	
Labeling	Customizable†	Silk-Screened Numbering	Mag Lens	Silk-Screened Blocks		Silk-Screened Blocks		Silk-Screened Numbering	Silk-Screened Blocks		Silk-Screened Numbering	
Cable Mgt.	Front and Rear	Sold Separately (P/N E2X1F-CMB)	3" Chanel Available	Included	Sold Separately (P/N 4W006-AMB)		Included	Sold Separately (P/N 49005-DMB)	Sold Separately (P/N 4W006-AMB)		Sold Separately (P/N 4W006-AMB)	
Country of Origin	USA	Taiwan	USA	Mexico	USA		USA		Mexico	USA		

† Customize composite patch panels with any design, color, or logo

* 3" and 6" channel available; fiber versions also available

[^] Flat/angled available

Released May 2018 7216 / E18



C1255-H48



E2X1F-S48



49280-QP3



4S256-D48