


# Commercial QuickPort® Patch Panels (empty)

	Flat							Angled						
	Standard				High Density	Diecast	High Density	Standard				High Density		
	49255-H24	49255-L24	49255-H48	49255-L48	49255-Q48	49255-D48	49255-D72	49256-H24	49256-L24	49256-H48	49256-L48	49256-D48	49256-D72	
RU	1RU		2RU		1RU		2RU	1RU		2RU		1RU	2RU	
Ports	24		48		48		72	24		48		72		
Labeling	Silk-Screened Blocks	Mag Lens	Silk-Screened Blocks	Mag Lens	Silk-Screened Numbering	Mag Lens	Silk-Screened Numbering	Silk-Screened Blocks	Mag Lens	Silk-Screened Blocks	Mag Lens	Silk-Screened Numbering		
Cable Mgt.	Included				Sold Separately (P/N 49005-DMB)		Included		Sold Separately (P/N 49006-AMB)					
Country of Origin	Taiwan	Mexico	Taiwan	USA				Mexico		Taiwan	USA	Mexico		

Released May 2019 7750 / E19



49255-H24



49255-D72



49256-L48

# Commercial Patch Panels

Cat 5e							
Flat			Angled		Composite Flat	Flat QuickPort Panel Kit <sup>^</sup>	
	5G596-U**	5G596-C48	5G596-L**	5G597-U**	5G597-L**	C1586-U48	5G270-U**
RU	1RU (12, 24 Port) 2RU (48 Port) 4RU (96 Port)	2RU	1RU (24 Port) 2RU (48 Port)	1RU (24 Port) 2RU (48 Port)		2RU	1RU (24 Port) 2RU (48 Port)
Ports	12, 24, 48, 96	48	24, 48	24, 48		48	24, 48
Labeling	Standard Color Coded	Central Labeling Color Coded	Mag Lens Color Coded	Standard Color Coded	Mag Lens Color Coded	Customizable <sup>†</sup>	Silk-Screened Blocks
PoE Rating	Up to 60W						
Primary Construction	Metal				40% Glass-Filled Polymer Composite		Metal
Color	Black <small>For custom colors, contact Leviton Inside Sales at 800.722.2082</small>				Custom		Black
Rear Cable Mgt. Bar	Included			Sold Separately <small>(P/N 49006-AMB)</small>		Included	
Country of Origin	USA						
Applications	All			<ul style="list-style-type: none"> <li>Racks w/ vertical cable management</li> <li>Free standing racks</li> <li>Applications with minimal clearance in front of mounting surface</li> </ul>		Showroom for Data Centers/TRs	All

\* Port Size    <sup>^</sup>Kitted with eXtreme Connectors    <sup>†</sup> Customize composite patch panels with any design, color, or logo

Released May 2019 7750 / E19



5G596-L24



5G596-U48

# Commercial Patch Panels

Cat 6								Cat 6A			
		Flat		Angled		Composite Flat	Flat QuickPort Panel Kit ^	Flat	Angled	Flat QuickPort Panel Kit ^	
	69586-U**	69586-C48	69586-L**	69587-U**	69587-L**	C1686-U48	69270-U**	6A586-U**	6A587-U**	6910G-U**	
RU	1RU (12, 24 Port) 2RU (48 Port) 4RU (96 Port)	2RU	1RU (24 Port) 2RU (48 Port)	1RU (24 Port) 2RU (48 Port)		2RU	1RU (24 Port) 2RU (48 Port)	1RU (24 Port) 2RU (48 Port)			
Ports	12, 24, 48, 96	48	24, 48	24, 48		48	24, 48	24, 48			
Labeling	Standard Color Coded	Central Labeling Color Coded	Mag Lens Color Coded	Standard Color Coded	Mag Lens Color Coded	Customizable†	Silk-Screened Blocks	Mag Lens Color Coded		Silk-Screened Blocks	
PoE Rating	Up to 100W						Up to 100W				
Primary Construction	Metal					40% Glass-Filled Poly. Composite	Metal	Metal			
Color	Black <small>For custom colors, contact Leviton Inside Sales at 800.722.2082</small>					Custom	Black	Black <small>For custom colors, contact Inside Sales at 800.722.2082</small>			
Rear Cable Mgt. Bar	Included			Sold Separately <small>(P/N 49006-AMB)</small>		Included					
Country of Origin	USA						USA				
Applications	All			<ul style="list-style-type: none"> <li>Racks w/ vertical cable mgt.</li> <li>Free standing racks</li> <li>Applications with minimal clearance in front of mounting surface</li> </ul>		Showroom for DCs/TRs	All	All	<ul style="list-style-type: none"> <li>Racks w/ vertical cable mgt.</li> <li>Free standing racks</li> <li>Applications with minimal clearance in front of mounting surface</li> </ul>	All	

\* Port Size    ^ Kitted with eXtreme Connectors    † Customize composite patch panels with any design, color, or logo



C1686-U48



6910G-U24



# Commercial QuickPort® Patch Panels (empty)

	Composite, e2XHD & Recessed				Shielded					
	Composite	e2XHD Flat and Angled	Vertigo	Recessed	Flat Standard		Flat High Density	Angled Standard		Angled High Density
	C1255-H48	E2X1^-S48	49280-QP*	49255-R24	4S255-S24	4S255-S48	4S255-D48	4S256-S24	4S256-S48	4S256-D48
RU	2RU	1RU	0RU	1RU	1RU	2RU	1RU	2RU	2RU	1RU
Ports	48		12	24	24	48		24	48	
Labeling	Customizable†	Silk-Screened Numbering	Mag Lens	Silk-Screened Blocks	Silk-Screened Blocks		Silk-Screened Numbering	Silk-Screened Blocks		Silk-Screened Numbering
Cable Mgt.	Front and Rear	Sold Separately (P/N E2X1F-CMB)	3" Chanel Available	Included	Included		Sold Separately (P/N 49005-DMB)	Sold Separately (P/N 4W006-AMB)		
Country of Origin	USA	Taiwan	USA		USA			Mexico	USA	

† Customize composite patch panels with any design, color, or logo

\* 3" and 6" channel available; fiber versions also available

^ Flat/angled available

Released May 2019 7750 / E19



E2X1F-S48



49280-QP3



4S256-D48