

HANDHELD NETWORK TEST (Hardware Solutions)

LinkSprinter	LinkRunner AT	LinkRunner G2	AirCheck G2	OneTouch AT, G2 or 10G
\$	\$\$	\$\$	\$\$	\$\$\$
Copper	Copper/Fiber	Copper/Fiber/Wi-Fi 1 /Bluetooth	Wi-Fi/Copper	Copper/Fiber/Wi-Fi
<p>10-second Network Connectivity Test:</p> <ul style="list-style-type: none"> 10/100/1G link validation PoE voltage Link speed/duplex w/1Gig downshift warning Switch detail including slot/port/VLAN/Voice VLAN DCHP or static IP validation Gateway router Internet reachability Cable test with distance to fault 	<p>Includes Functionality of LinkSprinter Plus:</p> <ul style="list-style-type: none"> 10/100/1G link validation TruePower™ PoE loaded power test up to Class 4 Network connectivity test over copper and fiber Programmable AutoTest profiles Up to 10 connectivity validation targets per AutoTest Remote reflector for OneTouch 	<p>Includes Functionality of LinkRunner AT Plus:</p> <ul style="list-style-type: none"> 10/100/1G link validation TruPower™ PoE loaded power test up to four pair UPOE Android™ OS¹ allows customization IoT device support via Android apps Wi-Fi² and Bluetooth allow network and device connection Color touch screen display Charge off PoE 	<p>Wireless Network Connectivity Test:</p> <ul style="list-style-type: none"> 802.11 a/b/g/n/ac test Wireless performance testing with iPerf Detect/locate access points View channel utilization Determine 802.11 vs. non-802.11 traffic by channel 10-second Network Connectivity Test 	<p>Wired/Wireless Network Connectivity Test:</p> <ul style="list-style-type: none"> 10/100/1G/10Gig link validation 802.11 a/b/g/n/ac test Inline VoIP analysis & packet capture (G2 only) 2 GByte packet capture Path performance testing top 10Gig Remote control and file transfer Programmable AutoTest profiles
PC Help Desk Technician MAC Support	Technicians MAC Support	Technicians MAC Support	Technicians MAC Support Wireless Architects	Technicians Network Engineers Network Administrators

Documentation: All testers support automated test result upload to the included Link-Live Cloud Service for results management and reporting. Link-Live provides a way for teams to easily keep track of wired and wireless network connectivity including additional information that can be appended to each test such as jack location to document the connection path to switch slot/port/VLAN, and even photos of end device attributes such as serial number, asset tag, QR/Barcode, etc.

Products are available in Combos, Packs and Kits to help you and your team deploy the right technology across your team. Visit the product web pages to learn more about these offerings, options and accessories and even **take a virtual test drive**.
<http://enterprise.netscout.com/industries/handheld-network-test-solutions>



Don't forget to add Gold Support for your products! As a Gold member, you are entitled to the advanced technical support you need to fully troubleshoot the complexities of your network plus your registered equipment will always be up-to-date with the latest software releases. 3-year Gold provides a 10% discount off current Gold pricing.

¹ Android is a trademark of Google Inc.

² Wi-Fi and Bluetooth require the optional Edimax combination adapter. Edimax is a registered trademark of Edimax Technologies, Inc.

© 2017 NETSCOUT SYSTEMS, INC. All rights reserved. NETSCOUT, and the NETSCOUT logo are registered trademarks of NETSCOUT SYSTEMS, INC., and/or its subsidiaries and/or affiliates in the USA and/or other countries. All other brands and product names and registered and unregistered trademarks are the sole property of their respective owners.