



# Promise Surveillance Solution Lineup

## HOW TO

To easily select the suitable Vess Series model for your various surveillance systems demand, we categorize by the following:

- Form Factors/HDD bays: Tower Base/1U4/2U6/2U8/3U16/4U24
- Camera Range: 8ch/35ch/64ch/100ch/150ch/200ch
- Processor Availability: Celeron/Intel Core/Intel Xeon
- Applications: Home Surveillance/NVR/Analytics Server/Management Server/IVA

Product Family	Vess A - Series									Vess RAID/JBOD series				
	Apollo Cloud Surveillance Limited	A2330	A3120	A6120	A3340	A6600	A6800	A7600	A7800	R2600	J2600	R3600	J3600	J3610
Product Models														
Camera Range	1 to 8	35	64	100	100	150	200	150	200	N/A	N/A	N/A	N/A	N/A
Form Factor	Tower	2U	1U	1U	2U	3U	4U	3U	4U	3U	3U	3U	3U	3U
CPU Level	Embedded	Celeron	Intel Core i3	Intel Xeon E5	Intel Xeon E3/ Intel Core i3, i5, i7	E3/i3	i7	E5	E5	Embedded	N/A	Intel	N/A	N/A
Number of Drives	2	6	4	4	8	16	24	16	24	16	16	16	16	16
Max. Unit Capacity (TB)	8	60	40	40	80	160	240	160	240	160	160	160	160	160
Hard Drive Interface	SATA 6Gb	SATA 6Gb	SATA 6Gb	SATA 6Gb	SATA 6Gb	SAS 12Gb/ SATA 6Gb	SAS 12Gb/ SATA 6Gb	SAS 12Gb/ SATA 6Gb	SAS 12Gb/ SATA 6Gb	SATA 6Gbs	SATA 6Gbs	6/12 Gb SAS, 6 Gb SATA HDD/SSD	6/12 Gb SAS, 6 Gb SATA HDD/SSD	6/12 Gb SAS, 6 Gb SATA HDD/SSD
Max. HDD Expansion Supported	N/A	112	112	112	112	136	144	136	144	112	16		16	16
Host Interface	1x Gigabit Ethernet	2x Gigabit Ethernet	2x Gigabit Ethernet	4x 1Gigabit Ethernet (Optional: 10G BaseT /SFP+/FC x 2)	2x Gigabit Ethernet	2x Gigabit Ethernet	2x Gigabit Ethernet	2x Gigabit Ethernet	2x Gigabit Ethernet	4x 1Gigabit Ethernet (per controller)	Dual, IN/OUT 6G SAS- wide (x4) port over SFF-8088 (per controller)	4x 1Gigabit Ethernet (per controller)	IN/OUT 12G SAS- wide (x4) port over SFF-8644 (per controller)	IN/OUT 12G SAS- wide (x4) port over SFF-8644 (per controller)
Add-On GPU Supported			○	○	○			○	○					
RAID Levels	0, 1	0, 1, 5, 6, 10, 50, 60	0, 1, 3, 5, 6, 10	0, 1, 3, 5, 6, 10	0, 1, 5, 6, 10, 50, 60	0, 1, 5, 6, 10, 50, 60	0, 1, 5, 6, 10, 50, 60	0, 1, 5, 6, 10, 50, 60	0, 1, 5, 6, 10, 50, 60	0, 1, 5, 6, 10, 50, 60		0, 1, 5, 6, 10, 50, 60		
Online Capacity Expansion		○	○	○	○	○	○	○	○	○		○		
SMARTBOOST™ Supported		○	○	○	○	○	○	○	○			○		
Auto Restart		○	○	○	○	○	○	○	○	○	○	○	○	○
Power Redundancy		○		○	○	○	○	○	○	○	○	○	○	
Warranty	2 years	3 years	3 years	3 years	3 years	3 years	3 years	3 years	3 years	3 years	3 years	3 years	3 years	3 years

# PROMISE SURVEILLANCE PORTFOLIO

## WHY PROMISE

- Over 30-Years Expertise at Storage Industry
- Registered SMARTBOOST™ Technology for Performance Optimization
- Comprehensive, One-Stop-Shopping Product Portfolio
- Purpose Built for Surveillance
- Surveillance Project Design Tool to Simply Planning Steps
- World-class Quality and Green Policy Compliance
- Global Service to Insure Customer Satisfaction

### Entry Level

Small Scale



### High-end

Large Scale

#### Home Security



Apollo Cloud



Vess A2330



Vess A3120



Vess A6600



Vess A3340



Vess A6800

#### Recording Appliance



Vess A6120



Vess A7600



Vess A7800

#### Video Analytics



Vess J3610



Vess R3600

#### Archiving



Contact us

© 2018 PROMISE Technology, Inc. All Rights Reserved. PROMISE, the PROMISE logo, VTrak, SmartStor, SuperTrak, FastTrak, VessRAID, Vess, PerfectPATH, PerfectRAID, SATA150, ULTRA133 VTrak S3000, BackTrak, HyperCache, HyperCache-R, HyperCache-W, DeltaScan and GreenRAID are registered or pending trademarks of PROMISE Technology, Inc. in the U.S. and other countries. All other trademarks are the property of their respective owners. Information regarding products, services and offerings may be superseded by subsequent documents and are subject to change without notice. For the latest information and specifications regarding PROMISE Technology, Inc. and any of its offerings or services, please contact your local PROMISE office or the corporate headquarters. Visit [www.promise.com](http://www.promise.com) for more information on PROMISE products.  
P/N: G61300000000xx

2018 August



# Quick Buyer Guide

## Promise Surveillance Solution

### YOUR INTELLIGENT SURVEILLANCE SOLUTION TO GUARD YOUR BUSINESS

PROMISE Technology has designed and manufactured sophisticated RAID & Storage solutions for 30 years. With proven expertise of storage technology by market, our profound knowledge and dedication can provide you the most intelligent surveillance solution to guard your business.

### COMPREHENSIVE PRODUCT COVERAGE FOR VIDEO SURVEILLANCE STORAGE

A well-preserved video archive can ensure we can get any necessary data to take the further actions. It is therefore important to realize that storage is not simply a space provided to store video stream, but a safe data center in which reliability and capability greatly matters when it comes to surveillance applications. To cover all various demands and applications of surveillance, you can get the complete storage solution from PROMISE surveillance portfolio including storage expansion subsystems if necessary, which provides a single umbrella storage solution able to execute any surveillance operations smoothly.