



SLIM-SPIN

Anixter's Slim-Spin reel is designed to simultaneously pull multiple cables for indoor applications. At only 32 inches wide, the Slim-Spin easily fits through standard 36-inch doorways. With four fixed-chamber reels and a single-chamber reel mounted on one pallet jack frame, standard load conductors can spin at the same rate on the four-chamber reel while smaller ground conductor can spin at its own rate on the single-chamber reel. The reels are delivered mounted on our custom-designed pallet reel caddies. Just roll into the pull position, raise the wheels and start pulling.

Return the Slim-Spin to Anixter for reloading future pulls. Gain additional time and labor savings with pre-installed staggered pulling heads.

Features and Benefits

- Eliminates jack stands
- Easily transported
- Fits through 36" doorways
- Locks in place for pulling
- Reduces injury risk
- Reduces unproductive labor
- Cut to exact circuit length
- Just-in-time delivery

Copper		Load Conductor	Ground Wire
THHN	OD	Feet per Chamber	Feet per Chamber
8	0.23	4,871	4,175
6	0.25	4,123	3,534
4	0.33	2,366	2,028
3	0.36	1,988	1,704
2	0.39	1,694	1,452
1	0.45	1,272	1,091
1/0	0.50	1,031	833
2/0	0.54	884	757
3/0	0.60	716	613
4/0	0.66	592	507
250	0.72	497	426
300	0.77	435	372
350	0.83	374	321
400	0.87	340	292
500	0.96	280	240
600	1.06	229	197



Dimensions: 32 inches wide, 74 inches long, empty weight 577lbs.

Anixter Contractor Services


Anixter offers electrical contractors a suite of cost-cutting solutions. These solutions are designed to:

- Reduce unproductive labor
- Mitigate risk
- Minimize scrap and excess
- Increase financial leverage.

Solutions:



Anixter's phase taping solution makes circuit identification easier at the job site.




Anixter's pulling grip solutions eliminate on-site termination by having low voltage pulling eyes installed.




Anixter's layering solution reduces the amount of reels required at the job site by layering multiple circuit lengths on the same reel.



SPEEDPULL bundles multiple, numbered circuit conductors to allow for a single pull.



PARAPULL eliminates waste and makes setup and pulls easy by using multiple chambers to load cable legs.



PARASPIN allows different diameters of cable to be pulled simultaneously by using independent spinning chambers.



PARAPLEX reduces the amount of reels at the job site by bundling of two or more cables paralleled on the same reel.




INSTA-REEL consists of a standard wooden reel that has oversized flanges attached to both sides and becomes a payout stand when chocked in place.

Anixter-Installed Pulling Eyes

Reduce unproductive labor by having Anixter install pulling eyes onto each leg. Eyes are installed in a clean and controlled environment.

- Reduces the need for on-site tooling
- Eliminates the need to order, receive, store and retrieve eyes



To learn more about our time-saving contractor services, contact us at **1.800.ANIXTER** or visit anixter.com/contractorsolutions.

About Anixter: anixter.com/aboutus
Legal Statement: anixter.com/legalstatement

19D0522GL © 2019 Anixter Inc. 5/19

Anixter Inc. World Headquarters
 2301 Patriot Boulevard
 Glenview, Illinois 60026
 224.521.8000

1.800.ANIXTER | anixter.com

