


PRODUCT SOLUTIONS BRIEF

HANWHA

HEALTHCARE FACILITY RISK MANAGEMENT



Through our strong global partnerships and alliances with manufacturers such as Hanwha, we are able to present you with the following offering to meet your specific healthcare requirements.

QNV-7080R Outdoor Vandal Dome Network Camera

The QNV-7080R from Hanwha's Q Series affordable network camera line is a 4 MP outdoor vandal dome network camera featuring WiseStream, Hanwha's compression technology.

It is part of the Wisenet Q series, whose cameras include simple but essential features ideal to secure small- to medium-sized applications.

Hanwha's QNV-7080R delivers 4 MP resolution with motion and defocus detection.

CHALLENGE SOLVERS

- Features of the QNV-7080R include triple codec H.265/H.264/MJPEG, 2.8 to 12.0 mm motorized varifocal lens, as well as True ICR and WDR technology.
- WiseStream advanced compression technology can reduce bandwidth by 50% using dynamic technology or up to 75% when combined with high-efficiency video coding (H.265).
- Delivers hallway view for monitoring vertical-shaped areas.



THE ANIXTER APPROACH

• Property Perimeter

Determine vulnerability areas around the property edge to deter external threats.

• Reception and Registration Area

Control the flow of visitors and patients to the facility and validate various levels of staff authorization.

• Specialty Units

Protect patients and comply with privacy regulations with attention to complex specialty units.

• Emergency Room

Improve staff safety and care through effective management of high-stress and high-traffic emergency settings.

• Pharmaceutical Assets

Achieve regulatory compliance and loss prevention by monitoring access and intrusion to pharmaceutical zones.

• Biomedical and Diagnostics

Protect valuable equipment and potentially harmful materials in biomedical and diagnostic areas.

WHAT WE HEAR

Healthcare stakeholders are dealing with a variety of challenges:



Creating **SAFE** environments for patients and staff



Preventing **THEFT** of medicine and radiological materials



Achieving **REGULATORY COMPLIANCE**



Preventing **CYBER THREATS** to patient records



Limiting physical building and network **ACCESSIBILITY**

THE HANWHA SOLUTION

FIELD OF VIEW

Horizontal: 109°-26°
Vertical: 60.8°-15.2°
Depth: 131.3°-30.1°

ANALYTICS

Motion detection
Tampering
Defocus detection

MOUNT OPTIONS

Wall	Corner
Pendant	Flush
Pole	Hanging

anixter.com/shopbhanwha

**Infrastructure
as a Platform**
by Anixter

Infrastructure as a Platform by Anixter provides a practical, configurable and integrated approach to deploy physical security infrastructure into your healthcare environment.

CONFIGURE

We help you discover and map your specific needs to the best solution.

- Monitoring software
- Environmental sensors
- Video analytics software

BUNDLE

Your validated, preconfigured solutions are packaged and site ready.

- Installation kits
- Surface-mount kits
- Software controls

DEPLOY

Controlled, repeatable solutions are delivered on time and under budget.

- Custom packaging and labeling
- Time-sensitive delivery options
- Staged project shipping
- Tailored last-mile delivery

HANWHA QNV-7080R OUTDOOR VANDAL DOME NETWORK CAMERA FEATURES

✓ PROVIDES A SAFE CARE FACILITY

- Minimizes image distortion with lens distortion correction
- Supports defocus detection, which helps to recognize when an image is out of focus and significantly improves efficiency
- IR viewable length 30 m, IP66, IK10



The QNV-7080R is part of Hanwha's Q Series, which offers an affordable line of cameras with simple but essential features ideal to secure small- to medium-sized applications.

> FOR MORE DETAILS VISIT [ANIXTER.COM/SHOPHANWHA](https://www.anixter.com/shop/hanwha)

About Anixter: [anixter.com/aboutus](https://www.anixter.com/aboutus)

Legal Statement: [anixter.com/legalstatement](https://www.anixter.com/legalstatement)

At Anixter, we enable the connected world. By building, connecting, protecting and powering valuable assets and critical infrastructures, we help to sustain and grow businesses and communities worldwide. We accomplish this by offering full-line solutions, technical intelligence, supply chain expertise and an unmatched global distribution network.

1.800.ANIXTER | [anixter.com](https://www.anixter.com)



18T0451GL © 2018 Anixter Inc.

Products. Technology. Services. Delivered Globally.